

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [85084-0700](#)
Status: **Active**
Overview: SRC - Sealed Rectangular Connectors
Description: 4.00mm SRC Housing, Female, Hybrid 66 Pin Mixed Power and Signal (60 x MX150™ + 6 x MX150L™), Nylon, Black



Series

image - Reference only

Documents:

- | | |
|--|--|
| Drawing (PDF) | Packaging Specification PK-85070-001 (PDF) |
| Product Specification PS-85083-001 (PDF) | RoHS Certificate of Compliance (PDF) |
| Application Specification AS-85083-001 (PDF) | Product Literature (PDF) |

General

Product Family	Crimp Housings
Series	85084
Application	Power, Signal, Wire-to-Wire
Comments	Polarized to mating part
Overview	SRC - Sealed Rectangular Connectors
Product Literature Order No	987650-7391
Product Name	SRC
UPC	883906945572

Physical

Circuits (maximum)	66
Circuits Detail	60 x MX150™ + 6 x MX150L™
Color - Resin	Black
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	106.910/g
Number of Rows	12
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	0.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	40A
-------------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-85083-001
Packaging Specification	PK-85070-001
Product Specification	PS-85083-001
Sales Drawing	SD-85084-700

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[85084Series](#)

Mates With

[85083](#) SRC Power Blade Housing

Use With

[33012](#) MX150 Female Terminals. [19434](#)
MX150L Female Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION