



Introducing

CII FCA-150 Series Relay
50 Amps, 1PST/NO (DM)

CII FCAC-150 Series Relay
*50 Amps, 1PST/NO (DM) with
1PDT Auxiliary Contacts*

FCA-150
FCAC-150
Series Relays



KEY FEATURES

- Non-latching relay
- Balanced force design
- Corrosion protected metal enclosure
- All welded hermetically sealed enclosure occupies about 1 in³
- 1 Form X (SPST-NO-DM)
Auxiliary versions available with 1 Form C (SPDT) aux.
- 6, 12 and 28 Vdc coils available
- Weight: 90 grams
- Designed and built in accordance with MIL-PRF-6106
- Rated for altitude up to 300,000 ft.
- Available with optional terminals and mounting styles

DESCRIPTION

The FCA-150 series relay is a polarized, single-side stable design, where the flux from a permanent magnet provides the armature holding force in the deactivated state, and its flux path is switched and combined with the coil flux in the operated state. This results in appreciably increased contact pressure in both states over that of a spring return non-polar design. The FCAC-150 series has a 1 Form C (SPDT) auxiliary contact set rated at 2 A available.

Designed and built to perform under the most demanding environmental conditions and can withstand such changing environmental factors as temperature, altitude, shock, vibration, and salt spray.

Minimum mechanical life expectancy is 50,000 cycles under resistive load.

3 available coil voltages (6, 12 and 28 Vdc) with optional transient suppression.

APPLICATIONS

- Used in military, aerospace, and associated ground support electrical and electronic systems. Principle areas of application include:
- Aircraft
 - Missiles
 - Power Distribution
 - Fuel Pumps
 - Avionics Main Power Feed
 - Weapons Systems
 - Ground Support Equipment

PART NUMBERING SYSTEM

Typical Part Number	FCA-150 or FCAC-150	-A	Y	3
Series and Contact Arrangement: FCA-150 = Relay with 1 Form X Main Contacts FCAC-150 = Relay with 1 Form X Main Contacts and 1 Form C Auxiliary Contacts				
Terminals (see drawings for details): B = Solder Pin Coil Terminals, Stud Power Terminals C = Solder Hook Coil Terminals, Stud Power Terminals K = Terminal Block, Stud Power Terminals				
Enclosure (see drawings for details): R = Horizontal Flange Mount, Rotated Y = Raised Vertical Flange Mount U = Flush Vertical Flange Mount Z = No Mount X = Horizontal Flange Mount				
Coil: 1 = 6Vdc nominal 2 = 12Vdc nominal 3 = 28Vdc nominal 4 = 28Vdc nominal, with back EMF suppression				

PERFORMANCE DATA

Specifications

Contact Data

Contact Form	FCA-150: 1 Form X (SPST-NO-DM) FCAC-150: 1Form X (SPST-NO-DM) with 1 Form C (SPDT) Auxiliary Contacts			
Contact Rating in Amps (Continuous Duty)	Type of Load	Life (Min.) Cycles	28 Vdc	115 Vac 400 Hz
	Resistive	50,000	50	50
	Inductive (L/R=5ms)	20,000	20	20
	Motor	20,000	20	20
	None	100,000	–	–
Overload Current (Resistive)	200 A, 50 cycles			
Max. Contact Drop at 10A	Initial 150 mV; After Life 175 mV			
Operate Time at Nominal Voltage	15 ms			
Release Time	15 ms			
Bounce Time	1 ms			

Coil Data

Coil Code	1	2	3	4
Nominal Operating Voltage (Vdc)	6	12	28	28
Maximum Operating Voltage (Vdc)	7.3	14.5	29	29
Maximum Pick-Up Voltage at +125°C	4.5	9	18	18
Maximum Pick-Up Voltage at +125°C, continuous current test (Vdc)	5.7	11.25	22.5	22.5
Drop-Out Voltage at +125°C	0.3 – 2.5	0.75 – 4.5	1.5 – 7.0	1.5 – 7.0
Maximum Coil Current at +25°C (mA)	.50	.26	.15	.15
Back EMF Suppressed to (Vdc)	N/A	N/A	N/A	-42
Coil Resistance	18 Ω	70 Ω	290 Ω	290 Ω

Electrical Data

Initial Insulation Resistance (note 1)	100 megohms, minimum, at 500 Vdc, between each pin and case
Insulation Resistance After Life or Environmental Test (note 1)	50 megohms, minimum, at 500 Vdc, between each pin and case
Dielectric Strength At Sea Level	
Contacts to Ground and Between Contacts	1,250 Vrms, 60 Hz
Coil to Ground	1,000 Vrms, 60 Hz
Dielectric Strength at 80,000 ft (25,000 m), All Points (note 4)	500 Vrms, 60 Hz

Environmental Data

Ambient Temperature Range, Operating	-70°C to +125°C
Altitude	300,000 ft
Shock Resistance	50 G's, 11 ms
Vibration Resistance, Sinusoidal	20 G's, 75-3000 Hz

Mechanical Data

Approximate Weight	3.2 oz. (90 g) Max.
--------------------	---------------------

NOTES


1. All wired terminals must be connected together during this test. Dielectric withstanding voltage and insulation resistance are measured between all mutually insulated wired terminals and between all these terminals and case.

FCA-150 FCAC-150 Series Relays

TERMINALS


CODE "B"

Solder Pin Terminals — Tin/Lead Plated
FCA-150 FCAC-150




CODE "C"

Solder Hook Terminals — Tin/Lead Plated
FCA-150 FCAC-150




CODE "K"


Terminal Shield
FCA-150




FCAC-150



Terminal View
FCA-150




FCAC-150




Terminal Wiring


DC Coils
FCA-150




FCAC-150



DC Coils w/Transient Suppression
FCA-150



FCAC-150




PRODUCT OUTLINE DIMENSIONS


The standard terminal types and enclosures are illustrated below with dimensions in inches ± 0.010 and (millimeters ± 0.25).

FCA-150 representative drawings are shown below.


**CODE
"U"**




**CODE
"Y"**







**CODE
"X"**



**CODE
"R"**



**CODE
"Z"**



FOR MORE INFORMATION

Technical Support

Internet:	www.te.com/ADM
USA:	+1 (800) 522-6752
Canada:	+1 (905) 470-4425
Mexico:	+52 (0) 55-1106-0814
C. America:	+52 (0) 55-1106-0814
South America:	+55 (0) 11-2103-6000
Germany:	+49 (0) 6251-133-1999
Great Britain:	+44 (0) 8706-080208
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

Follow us on Twitter for all the latest product news
@TEConnectivity, and on Facebook, TEConnectivity.

www.te.com/ADM

© 2012 Tyco Electronics Corporation. All Rights Reserved.

5-1773453-6 ADM/RRD 5M 01/2012

CII, TE Connectivity, and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies.

Other products, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information herein, nothing herein constitutes any guarantee that such information is error-free, or any other representation, warranty or guarantee that the information is accurate, correct, reliable current. The TE entity issuing this publication reserves the right to make any adjustments to the information contained herein at any time without notice. All implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose are expressly disclaimed. The dimensions herein are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

