

**3M™ D Sub Socket Series 8RXX
3M D Sub Plug Series 8PXX**

Product Specification 78-5102-0089-8

Revised: 06/27/11



Important notice 6-6

3M Electronic Solutions Division
Interconnect Products
6801 River Place Blvd.
Austin, TX 78726-9000
www.3Mconnectors.com

1. Scope

This document summarizes test methods, test conditions and product performance requirements for the 3M D Sub Solder Cup Socket 8RXX and D Sub Solder Cup Plug 8PXX. Listings of materials, finishes, test conditions, and test standards are included in this specification. In the event of conflict between this specification and any documents listed below, the listed documentation supersedes this specification.

2. 3M Customer Documents

78-5100-2357-1 Customer drawing for D Sub Solder Cup Socket 8RXX.

78-5100-2402-5 Customer drawing for D Sub Solder Cup Plug 8PXX.

3. Performance and Test Description

Unless otherwise specified, all tests shall be performed on 8R09-N001 sockets mated to 8P09-N001 plugs at ambient environmental conditions per EIA-364 using 20 AWG discrete wire. Unless otherwise specified, all values and limits are typical of those obtained by qualification testing of the subject product. All specifications are subject to revision and change without notice from 3M.

4. Requirements Overview

4.1 Ratings

Dielectric withstanding voltage: 1000 VAC_{RMS} at sea level

Current:

3.0 Amperes, All contacts powered.

Temperature: -55°C to +105°C

Insulation resistance: $>3 \times 10^9 \Omega$ at 500 VDC

4.2 Materials

Socket insulation: Thermal Plastic, 94V-0

Socket contact: Copper alloy

Shell: Stainless Steel

Rivet Boardlock: Copper Alloy

Plug insulation: Thermal Plastic, 94V-0

Plug pin: Copper alloy

4.3 Finishes

Plating: (socket and header)

Nickel: 40 μ inches

Gold options: 1 μ inches, 10 μ inches, 30 μ inches.

Solder Tails: 80 μ inches Tin (Lead Free) on solder tails

4.4 Regulatory Compliance

See the Regulatory Information Appendix (RIA) in the "RoHS compliance" section of www.3Mconnectors.com for compliance information. See customer drawings for regulatory specifics on each connector.

3M Electronic Solutions Division

Interconnect Products

6801 River Place Blvd.

Austin, TX 78726-9000

www.3Mconnectors.com

5. Electrical

Description or parameter	Values & limits	Units	Requirement or conditions	Test standard or method
Dielectric withstanding voltage	1000	VAC _{RMS}	Measured between adjacent and opposing contacts. No disruptive discharge during 1 minute duration. Sea level with 70% relative humidity.	EIA-364-20A
Current rating	3.0	Amperes	All contacts driven.	
Low level connection resistance	≤20 ≤100	Millivolts MilliAmps	15 milliohm maximum ΔR contact resistance per mated interface throughout testing.	EIA-364-23A
Insulation resistance	>3 x 10 ⁹	Ohms	Measured between adjacent and opposing contacts. 500 VDC for 1 minute duration.	EIA-364-21A

6. Mechanical

Description or parameter	Values & limits	Units	Requirement or conditions	Test standard or method
Mating Force / Contact	5.5	Kg	20 cycles / 1 pc	EIA-364-13A
Unmating Force / Contact	1.7	Kg	20 cycles / 1 pc	EIA-364-13A
Durability	20	Mating cycles	15 milliohm maximum ΔR contact resistance per mated interface throughout testing.	EIA-364-23A

7. Physical

Description or parameter	Values & limits	Units	Requirement or conditions	Test standard or method
Visual			No defects such as deformation, blister, damage, crack, etc.	Quality Inspection Plan
Plating thickness Nickel	40	Micro-inches	Average of random measurements from any 3 lots	Xray Coating Tester
Gold	1, 10, 30	Micro-inches		
Solder Tails	80	Micro-inches	Tin (Lead Free)	

8. Environmental

Description or parameter	Values & limits	Units	Requirement or conditions	Test standard or method
Thermal Shock	-55 - 105	degrees C	Ri = 15 milliohm. Rf = Ri ± 20milliohm. 5 cycles.	EIA-364-32B
Humidity	25 - 65 95%	degrees C RH	Ri = 15 milliohm. Rf = Ri ± 20milliohm. 48 HR with Connector mated.	EIA-364-31A
Header solderability, lead-free dip test	>95	Percent	Coverage of solderable area	EIA-364-52

3M is a trademark of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**

© 3M 2011. All rights reserved.

3M Electronic Solutions Division
Interconnect Products
6801 River Place Blvd.
Austin, TX 78726-9000
www.3Mconnectors.com