

## AVAILABLE TERMINALS FOR SNAP-IN AND SCREW-MOUNT TYPE

- We can make the following terminal type on custom design.
- There is a restriction for specification of product, please consult with us when the product is required.
- Please consult with us about terminal type other than those following listed.

### Snap-in type

[mm]

<p>Terminal, Dummy code : VNN</p> <p><b>D=φ22 to φ35</b></p>	<p>Terminal, Dummy code : LIN</p> <p><b>D=φ30 to φ40</b></p>
<p>Terminal, Dummy code : VRD</p> <p><b>D=φ35, φ40</b></p> <p>B : Positive, A, C : Dummy</p>	<p>Terminal, Dummy code : VND</p> <p><b>D=φ35, φ40</b></p> <p>B : Positive, A, C : Dummy</p>
<p>Terminal, Dummy code : LIS</p> <p><b>D=φ50</b></p> <p>A : Dummy</p>	<p>Horizontal mounting Terminal, Dummy code : LCN</p> <p><b>D=φ20×30 to 50L, φ22×30 to 50L</b></p>

\*1 Negative terminal : Mesh marking

\*2 Use the dummy terminals for mechanical support only.

The dummy terminals must not be connected to any circuit trace on PC board, be sure to electrically isolate from the negative and the positive terminals.

### Screw-mount type

[mm]

<p>Stud mounting type</p> <p><b>D=φ76.2</b></p> <p>Installation Recommendation plate thickness: 3.2mm</p> <p>Recommendation mounting hole: φ31±0.5</p> <p>Mounting screw and case are same potential as the cathode terminal. Please careful of isolation between chassis.</p>
--

Please consult with us about other size.