


# AEDR-850x

## 3 Channel Reflective Incremental Encoders



### Data Sheet




#### Description

The AEDR-850X encoder is the smallest 3 channels optical encoder with digital outputs in the market employing reflective technology for motion control purposes. The encoder is designed to operate over  $-20^{\circ}\text{C}$  to  $85^{\circ}\text{C}$  temperature range and hence suitable for both commercial and even industrial end applications.

The encoder houses an LED light source and a photo-detecting circuitry in a single package. The small size of 3.95 mm (L) x 3.4 mm (W) x 0.9562 mm (H), allows it to be even used in a wide range of miniature commercial application where size and space is a primary concern.

The AEDR-850X encoder offers two-channel quadrature digital outputs and a 3rd channel, index digital outputs. Being TTL compatible, the outputs of the AEDR-850X encoder can be interfaced directly with most of the signal processing circuitries. Hence the encoder provides great design-in flexibility and easy integration into existing systems.



Note: Drawing not to scale.

#### Features


- World smallest 3 channels reflective technology encoder.
- Surface mount leadless package 3.95 mm (L) x 3.4 mm (W) x 0.9562 mm (H)
- 3 channels; two channel quadrature digital outputs for direction sensing and a 3rd channel, Index digital output.
- Build in interpolator, factor of 1x, 2x and 4x selectable via external pinouts
- TTL compatible
- Single 5 V supply
- $-20^{\circ}\text{C}$  to  $85^{\circ}\text{C}$  absolute operating temperature
- Encoding resolution:
  - 304 (lines/inch) or 12 (lines/mm)

#### Applications


Ideal for high volume applications:

- Close Loop stepper Motors
- Miniature Motors
- Printers
- Copiers
- Card readers
- Scanners
- Projectors
- Consumer and Industrial Product Applications

## Output waveform



QUADRATURE SIGNALS A, B and I



Note: Drawing not to scale.

## Absolute Maximum Ratings

Storage Temperature, $T_S$	-20° C to 85° C
Operating Temperature, $T_A$	-20° C to 85° C
Supply Voltage, $V_{CC}$	7 V
Output Voltage, $V_O$	$V_{CC}$

### Notes:

1. Exposure to extreme light intensity (such as from flashbulbs or spotlights) may cause permanent damage to the device.
2. CAUTION: It is advised that normal static precautions should be taken when handling the encoder in order to avoid damage and/or degradation induced by ESD.
3. Proper operation of the encoder cannot be guaranteed if the maximum ratings are exceeded.



## Recommended Operating Conditions ( based on limited prototype samples testing @ 11 Rop codewheel)

Parameter	Sym.	Min.	Typ.	Max.	Units	Notes
Temperature	$T_A$	-20	25	85	°C	
Supply Voltage	$V_{CC}$	4.5	5	5.5	V	Ripple < 100mVp-p
LED Current	$I_{LED}$		15mA		mA	See note 1
Count Frequency <sup>2</sup>	F		56		kHz	1 x Interpolation Factor
Radial Misalignment	$E_R$			±0.2	mm	
Tangential Misalignment	$E_T$			±0.2	mm	
Codewheel Gap	G	0.5		1	mm	

### Notes:

1. LED Current Limiting Resistor: Recommended series resistor = 180  $\Omega$  ( $\pm 1\%$ )
2. Count frequency = velocity (rpm) x CPR / 60.

## Encoder Pin-Out



Pin configuration (Top view)

## Encoder's Built-in Interpolation

Pin (Interpolation)		Interpolation Factor	CPR @ ( $R_{OP} = 11 \text{ mm}$ )	Count Frequency
SEL 4X	SEL 2X			
L	L	1X	828	55 KHz
L	H	2X	1656	110 KHz
H	L	4X	3312	220 KHz
H	H	Factory use		

H = HIGH Logic Level L = LOW Logic Level

The interpolation factor above may be used in conjunction with the below formulae to cater the needs for various rotation speed (RPM) and count.

$$\text{RPM} = (\text{Count Frequency} \times 60) / \text{CPR}$$

The CPR (@ 1X interpolation) is based on the following formulae which is directly dependent on  $R_{OP}$

$$\text{CPR} = \text{LPI} \times 2\pi \times R_{OP} (\text{inch}) \text{ or}$$

**Note :** LPI (lines per inch) is fixed at 304 by the AEDR-850X.

$$\text{CPR} = \text{LPmm} \times 2\pi \times R_{OP} (\text{mm})$$

$$\text{LPmm (lines per mm)} = 304/25.4$$

## Encoding Characteristics (Codewheel of Rop @11 mm)

Encoding characteristics over the recommended operating condition and mounting conditions.

Parameter	Symbol	Typical			Unit
Interpolation factor		1 X	2 X	4 X	
Cycle Error	$\Delta C$	18	22	36	°e
Pulse Width Error	$\Delta P$	15	20	30	°e
Phase Error	$\Delta \phi$	9	15	18	°e
State Error	$\Delta S$	10	15	25	°e

Note:

Typical values represent the encoder performance at typical mounting alignment, whereas the maximum values represent the encoder performance across the range of recommended mounting tolerance.


## Electrical Characteristics

Characteristics over recommended operating conditions at 25° C.

Parameter	Symbol	Min.	Typ.	Max.	Unit	Notes
High Level Output Voltage	$V_{OH}$	2.4			V	
Low Level Output Voltage	$V_{OL}$			0.4	V	
Rise Time	$t_r$		<100		ns	
Fall Time	$t_f$		<100		ns	


## LED Current Limiting Resistor

A resistor to limit the current to the LED is required. The recommended value is 180  $\Omega$  ( $\pm 1\%$ ) and the resistor should be placed in series between the 5 V supply and pin VLED of the encoder. This will result in an LED current of approximately 15 mA for optimal encoder performance.



## Codewheel Characteristics

The most important dimension to remember is that the index (I) channel pattern on the codewheel, the width angle is made up of  $3 \times W_B^\circ$  (opaque-non reflective region).




$L_w = 1.8 \text{ mm (minimum)}$

**Caution:** As the Index track is generated by utilizing the  $3 \times W_b$  (opaque – non reflective) region, any dirt that blocked the tracks resulting in the encoder's detector sensing a  $3 \times W_b$  will result in another erroneous Index.


Index track width angle is made up of  $3 \times W_B^\circ$

## Codewheel Design Example

The following example demonstrates a codewheel design for a Rop of 11 mm @ 828 CPR for a typical 2 channels encoder. In the case for an index track design, special index tracks have to be utilized.



Codewheel pattern for a 2 channels encoder



Codewheel pattern for a 3 channels encoder

Notes:

- 2 tracks from the original 828 CPR, 2 channels codewheel design have been utilized for the special track(Index), but CPR remains the same.

## Recommended Codewheel Characteristics

Parameter	Symbol	Min.	Max.	Unit	Notes
Window/bar Ratio	Ww/Wb	0.9	1.1		
Window/bar Length	L <sub>W</sub>	1.80 (0.071)	–	mm (inches)	
Specular Reflectance	R <sub>f</sub>	60	–		Reflective area. See note 1.
		–	10		Non reflective area
Line Density	LPmm	11.968		lines/mm	
	LPI	304		lines/inch	Default value by design at IC level


Notes:

1. Measurements from TMA  $\mu$ Scan meter.
2. LPmm = CPR / [2 $\pi$ .Rop(mm)]

## Moisture Sensitivity Level

The AEDR-850X is specified to moisture sensitive level (MSL) 3.

## Outline Drawing




\* All dimensions in millimeter.  
Tolerance x.xx  $\pm 0.15$  mm

## Encoder Placement Orientation and Positioning

The AEDR-850X is designed such that both the emitter and detector IC should be placed parallel to the window/bar orientation, as shown (*with the encoder mounted on top of the codewheel*). See view below).


Most importantly, **the center of the lens** of the encoder unit; needs to be in line with the operating radius of the codewheel ( $R_{OP}$ ) or rather the center point of Lw (0.5 of the Length of Window). Lw is recommended to be 1.8 mm or greater.




## Direction of Movement

With the **detector side of the encoder placed closer to the codewheel centre**, see the above top view; Channel A leads Channel B when the codewheel rotates anti-clockwise and vice versa (*with the encoder mounted on top of the codewheel*).


The optimal gap setting recommended is between 0.5 mm to 1 mm (See side view below).



## Recommended Land Pattern for AEDR-850X




## Recommended Lead-free Reflow Soldering Temperature Profile





## Ordering Information

**AEDR – 850x – x 0 x**



For product information and a complete list of distributors, please go to our web site: [www.avagotech.com](http://www.avagotech.com)

Avago, Avago Technologies, and the A logo are trademarks of Avago Technologies in the United States and other countries.  
Data subject to change. Copyright © 2005-2011 Avago Technologies. All rights reserved.  
AV02-2790EN - February 23, 2011

**Avago**  
TECHNOLOGIES