


# CGJ series | High Reliability Series



## Contents

- Purpose / Objectives
- TDK MLCC Lineup
- Series Concept
- Cap Range
- Features
- Applications
- Design Tools/Resources
- Part Number Description
- Summary



# CGJ series I High Reliability Series

## Purpose

- To provide a general overview of TDK's "CGJ High Reliability Series" Capacitor

## Objectives


- Define TDK's CGJ High Reliability Series capacitors
- Highlight the features and applications of TDK's CGJ Series Capacitors
- Explain TDK's CGJ series part number structure




| SERIES |                               | FEATURES   | OFFERING  |
|--------|-------------------------------|--|---|
| C      | General Applications          | <ul style="list-style-type: none"> <li>• Wide range of case size and superior dimension precision</li> <li>• Available in EIA class 1 and 2 dielectrics up to 50V</li> <li>• Unique design allows for higher voltage in smaller case size</li> <li>• Available in 100V, 250V, 450V, and 630V</li> <li>• Advance design provides improved withstanding voltage</li> <li>• Available rating up to 3000V</li> <li>• Stable temperature characteristics up to 150°C</li> <li>• Highly precise temperature performance ( 7.5%) up to 125° C</li> <li>• Design with higher Q factor than standard capacitors</li> <li>• Excellent attenuation and high self resonance frequency (SRF)</li> <li>• Flipped geometry provides lower inductance than standard capacitor</li> <li>• Special design allows for adequate high frequency current to IC</li> <li>• Unique design allows for increase resistance to mechanical bending</li> <li>• Improved performance in vibration and electrical stresses</li> <li>• Improved bending resistance and temperature cycle performance</li> <li>• Termination technology available for most case sizes including arrays</li> <li>• AgPdCu termination for conductive glue mounting</li> <li>• Improved mechanical/thermal strength when used with conductive glue</li> </ul> | <ul style="list-style-type: none"> <li>• 01005 ~ 2220 / C0G, SL, X5R, X6S, X7R, X7S, Y5V</li> <li>• 4V ~ 50V / up to 100 µF</li> <li>• 0402 ~ 2220 / C0G, X6S, X7R, X7S, X7T</li> <li>• 100V ~ 630V / up to 15 µF</li> <li>• 1808 ~ 1812 / C0G, X7R, X7S</li> <li>• 1000V ~ 3000V / up to 10 nF</li> <li>• 0402 ~ 1210 / X8R</li> <li>• 16V ~ 100V / up to 10 µF</li> <li>• 0201 / C0G</li> <li>• 25V / up to 20 pF</li> <li>• 0204 ~ 0612 / X5R, X6S, X7R, X7S</li> <li>• 4V ~ 50V / up to 10 µF</li> <li>• 0805 ~ 2220 / X7R, X8R</li> <li>• 16V ~ 630V / up to 22 µF</li> <li>• 0805 ~ 3025 / X7R, X7S, X7T</li> <li>• 16V ~ 630V / up to 100 µF</li> <li>• 0402 ~ 1210 / C0G, X7R, X8R</li> <li>• 25V ~ 100V / up to 10 µF</li> </ul> |
|        | Mid Voltage                   |  |   |
|        | High Voltage                  |  |   |
|        | High Temperature              |  |   |
|        | High Q                        |  |   |
|        | Flip Type                     |  |   |
|        | Open Mode                     |  |   |
|        | Soft Termination              |  |   |
|        | Conductive Epoxy              |  |   |
| CER    | Controlled ESR                | <ul style="list-style-type: none"> <li>• Unique design allows for specified "controlled" ESR</li> <li>• Same no-hassle mounting method as standard 2-terminal components</li> <li>• ESR is controlled without affecting the ESL</li> </ul>   | <ul style="list-style-type: none"> <li>• 0603 ~ 0805 / X5R</li> <li>• 4V ~ 10V / up to 10 µF</li> </ul>   |
| CEU    | Serial Design                 | <ul style="list-style-type: none"> <li>• 2 series-connected capacitors in one body</li> <li>• Improved bending resistance and temperature cycle performance</li> <li>• Ultra high reliability design for automotive battery line applications</li> </ul>   | <ul style="list-style-type: none"> <li>• 0603 ~ 0805 / X7R</li> <li>• 50V / up to 100 nF</li> </ul>   |
| CGA    | Automotive Applications       | <ul style="list-style-type: none"> <li>• Qualified to CDF AEC Q-200 automotive testing standard</li> <li>• Manufactured using matured process for guaranteed performance</li> <li>• Available in C0G, X7R and X8R temperature characteristics</li> </ul>   | <ul style="list-style-type: none"> <li>• 0402 ~ 2220 / C0G, X5R, X7R, X7S, X7T, X8R</li> <li>• 6.3V ~ 630V / up to 47 µF</li> </ul>   |
| CGJ    | High Reliability Applications | <ul style="list-style-type: none"> <li>• Extensive testing to ensure higher reliability and longer life</li> <li>• Reliability tests based on MIL-STD requirements</li> <li>• Guaranteed TC Bias and Hot IR performance</li> </ul>   | <ul style="list-style-type: none"> <li>• 0402 ~ 1206 / C0G, X7R</li> <li>• 6.3V ~ 50V / up to 10 µF</li> </ul>  |
| CKC    | 2-in-1 Array<br>4-in-1 Array  | <ul style="list-style-type: none"> <li>• Allows for reduction of PCB space and mounting time</li> <li>• Unique electrode design reduces crosstalk</li> <li>• Also available in soft termination for higher reliability performance</li> </ul>  | <ul style="list-style-type: none"> <li>• CKCN27 ~ CKCA43 / C0G, X5R, X7R</li> <li>• 6.3V ~ 50V / up to 2.2 µF</li> </ul>  |
| CKD    | Feed Through                  | <ul style="list-style-type: none"> <li>• Optimized for noise bypass with signal and power source circuits</li> <li>• Can be used for meeting EMC requirements</li> <li>• Ideal for use at higher frequencies due to low parasitic inductance</li> </ul>  | <ul style="list-style-type: none"> <li>• 0402 ~ 1206 / up to 125°C temperature range</li> <li>• 6.3V ~ 50V / up to 22 µF</li> </ul>   |
| CKG    | Mega Cap                      | <ul style="list-style-type: none"> <li>• Advance design for twice the capacitance on single footprint</li> <li>• Improved vibration and thermal/mechanical stress performance</li> <li>• Lower ESR and ESL than ALU and TA capacitor</li> </ul>  | <ul style="list-style-type: none"> <li>• CKGxxK ~ CKGxxN / X5R, X7R, X7S, X7T</li> <li>• 16V ~ 630V / up to 100 µF</li> </ul>   |
| CLL    | Ultra Low Inductance          | <ul style="list-style-type: none"> <li>• Unique internal structure allows cancelation of magnetic fields to reduce equivalent series inductance</li> <li>• Eight sided terminal electrode design in one capacitor</li> </ul>   | <ul style="list-style-type: none"> <li>• 0603 ~ 0805 / X7R, X7S</li> <li>• 4V ~ 10V / up to 4.7 µF</li> </ul>   |



# CGJ series | High Reliability Series- Series Concept -


## Concept Image




**Commercial Grade  
C Series****Automotive Grade  
CGA Series****High Reliability Grade  
CGJ Series**

|  |                         |   |   |
|--|-------------------------|---|---|
| Insulation Resistance                    | ●<br>100% of each lot   | ●<br>100% of each lot                   | ●<br>100% of each lot                   |
| Voltage Proof Test (DWV)                 | ●<br>100% of each lot   | ●<br>100% of each lot                   | ●<br>100% of each lot                   |
| Capacitance / Dissipation Factor (DF, Q) | ●<br>100% of each lot   | ●<br>100% of each lot                   | ●<br>100% of each lot                   |
| External Appearance / Visual Inspection  | ⊙<br>Sampled each lot   | ●<br>100%                               | ●<br>100%                               |
| Physical Dimension                       | ⊙<br>Sampled each lot   | ⊙<br>Sampled each lot                   | ⊙<br>Sampled each lot                   |
| Solderability                            | ⊙<br>Sampled each lot   | ⊙<br>Sampled each lot                   | ⊙<br>Sampled each lot                   |
| Temperature Characteristics              | ⊙<br>Qualification Only | ⊙<br>Qualification Only                 | ⊙<br>Sampled each lot (n=10)            |
| Deflection (Bending; Board Flex)         | ⊙<br>Qualification Only | ⊙<br>Qualification Only                 | ⊙<br>Sampled each lot (n=10)            |
| Operating Life                           | ⊙<br>Qualification Only | ⊙<br>Qualification (X•RV for 1,000 hrs) | ⊙<br>Qualification (X•RV for 2,000 hrs) |
| Bias Humidity                            | -                       | ⊙<br>Qualification (RV only)            | ⊙<br>Qualification (RV and LV)          |
| Destructive Physical Analysis (DPA)      | -                       | ⊙<br>Qualification Only                 | ⊙<br>Sampled each lot (n=10)            |
| Highly Accelerated Life Test (HALT)      | -                       | -                                       | ⊙<br>Sampled each lot (n=60)            |
| DC Bias / ESR / Breakdown Voltage        | -                       | -                                       | ⊙<br>Qualification Only (n=50)          |
| Salt Water Immersion / Tin Whisker       | -                       | -                                       | ⊙<br>Qualification Only                 |


\*Please refer to TDK Specifications ([www.tdk.com](http://www.tdk.com)) and Certificate of Compliance for more detail on test method and acceptance criteria as well as sampled lot size.



**Commercial Grade  
C Series**



**Automotive Grade  
CGA Series**



**High Reliability Grade  
CGJ Series**

|                          |                           |   |                   |                  |
|--------------------------|---------------------------|---|-------------------|------------------|
| <b>Data Requirements</b> | Certificate of Compliance | - | -                 | Each Lot (Web)   |
|                          | Electrical Test Report    | - | -                 | Each Lot (Web)   |
|                          | Qualification             | - | PPAP              | PPAP+            |
|                          | Life Estimation           | - | FIT & MTTF (PPAP) | FIT & MTTF (web) |
|                          | Re-validation             | - | -                 | Annually         |

|                                   |                                   |          |                     |                      |
|-----------------------------------|-----------------------------------|----------|---------------------|----------------------|
| <b>Manufacturing Requirements</b> | TQS-9000 (internal qualification) | ●        | ●                   | ●                    |
|                                   | ISO-9001 Certification            | ●        | ●                   | ●                    |
|                                   | ISO-14001 Certification           | ●        | ●                   | ●                    |
|                                   | TS-16949 Certification            | -        | ●                   | ●                    |
|                                   | Product Maturity                  | 0 Months | 6 Months or greater | 12 Months or greater |

|                         |                                   |      |      |      |
|-------------------------|-----------------------------------|------|------|------|
| <b>Customer Support</b> | 3 / 3 / 7 Failure Analysis Policy | ●    | ●    | ●    |
|                         | Failure Analysis Priority         | FIFO | FIFO | RUSH |


|                         |    |      |    |
|-------------------------|----|------|----|
| Typical Price Premium * | 1x | 1.5x | 2x |
|-------------------------|----|------|----|

\*Typical premium are for standard values.

## CGJ series | High Reliability Series - Cap Range -

### Cap Range:

- ❖ Reliability tests based on MIL-STD requirements
- ❖ Qualified to AEC-Q200
- ❖ Manufactured using matured process for guaranteed performance
- ❖ 0402 ~ 1206 / C0G, X7R
- ❖ 6.3V ~ 50V / up to 10uF





# CGJ series I High Reliability Series- Features -

## Features:

### CGJ series

AEC Q-200

Select MIL-STD



#### Anti-Counterfeit

The seal to assist in the identification of authentic TDK CGJ products. The condition of the seal also indicates if the product has been tampered with in the supply chain




#### Certificate of Compliance

Documentation is provided for each CGJ lot online: <http://www.tdk.com/product-validation.php>



#### RFID Label

RFID Label to allow integration with inventory management programs



#### Premium Level Service

Customer priority backed by local US factory. TDK offers the highest level of customer service for claims, technical data and inventory needs for CGJ Series products.



#### Increased Evaluation



To promote extended life







## CGJ series | High Reliability Series- Applications -

### Decoupling





Reduces AC ripple voltage.

### Filtering



Removes unwanted frequency signals. In this example, f1 is removed.

### Bypassing/Smoothing



"Absorbs" DC voltage spikes.



High Reliability  
Guaranteed Applications



Smart Meter / Smart Grid



Electric Vehicle  
Charging Station



Telecom Base Station



**CGJ  
Series**

Solar Micro Inverter



LED Lighting



Military Communication  
Equipment



Class 1 & 2 Medical  
Equipment





## CGJ series I High Reliability Series- Design Tools/Resources -

### TVCL – TDK Virtual Component Library

<http://www.tdk.com/tvcl.php>

### CCV – Components Characteristics Viewer

<http://www.tdk.co.jp/ccv/index.asp>

### SEAT – Selection Assistant of TDK Components

<http://www.tdk.com/seat.php>

### MLCC Sample Kits

<http://www.mouser.com/Search/Refine.aspx?Ne=254016&N=1323038+4232846+4294963871>



# CGJ series I High Reliability Series- Part Number Description -

| (1)         | (2)      | (3)      | (4)        | (5)       | (6)        | (7)      |
|-------------|----------|----------|------------|-----------|------------|----------|
| <b>CGJ5</b> | <b>L</b> | <b>2</b> | <b>X7R</b> | <b>1A</b> | <b>106</b> | <b>K</b> |

(1) Series/Dimension Code

| Series                    | Code | EIA  | L (mm)      | W (mm) | T (mm) Nominal |
|---------------------------|------|------|-------------|--------|----------------|
| CGJ –<br>Extended<br>Life | 2    | 0402 | 1.00        | 0.50   | 0.50           |
|                           | 3    | 0603 | 1.60        | 0.80   | 0.80           |
|                           | 4    | 0805 | 2.00        | 1.20   | 1.25           |
|                           | 5    | 1206 | 3.20 x 1.60 |        | 1.60           |

(2) Nominal Thickness Code T(mm)

| Symbol | Thickness | Symbol | Thickness |
|--------|-----------|--------|-----------|
| B      | 0.50 mm   | H      | 1.15 mm   |
| C      | 0.60 mm   | J      | 1.25 mm   |
| E      | 0.80 mm   | L      | 1.60 mm   |
| F      | 0.85 mm   |        |           |

(3) Voltage Condition for Life Test

| Code | Condition | Code | Condition  |
|------|-----------|------|------------|
| 1    | 1 x R.V.  | 3    | 1.5 x R.V. |
| 2    | 2 x R.V.  | 4    | 1.2 x R.V. |

(4) Temperature Characteristics

| Temperature Characteristics | Temperature Range | Capacitance Change |
|-----------------------------|-------------------|--------------------|
| C0G                         | -55 ~ 125°C       | 0 30 ppm/°C        |
| X7R                         | -55 ~ 125°C       | 15%                |

(5) Rated Voltage Code (Vdc)

| Symbol | Rated Voltage (V <sub>DC</sub> ) |
|--------|----------------------------------|
| 0J     | 6.3                              |
| 1A     | 10                               |
| 1C     | 16                               |
| 1E     | 25                               |
| 1H     | 50                               |

(6) Nominal Capacitance (pF)

| Symbol | Cap Value (pF) | Cap Value (nF) | Cap Value (μF) |
|--------|----------------|----------------|----------------|
| 101    | 100 pF         | 0.1 nF         | 0.0001 μF      |
| 102    | 1,000pF        | 1 nF           | 0.001 μF       |
| 105    | 1,000,000 pF   | 1,000 nF       | 1 μF           |
| 106    | 10,000,000 pF  | 10,000 nF      | 10 μF          |

The capacitance is expressed in three digit codes and in units of pico Farads (pF). The first and second digits identify the first and second significant figures of the capacitance. The third digit identifies the multiplier. R designates a decimal point.

(7) Capacitance Tolerance Code

| Symbol | Capacitance Tolerance |
|--------|-----------------------|
| J      | 5%                    |
| K      | 10%                   |

## CGJ series I High Reliability Series- Summary -

### Summary:

- ❖ TDK's CGJ series is the highest reliability multilayer ceramic capacitor offered by TDK through increased evaluation in the manufacturing process
- ❖ The CGJ series offers additional benefits such as: Tamper Proof Seal, RFID Label, Certificate of Compliance, and Premium Level Service
- ❖ TDK has design tools to help support optimal MLCC component selection



### Why TDK:

- ❖ World Class Supplier
- ❖ ppb Quality
- ❖ Local Factory Support
- ❖ Zero restrictive or banned materials

