

HEYClip[™] MaxRunner[™] Cable Clip Array

Accommodates up to 12 Cables


The Ultimate in Solar Wire Management

PANEL THICKNESS CLAMPING RANGE Minimum Maximum				WIRE DIA. RANGE Maximum (12) Wires		PART NO.	DESCRIPTION	FOOTPRINT		OVERALL HEIGHT	
in.	mm.	in.	mm.	in.	mm.			in.	mm.	in.	mm.
.06	1,5	.25	6,4	.2028	5,2 - 7,2	S6403	MaxRunner 12 Clip	3.00 x 3.13	76,2 - 79,5	.98	24,9





- Patent Pending design is the ultimate in solar wire management.
- Holds up to 12 cables with wire diameters ranging from .20" (5,2 mm) to .28" (7,2 mm).
- Constructed from PPE+PS flame retardant "Noryl" material with a 301 stainless steel mounting clip.
- The versatile stainless steel mounting clip is designed to secure the holder to a wide variety of aluminum extruded mounting frames of various thicknesses and profiles up to .250" (6,4 mm) thick.
- The injection molded wire holder has a V0 flame rating and a UV (f1) rating for excellent resistance to outdoor exposure.
- Molded internal locking tabs securely hold the cables in place preventing side-to-side movement or slippage of the cables.





Material Certifications Flammability Rating Temperature Rating PPE & PS "Noryl" with 301 stainless steel mounting clip
Listed under Underwriters' Laboratories File E54523
94V-0

Maximum material rating 203°F (95°C)

