

# CE2 SERIES CONNECTORS

## Coaxial Connector for Transportation

### Product Release



#### General Specifications

- Applicable Frequency: DC to 1GHz
- No. of Contacts: 1, 2 Pos
- Impedance: 75 Ohms
- Insertion loss: 0.3 dB max
- V.S.W.R: 1.5 max
- Durability: 50 cycles
- Operating temperature: -30°C to +70°C
- Applicable cable: EM-1.5CS-QFBE, 1.5C-2V, or equivalent

#### Target Application

- Digital media connection such as audio and navigation for transportation and automotive.



#### Features

Small and robust coaxial connector for antenna connection in transportation applications.

- Pin arrangements include 1 coax, 1 coax and 1 power, or 2 coax and 1 power.
- Available as a board to cable and cable to cable connection.
- Reinforced cable connector that can withstand pulling force of over 100N.
- Mechanical lock included for secure mating.
- Anti-noise characteristic improved by outer terminal covering cable core area.

Enclosed you will find a Component Product Information guide and JACS for the series.



Technology to Inspire Innovation

MB-35-10-11  
November 2010