

SMD Surface mount lead terminals – General Purpose 85°C / 2000 h

Description

Capacitor for high density printed circuit board.

Applications

Coupling, decoupling, by-pass, filtering.

Features

Low profile vertical chip.


Marking

Series (G), Rated voltage (Vdc), Capacitance (µF)

Negative polarity: black line

Diagram of dimensions (Units=mm)

ØD	L	H	H1	A	B	C	P
4,0	5,4 +0,25/-0,1	5,5 MAX	4,3 ±0,2	0,65 ±0,1	1,8 ±0,2	0,35 ±0,2	1,0 ±0,2
5,0	5,4 +0,25/-0,1	6,5 MAX	5,3 ±0,2	0,65 ±0,1	2,2 ±0,2	0,35 ±0,2	1,5 ±0,2
6,3	5,4 +0,25/-0,1	7,8 MAX	6,6 ±0,2	0,65 ±0,1	2,6 ±0,2	0,35 ±0,2	1,8 ±0,2
6,3	7,7 ±0,3	7,8 MAX	6,6 ±0,2	0,65 ±0,1	2,6 ±0,2	0,35 ±0,2	1,8 ±0,2
8,0	6,2 ±0,3	9,5 MAX	8,3 ±0,2	0,65 ±0,1	3,4 ±0,2	0,35 ±0,2	2,0 ±0,2
8,0	10,2 ±0,3	10 MAX	8,3 ±0,2	0,90 ±0,2	3,4 ±0,2	0,70 ±0,2	3,4 ±0,2
10,0	10,2 ±0,3	13 MAX	10,3 ±0,2	0,90 ±0,2	3,5 ±0,2	0,70 ±0,2	4,6 ±0,2
12,5	13,5 ±0,5	15,2 MAX	12,8 ±0,2	1,25 ±0,2	4,9 ±0,2	1,0 ±0,2	4,6 ±0,2
12,5	16,0 ±0,5	15,2 MAX	12,8 ±0,2	1,25 ±0,2	4,9 ±0,2	1,0 ±0,2	4,6 ±0,2
16,0	16,5 ±1,0	18,7 MAX	16,3 ±0,2	2,0 ±0,2	5,8 ±0,2	1,0 ±0,2	6,0 ±0,2



Electrical characteristics

Rated voltage	4 to 450 Vdc
Operating temperature	-40 to 85°C
Capacitance range	0.1µF to 1000µF
Capacitance tolerance	± 20% at 120Hz / 20°C
Endurance test	2000 hours (see conditions in Test method and performance)
Leakage current	I = 0.01 CV (µA) or 3µA whichever is greater for rated voltage ≤ 100 V I = 0.04 CV + 100 (µA) for rated voltage ≥ 160 V C = rated capacitance (µF); V = rated voltage (Vdc) (after than D.C. rated working voltage at 20°C has been applied for 2 min)

Impedance Z characteristics at 120 Hz

Rated Voltage (Vdc)	4	6.3	10	16	25	35	50	63	100	160	200	250	400	450
Z (-25°C) / Z (20°C)	7	4	3	2	2	2	2	2	2	3	3	3	6	6
Z (-40°C) / Z (20°C)	15	8	6	4	4	3	3	3	3	6	6	6	10	10

Compensation factor of ripple current (R.C.) vs. frequency

Rated voltage	60 Hz	120 Hz	1 KHz	10 KHz
4 to 100 Vdc	0.80	1.00	1.15	1.25
160 to 450 Vdc	0.70	1.00	1.40	1.60

Compensation factor of ripple current (R.C.) vs. temperature

Rated voltage	50°C	75°C	85°C
4 to 100 Vdc	1.36	1.25	1.00
160 to 450 Vdc	1.60	1.25	1.00

Technical data and ordering codes

Rated capacitance 120 Hz 20°C (µF)	Case size DxL (mm)	4 Vdc Rated voltage - 5 Vdc Surge voltage			Arcotronics P/N
		D.F. 120 Hz 20°C (tanδ %)	R.C. 120 Hz 85°C (mA _{rms})	L.C. 20°C 2 min. (µA)	
22	4 x 5.4	35	19	3	EDK226M004A9BAA
33	4 x 5.4	35	26	3	EDK336M004A9BAA
47	4 x 5.4	35	34	3	EDK476M004A9BAA
100	5 x 5.4	35	61	4	EDK107M004A9DAA
220	6.3 x 5.4	35	82	9	EDK227M004A9GAA

SMD Surface mount lead terminals – General Purpose 85°C / 2000 h

6.3 Vdc Rated voltage - 8 Vdc Surge voltage					
Rated capacitance 120 Hz 20°C (μF)	Case size DxL (mm)	D.F. 120 Hz 20°C (tanδ %)	R.C. 120 Hz 85°C (mA _{rms})	L.C. 20°C 2 min. (μA)	Arcotronics P/N
22	4 x 5.4	26	20	3	EDK226M6R3A9BAA
33	5 x 5.4	26	22	3	EDK336M6R3A9DAA
47	5 x 5.4	26	46	3	EDK476M6R3A9DAA
100	6.3 x 5.4	26	71	6	EDK107M6R3A9GAA
220	8 x 6.2	35	250	14	EDK227M6R3A9LAA
330	8 x 6.2	35	300	21	EDK337M6R3A9LAA
470	8 x 10.2	35	380	30	EDK477M6R3A9MAA
680	10 x 10.2	35	458	43	EDK687M6R3A9PAA
1000	10 x 10.2	35	700	63	EDK108M6R3A9PAA

10 Vdc Rated voltage - 13 Vdc Surge voltage					
Rated capacitance 120 Hz 20°C (μF)	Case size DxL (mm)	D.F. 120 Hz 20°C (tanδ %)	R.C. 120 Hz 85°C (mA _{rms})	L.C. 20°C 2 min. (μA)	Arcotronics P/N
15	4 x 5.4	30	23	3	EDK156M010A9BAA
22	4 x 5.4	30	28	3	EDK226M010A9BAA
33	4 x 5.4	30	29	3	EDK336M010A9BAA
33	5 x 5.4	20	43	3	EDK336M010A9DAA
47	5 x 5.4	30	43	5	EDK476M010A9DAA
100	6.3 x 5.4	26	70	10	EDK107M010A9GAA
220	6.3 x 7.7	26	220	22	EDK227M010A9HAA
220	8 x 6.2	26	250	22	EDK227M010A9LAA
330	8 x 10.2	26	330	33	EDK337M010A9MAA
470	10 x 10.2	26	400	47	EDK477M010A9PAA

16 Vdc Rated voltage - 20 Vdc Surge voltage					
Rated capacitance 120 Hz 20°C (μF)	Case size DxL (mm)	D.F. 120 Hz 20°C (tanδ %)	R.C. 120 Hz 85°C (mA _{rms})	L.C. 20°C 2 min. (μA)	Arcotronics P/N
4.7	4 x 5.4	16	20	3	EDK475M016A9BAA
10	4 x 5.4	16	28	3	EDK106M016A9BAA
22	4 x 5.4	26	27	4	EDK226M016A9BAA
22	5 x 5.4	16	39	4	EDK226M016A9DAA
33	5 x 5.4	26	45	5	EDK336M016A9DAA
33	6.3 x 5.4	16	66	5	EDK336M016A9GAA
47	6.3 x 5.4	16	70	8	EDK476M016A9GAA
100	6.3 x 5.4	20	70	16	EDK107M016A9GAA
150	6.3 x 7.7	26	109	24	EDK157M016A9HAA
220	6.3 x 7.7	20	215	35	EDK227M016A9HAA
220	8 x 10.2	20	280	35	EDK227M016A9MAA
330	10 x 10.2	20	380	53	EDK337M016A9PAA
470	8 x 10.2	20	365	75	EDK477M016A9MAA
470	10 x 10.2	20	420	75	EDK477M016A9PAA

SMD Surface mount lead terminals – General Purpose 85°C / 2000 h

25 Vdc Rated voltage - 32 Vdc Surge voltage					
Rated capacitance 120 Hz 20°C (μ F)	Case size DxL (mm)	D.F. 120 Hz 20°C (tan δ %)	R.C. 120 Hz 85°C (mA _{rms})	L.C. 20°C 2 min. (μ A)	Arcotronics P/N
1	4 x 5.4	16	9	3	EDK105M025A9BAA
2.2	4 x 5.4	16	14	3	EDK225M025A9BAA
4.7	3 x 5.4	16	11	3	EDK475M025A9AAA
4.7	4 x 5.4	14	22	3	EDK475M025A9BAA
10	5 x 5.4	14	28	3	EDK106M025A9DAA
22	5 x 5.4	14	45	5	EDK226M025A9DAA
22	6.3 x 5.4	14	55	6	EDK226M025A9GAA
33	6.3 x 5.4	14	65	8	EDK336M025A9GAA
47	6.3 x 5.4	20	70	12	EDK476M025A9GAA
47	8 x 6.2	16	96	12	EDK476M025A9LAA
68	6.3 x 7.7	20	95	17	EDK686M025A9HAA
100	6.3 x 7.7	16	135	25	EDK107M025A9HAA
100	8 x 6.2	16	145	25	EDK107M025A9LAA
100	8 x 10.2	16	180	25	EDK107M025A9MAA
220	8 x 10.2	16	300	55	EDK227M025A9MAA
220	10 x 10.2	16	310	55	EDK227M025A9PAA
330	10 x 10.2	16	350	82	EDK337M025A9PAA
470	10 x 10.2	16	450	117	EDK477M025A9PAA

35 Vdc Rated voltage - 44 Vdc Surge voltage					
Rated capacitance 120 Hz 20°C (μ F)	Case size DxL (mm)	D.F. 120 Hz 20°C (tan δ %)	R.C. 120 Hz 85°C (mA _{rms})	L.C. 20°C 2 min. (μ A)	Arcotronics P/N
2.2	4 x 5.4	12	8	3	EDK225M035A9BAA
3.3	4 x 5.4	12	10	3	EDK335M035A9BAA
4.7	4 x 5.4	12	22	3	EDK475M035A9BAA
10	5 x 5.4	12	30	4	EDK106M035A9DAA
22	5 x 5.4	14	47	8	EDK226M035A9DAA
22	6.3 x 5.4	12	60	8	EDK226M035A9GAA
33	8 x 6.2	14	130	12	EDK336M035A9LAA
47	6.3 x 5.4	14	135	16	EDK476M035A9GAA
47	8 x 6.2	14	165	16	EDK476M035A9LAA
100	6.3 x 7.7	14	145	35	EDK107M035A9HAA
100	10 x 10.2	14	210	35	EDK107M035A9PAA
220	10 x 10.2	14	310	77	EDK227M035A9PAA
330	10 x 10.2	14	380	115	EDK337M035A9PAA

50 Vdc Rated voltage - 63 Vdc Surge voltage					
Rated capacitance 120 Hz 20°C (μ F)	Case size SIZE DxL (mm)	D.F. 120 Hz 20°C (tan δ %)	R.C. 120 Hz 85°C (mA _{rms})	L.C. 20°C 2 min. (μ A)	Arcotronics P/N
0.1	4 x 5.4	12	1	3	EDK104M050A9BAA
0.22	4 x 5.4	12	2	3	EDK224M050A9BAA
0.33	4 x 5.4	12	3	3	EDK334M050A9BAA
0.47	4 x 5.4	12	5	3	EDK474M050A9BAA
1	4 x 5.4	12	10	3	EDK105M050A9BAA
2.2	4 x 5.4	12	16	3	EDK225M050A9BAA
3.3	4 x 5.4	12	16	3	EDK335M050A9BAA
4.7	4 x 5.4	12	20	3	EDK475M050A9BAA
4.7	5 x 5.4	12	23	3	EDK475M050A9BAA
10	6.3 x 5.4	12	35	5	EDK106M050A9GAA
22	8 x 6.2	12	110	11	EDK226M050A9LAA
33	8 x 10.2	12	120	16.5	EDK336M050A9MAA
47	6.3 x 7.7	12	98	23.5	EDK476M050A9HAA
47	10 x 10.2	12	130	23.5	EDK476M050A9PAA
100	8 x 10.2	12	165	50	EDK107M050A9MAA
100	10 x 10.2	12	190	50	EDK107M050A9PAA
220	10 x 10.2	12	300	110	EDK227M050A9PAA

SMD Surface mount lead terminals – General Purpose 85°C / 2000 h

63 Vdc Rated voltage - 79 Vdc Surge voltage					
Rated capacitance 120 Hz 20°C (μ F)	Case size DxL (mm)	D.F. 120 Hz 20°C (tan δ %)	R.C. 120 Hz 85°C (mA _{rms})	L.C. 20°C 2 min. (μ A)	Arcotronics P/N
4.7	6.3 x 5.4	18	20	3	EDK475M063A9GAA
10	6.3 x 5.4	18	20	6	EDK106M063A9GAA
22	8 x 10.2	18	30	14	EDK226M063A9MAA
33	8 x 10.2	18	30	21	EDK336M063A9MAA
47	8 x 10.2	18	30	30	EDK476M063A9MAA
100	10 x 10.2	18	60	63	EDK108M065A9PAA

100 Vdc Rated voltage - 125 Vdc Surge voltage					
Rated capacitance 120 Hz 20°C (μ F)	Case size DxL (mm)	D.F. 120 Hz 20°C (tan δ %)	R.C. 120 Hz 85°C (mA _{rms})	L.C. 20°C 2 min. (μ A)	Arcotronics P/N
3.3	8 x 10.2	18	30	3	EDK335M100A9MAA
4.7	8 x 10.2	18	50	5	EDK475M100A9MAA
10	6.3 x 7.7	18	40	10	EDK106M100A9HAA
10	8 x 10.2	18	55	10	EDK106M100A9MAA
22	10 x 10.2	18	60	22	EDK226M100A9PAA
33	10 x 10.2	18	65	33	EDK336M100A9PAA

160 Vdc Rated voltage - 200 Vdc Surge voltage					
Rated capacitance 120 Hz 20°C (μ F)	Case size DxL (mm)	D.F. 120 Hz 20°C (tan δ %)	R.C. 120 Hz 85°C (mA _{rms})	L.C. 20°C 2 min. (μ A)	Arcotronics P/N
33	12.5 x 13.5	20	240	310	EDK336M160A9RAA
47	12.5 x 16	20	370	400	EDK476M160A9SAA
68	16 x 16.5	20	500	540	EDK686M160A9TAA

200 Vdc Rated voltage - 250 Vdc Surge voltage					
Rated capacitance 120 Hz 20°C (μ F)	Case size DxL (mm)	D.F. 120 Hz 20°C (tan δ %)	R.C. 120 Hz 85°C (mA _{rms})	L.C. 20°C 2 min. (μ A)	Arcotronics P/N
22	12.5 x 13.5	20	240	280	EDK226M200A9RAA
33	12.5 x 16	20	310	370	EDK336M200A9SAA
47	16 x 16.5	20	340	480	EDK476M200A9TAA
68	16 x 16.5	20	340	650	EDK686M200A9TAA

250 Vdc Rated voltage - 300 Vdc Surge voltage					
Rated capacitance 120 Hz 20°C (μ F)	Case size DxL (mm)	D.F. 120 Hz 20°C (tan δ %)	R.C. 120 Hz 85°C (mA _{rms})	L.C. 20°C 2 min. (μ A)	Arcotronics P/N
10	12.5 x 13.5	20	150	200	EDK106M250A9RAA
22	12.5 x 13.5	20	150	320	EDK226M250A9RAA
33	12.5 x 16	20	240	430	EDK336M250A9SAA
47	16 x 16.5	20	340	570	EDK476M250A9TAA

400 Vdc Rated voltage - 450 Vdc Surge voltage					
Rated capacitance 120 Hz 20°C (μ F)	Case size DxL (mm)	D.F. 120 Hz 20°C (tan δ %)	R.C. 120 Hz 85°C (mA _{rms})	L.C. 20°C 2 min. (μ A)	Arcotronics P/N
4.7	12.5 x 13.5	25	120	180	EDK475M400A9RAA
10	12.5 x 13.5	25	120	260	EDK106M400A9RAA
22	16 x 16.5	25	140	460	EDK226M400A9TAA
33	16 x 16.5	25	140	630	EDK336M400A9TAA

450 Vdc Rated voltage - 500 Vdc Surge voltage					
Rated capacitance 120 Hz 20°C (μ F)	Case size DxL (mm)	D.F. 120 Hz 20°C (tan δ %)	R.C. 120 Hz 85°C (mA _{rms})	L.C. 20°C 2 min. (μ A)	Arcotronics P/N
4.7	12.5 x 13.5	25	120	180	EDK475M450A9RAA
10	12.5 x 16	25	130	280	EDK106M450A9SAA
22	16 x 16.5	25	140	500	EDK226M450A9TAA

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.