



Engineering Kit for X and Y EMI Suppressor Capacitors

Kit Contents:

Part Number	Pieces	Agency Class	Cap. Value	Rated AC Voltage	Pitch (mm)
PHE840MK5100MK01	20	X2	10nF±20%	275(UL 280)	7.5
PHE840MA5100MA01	20	X2	10nF±20%	275(UL 280)	10
PHE840MK5220MK03	20	X2	22nF±20%	275(UL 280)	7.5
PHE840MA5220MA01	20	X2	22nF±20%	275(UL 280)	10
PHE840MK5330MK03	20	X2	33nF±20%	275(UL 280)	7.5
PHE840MA5330MA01	20	X2	33nF±20%	275(UL 280)	10
PHE840MA5470MA02	20	X2	47nF±20%	275(UL 280)	10
PHE840MB6100MB05	20	X2	100nF±20%	275(UL 280)	15
PHE840MX6220MB06	10	X2	220nF±20%	275(UL 280)	15
PHE840MY6680MD15	6	X2	680nF±20%	275(UL 280)	22.5
PHE840MY7100MD16	6	X2	1.0uF±20%	275(UL 280)	22.5
PHE840MZ7100MF11	4	X2	1.0uF±20%	275(UL 280)	27.5
PHE840MZ7220MF14	3	X2	2.2uF±20%	275(UL 280)	27.5
PHE850EA4100MA06	20	Y2	1.0nF±20%	300	10
PHE850EA4220MA01	20	Y2	2.2nF±20%	300	10
PHE850EA4330MA02	20	Y2	3.3nF±20%	300	10
PHE850EA4470MA03	20	Y2	4.7nF±20%	300	10
PHE850EB5100MB04	20	Y2	10nF±20%	300	15
PHE850EB5470MB14	10	Y2	47nF±20%	300	15
PHE850ED6100MD18	6	Y2	100nF±20%	300	22.5
PHE850ED6220MD20	6	Y2	220nF±20%	300	22.5
FLPENGKIT151	311	X2 & Y2			