

Innovation

D6F-PH Series Differential Pressure Sensor



High Impedance MEMS Mass Flow Technology

Economical

I²C Digital Output

Compact Package

High Accuracy, $\pm 3\%$ Reading

Linearized and Temperature Compensated

Resistant to Bypass Tube Length Variation

0-250 Pa, ± 50 Pa, ± 500 Pa

D6F-PH Series DIFFERENTIAL PRESSURE SENSOR

High Impedance MEMS Mass Flow Technology

- Economical
- High Accuracy, $\pm 3\%$ Reading
- I²C Digital Output
- Linearized and Temperature Compensated
- Compact Package
- Resistant to Bypass Tube Length Variation

Ordering Information

Measurement Range	Applicable Fluid	Model
0 to 250 Pa (0 to 1 in. H ₂ O)	Air	D6F-PH0025AD1
-50 to +50 Pa (± 0.2 in. H ₂ O)		D6F-PH0505AD3
-500 to +500 Pa (± 2 in. H ₂ O)		D6F-PH5050AD3

Note: The Sensor can be calibrated for different gas types. Consult Omron.

Characteristics

Model	D6F-PH0025AD1	D6F-PH0505AD3	D6F-PH5050AD3
Measurement Range (See Note 1)	0 to 250 Pa	± 50 Pa	± 500 Pa
Calibration Gas (See Note 2)	Air		
Port Type	Barb joint, Maximum outside diameter: 4.9mm		
Power Supply	2.3 to 3.6 VDC		
Current Consumption	6 mA max. with no load and V _{CC} of 3.3 V, GND=0 VDC, 25°C		
Resolution	12 bit		
Zero Point Tolerance (See Note 4)	± 0.2 Pa		
Span Tolerance (See Note 4)	$\pm 3\%$ R.D.		
Temperature Compensation	Yes		
Span shift due to Temperature Variation	$\pm 0.5\%$ R.D. per 10°C		
Response Time	25 ms typical at 12 bit resolution (50 ms max). The processing time is 6 ms typical at 12 bit resolution.		
Gas Flow through Sensor (See Note 3)	≤ 63 mL/min	≤ 23 mL/min	≤ 100 mL/min
Interface	I ² C		
Case Material	PPS		
Degree of Protection	IEC IP40		
Withstand Pressure	10 kPa		
Operating Temperature	-20 to 80°C (with no condensation or icing)		
Operating Humidity	35 to 85% RH (with no condensation or icing)		
Storage Temperature	-40 to 80°C (with no condensation or icing)		
Storage Humidity	35 to 85% RH (with no condensation or icing)		
Insulation Resistance	Between Sensor outer cover and lead terminals: 20 M Ω min. (at 500 VDC)		
Dielectric Strength	Between Sensor outer cover and lead terminals: 500 VAC, 50/60 Hz min. for 1 min (leakage current: 1 mA max.)		
Weight	5.2 g		

Note: 1. At standard atmospheric pressure (1013.25 hPa).

2. Dry gas must not contain large particles, e.g., dust, oil or mist.


3. Type D6F-PH is based on thermal flow principle. Air flow is needed to measure the differential pressure. Typical characteristic of air flow by differential pressure is shown in the "Engineering Data" section.

4. The zero point tolerance and span tolerance are independent uncertainties and add according to the principles of error propagation.

Communication

Method	I ² C
Master/Slave	Slave / Address: HEX: 0x6C BIN: 110_1100 (7 bit)
Speed mode	Fast Mode 400kHz
Signals	
SCL	Serial Clock
SDA	Data Signal

Relationship Between Pressure and Flow Rate



Note: Additional information can be found on the Omron website

Phone: 847-882-2288

www.components.omron.com

©2013 Omron Electronic Components LLC, Printed in U.S.A. 5/2013

OMRON
ELECTRONIC COMPONENTS