

MINI-BAT/24DC/0.8AH

Order No.: 2866666



<http://catalog.phoenixcontact.net/phoenix/treeViewClick.do?UID=2866666>

Power storage device, lead AGM, VRLA technology, 24 V DC, 0.8 Ah.



Commercial data

EAN	 4 046356 152129
sales group	H061
Pack	1 Pcs.
Customs tariff	85072080
Gross weight in pieces	0.894 KG
Net weight per piece	0.8771 KG
Catalog page information	Page 238 (C-6-2013)

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Dimensions

Width	67.5 mm
Height	99 mm
Depth	107 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 40 °C

Ambient temperature (storage/transport)	0 °C ... 40 °C
Max. permissible relative humidity (operation)	95 %

Input data

Nominal input voltage	24 V DC
Buffer period	20 min (1 A)
	7 min (2 A)

Output data

Nominal output voltage	24 V DC
Output current	max. 5 A
Connection in parallel	5
Connection in series	No
Output fuse	5 A

General

IQ technology	No
Disposal	Used batteries must not be thrown away with household waste, they should instead be disposed of in accordance with applicable national regulations. They can also be returned to Phoenix Contact or the manufacturer.
Net weight	0.9 kg
Protection class	III
UL approvals	UL ANSI/ISA-12.12.01 Class I, Division 2, Groups A, B, C, D (Hazardous Location)

Certificates / Approvals


Certification Ex: cULus Listed

Certification

Certifications applied for:

Drawings

Block diagram



Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>



© 2014 Phoenix Contact
Technical modifications reserved;