

San Ace 92 GA type

■ Features

Large air flow and high static pressure

Maximum airflow : increased by approx. 25%

Maximum static pressure : increased by approx. 58 %
compared with our conventional product*.

Energy-saving

Power consumption is reduced by approx. 17 % with
airflow performance that is identical to our
conventional product*.

Low noise

Sound pressure level is reduced by approx. 8 % with
airflow performance that is identical to our
conventional product*.

* Our conventional product is the DC cooling fan :
92 × 92 × 25 mm thick fan "San Ace 92" (9AH0912P4G03)



92×92×25mm

■ Specifications

Model No.	Rated Voltage [V]	Operating Voltage Range [V]	PWM duty cycle*[%]	Rated Current [A]	Rated Input [W]	Rated Speed [min⁻¹]	Air Flow [m³/min] [CFM]	Static Pressure [Pa] [inchH₂O]	SPL [dB(A)]	Operating Temperature [C]	Life Expectancy [h]
9GA0912P4J03 (031)	12	10.2 to 13.8	100	0.39	4.68	5,000	2.20 77.7	105 0.42	43	-10 to +70	60,000
9GA0912P4G03 (031)			0	0.06	0.72	1,500	0.66 23.3	9.5 0.04	14		
9GA0912P4S03 (031)	24	20.4 to 27.6	100	0.28	3.36	4,400	1.93 68.2	81 0.33	39	-10 to +70	60,000
9GA0912P4G03 (031)			0	0.06	0.72	1,500	0.66 23.3	9.5 0.04	14		
9GA0924P4S03 (031)	24	20.4 to 27.6	100	0.2	4.80	5,000	2.20 77.7	105 0.42	43	-10 to +70	60,000
9GA0924P4G03 (031)			0	0.04	0.96	1,500	0.66 23.3	9.5 0.04	14		
9GA0924P4S03 (031)	24	20.4 to 27.6	100	0.15	3.60	4,400	1.93 68.2	81 0.33	39	-10 to +70	60,000
9GA0924P4G03 (031)			0	0.04	0.96	1,500	0.66 23.3	9.5 0.04	14		
9GA0924P4S03 (031)	24	20.4 to 27.6	100	0.12	2.88	3,800	1.67 59.0	60.6 0.24	35	-10 to +70	60,000
9GA0924P4G03 (031)			0	0.04	0.96	1,500	0.66 23.3	9.5 0.04	14		

The numbers in()represent ribless models.

※ PWM Frequency:25kHz


■ Common Specifications

- Material Frame: Plastics (Flammability: UL94V-0) , Impeller: Plastics (Flammability: Min.UL94V-1)
- Life Expectancy Varies for each model
(L10: Survival rate: 90% at 60°C, rated voltage, and continuously run in a free air state)
- Motor Protection System Current blocking function and Reverse polarity protection
- Dielectric Strength 50/60 Hz, 500VAC, 1 minute (between lead conductor and frame)
- Sound Pressure Level (SPL) Expressed as the value at 1m from air inlet side
- Operating Temperature Varies for each model (Non-condensing)
- Storage Temperature -30°C to +70°C (Non-Condensing)
- Lead Wire ⊕red ⊖black Sensor: yellow Control: brown
- Mass 125g

San Ace 92 GA type


Air Flow and Static Pressure Characteristics

PWM Duty Cycle




9GA0912P4J03 (031)
9GA0924P4J03 (031)


Operating Voltage Range




9GA0912P4J03 (031)
9GA0924P4J03 (031)




9GA0912P4G03 (031)
9GA0924P4G03 (031)



9GA0912P4G03 (031)
9GA0924P4G03 (031)




9GA0912P4S03 (031)
9GA0924P4S03 (031)




9GA0912P4S03 (031)
9GA0924P4S03 (031)


PWM Duty - Speed Characteristics Example



9GA0912P4J03 (031)
9GA0924P4J03 (031)




9GA0912P4G03 (031)
9GA0924P4G03 (031)



9GA0912P4S03 (031)
9GA0924P4S03 (031)

PWM Input Signal Example

Input Signal Wave Form



$V_{IH} = 4.75V \text{ to } 5.25V$

$V_{IL} = 0V \text{ to } 0.4V$

$$\text{PWM Duty Cycle (\%)} = \frac{T_1}{T} \times 100$$

$$\text{PWM Frequency } 25 \text{ (kHz)} = \frac{1}{T}$$

Source Current : 1mA Max. at control voltage 0V


Sink Current : 1mA Max. at control voltage 5.25V

Control Terminal Voltage : 5.25V Max. (Open Circuit)

When the control lead wire is no connecting,
the speed is the same speed as at 100% of PWM cycle.

This fan speed should be controlled by PWM input signal
of either TTL input or open collector, drain input.

Connection Schematic



Specifications for Pulse Sensors

Output circuit : Open collector

Rated Voltage 12V fan

$V_{CE} = +13.8V \text{ MAX.}$


$I_C = 5\text{mA MAX. } [V_{OL} = V_{CE} (\text{SAT}) = 0.6V \text{ MAX.}]$

Rated Voltage 24V fan

$V_{CE} = +30V \text{ MAX.}$

$I_C = 10\text{mA MAX. } [V_{OL} = V_{CE} (\text{SAT}) = 0.6V \text{ MAX.}]$


Inside of DC fan




Output waveform (Need pull-up resistor)

In case of steady running


(One revolution)



Dimensions (unit : mm) (With ribs)



Reference dimension of mounting holes and vent opening (unit : mm)



Notice

- The products shown in the catalog are subject to Japanese Export Control Law. Diversion contrary to the law of exporting country is prohibited.
- To protect against electrolytic corrosion that may occur in locations with strong electromagnetic noise, we provide fans that are unaffected by electrolytic corrosion.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Sanyo Denki:](#)

[9GA0912P4G03](#) [9GA0912P4J03](#) [9GA0924P4J03](#)