# Notice for TAIYO YUDEN products

Please read this notice before using the TAIYO YUDEN products.

## REMINDERS

Product information in this catalog is as of October 2012. All of the contents specified herein are subject to change without notice due to technical improvements, etc. Therefore, please check for the latest information carefully before practical application or usage of the Products.

Please note that Taiyo Yuden Co., Ltd. shall not be responsible for any defects in products or equipment incorporating such products, which are caused under the conditions other than those specified in this catalog or individual specification.

- Please contact Taiyo Yuden Co., Ltd. for further details of product specifications as the individual specification is available.
- Please conduct validation and verification of products in actual condition of mounting and operating environment before commercial shipment of the equipment.
- All electronic components or functional modules listed in this catalog are developed, designed and intended for use in general electronics equipment.(for AV, office automation, household, office supply, information service, telecommunications, (such as mobile phone or PC) etc.). Before incorporating the components or devices into any equipment in the field such as transportation,( automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network (telephone exchange, base station) etc. which may have direct influence to harm or injure a human body, please contact Taiyo Yuden Co., Ltd. for more detail in advance. Do not incorporate the products into any equipment in fields such as aerospace, aviation, nuclear control, submarine system, military, etc. where higher safety and reliability are especially required.

In addition, even electronic components or functional modules that are used for the general electronic equipment, if the equipment or the electric circuit require high safety or reliability function or performances, a sufficient reliability evaluation check for safety shall be performed before commercial shipment and moreover, due consideration to install a protective circuit is strongly recommended at customer's design stage.

- The contents of this catalog are applicable to the products which are purchased from our sales offices or distributors (so called "TAIYO YUDEN's official sales channel").

  It is only applicable to the products purchased from any of TAIYO YUDEN's official sales channel.
- Please note that Taiyo Yuden Co., Ltd. shall have no responsibility for any controversies or disputes that may occur in connection with a third party's intellectual property rights and other related rights arising from your usage of products in this catalog. Taiyo Yuden Co., Ltd. grants no license for such rights.
- Caution for export


  Certain items in this catalog may require specific procedures for export according to "Foreign Exchange and Foreign Trade Control Law" of Japan, "U.S. Export Administration Regulations", and other applicable regulations. Should you have any question or inquiry on this matter, please contact our sales staff.

# METAL CORE WIRE-WOUND CHIP POWER INDUCTORS(MCOIL™ MA SERIES)



REFLOW

## ■PARTS NUMBER



 $\Delta$  = Blank space

①Series name

Code	Series name			
MA	Metal Core Wire-wound Chip Power Inductors			

## ${\bf 2}{\sf Dimensions}({\sf T})$

Code	Dimensions (T) [mm]			
KK	1.0			
MK	1.2			

3Dimensions (L × W)

©=	
Code	Dimensions (L × W) [mm]
2016	2.0 × 1.6
2520	2.5 × 2.0

## 4 Packaging

Code	Packaging
Т	Taping

## **⑤**Nominal inductance

Code (example)	Nominal inductance [ μ H]
R47	0.47
1R0	1.0
4R7	4.7

※R=Decimal point

#### **6**Inductance tolerance


Code	Inductance tolerance
М	±20%

#### (7)Special code

Dopecial code	
Code	Special code
Δ	Standard

®Internal code

## STANDARD EXTERNAL DIMENSIONS



Туре	L	W	Т	е	Standard quantity [pcs] Taping
MAKK2016	2.0±0.1 (0.079±0.004)	1.6±0.1 (0.063±0.004)	1.0 max (0.039 max)	$0.5\pm0.3$ (0.020±0.012)	3000
MAMK2520	2.5±0.2 (0.098±0.008)	2.0±0.2 (0.079±0.008)	1.2 max (0.047 max)	0.5±0.3 (0.020±0.012)	3000

Unit:mm(inch)

## PARTS NUMBER

#### MAKK2016 type

	N	Nominal inductance		Self-resonant	DC Resistance	Rated current ※) [mA]		Measuring
Parts number	EHS	[ $\mu$ H]	Inductance tolerance	frequency	[Ω](max.)	Saturation current	Temperature rise current	frequency[MHz]
		[ M 11]		[MHz] (min.)	Lat J (max.)	Idc1	Idc2	ir equency [iiii i2]
MAKK2016T1R0M	RoHS	1.0	±20%	-	0.075	2,200	2,200	2
MAKK2016T2R2M	RoHS	2.2	±20%	-	0.160	1,500	1,500	2
MAKK2016T3R3M	RoHS	3.3	±20%	-	0.255	1,150	1,200	2
MAKK2016T4R7M	R₀HS	4.7	±20%	-	0.380	1,000	950	2

## MAMK2520 type

	EHS	Nominal inductance [ μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] (max.)	Rated current ※) [mA]		Measuring
Parts number						Saturation current Idc1	Temperature rise current Idc2	
MAMK2520TR47M	RoHS	0.47	±20%	-	0.039	4,200	3,400	2
MAMK2520T1R0M	RoHS	1.0	±20%	-	0.059	3,100	2,700	2
MAMK2520T2R2M	RoHS	2.2	±20%	-	0.117	2,000	1,900	2
MAMK2520T3R3M	RoHS	3.3	±20%	-	0.156	1,800	1,700	2
MAMK2520T4R7M	RoHS	4.7	±20%	-	0.260	1,500	1,300	2

- $\divideontimes$ ) The saturation current value (Idc1) is the DC current value having inductance decrease down to 30%. (at 20°C)
- $\mbox{\%}$ ) The temperature rise current value (Idc2) is the DC current value having temperature increase up to 40°C. (at 20°C)
- X) The rated current is the DC current value that satisfies both of current value saturation current value and temperature rise current value.

<sup>▶</sup> This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/) .

## METAL CORE WOUND CHIP POWER INDUCTORS (MCOIL™ MA SERIES)


## PACKAGING

## 1 Minimum Quantity

Туре	Standard Quantity [pcs]
	Tape & Reel
MAKK 2016	3000
MAMK 2520	3000


## ②Tape Material

#### Embossed Tape




## ③Taping dimensions

## Embossed tape 8mm wide (0.315 inches wide)




T	Chip cavity		Insertion pitch	Tape thickness	
Туре	Α	В	F	T	K
MAKK 0016	1.9±0.1	2.3±0.1	4.0±0.1	0.25±0.05	1.1 max
MAKK 2016	$(0.075 \pm 0.004)$	$(0.091 \pm 0.004)$	$(0.157 \pm 0.004)$	$(0.009 \pm 0.002)$	(0.043 max)
MANAK OFOO	2.3±0.1	2.8±0.1	4.0±0.1	0.3±0.05	1.45 max
MAMK 2520	$(0.091 \pm 0.004)$	$(0.110 \pm .004)$	$(0.157 \pm 0.004)$	$(0.012\pm0.002)$	(0.057 max)
					Unit:mm(inch)

## 4 Leader and Blank portion



This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).


## ⑤Reel size



Type	Reel size (Reference values)				
туре	φD	φd	W		
MAKK 2016	180+0/-3	60+1/-0	10.0±1.5		
MAMK 2520	(7.087+0/-0.118)	(2.36+0.039/0)	$(0.394 \pm 0.059)$		
			Unit:mm(inch)		

## **©**Top Tape Strength

The top The top tape requires a peel-off force of 0.1 to 1.3N in the direction of the arrow as illustrated below.



This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

# METAL CORE WOUND CHIP POWER INDUCTORS (MCOIL™ MA SERIES)

## RELIABILITY DATA

1. Operating Tempe	erature Range			
	MAKK 2016			
Specified Value	MAMK 2520	-40~+105°C		
Test Methods and Remarks	Including self-generated heat			
2. Storage Tempera	ature Range			
Specified Value	MAKK 2016			
	MAMK 2520			
Test Methods and Remarks	-5 to 40°C for the product with taping.			
3. Rated current				
Specified Value	MAKK 2016	Within the specified tolerance		
	MAMK 2520	<u>'</u>		
4. Inductance	T			
Specified Value	MAKK 2016	Within the specified tolerance		
	MAMK 2520			
Test Methods and Remarks	Measuring equipment : LCR Meter (HP 4 Measuring frequency : 2MHz, 1V	1285A or equivalent)		
5 DO D				
5. DC Resistance	Luureana			
Specified Value	MAKK 2016	Within the specified tolerance		
Test Methods and Remarks	MAMK 2520  Measuring equipment : DC ohmmeter (HIOKI 3227 or equivalent)			
6. Self resonance fr	requency			
	MAKK 2016			
Specified Value	MAMK 2520	-		
7. Temperature cha	racteristic			
0 15 1141	MAKK 2016			
Specified Value	MAMK 2520	Inductance change : Within ±15%		
Test Methods and Remarks	Measurement of inductance shall be taken at With reference to inductance value at $\pm 20^\circ$	· ·		
8. Resistance to fle	xure of substrate			
	MAKK 2016			
Specified Value	MAMK 2520	No damage		
Test Methods and Remarks		esin Force Rod 10 20 R230		
		R5 Tost Sample 45±2mm		

<sup>►</sup> This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

9. Insulation resista	nce : between wires		
	MAKK 2016		
Specified Value	MAMK 2520	<u> </u>	
10. Insulation resist	ance : between wire and core		
	MAKK 2016		
Specified Value	MAMK 2520	DC25V 100kΩ min	
11. Withstanding vo	Itage : between wire and core		
	MAKK 2016		
Specified Value	MAMK 2520	<del>_</del>	
12. Adhesion of terr	minal electrode		
	MAKK 2016		
Specified Value	MAMK 2520	No abnormality.	
	The test samples shall be soldered to the	L e test board by the reflow.	
Test Methods and	•	and Y directions.	
Remarks	Duration : 5s.		
	Solder cream thickness : 0.12mm.		
10.75.11			
13. Resistance to v			
Specified Value MAKK 2016		Inductance change: Within ±10%	
	MAMK 2520	No significant abnormality in appearance.	
	The test samples shall be soldered to the Then it shall be submitted to below test	-	
	Then it shall be submitted to below test t	onditions.	
	Frequency Range 10~55Hz		
Test Methods and		not exceed acceleration 196m/s²)	
Remarks	Sweeping Method 10Hz to 55H	Iz to 10Hz for 1min.	
	Time Y	For 2 hours on each X. Y. and Z axis.	
	Z		
	Recovery : At least 2hrs of recovery u	nder the standard condition after the test, followed by the measurement within 48hrs.	
14.0.11122			
14. Solderability	L MANUE 2010		
Specified Value	MAKK 2016	At least 90% of surface of terminal electrode is covered by new solder.	
	MAMK 2520		
	The test samples shall be dipped in flux, a Flux: Methanol solution containing rosin	and then immersed in molten solder as shown in below table.	
Test Methods and Remarks	Solder Temperature 245±5°C		
	Time 5±0.5 se	с.	
	※Immersion depth : All sides of mounting	g terminal shall be immersed.	
15. Resistance to s	oldering heat		
Specified Value	MAKK 2016	Inductance change : Within ±10%	
Specified Value	MAMK 2520	No significant abnormality in appearance.	
	The test sample shall be exposed to reflo	w oven at 230°C for 40 seconds, with peak temperature at 260+0/ $-5$ °C for 5 seconds, 3 times	
Toot Mathada and	Toot boord metarial	oin aubatrata	
Test Methods and Remarks	Test board material : glass epoxy-re Test board thickness : 1.0mm	ISIN SUDSTRALE	

Recovery : At least 2hrs of recovery under the standard condition after the test, followed by the measurement within 48hrs.

<sup>▶</sup> This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

16. Thermal shock							
	MAKK 2016			Inductance change: Within ±10%			
Specified Value	e MAMK 2520			No significant abnormality in appearance.			
The test samples shall be soldered to the test board by the reflow. The test samples shall be placed at specified temperature for specified							
	time by step 1 to step 4 as shown in below table in sequence. The temperature cycle shall be repeated 100 cycles.						
		Conditions of 1 cycle					
Test Methods and $1$ Temperature (°C) $-40\pm3$			Duration (min)				
			30±3				
Remarks	Remarks 2 Room temperature			Within 3			
<del>                                   </del>		85±2 emperature		30±3 Within 3			
	4   Room t	emperature		WICHIN 3			
	Recovery : At least	2hrs of recovery ur	nder	er the standard condition after the test, followed by the measurement within 48hrs.			
17. Damp heat							
	MAKK 2016			Inductance change : Within ±10%			
Specified Value	MAMK 2520			No significant abnormality in appearance.			
		II ha aaldawad ta tha	+	st board by the reflow.			
	•			tatic oven set at specified temperature and humidity as shown in below table.			
Test Methods and	Temperature	60±2°C	000				
Remarks	Humidity	90∼95%RH					
	Time	500+24/-0 hour					
	Recovery: At least 2hrs of recovery under the standard condition after the test, followed by the measurement within 48hrs.						
18. Loading under d	amp heat						
0 15 11/1	MAKK 2016 Inductance change: Within ±10%			Inductance change: Within ±10%			
Specified Value	MAMK 2520			No significant abnormality in appearance.			
	The test samples sha	ll be soldered to the	tes	st board by the reflow.			
	The test samples shall be soldered to the test board by the reflow.  The test samples shall be placed in thermostatic oven set at specified temperature and humidity and applied the rated current						
Test Methods and	continuously as shown in below table.			_			
Remarks	Temperature						
	Humidity Applied current	90~95%RH Rated current		_			
	Time	500+24/-0 hour					
			r th	lhe standard condition after the test, followed by the measurement within 48hrs.			
	,			· ·			
19. Low temperature	a life test						
10. Low temperature							
Specified Value	MAKK 2016			Inductance change: Within ±10%			
	MAMK 2520 No significant abnormality in appearance.						
T . M .!	The test samples shall be soldered to the test board by the reflow. After that, the test samples shall be placed at test conditions as shown						
Test Methods and Remarks							
remarks	Time	500+24/-0 hour					
	Recovery : At least 2	hrs of recovery unde	r th	the standard condition after the test, followed by the measurement within 48hrs.			
20. High temperatur	e life test						
	MAKK 2016			To do the control of			
Specified Value	d Value			Inductance change: Within ±10%  No significant abnormality in appearance.			
	1						
The test samples shall be soldered to the test board by the reflow. After that, the test samples shall be placed at test conditions as should be conditionally and in below table.							
Remarks	Temperature 105±3°C			7			
	Time	500+24/-0 hour					
	Recovery : At least 2	hrs of recovery unde	r th	he standard condition after the test, followed by the measurement within 48hrs.			
	·						
21. Loading at high	temperature life test						
	MAKK 2016						

Specified Value

MAMK 2520

<sup>►</sup> This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

22. Standard condition		
	MAKK 2016	Standard test condition : Unless otherwise specified, temperature is 20±15°C and 65±20% of relative humidity.
Specified Value	MAMK 2520	When there is any question concerning measurement result: In order to provide correlation data, the test shall be condition of $20\pm2^{\circ}\text{C}$ of temperature, $65\pm5\%$ relative humidity. Inductance is in accordance with our measured value.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

## METAL CORE WOUND CHIP POWER INDUCTORS (MCOIL™ MA SERIES)

#### **PRECAUTIONS**

#### 1. Circuit Design

## ◆Operating environment

## Precautions

1. The products described in this specification are intended for use in general electronic equipment, (office supply equipment, telecommunications systems, measuring equipment, and household equipment). They are not intended for use in mission-critical equipment or systems requiring special quality and high reliability (traffic systems, safety equipment, aerospace systems, nuclear control systems and medical equipment including life-support systems,) where product failure might result in loss of life, injury or damage. For such uses, contact TAIYO YUDEN Sales Department in advance.

## 2. PCB Design

## Precautions

**♦**Land pattern design

1. Please refer to a recommended land pattern.

# Technical considerations

Land pattern design
 Surface Mounting

- · Mounting and soldering conditions should be checked beforehand.
- · Applicable soldering process to this products is reflow soldering only.

## 3. Considerations for automatic placement

## Precautions

- ◆Adjustment of mounting machine
  - 1. Excessive impact load should not be imposed on the products when mounting onto the PC boards.
  - 2. Mounting and soldering conditions should be checked beforehand.

# Technical considerations

- ◆Adjustment of mounting machine
  - 1. When installing products, care should be taken not to apply distortion stress as it may deform the products.

#### 4. Soldering

#### ◆Reflow soldering

- 1. Please contact any of our offices for a reflow soldering, and refer to the recommended condition specified.
- 2. The product shall be used reflow soldering only.
- 3. Please do not add any stress to a product until it returns in normal temperature after reflow soldering.

## **♦**Lead free soldering


## Precautions

- 1. When using products with lead free soldering, we request to use them after confirming adhesion, temperature of resistance to soldering heat, soldering etc sufficiently.
- ◆Recommended conditions for using a soldering iron (NR10050 Type)
  - · Put the soldering iron on the land-pattern.
  - Soldering iron's temperature Below 350°C
  - Duration 3 seconds or less
- The soldering iron should not directly touch the inductor.

## ◆Reflow soldering

- If products are used beyond the range of the recommended conditions, heat stresses may deform the products, and consequently degrade the reliability of the products.
  - •NR30/40/50/60/80, NRV20/30, NRH24/30, NRS20/40/50/60/80 Type, NR10050 Type, NS101/125 Type Recommended reflow condition (Pb free solder)

# Technical considerations



## 5. Cleaning

## Precautions

## ◆Cleaning conditions

1. Washing by supersonic waves shall be avoided.

# Technical considerations

## ◆Cleaning conditions

1. If washed by supersonic waves, the products might be broken.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

6. Handling	
Precautions	<ul> <li>♦ Handling</li> <li>1. Keep the product away from all magnets and magnetic objects.</li> <li>♦ Breakaway PC boards (splitting along perforations)</li> <li>1. When splitting the PC board after mounting product, care should be taken not to give any stresses of deflection or twisting to the board.</li> <li>2. Board separation should not be done manually, but by using the appropriate devices.</li> <li>♦ Mechanical considerations</li> <li>1. Please do not give the product any excessive mechanical shocks.</li> <li>2. Please do not add any shock and power to a product in transportation.</li> <li>♦ Pick-up pressure</li> <li>1. Please do not push to add any pressure to a winding part. Please do not give any shock and push into a ferrite core exposure part.</li> <li>♦ Packing</li> <li>1. Please avoid accumulation of a packing box as much as possible.</li> </ul>
Technical considerations	<ul> <li>✦ Handling</li> <li>1. There is a case that a characteristic varies with magnetic influence.</li> <li>✦ Breakaway PC boards (splitting along perforations)</li> <li>1. The position of the product on PCBs shall be carefully considered to minimize the stress caused from splitting of the PCBs.</li> <li>✦ Mechanical considerations</li> <li>1. There is a case to be damaged by a mechanical shock.</li> <li>2. There is a case to be broken by the handling in transportation.</li> <li>✦ Pick-up pressure</li> <li>1. Damage and a characteristic can vary with an excessive shock or stress.</li> <li>✦ Packing</li> <li>1. If packing boxes are accumulated, that could cause a deformation on packing tapes or a damage on the products.</li> </ul>

	♦Storage
Precautions	<ol> <li>To maintain the solderability of terminal electrodes and to keep the packing material in good condition, temperature and humidity in the storage area should be controlled.</li> <li>Recommended conditions         Ambient temperature: 0~40°C         Humidity: Below 70% RH     </li> <li>The ambient temperature must be kept below 30°C. Even under ideal storage conditions, solderability of products electrodes may decrease as time passes.</li> <li>For this reason, product should be used within 6 months from the time of delivery.</li> <li>In case of storage over 6 months, solderability shall be checked before actual usage.</li> </ol>
Technical considerations	◆Storage 1. Under a high temperature and humidity environment, problems such as reduced solderability caused by oxidation of terminal electrodes and deterioration of taping/packaging materials may take place.