

Solid Tantalum Chip Capacitors

TANTAMOUNT[®], Molded Case, Built-In-Fuse Miniature


FEATURES

- Terminations: 100 % matte tin standard, tin/lead available
- Molded package available in three case codes
- Compatible with "High Volume" automatic pick and place
- Electrically activated internal fuse
- Meets EIA 535BAAC and IEC specification QC300801/US0001
- Fuse activation at 25 °C: 0.1 s max. with 5 A min. applied current
- 100 % surge current tested (D and E case codes)
- Compliant to RoHS Directive 2002/95/EC
- Moisture sensitivity level 1


RoHS*
COMPLIANT

PERFORMANCE/ELECTRICAL CHARACTERISTICS

Operating Temperature: - 55 °C to + 125 °C
Capacitance Range: 0.47 µF to 470 µF
Voltage Rating: 4 V_{DC} to 50 V_{DC}
Capacitance Tolerance: ± 10 %, ± 20 %

Note

- **References:**
Molded Guide
www.vishay.com/doc?40074
Performance Characteristics
www.vishay.com/doc?/40088

ORDERING INFORMATION					
893D	106	X0	010	B	2WE3
TYPE	CAPACITANCE	CAPACITANCE TOLERANCE	DC VOLTAGE RATING AT + 85 °C	CASE CODE	TERMINATION AND PACKAGING
	This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow	X9 = ± 10 % X0 = ± 20 %	This is expressed in V. To complete the three-digit block, zeros precede the voltage rating. A decimal point is indicated by an "R" (6R3 = 6.3 V)	See Ratings and Case Codes table	2TE3: Matte tin, 7" (178 mm) reel 2WE3: Matte tin, 13" (330 mm) reel 8T: Tin/lead, 7" (178 mm) reel 8W: Tin/lead, 13" (330 mm) reel



Note

- We reserve the right to supply higher voltage ratings and tighter capacitance tolerance capacitors in the same case size. Voltage substitutions will be marked with the higher voltage rating. Effective July 15, 2008, part numbers with solderable termination codes "2T" and "2W" may have either matte tin or tin/lead terminations. Codes 2TE3 and 2WE3 specify only matte tin terminations. Codes 8T and 8W specify only tin/lead terminations.


DIMENSIONS in inches [millimeters]							
CASE CODE	EIA SIZE	L	W	H	P	T _W	T _H (MIN.)
C	6032-28	0.236 ± 0.012 [6.0 ± 0.30]	0.126 ± 0.012 [3.2 ± 0.30]	0.098 ± 0.012 [2.5 ± 0.30]	0.051 ± 0.012 [1.3 ± 0.30]	0.087 ± 0.004 [2.2 ± 0.10]	0.039 [1.0]
D	7343-31	0.287 ± 0.012 [7.3 ± 0.30]	0.170 ± 0.012 [4.3 ± 0.30]	0.110 ± 0.012 [2.8 ± 0.30]	0.051 ± 0.012 [1.3 ± 0.30]	0.095 ± 0.004 [2.4 ± 0.10]	0.039 [1.0]
E	7343-43	0.287 ± 0.012 [7.3 ± 0.30]	0.170 ± 0.012 [4.3 ± 0.30]	0.158 ± 0.012 [4.0 ± 0.30]	0.051 ± 0.012 [1.3 ± 0.30]	0.095 ± 0.004 [2.4 ± 0.10]	0.039 [1.0]

RATINGS AND CASE CODES

μF	4 V	6.3 V	10 V	16 V	20 V	25 V	35 V	50 V
0.47								C
0.68								C
1.0								C
1.5							C	C
2.2						D	C	C/D
3.3						C	C	C/D
4.7					C	C	C/D	D
6.8				C	C	C	D	D/E
10			C	C	C	C/D	D	
15		C	C	C	C/D	D	D/E	
22		C	C	C/D	D	D/E	E	
33		C	C/D	C/D	D/E	E		
47		C/D	C/D	D/E	E			
68	C	C/D	D/E	D	E			
100	C	D/E	D	E				
150	D	D	D/E	E				
220	D	D/E	E					
330	D/E	E						
470	E							

CONSTRUCTION AND MARKING

Marking:

Capacitors shall be marked with an anode polarity band, capacitance (in microfarads) and the rated DC working voltage, 85 °C. The capacitance voltage will be separated by the letter "F" indicating a fused capacitor. Units rated at 6.3 V shall be marked as 6 V.

FUSE ACTIVATION




STANDARD RATINGS						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DC LEAKAGE AT + 25 °C (μ A)	MAX. DF AT + 25 °C 120 Hz (%)	MAX. ESR AT + 25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I_{RMS} (A)
4 V_{DC} AT + 85 °C; 2.7 V_{DC} AT + 125 °C						
68	C	893D686(1)004C(2)	2.7	6	1.4	0.28
100	C	893D107(1)004C(2)	4.0	8	0.8	0.37
150	D	893D157(1)004D(2)	6.0	8	0.6	0.50
220	D	893D227(1)004D(2)	8.8	8	0.6	0.50
330	D	893D337(1)004D(2)	13.2	15	0.6	0.50
330	E	893D337(1)004E(2)	13.2	8	0.5	0.57
470	E	893D477(1)004E(2)	18.8	16	0.5	0.57
6.3 V_{DC} AT + 85 °C; 4 V_{DC} AT + 125 °C						
15	C	893D156(1)6R3C(2)	0.9	6	1.8	0.25
22	C	893D226(1)6R3C(2)	1.1	6	1.8	0.25
33	C	893D336(1)6R3C(2)	1.6	6	1.4	0.28
47	C	893D476(1)6R3C(2)	2.3	6	1.3	0.29
47	D	893D476(1)6R3D(2)	2.3	6	0.9	0.41
68	C	893D686(1)6R3C(2)	3.3	6	0.8	0.37
68	D	893D686(1)6R3D(2)	3.3	6	0.7	0.46
100	D	893D107(1)6R3D(2)	4.8	8	0.7	0.46
100	E	893D107(1)6R3E(2)	6.0	8	0.7	0.49
150	D	893D157(1)6R3D(2)	9.0	8	0.6	0.50
220	D	893D227(1)6R3D(2)	13.2	8	0.6	0.50
220	E	893D227(1)6R3E(2)	13.2	8	0.5	0.57
330	E	893D337(1)6R3E(2)	19.8	8	0.5	0.57
10 V_{DC} AT + 85 °C; 7 V_{DC} AT + 125 °C						
10	C	893D106(1)010C(2)	1.0	6	1.8	0.25
15	C	893D156(1)010C(2)	1.5	6	1.8	0.25
22	C	893D226(1)010C(2)	2.2	6	1.4	0.28
33	C	893D336(1)010C(2)	3.3	6	1.3	0.29
33	D	893D336(1)010D(2)	3.3	6	0.9	0.41
47	C	893D476(1)010C(2)	4.7	6	1.0	0.33
47	D	893D476(1)010D(2)	4.7	6	0.7	0.46
68	D	893D686(1)010D(2)	6.8	6	0.7	0.46
68	E	893D686(1)010E(2)	6.8	6	0.7	0.49
100	D	893D107(1)010D(2)	10.0	8	0.6	0.50
150	D	893D157(1)010D(2)	15.0	8	0.6	0.50
150	E	893D157(1)010D(2)	15.0	8	0.5	0.57
220	E	893D227(1)010E(2)	22.0	8	0.5	0.57
16 V_{DC} AT + 85 °C; 10 V_{DC} AT + 125 °C						
6.8	C	893D685(1)016C(2)	1.1	6	2.0	0.23
10	C	893D106(1)016C(2)	1.6	6	1.8	0.25
15	C	893D156(1)016C(2)	2.4	6	1.4	0.28
22	C	893D226(1)016C(2)	3.5	6	1.3	0.29
22	D	893D226(1)016D(2)	3.5	6	0.9	0.41
33	C	893D336(1)016C(2)	5.3	6	1.0	0.33
33	D	893D336(1)016D(2)	5.3	6	0.7	0.46
47	D	893D476(1)016D(2)	7.5	6	0.7	0.46
47	E	893D476(1)016E(2)	7.5	6	0.7	0.49
68	D	893D686(1)016D(2)	10.9	6	0.6	0.50
100	E	893D107(1)016E(2)	16.0	8	0.6	0.52
150	E	893D157(1)016E(2)	24.0	10	0.4	0.64

Note

- Part number definitions:
 - Tolerance: X0, X9
 - Terminations and packaging: 2TE3, 2WE3, 8T, 8W



STANDARD RATINGS						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DC LEAKAGE AT + 25 °C (μ A)	MAX. DF AT + 25 °C 120 Hz (%)	MAX. ESR AT + 25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I_{RMS} (A)
20 V_{DC} AT + 85 °C; 13 V_{DC} AT + 125 °C						
4.7	C	893D475(1)020C(2)	0.9	6	2.0	0.22
6.8	C	893D685(1)020C(2)	1.4	6	1.9	0.24
10	C	893D106(1)020C(2)	2.0	6	1.6	0.26
15	C	893D156(1)020C(2)	3.0	6	1.4	0.28
15	D	893D156(1)020D(2)	3.0	6	0.9	0.41
22	D	893D226(1)020D(2)	4.4	6	0.7	0.46
33	D	893D336(1)020D(2)	6.6	6	0.7	0.46
33	E	893D336(1)020E(2)	6.6	6	0.7	0.49
47	E	893D476(1)020E(2)	9.4	6	0.6	0.52
68	E	893D686(1)020E(2)	13.6	6	0.6	0.52
25 V_{DC} AT + 85 °C; 17 V_{DC} AT + 125 °C						
2.2	C	893D225(1)025C(2)	0.9	6	2.8	0.21
3.3	C	893D335(1)025C(2)	0.8	6	2.3	0.22
4.7	C	893D475(1)025C(2)	1.2	6	1.9	0.24
6.8	C	893D685(1)025C(2)	1.7	6	1.6	0.26
10	C	893D106(1)025C(2)	2.5	6	1.4	0.28
10	D	893D106(1)025D(2)	2.5	6	1.0	0.39
15	D	893D156(1)025D(2)	3.8	6	0.8	0.43
22	D	893D226(1)025D(2)	5.5	6	0.7	0.46
22	E	893D226(1)025E(2)	5.5	6	0.7	0.49
33	E	893D336(1)025E(2)	8.3	6	0.6	0.52
35 V_{DC} AT + 85 °C; 23 V_{DC} AT + 125 °C						
1.5	C	893D155(1)035C(2)	0.5	6	3.8	0.17
2.2	C	893D225(1)035C(2)	0.8	6	2.9	0.20
3.3	C	893D335(1)035C(2)	1.2	4	2.0	0.23
4.7	C	893D475(1)035C(2)	1.6	6	1.8	0.25
4.7	D	893D475(1)035D(2)	1.6	6	1.2	0.35
6.8	D	893D685(1)035D(2)	2.4	6	1.0	0.39
10	D	893D106(1)035D(2)	3.5	6	0.8	0.43
15	D	893D156(1)035D(2)	5.3	6	0.7	0.46
15	E	893D156(1)035E(2)	5.3	6	0.7	0.49
22	E	893D226(1)035E(2)	7.7	6	0.6	0.52
50 V_{DC} AT + 85 °C; 33 V_{DC} AT + 125 °C						
0.47	C	893D474(1)050C(2)	0.5	4	6.7	0.13
0.68	C	893D684(1)050C(2)	0.5	4	5.9	0.14
1.0	C	893D105(1)050C(2)	0.5	4	4.4	0.16
1.5	C	893D155(1)050C(2)	0.8	6	3.2	0.19
2.2	C	893D225(1)050C(2)	1.1	6	2.8	0.20
2.2	D	893D225(1)050D(2)	1.1	6	2.1	0.27
3.3	C	893D335(1)050C(2)	1.7	6	2.4	0.21
3.3	D	893D335(1)050D(2)	1.7	6	1.6	0.31
4.7	D	893D475(1)050D(2)	2.4	6	1.1	0.37
6.8	D	893D685(1)050D(2)	3.4	6	0.9	0.41
6.8	E	893D685(1)050E(2)	3.4	6	0.9	0.43

Note

- Part number definitions:
 - Tolerance: X0, X9
 - Terminations and packaging: 2TE3, 2WE3, 8T, 8W



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.