


Ultra High Precision Z-Foil Surface Mount 4 Resistor Network Dual-In-Line Package with TCR Tracking of 0.1 ppm/°C, PCR Tracking of 5 ppm at Rated Power, and Tolerance Match of 0.01 %



Any value and any ratio available within resistance range

INTRODUCTION

The Z-Foil Technology provides a significant reduction of the resistive components' sensitivity to ambient temperature variations (TCR) and applied power changes (PCR). 0.05 ppm/°C Absolute TCR removes errors due to temperature gradients.

Model SMNZ offers extremely low TCR (absolute and tracking), excellent load life stability, tight tolerance (absolute and matching), excellent ratio stability, low current noise, low voltage coefficient and non sensitivity to ESD - **all in the same resistor.**


The SMNZ Surface Mount Network is made up of 4 independent Bulk Metal® Z-Foil resistors in a small standard molded epoxy package with 50 MIL lead pitch (JEDEC MS-012 package).

The electrical specification of this integrated construction offers improved performance and better real estate utilization over discrete resistors and matched sets. The resistor may be used independently or as divider pairs.

Our application engineering department is available to advise and make recommendations. For non-standard technical requirements and special applications, please contact us.

APPLICATIONS

- Instrumentation amplifiers
- Bridge networks
- Differential amplifiers
- Ratio arms in bridge circuits
- Medical and test equipment
- Military
- Airborne etc




FEATURES

- Temperature coefficient of resistance (TCR):
absolute: ± 0.05 ppm/°C typical (0 °C to + 60 °C)
 ± 0.2 ppm/°C typical (-55 °C to + 125 °C, + 25 °C Ref.) (see table 1)
Tracking: 0.1 ppm/°C typical (see table 1)
- Tolerance match: 0.01 %
- Power coefficient tracking - "R2 -R1 due to self heating":
5 ppm at rated power
- Power rating: at 70 °C
Entire package: 0.4 W
Each resistor: 0.1 W
- Ratio stability: 0.005 % (0.1 W at 70 °C, 2000 h)
- Large variety of resistance ratios
- Electrostatic discharge (ESD) above 25 000 V
- Short time overload ≤ 0.0025 %
- Non-inductive, non-capacitive design
- Rise time: 1 ns without ringing
- Current noise: < - 40 dB
- Voltage coefficient < 0.1 ppm/V
- Non-inductive: < 0.08 μ H
- Non hot spot design
- Terminal Finishes available: lead (Pb)-free tin/lead alloy
- For better performances please contact us
- Any value available within resistance range (e.g. 1K2345)
- Prototype samples available from 48 h. For more information, please contact foil@vishaypg.com




RoHS*
COMPLIANT

FIGURE 1 - SCHEMATICS



OPTION 1

FOUR RESISTORS, SAME OHMIC VALUE
SAME ABSOLUTE TOLERANCE



OPTION 2

TWO RESISTOR PAIRS
R1/R2; R2/R1

Note

1. Different schematics are available (R1, R2, R3, R4)

TABLE 1 - MODEL SMNZ SPECIFICATIONS

MODEL	RESISTANCE VALUES ¹⁾	ABSOLUTE TCR (- 55 °C TO + 125 °C, + 25 °C REF.) (TYPICAL + MAX. SPREAD)	RESISTANCE RATIO	TCR TRACKING		TOLERANCE	
				MAX.	ABSOLUTE	MATCH	
SMNZ	100 Ω - 1 k Ω 1 k Ω - 10 k Ω	± 0.2 ± 2.8 ± 0.2 ± 1.8	R1/R2 = 1 1 < R1/R2 ≤ 10 10 < R1/R2 ≤ 100	0.5 ppm/°C 1.0 ppm/°C 2.0 ppm/°C	± 0.02 % ± 0.05 % ± 0.1 %	0.01 % 0.02 % 0.05 %	

Note

1. SMN (Classic Foil) available with values up to 20 k Ω

* Pb containing terminations are not RoHS compliant, exemptions may apply

FIGURE 2 - POWER DERATING CURVE




FIGURE 4 - TYPICAL TCR CURVE Z-FOIL




FIGURE 3 - DIMENSIONS AND IMPRINTING EXAMPLE in inches (millimeters)




FIGURE 5 - TRIMMING TO VALUES (conceptual illustration)




FIGURE 6 - LAND PATTERN in inches (millimeters)





TABLE 2 - PERFORMANCE SPECIFICATIONS (per MIL-PRF 914 test methods)

SPECIFICATIONS	TYPICAL LIMITS
Power Rating at + 70 °C	Each resistor: 0.1 W Entire package: 0.4 W
Maximum Working Voltage (each resistor)	$(P \times R)^{1/2}$
Thermal Shock 25 x (- 65 °C to + 125 °C)	$\Delta R = 0.01 \% (100 \text{ ppm})$ $\Delta \text{Ratio} = 0.01 \% (100 \text{ ppm})$
Thermal Shock 5 x (- 65 °C to + 125 °C) and Power Conditioning 1.5 rated power at 25 °C, 100 h	$\Delta R = 0.02 \% (200 \text{ ppm})$ $\Delta \text{Ratio} = 0.015 \% (150 \text{ ppm})$
DWV Atm. Pressure 200 V (A.C), 1 min	Successfully passed
Insulation Resistance 100 V (D.C), 1 min	$> 10^4 \text{ M}\Omega$
Resistance to Soldering Heat	$\Delta R = 0.01 \% (100 \text{ ppm})$ $\Delta \text{Ratio} = 0.005 \% (50 \text{ ppm})$
Moisture Resistance + 65 °C to - 10 °C; 90 % to 98 % RH; 0.1 x rated power; 240 h	$\Delta R = 0.02 \% (200 \text{ ppm})$ $\Delta \text{Ratio} = 0.005 \% (50 \text{ ppm})$
Shock (Specified Pulse) 100G	$\Delta R = 0.01 \% (100 \text{ ppm})$ $\Delta \text{Ratio} = 0.01 \% (100 \text{ ppm})$
Vibration, High Frequency (10 Hz to 2000 Hz), 20G	$\Delta R = 0.005 \% (50 \text{ ppm})$ $\Delta \text{Ratio} = 0.005 \% (50 \text{ ppm})$
High Temperature Exposure 100 h at 125 °C	$\Delta R = 0.01 \% (100 \text{ ppm})$ $\Delta \text{Ratio} = 0.005 \% (50 \text{ ppm})$
Low Temperature Storage 24 h at - 65 °C	$\Delta R = 0.005 \% (50 \text{ ppm})$ $\Delta \text{Ratio} = 0.005 \% (50 \text{ ppm})$
Load Life Stability at 70 °C; 0.1 W per resistor, 2000 h	$\Delta R = 0.005 \% (50 \text{ ppm})$ $\Delta \text{Ratio} = 0.005 \% (50 \text{ ppm})$
Short Time Overload 6.25 x rated power; 5 s	$\Delta R = 0.005 \% (50 \text{ ppm})$ $\Delta \text{Ratio} = 0.0025 \% (25 \text{ ppm})$
Weight	0.08 g

TABLE 3 - GLOBAL PART NUMBER INFORMATION

NEW GLOBAL PART NUMBER: Y1747V0204BA9W (preferred part number format)



FOR EXAMPLE: ABOVE GLOBAL ORDER Y1747 V0204 B A 9 W:

TYPE: SMNZ
VALUES: 10K/500R
ABSOLUTE TOLERANCE: ± 0.1 %
TOLERANCE MATCH: 0.05 %
TERMINATION: Lead (Pb)-free
PACKAGING: Waffle Pack

HISTORICAL PART NUMBER: SMNZ 10K/500R TCR0.2 B A S W (will continue to be used)

SMNZ	10K/500R	TCR0.2	B	A	S	W
MODEL	RESISTANCE VALUE	ABSOLUTE TCR	ABSOLUTE TOLERANCE	TOLERANCE MATCH	TERMINATION	PACKAGING
SMNZ	R ₁ = 10 kΩ R ₂ = 500 Ω	TCR0.2	Q = ± 0.02 % A = ± 0.05 % B = ± 0.1 %	T = 0.01 % Q = 0.02 % A = 0.05 %	S = lead (Pb)-free B = tin/lead	T = tape and reel W = waffle pack U = ESD tubes

Note

* For non-standard requests, please contact Application Engineering.

TABLE 4 - RESISTANCE VALUE CODE LIST FOR POPULAR RATIOS

(other values available upon request)

VCODES	R1/R2 RATIO	R1	R2	VCODES	R1/R2 RATIO	R1	R2
V0201	100	10K	100R	V0189	2.5	1K	400R
V0202	50	10K	200R	V0185		500R	200R
V0197		5K	100R	V0207	2	10K	5K
V0203	25	10K	400R	V0175		2K	1K
V0198	20	5K	200R	V0190		1K	500R
V0204		10K	500R	V0182		400R	200R
V0193	2K	100R	V0179	200R	100R	1.25	
V0205	10	10K	1K	V0186	500R		400R
V0194		2K	200R	V0178	100R	100R	
V0187		1K	100R	V0180	200R	200R	
V0200	5	5K	1K	V0183	400R	400R	1
V0195		2K	400R	V0023	500R	500R	
V0188		1K	200R	V0191	1K	1K	
V0184		500R	100R	V0176	2K	2K	
V0196	4	2K	500R	V0019	5K	5K	10K
V0181		400R	100R	V0008	10K	10K	

Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay Precision Group"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify Vishay Precision Group's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

Vishay Precision Group makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase. **To the maximum extent permitted by applicable law, Vishay Precision Group disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.**

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on Vishay Precision Group's knowledge of typical requirements that are often placed on Vishay Precision Group products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of Vishay Precision Group.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay Precision Group products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay Precision Group for any damages arising or resulting from such use or sale. Please contact authorized Vishay Precision Group personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.