


Solid Tantalum Chip Capacitors, TANTAMOUNT[®], High-Rel COTS, Conformal Coated Case



FEATURES

- High reliability; Weibull grading available
- Surge current testing per MIL-PRF-55365 options available
- Standard and low ESR options
- Terminations: SnPb, standard. 100 % tin available
- Compliant to RoHS directive 2002/95/EC



RoHS*
COMPLIANT

PERFORMANCE/ELECTRICAL CHARACTERISTICS

Operating Temperature: - 55 °C to + 85 °C
(To + 125 °C with voltage derating)

Capacitance Range: 0.15 µF to 680 µF

Capacitance Tolerance: ± 20 %, ± 10 % standard


Voltage Rating: 4 WV_{DC} to 50 WV_{DC}

ORDERING INFORMATION								
T95	D	107	K	010	E	A	S	
TYPE	CASE CODE	CAPACITANCE	CAPACITANCE TOLERANCE	DC VOLTAGE RATING AT + 85 °C	TERMINATION AND PACKAGING	RELIABILITY LEVEL	SURGE CURRENT	
	See Ratings and Case Codes table.	This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow.	K = ± 10 % M = ± 20 %	This is expressed in volts. To complete the three-digit block, zeros precede the voltage rating. A decimal point is indicated by an "R" (6R3 = 6.3 V).	E: Sn/Pb solder/7" (178 mm) reels L: Sn/Pb solder/7" (178 mm) ½ reel C: 100 % tin/7" (178 mm) reels H: 100 % tin/7" (178 mm) ½ reel Y = R-case only; Sn/Pb solder, side mounted, 7" reels	A = 1.0 % Weibull B = 0.1 % Weibull ⁽¹⁾ S = Hi-rel standard burn-in Z = Non-established reliability	A = 10 cycles at + 25 °C B = 10 cycles at - 55 °C/+ 85 °C S = 3 cycles at + 25 °C	S = Std L = Low

Note

⁽¹⁾ Weibull 0.1 % may not be available on all ratings. See detailed notes in ratings table or contact marketing for availability

DIMENSIONS in inches [millimeters]



CASE CODE	L (MAX.)	W	H	A	B	D (REF.)	J (MAX.)
A	0.146 [3.7]	0.072 ± 0.012 [1.8 ± 0.3]	0.056 ± 0.012 [1.4 ± 0.3]	0.031 ± 0.012 [0.80 ± 0.30]	0.085 ± 0.016 [2.2 ± 0.4]	0.115 [2.9]	0.004 [0.1]
B	0.158 [4.0]	0.110 + 0.012 - 0.016 [2.8 + 0.3 - 0.4]	0.075 + 0.012 - 0.024 [1.9 + 0.3 - 0.6]	0.031 ± 0.012 [0.80 ± 0.30]	0.097 ± 0.016 [2.5 ± 0.4]	0.138 [3.5]	0.004 [0.1]
C	0.281 [7.1]	0.126 ± 0.012 [3.2 ± 0.3]	0.098 ± 0.012 [2.5 ± 0.3]	0.051 ± 0.012 [1.3 ± 0.30]	0.180 ± 0.024 [4.6 ± 0.6]	0.236 [6.0]	0.004 [0.1]
D	0.293 [7.5]	0.170 ± 0.012 [4.3 ± 0.3]	0.110 ± 0.012 [2.8 ± 0.3]	0.051 ± 0.012 [1.3 ± 0.30]	0.180 ± 0.024 [4.6 ± 0.6]	0.253 [6.4]	0.004 [0.1]
R	0.283 [7.2]	0.235 + 0.012/- 0.024 [6.0 + 0.3/- 0.6]	0.136 ± 0.012 [3.5 ± 0.3]	0.051 ± 0.012 [1.3 ± 0.30]	0.180 ± 0.024 [4.6 ± 0.6]	0.243 [6.2]	0.004 [0.1]
S	0.143 [3.63]	0.072 ± 0.008 [1.83 ± 0.2]	0.048 ± 0.008 [1.22 ± 0.2]	0.023 ± 0.010 [0.58 ± 0.25]	0.085 ± 0.015 [2.16 ± 0.37]	0.115 [2.9]	0.004 [0.1]

* Pb containing terminations are not RoHS compliant, exemptions may apply



Solid Tantalum Chip Capacitors,
TANTAMOUNT[®], High-Rel COTS, Conformal Coated Case

Vishay Sprague

DIMENSIONS in inches [millimeters]							
CASE CODE	L (MAX.)	W	H	A	B	D (REF.)	J (MAX.)
V	0.143 [3.63]	0.104 ± 0.010 [2.65 ± 0.25]	0.051 ± 0.010 [1.3 ± 0.25]	0.023 ± 0.010 [0.58 ± 0.25]	0.085 ± 0.015 [2.16 ± 0.37]	0.115 [2.9]	0.004 [0.1]
X	0.285 [7.24]	0.104 ± 0.010 [2.65 ± 0.25]	0.051 ± 0.010 [1.3 ± 0.25]	0.040 ± 0.020 [1.0 ± 0.5]	0.200 ± 0.027 [5.08 ± 0.69]	0.243 [6.2]	0.004 [0.1]
Y	0.285 [7.24]	0.104 ± 0.010 [2.65 ± 0.25]	0.069 ± 0.010 [1.75 ± 0.25]	0.040 ± 0.020 [1.0 ± 0.5]	0.200 ± 0.027 [5.08 ± 0.69]	0.243 [6.2]	0.004 [0.1]
Z	0.285 [7.24]	0.104 ± 0.010 [2.65 ± 0.25]	0.104 ± 0.010 [2.65 ± 0.25]	0.040 ± 0.020 [1.0 ± 0.5]	0.200 ± 0.027 [5.08 ± 0.69]	0.243 [6.2]	0.004 [0.1]

Note

- The anode termination (D less B) will be a minimum of 0.010" (0.25 mm)

RATINGS AND CASE CODES								
µF	4 V	6.3 V	10 V	16 V	20 V	25 V	35 V	50 V
0.15							S	
0.22							S	
0.33							S	
0.47							S	
0.68						S	S	
1.0						S	S	
1.5					S	S	V	
2.2				S	S	V	X	
3.3			S	S	V			
4.7		S	S	V	X	X	Y	C
6.8	S	S	V	A/X	X	Y	Z	C/D
10	S	V	X	X	Y	C/Y	Z	R
15	V	X	B/X	B/Y	Z	Z	D/R	R
22	X	X	Y	B/Z	Z		R	R
33	X		Z	Z		D/R	R	
47	Y	Y	Z		R	D/R	R	
68	Y			R		D/R		
100	Z	Z	R	C/D	R	R		
120			D/R		R			
150			D/R	D	R			
180		R		R				
220		D/R	D/R	R				
270	D							
330	R	C	D/R	R				
390		R						
470		D	R					
680		R	R					



STANDARD RATINGS						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DC LEAKAGE AT + 25 °C (μ A)	MAX. DF AT + 25 °C 120 Hz (%)	STD. (S) MAX. ESR AT + 25 °C 100 kHz (Ω)	LOW (L) MAX. ESR AT + 25 °C 100 kHz (Ω)
4 WV_{DC} AT + 85 °C, 2.7 WV_{DC} AT + 125 °C						
6.8	S	T95S685(1)004(2)(3)(4)L	0.5	6	N/A	2.000
10	S	T95S106(1)004(2)(3)(4)L	0.5	6	N/A	2.000
15	V	T95V156(1)004(2)(3)(4)L	0.6	6	N/A	1.500
22	X	T95X226(1)004(2)(3)(4)L	0.9	6	N/A	1.000
33	X	T95X336(1)004(2)(3)(4)L	1.3	6	N/A	1.000
47	Y	T95Y476(1)004(2)(3)(4)L	1.9	6	N/A	0.600
68	Y	T95Y686(1)004(2)(3)(4)L	2.7	6	N/A	0.600
100	Z	T95Z107(1)004(2)(3)(4)L	4.0	6	N/A	0.400
270	D	T95D277(1)004(2)(3)(4)(5)	10.8	8	0.13	0.060
330	R	T95R337(1)004(2)(3)(4)(5)	13.2	8	0.13	0.080
6.3 WV_{DC} AT + 85 °C, 4 WV_{DC} AT 125 °C						
4.7	S	T95S475(1)6R3(2)(3)(4)L	0.5	6	N/A	2.000
6.8	S	T95S685(1)6R3(2)(3)(4)L	0.5	6	N/A	2.000
10	V	T95V106(1)6R3(2)(3)(4)L	0.6	6	N/A	1.500
15	X	T95X156(1)6R3(2)(3)(4)L	0.9	6	N/A	1.000
22	X	T95X226(1)6R3(2)(3)(4)L	1.4	6	N/A	1.000
47	Y	T95Y476(1)6R3(2)(3)(4)L	2.8	6	N/A	0.600
100	Z	T95Z107(1)6R3(2)(3)(4)L	6.0	6	N/A	0.400
180	R	T95R187(1)6R3(2)(3)(4)(5)	10.8	8	0.13	0.080
220	D	T95R227(1)6R3(2)(6)(4)(5)	22.0	8	0.14	0.065
220	R	T95R227(1)6R3(2)(3)(4)(5)	13.2	8	0.13	0.080
330	C	T95C337(1)6R3(2)(6)(4)(5)	20.8	8	0.08	0.170
390	R	T95R397(1)6R3(2)(3)(4)(5)	23.4	8	0.13	0.045
470	D	T95D477(1)6R3(2)(3)(4)(5)	28.2	10	0.13	0.060
680	R	T95R687(1)6R3(2)(3)(4)(5)	40.8	12	0.09	0.045
10 WV_{DC} AT + 85 °C, 7 WV_{DC} AT 125 °C						
3.3	S	T95S335(1)010(2)(3)(4)L	0.5	6	N/A	2.500
4.7	S	T95S475(1)010(2)(3)(4)L	0.5	6	N/A	2.000
6.8	V	T95V685(1)010(2)(3)(4)L	0.7	6	N/A	2.000
10	X	T95X106(1)010(2)(3)(4)L	1.0	6	N/A	1.500
15	B	T95B156(1)010(2)(6)(4)(5)	2.4	6	0.75	0.550
15	X	T95X156(1)010(2)(3)(4)L	1.5	6	N/A	1.000
22	Y	T95Y226(1)010(2)(6)(4)L	2.2	6	N/A	0.600
33	Z	T95Z336(1)010(2)(3)(4)L	3.3	6	N/A	0.400
47	Z	T95Z476(1)010(2)(3)(4)L	4.7	6	N/A	0.400
100	R	T95R107(1)010(2)(3)(4)(5)	10.0	8	0.14	0.075
120	D	T95D127(1)010(2)(6)(4)(5)	12.0	8	0.14	0.085
120	R	T95R127(1)010(2)(6)(4)(5)	12.0	8	0.14	0.070
150	D	T95D157(1)010(2)(3)(4)(5)	15.0	8	0.14	0.075
150	R	T95R157(1)010(2)(3)(4)(5)	15.0	8	0.13	0.065
220	D	T95D227(1)010(2)(6)(4)(5)	22.0	8	0.14	0.065
220	R	T95R227(1)010(2)(3)(4)(5)	22.0	8	0.13	0.055
330	D	T95D337(1)010(2)(6)(4)(5)	33.0	8	0.14	0.065
330	R	T95R337(1)010(2)(3)(4)(5)	33.0	8	0.13	0.045
470	R	T95R477(1)010(2)(6)(4)(5)	47.0	8	0.13	0.045
680	R	T95R687(1)010(2)(6)(4)(5)	68.0	14	0.09	N/A



Solid Tantalum Chip Capacitors,
TANTAMOUNT[®], High-Rel COTS, Conformal Coated Case

Vishay Sprague

STANDARD RATINGS						
CAPACITANCE (μF)	CASE CODE	PART NUMBER	MAX. DC LEAKAGE AT + 25 °C (μA)	MAX. DF AT + 25 °C 120 Hz (%)	STD. (S) MAX. ESR AT + 25 °C 100 kHz (Ω)	LOW (L) MAX. ESR AT + 25 °C 100 kHz (Ω)
16 WV_{DC} AT + 85 °C, 10 WV_{DC} AT + 125 °C						
2.2	S	T95S225(1)016(2)(3)(4)L	0.5	6	N/A	3.500
3.3	S	T95S335(1)016(2)(3)(4)L	0.5	6	N/A	2.500
4.7	V	T95V475(1)016(2)(3)(4)L	0.8	6	N/A	2.000
6.8	X	T95X685(1)016(2)(3)(4)L	1.1	6	N/A	1.500
6.8	A	T95A685(1)016(2)(3)(4)(5)	1.1	6	2.8	0.800
10	X	T95X106(1)016(2)(3)(4)L	1.6	6	N/A	1.500
15	B	T95B156(1)016(2)(3)(4)(5)	2.4	6	0.75	0.550
15	Y	T95Y156(1)016(2)(3)(4)L	2.4	6	N/A	0.600
22	B	T95B226(1)016(2)(6)(4)(5)	3.5	6	0.75	0.500
22	Z	T95Z226(1)016(2)(3)(4)L	3.5	6	N/A	0.400
33	Z	T95Z336(1)016(2)(3)(4)L	5.3	6	N/A	0.400
68	R	T95R686(1)016(2)(3)(4)(5)	10.9	6	0.6	0.095
100	C	T95C107(1)016(2)(6)(4)(5)	16.0	8	0.6	0.090
100	D	T95D107(1)016(2)(6)(4)(5)	16.0	8	0.14	0.080
150	D	T95D157(1)016(2)(3)(4)(5)	24.0	8	0.14	0.085
180	R	T95R187(1)016(2)(6)(4)(5)	28.8	8	0.13	0.055
220	R	T95R227(1)016(2)(6)(4)(5)	35.2	8	0.12	0.055
330	R	T95R337(1)016(2)(6)(4)(5)	52.8	14	0.11	0.055
20 WV_{DC} AT + 85 °C, 13 WV_{DC} AT + 125 °C						
1.5	S	T95S155(1)020(2)(3)(4)L	0.5	6	N/A	3.500
2.2	S	T95S225(1)020(2)(3)(4)L	0.5	6	N/A	3.500
3.3	V	T95V335(1)020(2)(3)(4)L	0.7	6	N/A	3.000
4.7	X	T95X475(1)020(2)(3)(4)L	0.9	6	N/A	1.500
6.8	X	T95X685(1)020(2)(3)(4)L	1.4	6	N/A	1.500
10	Y	T95Y106(1)020(2)(3)(4)L	2.0	6	N/A	1.000
15	Z	T95Z156(1)020(2)(3)(4)L	3.0	6	N/A	0.600
22	Z	T95Z226(1)020(2)(3)(4)L	4.4	6	N/A	0.400
47	R	T95R476(1)020(2)(3)(4)L	9.4	6	0.20	0.110
100	R	T95R107(1)020(2)(6)(4)S	20.0	8	0.14	N/A
120	R	T95R127(1)020(2)(6)(4)(5)	24.0	8	0.14	0.080
150	R	T95R157(1)020(2)(3)(4)(5)	30.0	8	0.14	0.075
25 WV_{DC} AT + 85 °C, 17 WV_{DC} AT + 125 °C						
0.68	S	T95S684(1)025(2)(3)(4)L	0.5	4	N/A	5.000
1	S	T95S105(1)025(2)(3)(4)L	0.5	4	N/A	3.500
1.5	S	T95S155(1)025(2)(3)(4)L	0.5	6	N/A	3.500
2.2	V	T95V225(1)025(2)(3)(4)L	0.6	6	N/A	2.000
4.7	X	T95X475(1)025(2)(3)(4)L	1.2	6	N/A	1.500
6.8	Y	T95Y685(1)025(2)(3)(4)L	1.7	6	N/A	1.000
10	C	T95C106(1)025(2)(3)(4)(5)	2.5	6	0.57	0.280
10	Y	T95Y106(1)025(2)(3)(4)L	2.5	6	N/A	1.000
15	Z	T95Z156(1)025(2)(3)(4)L	3.8	6	N/A	0.600
33	D	T95D336(1)025(2)(3)(4)(5)	8.3	6	0.26	0.130
33	R	T95R336(1)025(2)(3)(4)(5)	8.3	6	0.25	0.130
47	D	T95D476(1)025(2)(6)(4)(5)	11.8	6	0.26	0.130
47	R	T95R476(1)025(2)(3)(4)(5)	11.8	6	0.20	0.108
68	D	T95D686(1)025(2)(6)(4)(5)	17.0	8	0.26	0.200
68	R	T95R686(1)025(2)(6)(4)(5)	17.0	6	0.20	0.095
100	R	T95R107(1)025(2)(6)(4)(5)	25.0	8	0.20	0.090



STANDARD RATINGS						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DC LEAKAGE AT + 25 °C (μ A)	MAX. DF AT + 25 °C 120 Hz (%)	STD. (S) MAX. ESR AT + 25 °C 100 kHz (Ω)	LOW (L) MAX. ESR AT + 25 °C 100 kHz (Ω)
35 WV_{DC} AT + 85 °C, 23 WV_{DC} AT + 125 °C						
0.15	S	T95S154(1)035(2)(3)(4)L	0.5	4	N/A	18.000
0.22	S	T95S224(1)035(2)(3)(4)L	0.5	4	N/A	15.000
0.33	S	T95S334(1)035(2)(3)(4)L	0.5	4	N/A	12.000
0.47	S	T95S474(1)035(2)(3)(4)L	0.5	4	N/A	9.000
0.68	S	T95S684(1)035(2)(3)(4)L	0.5	4	N/A	5.000
1	S	T95S105(1)035(2)(3)(4)L	0.5	4	N/A	3.500
1.5	V	T95V155(1)035(2)(3)(4)L	0.5	6	N/A	3.000
2.2	X	T95X225(1)035(2)(3)(4)L	0.8	6	N/A	2.000
4.7	Y	T95Y475(1)035(2)(3)(4)L	1.6	6	NA	0.800
6.8	Z	T95Z685(1)035(2)(6)(4)L	2.4	6	N/A	0.800
10	Z	T95Z106(1)035(2)(3)(4)L	3.5	6	N/A	0.600
15	D	T95D156(1)035(2)(3)(4)(5)	5.3	6	0.41	0.270
15	R	T95R156(1)035(2)(3)(4)(5)	5.3	6	0.38	0.190
22	R	T95R226(1)035(2)(3)(4)(5)	7.7	6	0.28	0.240
33	R	T95R336(1)035(2)(3)(4)(5)	11.6	6	0.28	0.200
47	R	T95R476(1)035(2)(3)(4)(5)	16.5	6	0.28	0.320
50 WV_{DC} AT + 85 °C, 33 WV_{DC} AT + 125 °C						
4.7	C	T95C475(1)050(2)(3)(4)(5)	2.4	6	1.4	0.800
6.8	C	T95C685(1)050(2)(3)(4)(5)	3.4	6	0.7	1.300
6.8	D	T95D685(1)050(2)(3)(4)(5)	3.4	6	0.82	0.450
10	R	T95R106(1)050(2)(6)(4)(5)	5.0	6	0.65	0.500
15	R	T95R156(1)050(2)(3)(4)(5)	7.5	6	0.40	0.350
22	R	T95R226(1)050(2)(3)(4)(5)	11.0	6	0.39	0.300

Notes

- (1) Capacitance tolerance: K, M
- (2) Termination and packaging: C, E, H, L
- (3) Reliability level: A, S, Z
- (4) Surge current: A, B, S
- (5) ESR: L, S
- (6) Reliability level: A, B, S, Z



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.