

AC ADAPTER PART NUMBER CONFIGURATION

WALL MOUNT TYPE AC ADAPTER

TRXXXX - X - XX X XX

Model No.	AC Plug Type	DC Plug Type	OVP Option	DC Cable Length and Type	
	A : USA 2 Pin E : Europe 2 Pin U : British 3 Pin S : Australia 2 Pin	Straight / Inner+Outer- + — ●) — - 11 : 5.5 x 2.1 x 12mm 12 : 5.5 x 2.5 x 12mm 18 : 5.5 x 2.5 x 11mm 23 : 5.5 x 2.1 x 9.5mm 26 : 5.5 x 2.5 x 9.5mm 32 : 5.5 x 2.1 x 7.5mm 33 : 5.5 x 2.1 x 11.5mm 35 : 4.0 x 1.7 x 9.5mm 37 : 5.5 x 2.5 x 7.5mm 39 : 3.5 x 1.35 x 9mm 41 : 3.5 x 1.35 x 7.5mm 45 : 4.75 x 1.7 x 9.5mm 50 : 4.0 x 1.7 x 11mm 104 : 5.5 x 2.1 x 14mm 107 : 6.3 x 3.0 x 12mm 113 : 5.5 x 2.5 x 14mm 115 : 3.0 x 1.1 x 10mm 116 : 3.5 x 1.35 x 9.5mm 118 : 6.5 x 3 x 11mm 119 : 4.0 x 1.35 x 7.5mm 120 : 4.0 x 1.35 x 9.5mm 121 : 3.8 x 1.35 x 9.5mm 123 : 3.5 x 0.7 x 8mm 124 : 3.5 x 1.1 x 11mm 125 : 6.2 x 1.9 x 14mm 126 : 3.5 x 1.35 x 8.4mm 127 : 2.35 x 0.7 x 9.5mm 130 : 3.4 x 1.35 x 10mm 131 : 5.5 x 2.5 x 11mm 133 : 3.5 x 1.35 x 9mm 134 : 3.5 x 1.35 x 10mm 137 : 4.75 x 1.7 x 12mm 140 : 5.5 x 1.0 x 9.5mm 143 : 4.0 x 1.7 x 10mm 144 : 3.5 x 1.35 x 12mm 146 : 3.5 x 1.35 x 14mm 149 : 2.5 x 0.7 x 9mm 301 : 6.5 x 3.0 x 9.5mm 311 : 3.5 x 1.35 x 6mm 312 : 5.5 x 2.1 x 11mm 319 : 3.5 x 1.9 x 9.0mm 330 : 3.5 x 1.35 x 6.5mm 331 : 3.0 x 1.1 x 8.5 333 : 3.5 x 1.1 x 7.5mm 334 : 3.5 x 1.1 x 8.7mm 335 : 3.5 x 1.35 x 7mm 338 : 3.5 x 1.35 x 11mm 340 : 5.5 x 2.5 x 11.5mm 341 : 3.5 x 1.1 x 7.6mm 343 : 4.75 x 1.7 x 10mm 348 : 3.5 x 1.3 x 7.5mm 350 : 5.0 x 1.9 x 8mm Straight / Inner-Outer+ + - — ●) — + 05 : 5.5 x 2.1 x 12mm 13 : 5.5 x 2.1 x 12mm 14 : 5.5 x 2.5 x 12mm 27 : 5.5 x 2.5 x 9.5mm 102 : 5.5 x 2.1 x 9.5mm 108 : 3.5 x 1.35 x 7.5mm	117 : 2.5 x 0.7 x 9mm 128 : 4.0 x 1.7 x 9.5mm 129 : 3.5 x 1.1 x 7.5mm 136 : 3.5 x 1.35 x 9mm 147 : 3.0 x 1.1 x 9mm 329 : 3.8 x 1.05 x 9.5mm 62 : Open end XX : For special plugs, please inquire your distributor Right Angle / Inner+Outer- + — ●) — - 01 : 5.5 x 2.1 x 12mm 02 : 5.5 x 2.5 x 12mm 17 : 5.5 x 2.1 x 11mm 19 : 5.5 x 2.5 x 10.5mm 20 : 5.5 x 2.5 x 9mm 21 : 5.5 x 2.5 x 9.5mm 24 : 5.5 x 2.1 x 9.5mm 31 : 3.5 x 1.35 x 7.5mm 34 : 5.5 x 2.1 x 11.5mm 36 : 3.5 x 1.35 x 9mm 38 : 3.5 x 1.7 x 9mm 40 : 4.0 x 1.7 x 9.5mm 42 : 3.5 x 1.35 x 9.5mm 46 : 4.0 x 1.7 x 12mm 48 : 5 x 1.5 x 9.5mm 49 : 2.35 x 0.7 x 9.5mm 103 : 3.5 x 1.05 x 9.5mm 106 : 4.0 x 1.7 x 10mm 109 : 5.5 x 2.2 x 11mm 110 : 6.5 x 3.0 x 9.5mm 112 : 6.5 x 3.0 x 10mm 114 : 3.0 x 1.1 x 10mm 117 : 3.5 x 1.3 x 9mm 138 : 3.5 x 1.35 x 12mm 142 : 3.8 x 1.1 x 10mm 148 : 3.5 x 1.35 x 10mm 303 : 4.75 x 1.7 x 11mm 304 : 5.5 x 2.1 x 9mm 305 : 3.5 x 1.3 x 8mm 309 : 5.5 x 2.5 x 11mm 324 : 4.0 x 1.7 x 11mm 501 : 3.5 x 1.35 x 6.5mm 503 : 5.5 x 2.1 x 9.5 507 : 3.5 x 1.1 x 9mm 509 : 3.5 x 1.35 x 11.5mm 512 : 6.3 x 3.0 x 12mm 513 : 3.5 x 1.1 x 9.5mm Right Angle / Inner-Outer+ + - — ●) — + 03 : 5.5 x 2.1 x 12mm 04 : 5.5 x 2.5 x 12mm 16 : 5.5 x 2.1 x 11mm 22 : 5.5 x 2.5 x 9.5mm 43 : 5.5 x 2.1 x 9.5mm 44 : 3.5 x 1.35 x 7.5mm 105 : 3.5 x 1.05 x 9.5mm 111 : 3.5 x 1.35 x 9.5mm 122 : 3.5 x 1.35 x 12mm 141 : 5.5 x 2.1 x 11mm 150 : 3.5 x 1.35 x 9mm 317 : 5.5 x 2.5 x 9mm	A : Without OVP Option E : With OVP Option	01 : 720mm 02 : 1200mm 03 : 1800mm 11 : 720mm with Ferrite Core 12 : 1200mm with Ferrite Core 13 : 1800mm with Ferrite Core

DESK TOP TYPE AC ADAPTER

TRXXXXX - XX X XX

Model No.	DC Plug Type	OVP Option	DC Cable Length and Type
	Straight / Inner+Outer- + — ●) — -	A : Without OVP Option E : With OVP Option	01 :720mm 02 :1200mm 03 :1800mm 11 :720mm with Ferrite Core 12 :1200mm with Ferrite Core 13 :1800mm with Ferrite Core 21 :720mm with Ferrite Core (Only for TR100 Series)) 22 :1200mm with Ferrite Core (Only for TR100 Series) 23 :1800mm with Ferrite Core (Only for TR100 Series)
	11 : 5.5 x 2.1 x 12mm 12 : 5.5 x 2.5 x 12mm 18 : 5.5 x 2.5 x 11mm 23 : 5.5 x 2.1 x 9.5mm 26 : 5.5 x 2.5 x 9.5mm 32 : 5.5 x 2.1 x 7.5mm 33 : 5.5 x 2.1 x 11.5mm 35 : 4.0 x 1.7 x 9.5mm 37 : 5.5 x 2.5 x 7.5mm 39 : 3.5 x 1.35 x 9mm 41 : 3.5 x 1.35 x 7.5mm 45 : 4.75 x 1.7 x 9.5mm 50 : 4.0 x 1.7 x 11mm 104 : 5.5 x 2.1 x 14mm 107 : 6.3 x 3.0 x 12mm 113 : 5.5 x 2.5 x 14mm 115 : 3.0 x 1.1 x 10mm 116 : 3.5 x 1.35 x 9.5mm 118 : 6.5 x 3 x 11mm 119 : 4.0 x 1.35 x 7.5mm 120 : 4.0 x 1.35 x 9.5mm 121 : 3.8 x 1.35 x 9.5mm 123 : 3.5 x 0.7 x 8mm 124 : 3.5 x 1.1 x 11mm 125 : 6.2 x 1.9 x 14mm 126 : 3.5 x 1.35 x 8.4mm 127 : 2.35 x 0.7 x 9.5mm 130 : 3.4 x 1.35 x 10mm 131 : 5.5 x 2.5 x 11mm 133 : 3.5 x 1.35 x 9mm 134 : 3.5 x 1.35 x 10mm 137 : 4.75 x 1.7 x 12mm 140 : 5.5 x 1.0 x 9.5mm 143 : 4.0 x 1.7 x 10mm 144 : 3.5 x 1.35 x 12mm 146 : 3.5 x 1.35 x 14mm 149 : 2.5 x 0.7 x 9mm 301 : 6.5 x 3.0 x 9.5mm 311 : 3.5 x 1.35 x 6mm 312 : 5.5 x 2.1 x 11mm 319 : 3.5 x 1.9 x 9.0mm 330 : 3.5 x 1.35 x 6.5mm 331 : 3.0 x 1.1 x 8.5 333 : 3.5 x 1.1 x 7.5mm 334 : 3.5 x 1.1 x 8.7mm 335 : 3.5 x 1.35 x 7mm 338 : 3.5 x 1.35 x 11mm 340 : 5.5 x 2.5 x 11.5mm 341 : 3.5 x 1.1 x 7.6mm 343 : 4.75 x 1.7 x 10mm 348 : 3.5 x 1.3 x 7.5mm 350 : 5.0 x 1.9 x 8mm	117 : 2.5 x 0.7 x 9mm 128 : 4.0 x 1.7 x 9.5mm 129 : 3.5 x 1.1 x 7.5mm 136 : 3.5 x 1.35 x 9mm 147 : 3.0 x 1.1 x 9mm 329 : 3.8 x 1.05 x 9.5mm 62 : Open end XX : For special plugs, please inquire your distributor	
	Right Angle / Inner+Outer- + — ●) — -		
	01 : 5.5 x 2.1 x 12mm 02 : 5.5 x 2.5 x 12mm 17 : 5.5 x 2.1 x 11mm 19 : 5.5 x 2.5 x 10.5mm 20 : 5.5 x 2.5 x 9mm 21 : 5.5 x 2.5 x 9.5mm 24 : 5.5 x 2.1 x 9.5mm 31 : 3.5 x 1.35 x 7.5mm 34 : 5.5 x 2.1 x 11.5mm 36 : 3.5 x 1.35 x 9mm 38 : 3.5 x 1.7 x 9mm 40 : 4.0 x 1.7 x 9.5mm 42 : 3.5 x 1.35 x 9.5mm 46 : 4.0 x 1.7 x 12mm 48 : 5 x 1.5 x 9.5mm 49 : 2.35 x 0.7 x 9.5mm 103 : 3.5 x 1.05 x 9.5mm 106 : 4.0 x 1.7 x 10mm 109 : 5.5 x 2.2 x 11mm 110 : 6.5 x 3.0 x 9.5mm 112 : 6.5 x 3.0 x 10mm 114 : 3.0 x 1.1 x 10mm 117 : 3.5 x 1.3 x 9mm 138 : 3.5 x 1.35 x 12mm 142 : 3.8 x 1.1 x 10mm 148 : 3.5 x 1.35 x 10mm 303 : 4.75 x 1.7 x 11mm 304 : 5.5 x 2.1 x 9mm 305 : 3.5 x 1.3 x 8mm 309 : 5.5 x 2.5 x 11mm 324 : 4.0 x 1.7 x 11mm 501 : 3.5 x 1.35 x 6.5mm 503 : 5.5 x 2.1 x 9.5 507 : 3.5 x 1.1 x 9mm 509 : 3.5 x 1.35 x 11.5mm 512 : 6.3 x 3.0 x 12mm 513 : 3.5 x 1.1 x 9.5mm		
	Right Angle / Inner-Outer+ - — ●) — +		
	03 : 5.5 x 2.1 x 12mm 04 : 5.5 x 2.5 x 12mm 16 : 5.5 x 2.1 x 11mm 22 : 5.5 x 2.5 x 9.5mm 43 : 5.5 x 2.1 x 9.5mm 44 : 3.5 x 1.35 x 7.5mm 105 : 3.5 x 1.05 x 9.5mm 111 : 3.5 x 1.35 x 9.5mm 122 : 3.5 x 1.35 x 12mm 141 : 5.5 x 2.1 x 11mm 150 : 3.5 x 1.35 x 9mm 317 : 5.5 x 2.5 x 9mm		
	Straight / Inner-Outer+ - — ●) — +		
	05 : 5.5 x 2.1 x 12mm 13 : 5.5 x 2.1 x 12mm 14 : 5.5 x 2.5 x 12mm 27 : 5.5 x 2.5 x 9.5mm 102 : 5.5 x 2.1 x 9.5mm 108 : 3.5 x 1.35 x 7.5mm		

Typical at 25°C, nominal line and 75% load, unless otherwise Specified