

Product Brief

Mobile Intel® 910GML Express Chipset

Embedded Computing



Mobile Intel® 910GML Express Chipset for Embedded Computing


Product Overview

The Mobile Intel® 910GML Express chipset offers an optimized integrated graphics solution with a 400 MHz front-side bus. The integrated 32-bit 3D graphics engine, based on Intel® Graphics Media Accelerator 900 (Intel® GMA 900) architecture, operates at core speeds of up to 200 MHz. The chipset consists of the Intel® 910GML Graphic Memory Controller Hub (GMCH) and the Intel® I/O Controller Hub 6-M (ICH6-M). It features a low-power design, is validated with Intel® Celeron® M processors on 90nm process, and supports up to 2 GB of DDR2 400 MHz system memory.

Intel's platform architecture delivers the performance and high scalability required for today's embedded computing applications. The Intel 910GML GMCH and ICH6-M are part of Intel's comprehensive validation process that enables fast deployment of platforms to maximize competitive advantage while minimizing development risks.

Product Highlights

- Designed, validated, and optimized for Intel Celeron M processors on 90nm
- 400 MHz front-side bus delivers a high-bandwidth connection between the processor and platform
- Supports dual-channel non-ECC DDR2 400 MHz and single-channel DDR 333
- New graphics core based on Intel GMA 900
- Long-term system reliability over wide operating conditions
- Direct Media Interface (DMI) chip interconnect can be implemented x4 or x2 widths, and provides up to 1 GB/s in each direction in full duplex
- Four USB host controllers provide high-performance peripherals with 480 Mb/s of bandwidth, while enabling support for up to eight USB 2.0 ports. This results in a significant increase over previous integrated one- to four-port hubs at 12 Mb/s
- Four x1 PCI Express ports, fully PCI Express 1.0a-compliant, and support for full 250 MB/s in each direction
- Intel® High Definition Audio[†] (Intel® HD Audio) interface for full surround sound support
- LAN Connect Interface (LCI) provides flexible network solutions such as 10/100 Mb/s Ethernet and 10/100 Mb/s Ethernet with LAN manageability
- Integrated Serial ATA host controller supports two ports and data transfers up to 1.5 MB/s



Product Highlights (continued)

Display

- Analog display support
- Dual display support
 - Independent: different images and native display timings on each display device
 - Simultaneous: same images and native display timings on each display device
- SDVO support
 - Dual SDVO channels provide support for a wide array of displays
- Dedicated Local Flat Panel (LFP) LVDS interface

Internal Graphics Features

- Core frequency
 - Display core frequency up to 200 MHz
 - Render core frequency up to 166 MHz
 - Dynamic Video Memory Technology (DVMT) 3.0 to dynamically allocate up to 128 MB of system memory for graphics usage

Mobile Intel® 910GML Express Chipset for Embedded Computing

Product	Product Code	Package	Features
Intel® 910GML Express Graphics Memory Controller Hub (GMCH)	QG82910GML	1257 µFC-BGA	<ul style="list-style-type: none">▪ 400 MHz front-side bus▪ Up to DDR2 400 MHz system memory▪ Intel® Graphics Media Accelerator 900
Intel® I/O Controller Hub 6-M (ICH6-M)	NH82801FBM	609 µ-BGA	<ul style="list-style-type: none">▪ Direct connection to GMCH via Direct Media Interface▪ Supports four PCI Express root ports▪ Two-port Serial ATA controller▪ Support for up to eight USB 2.0 ports▪ Intel® High Definition Audio[†] interface

[†] Intel® High Definition Audio requires a system with an appropriate Intel chipset and a motherboard with an appropriate codec and the necessary drivers installed. System sound quality will vary depending on actual implementation, controller, codec, drivers and speakers. For more information about Intel® HD audio, refer to www.intel.com <http://www.intel.com/>

Intel Access

- Embedded Intel® Architecture Home Page: intel.com/design/intarch
Developer's Site: intel.com/design
Intel in Embedded and Communications: intel.com/go/embedded
General Information Hotline: (800) 628-8686 or (916) 356-3104 5 a.m. to 5 p.m. PST
Intel® Literature Center: (800) 548-4725 7 a.m. to 7 p.m. CST (U.S. and Canada)
[International locations please contact your local sales office.](#)

INFORMATION IN THIS DOCUMENT IS PROVIDED IN CONNECTION WITH INTEL® PRODUCTS. NO LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE, TO ANY INTELLECTUAL PROPERTY RIGHTS IS GRANTED BY THIS DOCUMENT. EXCEPT AS PROVIDED IN INTEL'S TERMS AND CONDITIONS OF SALE FOR SUCH PRODUCTS, INTEL ASSUMES NO LIABILITY WHATSOEVER, AND INTEL DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY, RELATING TO SALE AND/OR USE OF INTEL PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

Intel products are not intended for use in medical, life saving, life sustaining, critical control or safety systems, or in nuclear facility applications. Intel may make changes to specifications and product descriptions at any time, without notice. Designers must not rely on the absence or characteristics of any features or instructions marked "reserved" or "undefined." Intel reserves these for future definition and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to them. The information here is subject to change without notice. Do not finalize a design with this information. The products described in this document may contain design defects or errors known as errata which may cause the product to deviate from published specifications. Current characterized errata are available on request. Contact your local Intel sales office or your distributor to obtain the latest specifications and before placing your product order. Copies of documents which have an order number and are referenced in this document, or other Intel literature, may be obtained by calling 1-800-548-4725, or by visiting Intel's Web Site <http://www.intel.com/>.

Intel, the Intel logo, Intel. Leap ahead., Intel. Leap ahead. logo, and Celeron are trademarks of Intel Corporation in the U.S. and other countries.

*Other names and brands may be claimed as the property of others.

Copyright © 2007 Intel Corporation. All rights reserved.

Printed in USA

0407/KSC/OCG/XX/PDF

 Please Recycle

317225-001US

