



Product/Process Change Notice - PCN 24_0171 Rev. -

Analog Devices, Inc. One Analog Way, Wilmington, MA 01887, USA

This notice is to inform you of a change that will be made to certain ADI products (see Appendix A) that you may have purchased in the last 2 years. **Any inquiries or requests with this PCN (additional data or samples) must be sent to ADI within 30 days of publication date.** ADI contact information is listed below.

PCN Title:	LTM4700 Internal Component Second Source
Publication Date:	05-Aug-2024
Effectivity Date:	07-Nov-2024 <i>(the earliest date that a customer could expect to receive changed material)</i>
Revision Description:	Initial Release

Description Of Change:

- Analog Devices, Inc. qualified an alternate FET for use in the assembly of LTM4700.
- Substrate Design revised and qualified for alternate FET.

Reason For Change:

Product resiliency with second sourcing of key internal component.

Impact of the change (positive or negative) on fit, form, function & reliability:

There is no impact on the product's fit, form, function or reliability.

Product Identification *(this section will describe how to identify the changed material)*

The cut-off date code will identify the product. A cut-off date code will be provided upon customer request.

Summary of Supporting Information:

Qualification has been performed per Industry Standard Test Methods. See attached Qualification Results Summary.

Supporting Documents

Attachment 1: Type: Qualification Results Summary

[ADI_PCN_24_0171_Rev_-_Reliability_Report_for_LTM4700_Second_Source_FET...](#)

Note: If applicable, the device material declaration will be updated due to material change.

ADI Contact Information:

For questions on this PCN, please send an email to the regional contacts below or contact your local ADI sales representatives.

Americas:	Europe:	Japan:	Korea:	Rest of Asia:
PCN_Americas@analog.com	PCN_Europe@analog.com	PCN_Japan@analog.com	PCN_Korea@analog.com	PCN_ROA@analog.com

Appendix A - Affected ADI Models:

Added Parts On This Revision - Product Family / Model Number (4)

LTM4700 / LTM4700EY#3QFPBF


LTM4700 / LTM4700EY#PBF

LTM4700 / LTM4700Y

LTM4700 / LTM4700Y#PBF

Appendix B - Revision History:

Rev	Publish Date	Effectivity Date	Rev Description
Rev. -	05-Aug-2024	07-Nov-2024	Initial Release



Reliability Report

Report Title: LTM4700 Material Set Change Qualification

Report Number: 19501

Revision: A

Date: 19 November 2023

Summary

This report documents the successful completion of the reliability qualification requirements for the release of the LTM4700 product in a 330-BGA package using alternate source Alpha & Omega FET and PMS0518PG00E09 substrate.

Die/Fab Product Characteristics

Table 1: Die/Fab Product Characteristics

Product Characteristics	Product(s) to be qualified	
Generic/Root Part #	LTM4700	LTM4700
Die Id	3104	3884
Die Size (mm)	1.41 x 1.33	2.92 x 2.67
Wafer Fabrication Site	Vanguard	ADI Camas
Wafer Fabrication Process	0.6µm BiCMOS	0.6µm BiCMOS
Die Substrate	Si	Si
Metallization / # Layers	AlSiCu	AlCu
Polyimide	No	No
Passivation	undoped-oxide/SiN	doped-oxide/SiN

Die/Fab Test Results

Table 2: Die/Fab Test Results - 0.6µm BiCMOS at Vanguard-Taiwan

Test Name	Spec	Conditions	Generic/Root Part #	Lot #	Fail/SS
High Temperature Operating Life (HTOL)	JESD22-A108	125°C<Tj<135°C, Biased, 1,000 Hours	LTM4700	Q19501.1HTOL	0/77
High Temperature Storage Life (HTSL)	JESD22-A103	150°C, 1,000 Hours	LTM4700	Q19501.1HTS	0/45
Highly Accelerated Temperature and Humidity Stress Test (HAST) ¹	JESD22-A110	110C 85%RH 17.7 psia, Biased, 264hrs	LTM4700	Q19501.1HAST	0/30

¹ These samples were subjected to preconditioning at MSL 4 with 3x reflow peak temp of 245°C prior to the start of the stress test. MSL4 consists of the following: Bake: 48 hrs @ 125°C, Unbiased Soak: 96 hrs @ 30°C, 60%RH.

Package/Assembly Product Characteristics
Table 3: Package/Assembly Product Characteristics - 330-BGA at ADI Penang

Product Characteristics	Product(s) to be qualified
Generic/Root Part #	LTM4700
Package	330-BGA
Body Size (mm)	22.00 x 15.00 x 7.87
Assembly Location	ADI Penang
MSL/Peak Reflow Temperature(°C)	4 / 245
Mold Compound	Sumitomo G311E
Substrate Laminate Supplier	Daisho Denshi
Leadframe Material	BT Resin
Lead Finish	96.5Sn_3.0Ag_0.5Cu
Wire Bond Material/Diameter (mils)	Gold / 1.00

QMCL

P/N	Description	Vendor
PMS0518PG00E09-01	22x15mm Substrate	Daisho Denshi
SE006518-01	Discrete FET	Alpha & Omega

Package/Assembly Test Results
Table 4: Package/Assembly Test Results - BGA at ADI Penang

Test Name	Spec	Conditions	Generic/Root Part #	Lot #	Fail/SS
High Temperature Storage Life (HTSL)	JESD22-A103	150°C, 1,000 Hours	LTM4700	Q19501.1HTS	0/45
Highly Accelerated Temperature and Humidity Stress Test (HAST) ¹	JESD22-A110	110C 85%RH 17.7 psia, Biased, 264hrs	LTM4700	Q19501.1HAST	0/30
Temperature Cycling (TC) ¹	JESD22-A104	-55°C/+125°C, 1,000 Cycles	LTM4700	Q19501.1TC	0/77
Unbiased HAST (UHST) ¹	JESD22-A118	110C 85%RH 17.7 psia, 264hrs	LTM4700	Q19501.1UHAST	0/77

¹ These samples were subjected to preconditioning at MSL 4 with 3x reflow peak temp of 245°C prior to the start of the stress test. MSL4 consists of the following: Bake: 48 hrs @ 125°C, Unbiased Soak: 96 hrs @ 30°C, 60%RH.

Approvals

Reliability Engineer: Lay Yong Ong