



PRODUCT INFORMATION LETTER

PIL AMS-MSH/12/7407
Dated 03 Aug 2012

LIS3DH and LIS3DHTR Transfer to Calamba BE plant

Sales Type/product family label	LIS3DH and LIS3DHTR
Type of change	Assembly additional location
Reason for change	Capacity BE Flexibility
Description	Transfer to St Calamba BE (assembly and Final Test) plant
Forecasted date of implementation	03-Sep-2012
Forecasted date of samples for customer	20-Aug-2012
Forecasted date for STMicroelectronics change Qualification Plan results availability	27-Jul-2012
Involved ST facilities	Calamba

DOCUMENT APPROVAL

Name	Function
Fontanella, Luca	Marketing Manager
Pozzi, Stefano	Process Owner
Speroni, Ernesto Fabrizio	Q.A. Manager

Transfer of LIS3DH and LIS3DHTR to ST Calamba back end plant

1. Introduction

The scope of this Product Information Letter (PIL) is to inform the Customer about the transfer of LIS3DH and LIS3DHTR to ST Calamba plant as Back End 2nd source.

Calamba BE plant is already qualified for Motion MEMS LGA line based on MV55 product line as test vehicle (LIS331DLH commercial product). This product line was fully qualified through the wide reliability program in H1 2011 and it is in mass production since Q2 2011.

Considering that:

- Calamba BE plant is already qualified for MEMS LGA package
- LIS3DH is assembled in the same LGA 3x3 package of MV55

and taking into account that LIS3DH product is already qualified; therefore its transfer on Calamba BE plant has been validated based on similarity criteria and with additional package oriented reliability tests on two lots for further verification.

LIS3DH is considered qualified in Calamba and ready for mass production based on similarity data available for Calamba MEMS LGA line and considering the positive results of the additional tests on LIS3DH.

2. Qualification Results

Here follow the list of Calamba LGA line qualification test Matrix on MV55 production line (*figure1*) and the list of the additional tests for LIS3DH transfer validation (*figure 2*).

TEST							
N	TEST NAME	PREC	CONDITION METHOD	STEPS	FAILS/SS		
					LOT 1	LOT 2	LOT 3
1	PC (JL3)	na	Reference specification Jedec J-STD-020 MSL = 3	0h	0/300	0/300	0/300
				final	0/300	0/300	0/300
2	AC	Y	Ta = 121°C , Pressure = 2atm Reference specification JESD22-A102	0h	0/77	0/77	0/77
				96h	0/77	0/77	0/77
3	HTOL	Y	Ta = 125°C, Tj = 125°C Vdd=3.6V with Self-test actuation Reference specification JESD22-A108	0h	0/40	0/40	0/40
				168h	0/40	0/40	0/40
				500h	0/40	0/40	0/40
				1000h	0/40	0/40	0/40
4	TCT	Y	Low T = - 40°C, High T = +125°C, Reference specification JESD22-A104	0c	0/77	0/77	0/77
				200c	0/77	0/77	0/77
				500c	0/77	0/77	0/77
				1000c	0/77	0/77	0/77
5	THB	Y	TA / RH = +85°C/85%, Tj = 85°C Vdd = 3.0V Reference specification = JESD22-A101	0h	0/40	0/40	0/40
				168h	0/40	0/40	0/40
				500h	0/40	0/40	0/40
				1000h	0/40	0/40	0/40
6	THS	Y	TA / RH = +85°C/85% Reference specification = JESD22-A101	0h	0/77	0/77	0/77
				168h	0/77	0/77	0/77
				500h	0/77	0/77	0/77
				1000h	0/77	0/77	0/77
7	HTS	N	Ta = 150°C Reference specification JESD22-A103	0h	0/77	0/77	0/77
				168h	0/77	0/77	0/77
				500h	0/77	0/77	0/77
				1000h	0/77	0/77	0/77
8	LTS	N	Ta = -40°C Reference specification JESD22-A103	0h	0/77	0/77	0/77
				168h	0/77	0/77	0/77
				500h	0/77	0/77	0/77
				1000h	0/77	0/77	0/77
9	MS	N	3000g Reference specification MIL SDT 883	0h	0/15	0/15	0/15
				Final	0/15	0/15	0/15
10	MS	N	10000g Reference specification MIL SDT 883	0h	0/15	0/15	0/15
				Final	0/15	0/15	0/15

Figure 1: Calamba LGA line Qualification Test Matrix on MV55

TEST							
N	TEST NAME	PREC	CONDITION METHOD	STEPS	FAILS/SS		
					LOT 1	LOT 2	LOT 3
1	PC (JL3)	na	Reference specification Jedec J-STD-020 MSL = 3	0h	0/250	0/250	0/250
				final	0/250	0/250	0/250
2	AC	Y	Ta = 121°C , Pressure = 2 atm Reference specification Jesd22-A102	0h	0/77	0/77	0/77
				96h	0/77	0/77	0/77
3	TCT	Y	Low T = - 40°C, High T = +125°C, Reference specification JESD22-A104	0c	0/77	0/77	0/77
				200c	0/77	0/77	0/77
				500c	0/77	0/77	0/77
4	THS	Y	TA / RH = +85°C/85% Reference specification = JESD22-A101	0h	0/77	0/77	0/77
				168h	0/77	0/77	0/77
				500h	0/77	0/77	0/77
5	HTS	N	Ta = 150°C Reference specification JESD22-A103	0h	0/77	0/77	0/77
				168h	0/77	0/77	0/77
				500h	0/77	0/77	0/77

Figure 2: Additional Test for LIS3DH Transfer Validation

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND / OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners

© 2012 STMicroelectronics - All rights reserved.

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

