

| | |
|---------------------------------------|--|
| PRODUCT / PROCESS CHANGE NOTIFICATION | |
|---------------------------------------|--|

| | |
|-------------------|--|
| 1. PCN basic data | |
|-------------------|--|

| | | |
|----------------------|---|---|
| 1.1 Company |  | STMicroelectronics International N.V |
| 1.2 PCN No. | | AMS/20/12004 |
| 1.3 Title of PCN | | Power Management BU: Introduction of the HBIP40 technology for the LM317Lxx & LM217Lxx series (100mA) assembled in TO92 and SO-8 packages |
| 1.4 Product Category | | See product list |
| 1.5 Issue date | | 2020-04-28 |

| | |
|-------------|--|
| 2. PCN Team | |
|-------------|--|

| | |
|---------------------------|--------------------------|
| 2.1 Contact supplier | |
| 2.1.1 Name | ROBERTSON HEATHER |
| 2.1.2 Phone | +1 8475853058 |
| 2.1.3 Email | heather.robertson@st.com |
| 2.2 Change responsibility | |
| 2.2.1 Product Manager | Marcello SAN BIAGIO |
| 2.1.2 Marketing Manager | Salvatore DI VINCENZO |
| 2.1.3 Quality Manager | Giuseppe LISI |

| | | |
|-----------|--|--|
| 3. Change | | |
|-----------|--|--|

| 3.1 Category | 3.2 Type of change | 3.3 Manufacturing Location |
|--------------------------|---|--|
| General Product & Design | Die redesign: Mask or mask set change with new die design – Pad modification (sizes, vertical structure, metal thickness) | Front end location : ST Ang Mo Kio (Singapore) |

| | | |
|--------------------------|--|--|
| 4. Description of change | | |
|--------------------------|--|--|

| | | |
|---|---|-------------------|
| | Old | New |
| 4.1 Description | LAAT Technology | HBIP40 Technology |
| 4.2 Anticipated Impact on form,fit, function, quality, reliability or processability? | No changes of the Electrical Characteristics and Quality. | |

| | |
|-----------------------------------|--|
| 5. Reason / motivation for change | |
|-----------------------------------|--|

| | |
|----------------------|--|
| 5.1 Motivation | Following Divisional commitment towards a continuous improvement philosophy, a more fine geometry Bipolar technology has been qualified in ST called HBip40. As already done for the L78xx and L79xx series, ST is going to use this improved technology to redesign the LM317Lxx/LM217Lxx Linear Voltage Regulator series also. The HBM value has been updated according to the ST Specification on "Reliability Tests and Criteria for Qualifications". Electrical characteristics remain unchanged. Quality and Reliability parameters are still guaranteed at the same level as in the past. |
| 5.2 Customer Benefit | SERVICE IMPROVEMENT |

| | |
|--|--|
| 6. Marking of parts / traceability of change | |
|--|--|

| | |
|-----------------|--|
| 6.1 Description | The traceability of the new parts will be ensured by different internal codification and QA number |
|-----------------|--|

| | |
|----------------------|--|
| 7. Timing / schedule | |
|----------------------|--|

| | |
|-------------------------------------|--------------|
| 7.1 Date of qualification results | 2020-02-13 |
| 7.2 Intended start of delivery | 2020-07-20 |
| 7.3 Qualification sample available? | Upon Request |

| | |
|-------------------------------|--|
| 8. Qualification / Validation | |
|-------------------------------|--|

| | | | |
|--|---|------------|------------|
| 8.1 Description | 12004 W486-W901 19- Report Customer LM317L in TO92 and SO8 (HBIP40).pdf | | |
| 8.2 Qualification report and qualification results | Available (see attachment) | Issue Date | 2020-04-28 |

9. Attachments (additional documentations)

12004 Public product.pdf
12004 W486-W901 19- Report Customer LM317L in TO92 and SO8 (HBIP40).pdf

10. Affected parts

| 10. 1 Current | | 10.2 New (if applicable) |
|--------------------------------|--------------------------------|---------------------------------|
| 10.1.1 Customer Part No | 10.1.2 Supplier Part No | 10.1.2 Supplier Part No |
| LM217LD13TR | LM217LD13TR | |
| LM217LZ-TR | LM217LZ-TR | |
| LM317LD13TR | LM317LD13TR | |
| LM317LZ | LM317LZ | |
| LM317LZ-AP | LM317LZ-AP | |
| LM317LZ-TR | LM317LZ-TR | |

IMPORTANT NOTICE – PLEASE READ CAREFULLY

Subject to any contractual arrangement in force with you or to any industry standard implemented by us, STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2018 STMicroelectronics – All rights reserved



Public Products List

Public Products are off the shelf products. They are not dedicated to specific customers, they are available through ST Sales team, or Distributors, and visible on ST.com

PCN Title : Power Management BU: Introduction of the HBIP40 technology for the LM317Lxx & LM217Lxx series (100mA) assembled in TO92 and SO-8 packages

PCN Reference : AMS/20/12004

Subject : Public Products List

Dear Customer,

Please find below the Standard Public Products List impacted by the change.

| | | |
|-------------|-------------|------------|
| LM317LZ | LM317LD13TR | LM317LZ-AP |
| LM217LD13TR | LM217LZ-TR | LM317LZ-TR |



IMPORTANT NOTICE – PLEASE READ CAREFULLY

Subject to any contractual arrangement in force with you or to any industry standard implemented by us, STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2018 STMicroelectronics – All rights reserved

Reliability Evaluation Report

On Technology HBIP40

T.V.:

LM317LD13TR Pkg SO8 STS

LM317LZ-TRL Pkg TO92 ASE

| Product Lines | | Locations |
|-----------------------------------|--|-----------------------|
| Product Description | <i>AL1701</i> Low current 1.2 to 37 V adj Vreg <i>1.2 V to 37 V adjustable voltage regulators</i> <i>LM317LD13TR</i> <i>LM317Z-TRL</i> AMG GENERAL PURPOSE ANALOG & RF <i>-SO8 TO92</i> HBIP40 | SINGAPORE Ang Mo Kio |
| P/N | Wafer fab | |
| Product Group | Assembly site | <i>Shenzhen / ASE</i> |
| Product division | Reliability Lab | Catania |
| Package | Reliability assessment | |
| Silicon Process technology | | |

DOCUMENT INFORMATION

| Version | Date | Pages | Prepared by | Approved by | Comment |
|----------------|---------------|--------------|--------------------|---------------------|----------------|
| 1.0 | November 2019 | 6 | Angelo Basile | Giuseppe Giacopello | Final Report |

Note: This report is a summary of the reliability trials performed in good faith by STMicroelectronics in order to evaluate the potential reliability risks during the product life using a set of defined test methods.

This report does not imply for STMicroelectronics expressly or implicitly any contractual obligations other than as set forth in STMicroelectronics general terms and conditions of Sale. This report and its contents shall not be disclosed to a third party without previous written agreement from STMicroelectronics.



TABLE OF CONTENTS

| | |
|---|----------|
| 1 APPLICABLE AND REFERENCE DOCUMENTS | 3 |
| 2 GLOSSARY | 3 |
| 3 RELIABILITY EVALUATION OVERVIEW..... | 3 |
| 3.1 OBJECTIVES | 3 |
| 3.2 CONCLUSION | 3 |
| DEVICE CHARACTERISTICS | 4 |
| 3.3 DEVICE DESCRIPTION | 4 |
| 3.4 CONSTRUCTION NOTE | 4 |
| 4 TESTS RESULTS SUMMARY | 5 |
| 4.1 TEST VEHICLE | 5 |
| 4.2 TEST PLAN AND RESULTS SUMMARY | 5 |
| 4.3 TESTS DESCRIPTION | 6 |



1 APPLICABLE AND REFERENCE DOCUMENTS

| Document reference | Short description |
|--------------------|---|
| JESD47 | Stress-Test-Driven Qualification of Integrated Circuits |

2 GLOSSARY

| | |
|------------|-------------------|
| DUT | Device Under Test |
| SS | Sample Size |

3 RELIABILITY EVALUATION OVERVIEW

3.1 Objectives

Qualification New Product LM317LD13TR and the LM317LZ-TR in HBIP40 technology assembled in SO8 Shenzhen and TO92 ASE Subcontractor.

3.2 Conclusion

Qualification Plan requirements have been fulfilled without exception. It is stressed that reliability tests has how that the devices behave correctly against environmental tests (no failure). Moreover, the stability of electrical parameters during the accelerated tests demonstrates the ruggedness of the products and safe operation, which is consequently expected during their lifetime

The present reliability results are positive.

DEVICE CHARACTERISTICS

3.3 Device description

The LM217 LM317 are monolithic integrated circuits in TO-220, TO-220FP and D²PAK packages intended for use as positive adjustable voltage regulators. They are designed to supply more than 1.5 A of load current with an output voltage adjustable over a 1.2 to 37 V range. The nominal output voltage is selected by means of a resistive divider, making the device exceptionally easy to use and eliminating the stocking of many fixed regulators

3.4 Construction note

| | | P/N - LM317LZ-TR | P/N LM317LD13TR |
|--|-----------------|----------------------|-----------------|
| Wafer/Die fab. information | | | |
| Wafer fab manufacturing location | | SINGAPORE Ang Mo Kio | |
| Technology | | HBiP40V | |
| Die finishing back side | | Lapped silicon | |
| Die size | 980x960 micron | | 980x960 micron |
| Passivation type | P-VAPOX/NITRIDE | | |
| Wafer Testing (EWS) Information | | | |
| Electrical testing manuf. | Ang Mo Kio EWS | | |
| Assembly information | | | |
| Assembly site | ASE | | SHENZHEN |
| Package description | TO92 | | SO8 |
| Molding Compound | EPOXY | | |
| Die Attach Material | EPOXY | | |
| Wires Bonding Mat. | WIRE Cu 1mils | | |

4 TESTS RESULTS SUMMARY

4.1 Test vehicle

| Lot # | Diffusion Lot | Assy Lot | Trace Code | Process/ Package | Product Line | Comments |
|-------|---------------|------------|------------|------------------|--------------|----------|
| 1 | V67209TN | GK8110M401 | GK8110M4 | SO8 | AL1701 | |
| 2 | V67209TN | A1936NUZ | GE936063 | TO92 | AL1701 | |

4.2 Test plan and results summary

| Test | | Std ref. | Conditions | SS | Steps | Failure/SS | | Note |
|-------------------------------|---|-----------------------------|---|----|-------------|------------|------------|------|
| | | | | | | Lot 1 SO8 | Lot 2 TO92 | |
| Die Oriented Tests | | | | | | | | |
| HTOL | N | JESD22 A-108 | Ta = 125°C, BIAS 40 V | 77 | 168 h | 0/77 | 0/77 | |
| | | | | | 500 h | 0/77 | 0/77 | |
| | | | | | 1000 h | 0/77 | 0/77 | |
| HTSL | N | JESD22 A-103 | Ta = 150°C | 45 | 168 h | 0/45 | | |
| | | | | | 500 h | 0/45 | | |
| | | | | | 1000 h | 0/45 | | |
| Package Oriented Tests | | | | | | | | |
| PC | | JESD22-A113 | Drying 24 H @ 125°C Store 168h @ Ta=85°C Rh=85% Oven Reflow @ Tpeak=260°C 3 times | | Final | Pass | | |
| AC | Y | JESD22 A-102 | Pa=2Atm / Ta=121°C | 77 | 168 h | 0/77 | | |
| TC | Y | JESD22 A-104 | Ta = -65°C to 150°C | 77 | 100 cy | 0/77 | | |
| | | | | | 200 cy | 0/77 | | |
| | | | | | 500 cy | 0/77 | | |
| THB | Y | JESD22 A-101 | Ta = 85°C, RH = 85%, BIAS 24V | 77 | 168 h | 0/77 | 0/77 | |
| | | | | | 500 h | 0/77 | 0/77 | |
| | | | | | 1000 h | 0/77 | 0/77 | |
| Others Test | | | | | | | | |
| ESD | N | ANSI / ESDA JEDEC JS-001 | HBM | 3 | +- 1000V | Pass | | |
| | | ANSI/ESDA JEDEC JS002 | CDM | 3 | +- 500V | | | |

4.3 Tests Description

| Test name | Description | Purpose |
|---|--|---|
| Die Oriented | | |
| HTOL HighTemperature Operating Life | The device is stressed in static or dynamic configuration, approaching the operative max. absolute ratings in terms of junction temperature and bias condition. | To determine the effects of bias conditions and temperature on solid state devices over time. It simulates the devices' operating condition in an accelerated way. The typical failure modes are related to, silicon degradation, wire-bonds degradation, oxide faults. |
| HTSL High Temperature Storage Life | The device is stored in unbiased condition at the max. temperature allowed by the package materials, sometimes higher than the max. operative temperature. | To investigate the failure mechanisms activated by high temperature, typically wire-bonds solder joint ageing, data retention faults, metal stress-voiding. |
| Package Oriented | | |
| PC Preconditioning | The device is submitted to a typical temperature profile used for surface mounting devices, after a controlled moisture absorption. | As stand-alone test: to investigate the moisture sensitivity level. As preconditioning before other reliability tests: to verify that the surface mounting stress does not impact on the subsequent reliability performance. The typical failure modes are "pop corn" effect and delamination. |
| AC Auto Clave (Pressure Pot) | The device is stored in saturated steam, at fixed and controlled conditions of pressure and temperature. | To investigate corrosion phenomena affecting die or package materials, related to chemical contamination and package hermeticity. |
| TC Temperature Cycling | The device is submitted to cycled temperature excursions, between a hot and a cold chamber in air atmosphere. | To investigate failure modes related to the thermo-mechanical stress induced by the different thermal expansion of the materials interacting in the die-package system. Typical failure modes are linked to metal displacement, dielectric cracking, molding compound delamination, wire-bonds failure, die-attach layer degradation. |
| THB Temperature Humidity Bias | The device is biased in static configuration minimizing its internal power dissipation, and stored at controlled conditions of ambient temperature and relative humidity. | To evaluate the package moisture resistance with electrical field applied, both electrolytic and galvanic corrosion are put in evidence. |
| Other Test | | |
| ESD Electro Static Discharge | The device is submitted to a high voltage peak on all his pins simulating ESD stress according to different simulation models. HBM: Human Body Model CDM: Charged Device Model | To classify the device according to his susceptibility to damage or degradation by exposure to electrostatic discharge. |