



PRODUCT/PROCESS CHANGE NOTIFICATION

PCN AMS-AAS/13/7840

Dated 29 Apr 2013

TBA820M Wafer Diameter change

Table 1. Change Implementation Schedule

Forecasted implementation date for change	22-Apr-2013
Forecasted availability date of samples for customer	22-Apr-2013
Forecasted date for STMicroelectronics change Qualification Plan results availability	22-Apr-2013
Estimated date of changed product first shipment	29-Jul-2013

Table 2. Change Identification

Product Identification (Product Family/Commercial Product)	TBA820M
Type of change	Waferfab process change
Reason for change	To rationalize the production capacity
Description of the change	The wafer diameter for the product TBA820M, (diffused on LABT process in Ang Mo Kyo plant) will be changed from 5" to 6".
Change Product Identification	Finished Good internal code
Manufacturing Location(s)	

DOCUMENT APPROVAL

Name	Function
Ferri, Simone	Marketing Manager
Onetti, Andrea Mario	Product Manager
Speroni, Ernesto Fabrizio	Q.A. Manager

TBA820M Wafer Diameter change

WHAT

As part of the running program to convert to 6" wafers the silicon lines diffused on the bipolar processes in the Ang Mo Kio plant, the wafer diameter for the product TBA820M, (diffused on LABT process) will be changed from 5" to 6"

WHY

To rationalize the production capacity.

HOW

The qualification has been done through test vehicles belonging to the same LABT process family (namely KSAD).

The bipolar LABT diffusion process family is qualified and running in volumes on 6" wafers.

The alignment of electrical parameters of the TBA820M will be monitored as well.



Internal Reliability Evaluation Report

Qualify AMK5 versus **AMJ9 6"**

[LABT100 Technology]

T.V: KSADAAW - LD1117SC-R SOT223

General Information

Product Line	KSADAAW
Product Description	Adj semi Id postive 800mA
P/N	LD1117SC-R
Product Group	APM
Product division	IPC
Package	SOT223
Silicon Process technology	BIPOLAR >6 um
Production mask set rev.	NKSADA6

Locations

Wafer fab	AMJ9 6"
Assembly plant	NANTONG FUJITSU CHINA
Reliability Lab	Catania
Reliability assessment	Pass

DOCUMENT INFORMATION

Version	Date	Pages	Prepared by	Approved by	Comment
1.0	08-July-2011	9	Alfio Rao	Giuseppe Giacobello	First issue

Note: This report is a summary of the reliability trials performed in good faith by STMicroelectronics in order to evaluate the potential reliability risks during the product life using a set of defined test methods.
This report does not imply for STMicroelectronics expressly or implicitly any contractual obligations other than as set forth in STMicroelectronics general terms and conditions of Sale. This report and its contents shall not be disclosed to a third party without previous written agreement from STMicroelectronics.



TABLE OF CONTENTS

1	APPLICABLE AND REFERENCE DOCUMENTS	3
2	GLOSSARY	3
3	RELIABILITY EVALUATION OVERVIEW	3
3.1	OBJECTIVES	3
3.2	CONCLUSION	3
4	DEVICE CHARACTERISTICS	4
4.1	DEVICE DESCRIPTION	4
4.2	CONSTRUCTION NOTE	5
5	TESTS RESULTS SUMMARY	6
5.1	TEST VEHICLE	6
5.2	TEST PLAN AND RESULTS SUMMARY	6
6	ANNEXES	7
6.1	DEVICE DETAILS	7
6.2	TESTS DESCRIPTION	9



1 APPLICABLE AND REFERENCE DOCUMENTS

Document reference	Short description
JESD47	Stress-Test-Driven Qualification of Integrated Circuits

2 GLOSSARY

DUT	Device Under Test
SS	Sample Size

3 RELIABILITY EVALUATION OVERVIEW

3.1 Objectives

LABT100 Bipolar Technology diffused in AMJ9 6" (Transferring project).

TV: KSADA AW – LD1117SC assembled in SOT223.

Shared qualification

3.2 Conclusion

Qualification Plan requirements have been fulfilled without exception. It is stressed that reliability tests have shown that the devices behave correctly against environmental tests (no failure). Moreover, the stability of electrical parameters during the accelerated tests demonstrates the ruggedness of the products and safe operation, which is consequently expected during their lifetime.



4 DEVICE CHARACTERISTICS

4.1 Device description

Features

- Low dropout voltage:
 - 1.15 V typ. @ $I_{OUT} = 1\text{ A}$, 25 °C
- Very low quiescent current:
 - 5 mA typ. @ 25 °C
- Output current up to 1 A
- Fixed output voltage of:
 - 1.2 V, 1.8 V, 2.5 V, 3.3 V
- Adjustable version availability ($V_{REL} = 1.25\text{ V}$)
- Internal current and thermal limit
- Only 10 μF for stability
- Available in $\pm 2\%$ (at 25 °C) and 4 % in full temperature range
- High supply voltage rejection:
 - 80 dB typ. (at 25 °C)
- Temperature range: 0 °C to 125 °C



SOT-223

Description

The LD1117Axx is a low drop voltage regulator able to provide up to 1 A of output current, available even in adjustable version ($V_{REF} = 1.25\text{ V}$). Concerning fixed versions, are offered the following output voltages: 1.2 V, 1.8 V, 2.5 V and 3.3 V. The device is supplied in: SOT-223, DPAK and TO-220. Surface mount packages optimize the thermal characteristics even offering a relevant space saving effect. High efficiency is assured by NPN pass transistor. Only a very common 10 μF minimum capacitor is needed for stability. Only chip trimming allows the regulator to reach a very tight output voltage tolerance, within $\pm 2\%$ at 25 °C.



4.2 Construction note

P/N: LD1117SC-R	
Wafer/Die fab. information	
Wafer fab manufacturing location	AMJ9 6"
Technology	LABT
Process family	BT/B
Die finishing back side	Cr/Ni/Au
Die size	1.990X1.860mm2
Bond pad metallization layers	AISi
Passivation type	SiN (nitride)
Wafer Testing (EWS) information	
Electrical testing manufacturing location	APPE (Singapore)
Assembly information	
Assembly site	NANTONG FUJITSU CHINA
Package description	SOT223
Molding compound	SUMITOMO EMEG600F
Frame material	Copper 118x93
Die attach process	Glue
Die attach material	ABLESTICK 8352L
Die pad size	146X200, 146X410, 146X360, 167X167
Wires bonding materials/diameters	Au 1.5 mils
Lead finishing process	Matte Tin Plating
Final testing information	
Testing location	NANTONG FUJITSU CHINA
Tester	QT200
Test program	KSX2FAAD.CTS



5 TESTS RESULTS SUMMARY

5.1 Test vehicle

P/N: LD1117SC-R

Lot #	Diffusion Lot	Assy Lot	Technical Code	Package	Product Line	Data Code
1	W047K34	GF113030	FMLL*KSADAAW	SOT223	KSADAAW	'113

5.2 Test plan and results summary

P/N: LD1117SC-R


Test	PC	Std ref.	Conditions	SS	Steps	Failure/SS	Note
						Lot 1	
Die Oriented Tests							
HTOL	N	JESD22 A-108	Tj = 125°C, BIAS= 15V	77	168 h	0/77	
					500 h	0/77	
					1000 h	0/77	
HTSL	N	JESD22 A-103	Ta = 150°C	45	168 h	0/45	
					500 h	0/45	
					1000 h	0/45	
Package Oriented Tests							
PC		JESD22 A-113	Drying 24 H @ 125°C Store 168h @ Ta= 85°C Rh= 85 % Over Reflow @ Tpeak= 260°C 3 times	250	Final	Pass	
AC	Y	JESD22 A-102	Pa= 2Atm / Ta= 121°C	77	168 h	0/77	
TC	Y	JESD22 A-104	Ta = -65°C to 150°C	77	100 cy	0/77	
					200 cy	0/77	
					500 cy	0/77	
THB	Y	JESD22 A-101	Ta= 85°C, RH = 85%, BIAS= 12V	77	168 h	0/77	
					500 h	0/77	
					1000 h	0/77	




6 ANNEXES

6.1 Device details

6.1.1 Pin connection



6.1.2 Block diagram



6.1.3 Bonding diagram


8319707



6.1.4 Package outline/Mechanical data

SOT-223 mechanical data

Dim.	mm.			mils.		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A			1.8			70.9
A1	0.02		0.1	0.8		3.9
B	0.6	0.7	0.85	23.6	27.6	33.5
B1	2.9	3	3.15	114.2	118.1	124.0
c	0.24	0.26	0.35	9.4	10.2	13.8
D	6.3	6.5	6.7	248.0	255.9	263.8
e		2.3			90.6	
e1		4.6			181.1	
E	3.3	3.5	3.7	129.9	137.8	145.7
H	6.7	7	7.3	263.8	275.7	287.5
V			10°			10°





6.2 Tests Description

Test name	Description	Purpose
Die Oriented		
HTOL High Temperature Operating Life	The device is stressed in static or dynamic configuration, approaching the operative max. absolute ratings in terms of junction temperature and bias condition.	To determine the effects of bias conditions and temperature on solid state devices over time. It simulates the devices' operating condition in an accelerated way. The typical failure modes are related to, silicon degradation, wire-bonds degradation, oxide faults.
HTSL High Temperature Storage Life	The device is stored in unbiased condition at the max. temperature allowed by the package materials, sometimes higher than the max. operative temperature.	To investigate the failure mechanisms activated by high temperature, typically wire-bonds solder joint ageing, data retention faults, metal stress-voiding.
Package Oriented		
PC Preconditioning	The device is submitted to a typical temperature profile used for surface mounting devices, after a controlled moisture absorption.	As stand-alone test: to investigate the moisture sensitivity level. As preconditioning before other reliability tests: to verify that the surface mounting stress does not impact on the subsequent reliability performance. The typical failure modes are "pop corn" effect and delamination.
AC Auto Clave (Pressure Pot)	The device is stored in saturated steam, at fixed and controlled conditions of pressure and temperature.	To investigate corrosion phenomena affecting die or package materials, related to chemical contamination and package hermeticity.
TC Temperature Cycling	The device is submitted to cycled temperature excursions, between a hot and a cold chamber in air atmosphere.	To investigate failure modes related to the thermo-mechanical stress induced by the different thermal expansion of the materials interacting in the die-package system. Typical failure modes are linked to metal displacement, dielectric cracking, molding compound delamination, wire-bonds failure, die-attach layer degradation.
THB Temperature Humidity Bias	The device is biased in static configuration minimizing its internal power dissipation, and stored at controlled conditions of ambient temperature and relative humidity.	To evaluate the package moisture resistance with electrical field applied, both electrolytic and galvanic corrosion are put in evidence.



Public Products List

PCN Title : TBA820M Wafer Diameter change

PCN Reference : AMS-AAS/13/7840

PCN Created on : 21-MAY-2013

Subject : Public Products List

Dear Customer,

Please find below the Standard Public Products List impacted by the change:

ST COMMERCIAL PRODUCT

TBA820M

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND / OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY TWO AUTHORIZED ST REPRESENTATIVES, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners

© 2013 STMicroelectronics - All rights reserved.

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com