

## PRODUCT / PROCESS CHANGE INFORMATION

### 1. PCI basic data

1.1 Company		STMicroelectronics International N.V
1.2 PCI No.		ADG/20/12358
1.3 Title of PCI		Datasheet update for Maximum Operating Junction Temperature from 150°C to 175°C
1.4 Product Category		STPS200170TV1Y Diode
1.5 Issue date		2020-11-25

### 2. PCI Team

2.1 Contact supplier	
2.1.1 Name	ROBERTSON HEATHER
2.1.2 Phone	+1 8475853058
2.1.3 Email	heather.robertson@st.com
2.2 Change responsibility	
2.2.1 Product Manager	Stephane CHAMARD
2.1.2 Marketing Manager	Philippe LEGER
2.1.3 Quality Manager	Jean-Paul REBRASSE

### 3. Change

3.1 Category	3.2 Type of change	3.3 Manufacturing Location
General Product & Design	Modification of datasheet :parameters/electrical specification (min./max./typ. values) and/or AC/DC specification	ST assy site in Morocco

### 4. Description of change

	Old	New
4.1 Description	Maximum Operating Junction Temperature @150°C	Maximum Operating Junction Temperature @175°C
4.2 Anticipated Impact on form,fit, function, quality, reliability or processability?	no	

### 5. Reason / motivation for change

5.1 Motivation	Allowing Tj max 175°C will give more margin for thermal customer design.
5.2 Customer Benefit	QUALITY IMPROVEMENT

### 6. Marking of parts / traceability of change

6.1 Description	n/a
-----------------	-----

### 7. Timing / schedule

7.1 Date of qualification results	2020-11-13
7.2 Intended start of delivery	2020-11-26
7.3 Qualification sample available?	Not Applicable

### 8. Qualification / Validation

8.1 Description		
8.2 Qualification report and qualification results	In progress	Issue Date

**9. Attachments (additional documentations)**

12358 Public product.pdf  
12358 Datasheet update for Maximum Operating Junction Temperature.pdf

**10. Affected parts**

<b>10. 1 Current</b>		<b>10.2 New (if applicable)</b>
<b>10.1.1 Customer Part No</b>	<b>10.1.2 Supplier Part No</b>	<b>10.1.2 Supplier Part No</b>
	STPS200170TV1Y	

**IMPORTANT NOTICE – PLEASE READ CAREFULLY**

Subject to any contractual arrangement in force with you or to any industry standard implemented by us, STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2018 STMicroelectronics – All rights reserved

(1) ADG: Automotive & Discretes Group

## PCI

# Product/Process Change Information

### Datasheet update for Maximum Operating Junction Temperature from 150°C to 175°C

<b>Notification number:</b>	ADG/20/12358	<b>Issue Date</b>	2020 Nov 25th
<b>Issued by</b>	Isabelle BALLON		
<b>Product series affected by the change</b>	STPS200170TV1Y		

#### Reason for change

Datasheet update for Maximum Operating Junction Temperature (T<sub>j</sub> max) from 150°C to 175°C

#### Effects of change

Allowing T<sub>j</sub> max 175°C will give more margin for thermal customer design.

#### Product identification and traceability

No changes from existing marking.

Traceability will refer to the assembly date codes beginning of production schedule start.

#### Qualification complete date

W46-2020

#### Forecasted sample availability

Not applicable

#### Change implementation schedule

Sales types	Estimated production start	Estimated first shipments
STPS200170TV1Y	Already in production	Only datasheet update

# Reliability Evaluation Report

*Upgrade of STPS200170TV1Y*

*maximum junction temperature (T<sub>j</sub> max) at 175°C*

General Information		Locations	
Product Line	Rectifiers	Wafer fab	ST SINGAPORE
Product Description	Power Schottky rectifiers	Assembly plant	ST BOUSKOURA - MOROCCO
Product perimeter	STPS200170TV1Y	Reliability Lab	ST TOURS - FRANCE
Product Group	ADG	Reliability assessment	PASS
Product division	Discrete & Filter		
Package	ISOTOP		
Maturity level step	QUALIFIED		

## DOCUMENT INFORMATION

Version	Date	Pages	Prepared by	Approved by	Comments
1.0	13-Nov-2020	6	Christophe GOIN	Julien MICHELON	Initial release

Note: This report is a summary of the reliability trials performed in good faith by STMicroelectronics in order to evaluate the potential reliability risks during the product life using a set of defined test methods.

This report does not imply for STMicroelectronics expressly or implicitly any contractual obligations other than as set forth in STMicroelectronics general terms and conditions of Sale. This report and its contents shall not be disclosed to a third party without previous written agreement from STMicroelectronics.

---

**TABLE OF CONTENTS**

<b>1</b>	<b>APPLICABLE AND REFERENCE DOCUMENTS .....</b>	<b>3</b>
<b>2</b>	<b>GLOSSARY .....</b>	<b>3</b>
<b>3</b>	<b>RELIABILITY EVALUATION OVERVIEW.....</b>	<b>4</b>
3.1	OBJECTIVES.....	4
3.2	CONCLUSION.....	4
<b>4</b>	<b>DEVICE CHARACTERISTICS .....</b>	<b>5</b>
4.1	DEVICE DESCRIPTION.....	5
4.2	CONSTRUCTION NOTE.....	6
<b>5</b>	<b>TESTS RESULTS SUMMARY .....</b>	<b>6</b>
5.1	TEST VEHICLES .....	6
5.2	TEST PLAN AND RESULTS SUMMARY .....	6

## 1 APPLICABLE AND REFERENCE DOCUMENTS

Document reference	Short description
<b>JESD 47</b>	Stress-Test-Driven Qualification of Integrated Circuits
<b>JESD 94</b>	Application specific qualification using knowledge based test methodology
<b>JESD 22</b>	Reliability test methods for packaged devices
<b>MIL-STD-750C</b>	Test method for semiconductor devices
<b>AEC-Q005</b>	Pb-Free Test Requirements

## 2 GLOSSARY

<b>SS</b>	Sample Size
<b>PC</b>	Pre-Conditioning
<b>HTRB</b>	High Temperature Reverse Bias
<b>TC</b>	Temperature Cycling
<b>H3TRB</b>	High Humidity High Temperature Reverse Bias
<b>IOLT</b>	Intermittent Operating Life Test
<b>UHAST</b>	Unbiased Highly Accelerated Stress Test
<b>DPA</b>	Destructive Physical Analysis (after TC and THB)
<b>GD</b>	Generic Data
<b>SD</b>	Solderability test
<b>RSH</b>	Resistance to Soldering Heat
<b>THS</b>	Temperature Humidity Storage
<b>TJ max</b>	Maximum junction temperature

### 3 RELIABILITY EVALUATION OVERVIEW

#### 3.1 Objectives

The objective of this report is to validate that STPS200170TV1Y product can reach a maximum junction temperature of 175°C.

The involved products are listed in the table here below:

Product	Product Family	Package	Wafer Fab	Assembly Location
STPS200170TV1Y	POWER SCHOTTKY	ISOTOP	ST SINGAPORE	ST BOUSKOURA – MOROCCO

The test methodology follows ST internal procedure:

- Wafer level test to guarantee that there will be no deterioration of the products characteristics after exploring a maximum junction temperature of 175°C
- Package level test to guarantee that package materials can sustain an exploration of the maximum junction temperature of 175°C at die level

#### 3.2 Conclusion

Qualification Plan requirements have been fulfilled without exception. Tests have shown that the devices behave correctly after exploring a maximum junction temperature of 175°C.

## 4 DEVICE CHARACTERISTICS

### 4.1 Device description


ST specification:



STPS200170TV1Y

Datasheet

Automotive 170 V, 2 x 100 A, high voltage power Schottky rectifier



#### Features



- AEC-Q101 qualified
- PPAP capable
- Operating  $T_j$  from  $-40^\circ\text{C}$  to  $+175^\circ\text{C}$
- Negligible switching losses
- Low leakage current
- Avalanche rated
- Good trade-off between leakage current and forward voltage drop
- Insulated package ISOTOP comply with UL1557 insulation:
  - Insulated voltage: 2500 V<sub>RMS</sub> sine
- ECOPACK2 compliant component

#### Applications

- DC/DC converter, especially in hybrid or electrical vehicles
- Secondary rectification
- LLC topologies
- Phase shift topologies

#### Description

This high voltage Schottky rectifier is suitable for high frequency switch mode power supplies.

Packaged in ISOTOP, the STPS200170TV1Y is intended for use in secondary rectification applications and more precisely in DC/DC converters in hybrid and electrical vehicles.

Product status link	
STPS200170TV1Y	
Product summary	
Symbol	
$I_{F(AV)}$	2 x 100 A
$V_{RRM}$	170 V
$T_j$ (max.)	175 °C
$V_F$ (typ.)	0.63 V

## 4.2 Construction Note

STPS200170TV1Y	
<b>Wafer/Die fab. information</b>	
Wafer fab manufacturing location	ST SINGAPORE
Technology / Process family	Power Schottky Rectifier
<b>Wafer Testing (EWS) information</b>	
Electrical testing manufacturing location	ST SINGAPORE
<b>Assembly information</b>	
Assembly site	ST BOUSKOURA - MOROCCO
Package description	ISOTOP
<b>Final testing information</b>	
Testing location	ST BOUSKOURA - MOROCCO

## 5 TESTS RESULTS SUMMARY

### 5.1 Test vehicles

Lot #	Part Number	Package	Comments
L1	STPS200170TV1Y	ISOTOP	Qualification lot

Detailed results in below chapter will refer to these references.

### 5.2 Test plan and results summary

Test	Std ref.	Conditions	Steps / Duration	SS	Failure/SS	
					L1	
<b>Die Oriented Tests</b>						
Wafer level test to guarantee Tj max	ST internal specification	Ir, Vf parameters after 175°C exploration	-	30	0/30	
<b>Package Oriented Tests</b>						
Package level test to guarantee Tj max	UL Certification 1557 (File E81734)	201°C	5Khrs	21	0/21	



## Public Products List

Public Products are off the shelf products. They are not dedicated to specific customers, they are available through ST Sales team, or Distributors, and visible on ST.com

**PCI Title :** Datasheet update for Maximum Operating Junction Temperature from 150°C to 175°C

**PCI Reference :** ADG/20/12358

**Subject :** Public Products List

Dear Customer,

Please find below the Standard Public Products List impacted by the change.

STPS200170TV1Y		
----------------	--	--



### **IMPORTANT NOTICE – PLEASE READ CAREFULLY**

Subject to any contractual arrangement in force with you or to any industry standard implemented by us, STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2018 STMicroelectronics – All rights reserved