



12500 TI Boulevard, MS 8640, Dallas, Texas 75243

**PCN# 20241106000.2**  
**Qualification of RFAB as additional Fab site for select LBC9 devices**  
**Change Notification / Sample Request**

**Date:** November 07, 2024  
**To:** MOUSER PCN

Dear Customer:

This is an announcement of a change to a device that is currently offered by Texas Instruments. The details of this change are on the following pages.

Texas Instruments requires acknowledgement of receipt of this notification within **30** days of the date of this notice. Lack of acknowledgement of this notice within 30 days constitutes acceptance of the change. If samples or additional data are required, requests must be received within **30 days** of this notification.

The changes discussed within this PCN will not take effect any earlier than the proposed first ship date on Page 3 of this notification, unless customer agreement has been reached on an earlier implementation of the change.

This notice does not change the end-of-life status of any product. Should product affected be on a previously issued product withdrawal/discontinuance notice, this notification does not extend the life of that product or change the life time buy offering/discontinuance plan.

For questions regarding this notice or to provide acknowledgement of this PCN, you may contact your local Field Sales Representative or the Change Management team.

For sample requests or sample related questions, contact your local Field Sales Representative.

Sincerely,

Change Management Team  
SC Business Services

**20241106000.2**  
**Attachment: 1**

**Products Affected:**

The devices listed on this page are a subset of the complete list of affected devices. According to our records, you have recently purchased these devices. The corresponding customer part number is also listed, if available.

| <b>DEVICE</b>   | <b>CUSTOMER PART NUMBER</b> |
|-----------------|-----------------------------|
| UCC27624QDRQ1   | NULL                        |
| UCC27624QDGNRQ1 | NULL                        |

Technical details of this Product Change follow on the next page(s).

|                    |               |                  |                   |
|--------------------|---------------|------------------|-------------------|
| <b>PCN Number:</b> | 20241106000.2 | <b>PCN Date:</b> | November 07, 2024 |
|--------------------|---------------|------------------|-------------------|

**Title:** Qualification of RFAB as additional Fab site for select LBC9 devices

**Customer Contact:** Change Management team    **Dept:** Quality Services

**Proposed 1<sup>st</sup> Ship Date:** May 06, 2025    **Sample requests accepted until:** December 07, 2024\*

**\*Sample requests received after December 07, 2024 will not be supported.**

|                                     |                           |                          |                    |                                     |                     |
|-------------------------------------|---------------------------|--------------------------|--------------------|-------------------------------------|---------------------|
| <b>Change Type:</b>                 |                           |                          |                    |                                     |                     |
| <input type="checkbox"/>            | Assembly Site             | <input type="checkbox"/> | Design             | <input type="checkbox"/>            | Wafer Bump Material |
| <input type="checkbox"/>            | Assembly Process          | <input type="checkbox"/> | Data Sheet         | <input type="checkbox"/>            | Wafer Bump Process  |
| <input type="checkbox"/>            | Assembly Materials        | <input type="checkbox"/> | Part number change | <input checked="" type="checkbox"/> | Wafer Fab Site      |
| <input type="checkbox"/>            | Mechanical Specification  | <input type="checkbox"/> | Test Site          | <input type="checkbox"/>            | Wafer Fab Materials |
| <input checked="" type="checkbox"/> | Packing/Shipping/Labeling | <input type="checkbox"/> | Test Process       | <input type="checkbox"/>            | Wafer Fab Process   |

**PCN Details**

**Description of Change:**

Texas Instruments is pleased to announce the addition of RFAB as an additional Wafer Fab site option for the products listed in the "Product Affected" section of this document.

| Current Fab Site |         |                | Additional Fab Site |         |                |
|------------------|---------|----------------|---------------------|---------|----------------|
| Current Fab Site | Process | Wafer Diameter | Additional Fab Site | Process | Wafer Diameter |
| DMOS6            | LBC9    | 300 mm         | RFAB                | LBC9    | 300 mm         |

Qual details are provided in the Qual Data Section.

**Reason for Change:**

Continuity of Supply.

**Anticipated impact on Form, Fit, Function, Quality or Reliability (positive / negative):**

None

**Changes to product identification resulting from this PCN:**

**Fab Site Information:**

| Chip Site   | Chip Site Origin Code (20L) | Chip Site Country Code (21L) | Chip Site City    |
|-------------|-----------------------------|------------------------------|-------------------|
| DMOS6       | DM6                         | USA                          | Dallas            |
| <b>RFAB</b> | <b>RFB</b>                  | <b>USA</b>                   | <b>Richardson</b> |

Sample product shipping label (not actual product label)

TEXAS INSTRUMENTS  
 MADE IN: Malaysia  
 2DC: 20:  
 MSL '2 /260C/1 YEAR SEAL DT  
 MSL 1 /235C/UNLIM 03/29/04  
 OPT:  
 ITEM: 39  
 LBL: 5A (L)T0:1750

(1P) SN74LS07NSR  
 (Q) 2000 (D) 0336  
 (31T) LOT: 3959047MLA  
 (4W) TKY (1T) 7523483SI2  
 (P)  
 (2P) REV: (V) 6833317  
 (20L) CSO: SHE (21L) CCO:USA  
 (22L) ASO: MLA (23L) ACO: MYS

**Product Affected:**

|                 |               |
|-----------------|---------------|
| UCC27624QDGNRQ1 | UCC27624QDRQ1 |
|-----------------|---------------|

**Automotive Qualification Summary**  
(As per AEC-Q100 Rev. J and JEDEC Guidelines)

Jade UCC27624-Q1 in D and DGN Product Offload to RFAB  
Approve Date 25-January-2024

**Product Attributes**

| Attributes               | Qual Device:<br>UCC27624QDGNRQ1 | Qual Device:<br>UCC27624QDRQ1 | QBS Package Reference:<br>SN65HVD1040AQDRQ1 | QBS Package Reference:<br>UCC27624QDRQ1 | QBS Package Reference:<br>UCC27624QDGNRQ1 | QBS Process Reference:<br>LM74700QDBVRQ1 |
|--------------------------|---------------------------------|-------------------------------|---|---|---|--|
| Automotive Grade Level   | Grade 1                         | Grade 1                       | Grade 1                                     | Grade 1                                 | Grade 1                                   | Grade 1                                  |
| Operating Temp Range (C) | -40 to 125                      | -40 to 125                    | -40 to 125                                  | -40 to 125                              | -40 to 125                                | -40 to 125                               |
| Product Function         | Power Management                | Power Management              | Interface                                   | Power Management                        | Power Management                          | Power Management                         |
| Wafer Fab Supplier       | RFAB                            | RFAB                          | DL-LIN                                      | DMOS6                                   | DMOS6                                     | RFAB                                     |
| Assembly Site            | MLA                             | MLA                           | MLA   | MLA                                     | MLA                                       | UTL2                                     |
| Package Group            | VSSOP                           | SOIC                          | -   | SOIC                                    | VSSOP                                     | SOT                                      |
| Package Designator       | DGN                             | D                             | D   | D                                       | DGN                                       | DBV                                      |
| Pin Count                | 8                               | 8                             | 8   | 8                                       | 8   | 6  |

- QBS: Qual By Similarity
- Qual Device UCC27624QDGNRQ1 is qualified at MSL1 260C
- Qual Device UCC27624QDRQ1 is qualified at MSL1 260C

**Qualification Results**

Data Displayed as: Number of lots / Total sample size / Total failed

| Type  | #  | Test Spec                           | Min Lot Qty | SS / Lot | Test Name                     | Condition                               | Duration   | Qual Device:<br>UCC27624QDGNRQ1               | Qual Device:<br>UCC27624QDRQ1                 | QBS Package Reference:<br>SN65HVD1040AQDRQ1   | QBS Package Reference:<br>UCC27624QDRQ1       | QBS Package Reference:<br>UCC27624QDGNRQ1     | QBS Process Reference:<br>LM74700QDBVRQ1      |
|---|----|-------------------------------------|-------------|----------|-------------------------------|---|------------|---|---|---|---|---|---|
| <b>Test Group A - Accelerated Environment Stress Tests</b>  |    |                                     |             |          |                               |   |            |   |   |   |   |   |   |
| PC  | A1 | JEDEC J-STD-020 JESD22-A113         | 3           | 77       | Preconditioning               | MSL1 260C                               | -          | -   | -   | 3/0/0   | 1/0/0   | 3/0/0   | -   |
| HAST  | A2 | JEDEC JESD22-A110                   | 3           | 77       | Biased HAST                   | 130C/85%RH                              | 96 Hours   | -   | -   | 3/231/0                                       | 1/77/0  | 3/231/0                                       | -   |
| AC/UHAST  | A3 | JEDEC JESD22-A102/JEDEC JESD22-A118 | 3           | 77       | Autoclave                     | 121C/15psig                             | 96 Hours   | -   | -   | 3/231/0                                       | 1/77/0  | 3/231/0                                       | -   |
| TC  | A4 | JEDEC JESD22-A104 and Appendix 3    | 3           | 77       | Temperature Cycle             | -65C/150C                               | 500 Cycles | -   | -   | 3/231/0                                       | 1/77/0  | 3/231/0                                       | -   |
| TC-BP   | A4 | MIL-STD883 Method 2011              | 1           | 5        | Post Temp Cycle Bond Pull     | -                                       | -          | -   | -   | -   | -   | 1/5/0   | -   |
| TC-SAM  | A4 | -                                   | 3           | 3        | Post TC SAM                   | <50% delamination                       | -          | -   | -   | -   | -   | 3/36/0  | -   |
| HTSL  | A6 | JEDEC JESD22-A103                   | 1           | 45       | High Temperature Storage Life | 150C                                    | 1000 Hours | -   | -   | 3/135/0                                       | 1/77/0  | 3/231/0                                       | -   |
| <b>Test Group B - Accelerated Lifetime Simulation Tests</b> |    |                                     |             |          |                               |   |            |   |   |   |   |   |   |
| HTOL  | B1 | JEDEC JESD22-A108                   | 3           | 77       | Life Test                     | 150C                                    | 408 Hours  | -   | -   | -   | -   | -   | 2/154/0                                       |
| ELFR  | B2 | AEC Q100-008                        | 3           | 800      | Early Life Failure Rate       | 150C                                    | 24 Hours   | -   | -   | -   | -   | -   | 3/2400/0                                      |
| <b>Test Group C - Package Assembly Integrity Tests</b>      |    |                                     |             |          |                               |   |            |   |   |   |   |   |   |
| WBS   | C1 | AEC Q100-001                        | 1           | 30       | Wire Bond Shear               | Minimum of 5 devices, 30 wires Cpk>1.67 | Wires      | 1/30/0  | 1/30/0  | 3/90/0  | 1/30/0  | 3/90/0  | -   |
| WBP   | C2 | MIL-STD883 Method 2011              | 1           | 30       | Wire Bond Pull                | Minimum of 5 devices, 30 wires Cpk>1.67 | Wires      | 1/30/0  | 1/30/0  | 3/90/0  | 1/30/0  | 3/90/0  | -   |
| SD  | C3 | JEDEC J-STD-002                     | 1           | 15       | PB Solderability              | >95% Lead Coverage                      | -          | -   | -   | 1/15/0  | -   | -   | -   |
| SD  | C3 | JEDEC J-STD-002                     | 1           | 15       | PB-Free Solderability         | >95% Lead Coverage                      | -          | -   | -   | 1/15/0  | -   | -   | -   |
| PD  | C4 | JEDEC JESD22-B100 and B108          | 3           | 10       | Physical Dimensions           | Cpk>1.67                                | -          | -   | 1/10/0  | 3/30/0  | 1/10/0  | 3/30/0  | -   |
| <b>Test Group D - Die Fabrication Reliability Tests</b>     |    |                                     |             |          |                               |   |            |   |   |   |   |   |   |
| EM  | D1 | JESD61                              | -           | -        | Electromigration              | -                                       | -          | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements |

| Type  | #  | Test Spec    | Min Lot Qty | SS / Lot | Test Name                           | Condition                    | Duration   | Qual Device:                                  | Qual Device:                                  | QBS Package Reference:                        | QBS Package Reference:                        | QBS Package Reference:                        | QBS Process Reference:                        |
|---|----|--------------|-------------|----------|-------------------------------------|------------------------------|------------|---|---|---|---|---|---|
|   |    |              |             |          |                                     |                              |            | UCC27624QDGNRQ1                               | UCC27624QDRQ1                                 | SN65HVDA1040AQDRQ1                            | UCC27624QDRQ1                                 | UCC27624QDGNRQ1                               | LM74700QDBVRQ1                                |
| TDD   | D2 | JESD35       | -           | -        | Time Dependent Dielectric Breakdown | -                            | -          | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements |
| HCI   | D3 | JESD60 & 28  | -           | -        | Hot Carrier Injection               | -                            | -          | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements |
| BTI   | D4 | -            | -           | -        | Bias Temperature Instability        | -                            | -          | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements |
| SM  | D5 | -            | -           | -        | Stress Migration                    | -                            | -          | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements | Completed Per Process Technology Requirements |
| <b>Test Group E - Electrical Verification Tests</b> |    |              |             |          |                                     |                              |            |   |   |   |   |   |   |
| ESD   | E2 | AEC Q100-002 | 1           | 3        | ESD HBM                             | -                            | 2000 Volts | 1/3/0   | Device specific data <sup>1</sup>             | -   | 1/3/0   | -   | -   |
| ESD   | E3 | AEC Q100-011 | 1           | 3        | ESD CDM                             | -                            | 500 Volts  | 1/3/0   | 1/3/0   | -   | 1/3/0   | -   | -   |
| LU  | E4 | AEC Q100-004 | 1           | 3        | Latch-Up                            | Per AEC Q100-004             | -          | Device specific data <sup>1</sup>             | 1/3/0   | -   | 1/6/0   | -   | -   |
| ED  | E5 | AEC Q100-009 | 3           | 30       | Electrical Distributions            | Cpl>1.67 Room, hot, and cold | -          | 1/30/0  | -   | 3/90/0  | 3/90/0  | 1/30/0  | -   |
| <b>Additional Tests</b>                             |    |              |             |          |                                     |                              |            |   |   |   |   |   |   |

- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV: 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47: -55C/125C/700 Cycles and -65C/150C/500 Cycles

**Ambient Operating Temperature by Automotive Grade Level:**

- Grade 0 (or E): -40C to +150C
- Grade 1 (or Q): -40C to +125C
- Grade 2 (or T): -40C to +105C
- Grade 3 (or I): -40C to +85C

**E1 (TEST): Electrical test temperatures of Qual samples (High temperature according to Grade level):**

- Room/Hot/Cold : HTOL, ED
- Room/Hot : THB / HAST, TC / PTC, HTSL, ELFR, ESD & LU
- Room : AC/uHAST

Quality and Environmental data is available at TI's external Web site: <http://www.ti.com/>

TI Qualification ID: R-CHG-2302-060

[1] Qual device UCC27624QDGNRQ1 and UCC27624QDRQ1 use the same silicon die and bondout

ZVEI ID's: SEM-PW-13

For questions regarding this notice, e-mails can be sent to the Change Management team or your local Field Sales Representative.

**IMPORTANT NOTICE AND DISCLAIMER**

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale ([www.ti.com/legal/termsofsale.html](http://www.ti.com/legal/termsofsale.html)) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.