



12500 TI Boulevard, MS 8640, Dallas, Texas 75243

PCN# 20251118001.1

**Qualify UTL as an additional Assembly/Test site for select devices
Change Notification / Sample Request**

Date: November 19, 2025

To: MOUSER PCN

Dear Customer:

This is an announcement of a change to a device that is currently offered by Texas Instruments. The details of this change are on the following pages.

Texas Instruments requires acknowledgement of receipt of this notification within 60 days of the date of this notice. Lack of acknowledgement of this notice within 60 days constitutes acceptance and approval of this change. If samples or additional data are required, requests must be received within 60 days of this notification.

The changes discussed within this PCN will not take effect any earlier than the proposed first ship date on Page 3 of this notification, unless customer agreement has been reached on an earlier implementation of the change.

This notice does not change the end-of-life status of any product. Should product affected be on a previously issued product withdrawal/discontinuance notice, this notification does not extend the life of that product or change the life time buy offering/discontinuance plan.

For questions regarding this notice or to provide acknowledgement of this PCN, you may contact your local Field Sales Representative or the change management team.

For sample requests or sample related questions, contact your local Field Sales Representative.

TI values customer engagement and feedback related to TI changes. Customers should contact TI if there are questions or concerns regarding a change notification.

Sincerely,

Change Management Team
SC Business Services

20251118001.1
Attachment: 1

Products Affected:

The devices listed on this page are a subset of the complete list of affected devices. According to our records, you have recently purchased these devices. The corresponding customer part number is also listed, if available.

DEVICE	CUSTOMER PART NUMBER
SN74LVC1G19DRYR	SN74LVC1G19DRYR
SN74LVC1G3157DRYR	SN74LVC1G3157DRYR
SN74LVC1G126DRYR	SN74LVC1G126DRYR
SN74LVC1G04DRYR	SN74LVC1G04DRYR
SN74LVC1G07DRYR	SN74LVC1G07DRYR
SN74LVC1G125DRYR	SN74LVC1G125DRYR
SN74LVC1G175DRYR	NULL
SN74LVC1G14DRYR	SN74LVC1G14DRYR
SN74LVC1G97DRYR	SN74LVC1G97DRYR

Technical details of this Product Change follow on the next page(s).

PCN Number:	20251118001.1		PCN Date:	November 19, 2025																
Title:	Qualify UTL as an additional Assembly/Test site for select devices																			
Customer Contact:	Change Management team		Dept:	Quality Services																
Proposed 1st Ship Date:	February 17, 2026		Sample requests accepted until:	January 18, 2026*																
*Sample requests received after January 18, 2026 will not be supported.																				
Change Type:																				
☒	Assembly Site	☐	Design	☐	Wafer Bump Material															
☐	Assembly Process	☐	Data Sheet	☐	Wafer Bump Process															
☒	Assembly Materials	☐	Part number change	☐	Wafer Fab Site															
☐	Mechanical Specification	☒	Test Site	☐	Wafer Fab Material															
☒	Packing/Shipping/Labeling	☐	Test Process	☐	Wafer Fab Process															
PCN Details																				
Description of Change:																				
Texas Instruments is pleased to announce the qualification of TI Malaysia (MLA) as an additional Assembly/Test site for the list of devices shown below. Material differences between sites are as follows. <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="3">Assembly Site</th> </tr> <tr> <th></th> <th>Current Site</th> <th>Additional Site</th> </tr> </thead> <tbody> <tr> <td>Assembly Site</td> <td>ATXSZ</td> <td>UTL</td> </tr> <tr> <td>LEAD Frame</td> <td>SID#1107151101</td> <td>SID#FU0148</td> </tr> <tr> <td>Mount Compound</td> <td>Sid#1400336111</td> <td>SID#PZ0084</td> </tr> </tbody> </table> Qual details are provided in the Qual Data Section. Test coverage, insertions, conditions will remain consistent with current testing.						Assembly Site				Current Site	Additional Site	Assembly Site	ATXSZ	UTL	LEAD Frame	SID#1107151101	SID#FU0148	Mount Compound	Sid#1400336111	SID#PZ0084
Assembly Site																				
	Current Site	Additional Site																		
Assembly Site	ATXSZ	UTL																		
LEAD Frame	SID#1107151101	SID#FU0148																		
Mount Compound	Sid#1400336111	SID#PZ0084																		
Reason for Change:																				
Continuity of supply.																				
Anticipated impact on Fit, Form, Function, Quality or Reliability (positive / negative):																				
None.																				
Impact on Environmental Ratings																				
Checked boxes indicate the status of environmental ratings following implementation of this change. If below boxes are checked, there are no changes to the associated environmental ratings. <table border="1" style="width: 100%;"> <thead> <tr> <th>RoHS</th> <th>REACH</th> <th>Green Status</th> <th>IEC 62474</th> </tr> </thead> <tbody> <tr> <td>☒ No Change</td> <td>☒ No Change</td> <td>☒ No Change</td> <td>☒ No Change</td> </tr> </tbody> </table>						RoHS	REACH	Green Status	IEC 62474	☒ No Change	☒ No Change	☒ No Change	☒ No Change							
RoHS	REACH	Green Status	IEC 62474																	
☒ No Change	☒ No Change	☒ No Change	☒ No Change																	
Changes to product identification resulting from this PCN:																				

Assembly Site	Assembly Site Origin (22L)	Assembly Country Code (23L)	Assembly City
ATXSZ	ASN	CHN	Suzhou
UTL	UTL1/2/3	TH	Bangkok

Sample product shipping label (not actual product label)

**TEXAS
INSTRUMENTS**
MADE IN: Malaysia
2DC: 2d:
MSL 2 / 260C / 1 YEAR
MSL 1 / 235C / UNLIM
SEAL DT
03/29/04
OPT:
ITEM: 39
LBL: 5A (L)T0:1750

**G4**



(1P) **SN74LS07NSR**
(Q) **2000** (D) **0336**
(31T) LOT: 3959047MLA
(4W) TKY (1T) 7523483SI2
(P)
(2P) REV: (V) 0033317
(20L) CS0: SHE (21L) CC0: USA
(22L) AS0: MLA (23L) ACO: MYS

Product Affected:		
SN74LVC1G04DRY2	SN74LVC1G04DRYR	SN74LVC1G07DRYR
SN74LVC1G125DRYR	SN74LVC1G125DRYR-M	SN74LVC1G3157DRYR
SN74LVC1G126DRYR	SN74LVC1G126DRYR-M	SN74LVC1G04DRYRG4
SN74LVC1G19DRYR	SN74LVC1G97DRYR	SN74LVC1G07DRYRG4
SN74LVC1G14DRYR	SN74LVC1G175DRYR	

Automotive Qualification Summary (As per AEC-Q100 Rev. J and JEDEC Guidelines)

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Type	#	Test Spec	Min Lot Qty	SS / Lot	Test Name	Condition	Duration	Qual Device: SN74LVC1G08QDRYRQ1	QBS Process Reference: SN3257QDYRQ1	QBS Package Reference: TMP451A QDQFRQ1
Test Group A - Accelerated Environment Stress Tests										
PC	A1	JEDEC J-STD-020 JESD22-A113	3	77	Preconditioning	MSL1 260C	-	3/0/0	3/0/0	3/0/0
HAST	A2	JEDEC JESD22-A110	3	77	Biased HAST	130C/85%RH	96 Hours	3/231/0	3/231/0	3/231/0
AC/UHAST	A3	JEDEC JESD22-A102/JEDEC JESD22-A118	3	77	Autoclave	121C/15psig	96 Hours	-	3/231/0	3/231/0
AC/UHAST	A3	JEDEC JESD22-A102/JEDEC JESD22-A118	3	77	Unbiased HAST	130C/85%RH	96 Hours	3/231/0	-	-
TC	A4	JEDEC JESD22-A104 and Appendix 3	3	77	Temperature Cycle	-65C/150C	500 Cycles	3/231/0	3/231/0	3/231/0
TC-BP	A4	MIL-STD883 Method 2011	1	5	Post Temp Cycle Bond Pull	-	-	1/5/0	-	1/5/0
HTSL	A6	JEDEC JESD22-A103	1	45	High Temperature Storage Life	150C	1000 Hours	1/45/0	3/135/0	-
HTSL	A6	JEDEC JESD22-A103	1	45	High Temperature Storage Life	175C	500 Hours	-	-	1/45/0
Test Group B - Accelerated Lifetime Simulation Tests										

Type	#	Test Spec	Min Lot Qty	SS / Lot	Test Name	Condition	Duration	Qual Device: SN74LVC1G08QDRYRQ1	QBS Process Reference: SN3257QDYYRQ1	QBS Package Reference: TMP451AQDQFRQ1
HTOL	B1	JEDEC JESD22-A108	3	77	Life Test	150C	300 Hours	-	3/231/0	-
HTOL	B1	JEDEC JESD22-A108	3	77	Life Test	150C	408 Hours	-	-	3/231/0
ELFR	B2	AEC Q100-008	3	800	Early Life Failure Rate	150C	24 Hours	-	3/2400/0	3/2400/0
Test Group C - Package Assembly Integrity Tests										
WBS	C1	AEC Q100-001	1	30	Wire Bond Shear	Minimum of 5 devices, 30 wires Cpk>1.67	Wires	1/30/0	3/90/0	3/90/0
WBP	C2	MIL-STD883 Method 2011	1	30	Wire Bond Pull	Minimum of 5 devices, 30 wires Cpk>1.67	Wires	1/30/0	3/90/0	3/90/0
SD	C3	JEDEC J-STD-002	1	15	PB Solderability	>95% Lead Coverage	-	-	1/15/0	-
SD	C3	JEDEC J-STD-002	1	15	PB-Free Solderability	>95% Lead Coverage	-	-	1/15/0	-
PD	C4	JEDEC JESD22-B100 and B108	3	10	Physical Dimensions	Cpk>1.67	-	1/10/0	3/30/0	3/30/0
Test Group D - Die Fabrication Reliability Tests										
EM	D1	JESD61	-	-	Electromigration	-	-	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements
Tddb	D2	JESD35	-	-	Time Dependent Dielectric Breakdown	-	-	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements

Type	#	Test Spec	Min Lot Qty	SS / Lot	Test Name	Condition	Duration	Qual Device: SN74LVC1G08QDRYRQ1	QBS Process Reference: SN3257QDYYRQ1	QBS Package Reference: TMP451AQDQFRQ1
HCI	D3	JESD60 & 28	-	-	Hot Carrier Injection	-	-	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements
BTI	D4	-	-	-	Bias Temperature Instability	-	-	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements
SM	D5	-	-	-	Stress Migration	-	-	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements
Test Group E - Electrical Verification Tests										
ESD	E2	AEC Q100-002	1	3	ESD HBM	-	2000 Volts	1/3/0	1/3/0	1/3/0
ESD	E3	AEC Q100-011	1	3	ESD CDM	-	1500 Volts	-	1/3/0	-
ESD	E3	AEC Q100-011	1	3	ESD CDM	-	500 Volts	1/3/0	-	1/3/0
LU	E4	AEC Q100-004	1	3	Latch-Up	Per AEC Q100-004	-	1/3/0	1/6/0	1/6/0
ED	E5	AEC Q100-009	3	30	Electrical Distributions	Cpk>1.67 Room, hot, and cold	-	1/30/0	3/90/0	3/90/0
Additional Tests										

- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV : 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV : 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles

Ambient Operating Temperature by Automotive Grade Level:

- Grade 0 (or E): -40C to +150C
- Grade 1 (or Q): -40C to +125C
- Grade 2 (or T): -40C to +105C
- Grade 3 (or L): -40C to +85C

E1 (TEST): Electrical test temperatures of Qual samples (High temperature according to Grade level):

- Room/Hot/Cold : HTOL, ED
- Room/Hot : THB / HAST, TC / PTC, HTSL, ELFR, ESD & LU
- Room : AC/uHAST

Quality and Environmental data is available at TI's external Web site: <http://www.ti.com/>

TI Qualification ID: R-CHG-2409-069

In performing change qualifications, Texas Instruments follows integrated circuit industry standards in performing defect mechanism analysis and failure mechanism-based accelerated environmental testing to ensure wafer fab process, assembly process and product quality and reliability. As encouraged by these standards, TI uses both product-specific and generic (family) data in qualifying its changes. For devices to be categorized as a 'product qualification family' for generic data purposes, they must share similar product, wafer fab process and assembly process elements. The applicability of generic data (also known at TI as Qualification by Similarity (QBS)) is determined by the Reliability Engineering function following these industry standards. Generic data is shown in the qualification report in columns titled "QBS Process" (for wafer fab process), "QBS Package" (for assembly process) and "QBS Product" (for product family).

For questions regarding this notice, e-mails can be sent to the Change Management team or your local Field Sales Representative.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for,

and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.