



**12500 TI Boulevard, MS 8640, Dallas, Texas 75243**

**PCN# 20251118000.2A**

**Qualify UTL as an additional Assembly/Test site for select devices  
Change Notification / Sample Request**

**Purpose of this revision A is to correct the site originally stated in the Description of  
Change**

**Date:** November 21, 2025

**To:** MOUSER PCN

Dear Customer:

This is an announcement of a change to a device that is currently offered by Texas Instruments. The details of this change are on the following pages.

Texas Instruments requires acknowledgement of receipt of this notification within 60 days of the date of this notice. Lack of acknowledgement of this notice within 60 days constitutes acceptance and approval of this change. If samples or additional data are required, requests must be received within 60 days of this notification.

The changes discussed within this PCN will not take effect any earlier than the proposed first ship date on Page 3 of this notification, unless customer agreement has been reached on an earlier implementation of the change.

This notice does not change the end-of-life status of any product. Should product affected be on a previously issued product withdrawal/discontinuance notice, this notification does not extend the life of that product or change the life time buy offering/discontinuance plan.

For questions regarding this notice or to provide acknowledgement of this PCN, you may contact your local Field Sales Representative or the change management team.

For sample requests or sample related questions, contact your local Field Sales Representative.

TI values customer engagement and feedback related to TI changes. Customers should contact TI if there are questions or concerns regarding a change notification.

Sincerely,

Change Management Team  
SC Business Services

**20251118000.2A****Attachment: 1****Products Affected:**

The devices listed on this page are a subset of the complete list of affected devices. According to our records, you have recently purchased these devices. The corresponding customer part number is also listed, if available.

<b>DEVICE</b>	<b>CUSTOMER PART NUMBER</b>
SN74AXC1T45QDRYRQ1	NULL
1P2GU04QDRYRQ1	NULL
SN74LVC1G14QDRYRQ1	NULL
SN74LVC1G07QDRYRQ1	NULL
TXU0101QDRYRQ1	NULL
SN74LVC1G32QDRYRQ1	NULL
1P1G126QDRYRQ1	NULL
SN74LVC1G08QDRYRQ1	NULL

Technical details of this Product Change follow on the next page(s).

<b>PCN Number:</b>	20251118000.2A	<b>PCN Date:</b>	November 21, 2025
<b>Title:</b>	Qualify UTL as an additional Assembly/Test site for select devices		
<b>Customer Contact:</b>	Change Management team	<b>Dept:</b>	Quality Services
<b>Proposed 1<sup>st</sup> Ship Date:</b>	February 19, 2026	<b>Sample requests accepted until:</b>	January 20, 2026*
<b>*Sample requests received after January 20, 2026 will not be supported.</b>			
<b>Change Type:</b>			
<input checked="" type="checkbox"/> Assembly Site	<input type="checkbox"/>	Design	<input type="checkbox"/> Wafer Bump Material
<input type="checkbox"/> Assembly Process	<input type="checkbox"/>	Data Sheet	<input type="checkbox"/> Wafer Bump Process
<input checked="" type="checkbox"/> Assembly Materials	<input type="checkbox"/>	Part number change	<input type="checkbox"/> Wafer Fab Site
<input type="checkbox"/> Mechanical Specification	<input checked="" type="checkbox"/>	Test Site	<input type="checkbox"/> Wafer Fab Material
<input checked="" type="checkbox"/> Packing/Shipping/ Labeling	<input type="checkbox"/>	Test Process	<input type="checkbox"/> Wafer Fab Process

### PCN Details

#### Description of Change:

Texas Instruments is pleased to announce the qualification of **TI-Malaysia (MLA)** UTL (Subcon) as an additional Assembly/Test site for the list of devices shown below. Material differences between sites are as follows.

#### Assembly Site

	<b>Current Site</b>	<b>Additional Site</b>
Assembly Site	ATXSZ	<b>UTL</b>
<b>LEAD Frame</b>	SID#1107151101	<b>SID#FU0148</b>
<b>Mount Compound</b>	Sid#1400336111	<b>SID#PZ0084</b>

Qual details are provided in the Qual Data Section.

Test coverage, insertions, conditions will remain consistent with current testing.

#### Reason for Change:

Continuity of supply.

#### Anticipated impact on Fit, Form, Function, Quality or Reliability (positive / negative):

None.

#### Impact on Environmental Ratings

Checked boxes indicate the status of environmental ratings following implementation of this change. If below boxes are checked, there are no changes to the associated environmental ratings.

<b>RoHS</b>	<b>REACH</b>	<b>Green Status</b>	<b>IEC 62474</b>
<input checked="" type="checkbox"/> No Change			

#### Changes to product identification resulting from this PCN:

Assembly Site	Assembly Site Origin (22L)	Assembly Country Code (23L)	Assembly City
ATXSZ	ASN	CHN	Suzhou
<b>UTL</b>	<b>UTL1/2/3</b>	<b>TH</b>	<b>Bangkok</b>

Sample product shipping label (not actual product label)



#### Product Affected:

1P1G125QDRYRQ1	1P1G126QDRYRQ1	1P2GU04QDRYRQ1
SN74LVC1G07QDRYRQ1	SN74LVC1G08QDRYRQ1	SN74LVC1G14QDRYRQ1
SN74LVC1G32QDRYRQ1	TXU0101QDRYRQ1	
SN74AXC1T45QDRYRQ1	SN74LVC1G17QDRYRQ1	

# Automotive Qualification Summary

## (As per AEC-Q100 Rev. J and JEDEC Guidelines)

### Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Type	#	Test Spec	Min Lot Qty	SS / Lot	Test Name	Condition	Duration	Qual Device: <a href="#">SN74LVC1G08QDRYRQ1</a>	QBS Process Reference: <a href="#">SN3257QDYYRQ1</a>	QBS Package Reference: <a href="#">TMP451AQDQFRQ1</a>
<b>Test Group A - Accelerated Environment Stress Tests</b>										
PC	A1	JEDEC J-STD-020 JESD22-A113	3	77	Preconditioning	MSL1 260C	-	3/0/0	3/0/0	3/0/0
HAST	A2	JEDEC JESD22-A110	3	77	Biased HAST	130C/85%RH	96 Hours	3/231/0	3/231/0	3/231/0
AC/UHAST	A3	JEDEC JESD22-A1020JEDEC JESD22-A118	3	77	Autoclave	121C/15psig	96 Hours	-	3/231/0	3/231/0
AC/UHAST	A3	JEDEC JESD22-A1020JEDEC JESD22-A118	3	77	Unbiased HAST	130C/85%RH	96 Hours	3/231/0	-	-
TC	A4	JEDEC JESD22-A104 and Appendix 3	3	77	Temperature Cycle	-65C/150C	500 Cycles	3/231/0	3/231/0	3/231/0
TC-BP	A4	MIL-STD883 Method 2011	1	5	Post Temp Cycle Bond Pull	-	-	1/5/0	-	1/5/0
HTSL	A6	JEDEC JESD22-A103	1	45	High Temperature Storage Life	150C	1000 Hours	1/45/0	3/135/0	-
HTSL	A6	JEDEC JESD22-A103	1	45	High Temperature Storage Life	175C	500 Hours	-	-	1/45/0
<b>Test Group B - Accelerated Lifetime Simulation Tests</b>										

Type	#	Test Spec	Min Lot Qty	SS / Lot	Test Name	Condition	Duration	Qual Device: <a href="#">SN74LVC1G08QDRYRQ1</a>	QBS Process Reference: <a href="#">SN3257QDYYRQ1</a>	QBS Package Reference: <a href="#">TMP451A QD QFR Q1</a>
HTOL	B1	JEDEC JESD22-A108	3	77	Life Test	150C	300 Hours	-	3/231/0	-
HTOL	B1	JEDEC JESD22-A108	3	77	Life Test	150C	408 Hours	-	-	3/231/0
ELFR	B2	AEC Q100-008	3	800	Early Life Failure Rate	150C	24 Hours	-	3/2400/0	3/2400/0
<b>Test Group C - Package Assembly Integrity Tests</b>										
WBS	C1	AEC Q100-001	1	30	Wire Bond Shear	Minimum of 5 devices, 30 wires Cpk>1.67	Wires	1/30/0	3/90/0	3/90/0
WBP	C2	MIL-STD883 Method 2011	1	30	Wire Bond Pull	Minimum of 5 devices, 30 wires Cpk>1.67	Wires	1/30/0	3/90/0	3/90/0
SD	C3	JEDEC J-STD-002	1	15	PB Solderability	>95% Lead Coverage	-	-	1/15/0	-
SD	C3	JEDEC J-STD-002	1	15	PB-Free Solderability	>95% Lead Coverage	-	-	1/15/0	-
PD	C4	JEDEC JESD22-B100 and B108	3	10	Physical Dimensions	Cpk>1.67	-	1/10/0	3/30/0	3/30/0
<b>Test Group D - Die Fabrication Reliability Tests</b>										
EM	D1	JESD61	-	-	Electromigration	-	-	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements
TDDB	D2	JESD35	-	-	Time Dependent Dielectric Breakdown	-	-	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements
Type	#	Test Spec	Min Lot Qty	SS / Lot	Test Name	Condition	Duration	Qual Device: <a href="#">SN74LVC1G08QDRYRQ1</a>	QBS Process Reference: <a href="#">SN3257QDYYRQ1</a>	QBS Package Reference: <a href="#">TMP451A QD QFR Q1</a>
HCI	D3	JESD60 & 28	-	-	Hot Carrier Injection	-	-	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements
BTI	D4	-	-	-	Bias Temperature Instability	-	-	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements
SM	D5	-	-	-	Stress Migration	-	-	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements	Completed Per Process Technology Requirements
<b>Test Group E - Electrical Verification Tests</b>										
ESD	E2	AEC Q100-002	1	3	ESD HBM	-	2000 Volts	1/3/0	1/3/0	1/3/0
ESD	E3	AEC Q100-011	1	3	ESD CDM	-	1500 Volts	-	1/3/0	-
ESD	E3	AEC Q100-011	1	3	ESD CDM	-	500 Volts	1/3/0	-	1/3/0
LU	E4	AEC Q100-004	1	3	Latch-Up	Per AEC Q100-004	-	1/3/0	1/6/0	1/6/0
ED	E5	AEC Q100-009	3	30	Electrical Distributions	Cpk>1.67 Room, hot, and cold	-	1/30/0	3/90/0	3/90/0
<b>Additional Tests</b>										
<ul style="list-style-type: none"> <li>Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable</li> <li>The following are equivalent HTOL options based on an activation energy of 0.7eV : 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours</li> <li>The following are equivalent HTSL options based on an activation energy of 0.7eV : 150C/1k Hours, and 170C/420 Hours</li> <li>The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles</li> </ul>										

- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV : 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV : 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles

**Ambient Operating Temperature by Automotive Grade Level:**

- Grade 0 (or E): -40C to +150C
- Grade 1 (or Q): -40C to +125C
- Grade 2 (or T): -40C to +105C
- Grade 3 (or I) : -40C to +85C

**E1 (TEST): Electrical test temperatures of Qual samples (High temperature according to Grade level):**

- Room/Hot/Cold : HTOL, ED
- Room/Hot : THB / HAST, TC / PTC, HTSL, ELFR, ESD & LU
- Room : AC/uHAST

Quality and Environmental data is available at TI's external Web site: <http://www.ti.com/>

TI Qualification ID: R-CHG-2409-069

In performing change qualifications, Texas Instruments follows integrated circuit industry standards in performing defect mechanism analysis and failure mechanism-based accelerated environmental testing to ensure wafer fab process, assembly process and product quality and reliability. As encouraged by these standards, TI uses both product-specific and generic (family) data in qualifying its changes. For devices to be categorized as a 'product qualification family' for generic data purposes, they must share similar product, wafer fab process and assembly process elements. The applicability of generic data (also known at TI as Qualification by Similarity (QBS)) is determined by the Reliability Engineering function following these industry standards. Generic data is shown in the qualification report in columns titled "QBS Process" (for wafer fab process), "QBS Package" (for assembly process) and "QBS Product" (for product family).

**ZVEI ID:** SEM-PA-03, SEM-PA-05, SEM-PA-07, SEM-PA-18, SEM-TF-01

For questions regarding this notice, e-mails can be sent to the Change Management team or your local Field Sales Representative.

**IMPORTANT NOTICE AND DISCLAIMER**

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for,

and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale ([www.ti.com/legal/termsofsale.html](http://www.ti.com/legal/termsofsale.html)) or other applicable terms available either on [ti.com](http://ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.