



12500 TI Boulevard, MS 8640, Dallas, Texas 75243

**PCN# 20260223008.1
Add Cu as Alternative Wire Base Metal for Selected Device(s)
Change Notification / Sample Request**

Date: February 24, 2026
To: MOUSER PCN

Dear Customer:

This is an announcement of a change to a device that is currently offered by Texas Instruments. The details of this change are on the following pages.

Texas Instruments requires acknowledgement of receipt of this notification within 60 days of the date of this notice. Lack of acknowledgement of this notice within 60 days constitutes acceptance and approval of this change. If samples or additional data are required, requests must be received within 60 days of this notification.

The changes discussed within this PCN will not take effect any earlier than the proposed first ship date on Page 3 of this notification, unless customer agreement has been reached on an earlier implementation of the change.

This notice does not change the end-of-life status of any product. Should product affected be on a previously issued product withdrawal/discontinuance notice, this notification does not extend the life of that product or change the life time buy offering/discontinuance plan.

For questions regarding this notice or to provide acknowledgement of this PCN, you may contact your local Field Sales Representative or the change management team.

For sample requests or sample related questions, contact your local Field Sales Representative.

TI values customer engagement and feedback related to TI changes. Customers should contact TI if there are questions or concerns regarding a change notification.

Sincerely,

Change Management Team
SC Business Services

20260223008.1
Change Notification / Sample Request
Attachments

Products Affected:

The devices listed on this page are a subset of the complete list of affected devices. According to our records, you have recently purchased these devices. The corresponding customer part number is also listed, if available.

DEVICE	CUSTOMER PART NUMBER
TPSI3050DWZR	NULL
TPSI3052DWZR	NULL
TPSI3052SDWZR	NULL

Technical details of this Product Change follow on the next page(s).

PCN Number:	20260223008.1			PCN Date:	February 24, 2026								
Title:	Add Cu as Alternative Wire Base Metal for Selected Device(s)												
Customer Contact:	Change Management team		Dept:	Quality Services									
Proposed 1st Ship Date:	May 25, 2026		Estimated Sample Availability:	April 25, 2026									
*Sample requests received after April 25, 2026 will not be supported.													
Change Type:													
<input type="checkbox"/>	Assembly Site	<input type="checkbox"/>	Design	<input type="checkbox"/>	Wafer Bump Material								
<input checked="" type="checkbox"/>	Assembly Process	<input type="checkbox"/>	Data Sheet	<input type="checkbox"/>	Wafer Bump Process								
<input checked="" type="checkbox"/>	Assembly Materials	<input type="checkbox"/>	Part number change	<input type="checkbox"/>	Wafer Fab Site								
<input type="checkbox"/>	Mechanical Specification	<input type="checkbox"/>	Test Site	<input type="checkbox"/>	Wafer Fab Material								
<input type="checkbox"/>	Packing/Shipping/Labeling	<input type="checkbox"/>	Test Process	<input type="checkbox"/>	Wafer Fab Process								
PCN Details													
Description of Change:													
Texas Instruments is pleased to announce the qualification of new assembly material set to add Cu as an additional bond wire option for devices listed in "Product affected" section below. Devices will remain in current assembly facility and piece part changes as follows:													
<table border="1"> <thead> <tr> <th>Material</th> <th>Current</th> <th>Proposed</th> </tr> </thead> <tbody> <tr> <td>Wire diam/type</td> <td>1.0mil Au</td> <td>0.8mil Cu</td> </tr> </tbody> </table>						Material	Current	Proposed	Wire diam/type	1.0mil Au	0.8mil Cu		
Material	Current	Proposed											
Wire diam/type	1.0mil Au	0.8mil Cu											
Reason for Change:													
Continuity of supply. 1) To align with world technology trends and use wiring with enhanced mechanical and electrical properties 2) Maximize flexibility within our Assembly/Test production sites. 3) Cu is easier to obtain and stock													
Anticipated impact on Form, Fit, Function, Quality or Reliability (positive / negative):													
Review the SDP for full evaluation of the change based on the customer use case.													
Impact on Environmental Ratings:													
Checked boxes indicate the status of environmental ratings following implementation of this change. If below boxes are checked, there are no changes to the associated environmental ratings.													
<table border="1"> <thead> <tr> <th>RoHS</th> <th>REACH</th> <th>Green Status</th> <th>IEC 62474</th> </tr> </thead> <tbody> <tr> <td><input checked="" type="checkbox"/> No Change</td> </tr> </tbody> </table>						RoHS	REACH	Green Status	IEC 62474	<input checked="" type="checkbox"/> No Change			
RoHS	REACH	Green Status	IEC 62474										
<input checked="" type="checkbox"/> No Change	<input checked="" type="checkbox"/> No Change	<input checked="" type="checkbox"/> No Change	<input checked="" type="checkbox"/> No Change										
Changes to product identification resulting from this PCN:													
None													
Product Affected:													
TPSI3050DWZR		TPSI3052DWZR											
TPSI3050SDWZR		TPSI3052SDWZR											

Qualification Report

Automotive New Product Qualification Summary

(As per AEC-Q100 Rev. J and JEDEC Guidelines)
Approve Date 19-December-2025

Product Attributes

Attributes	Qual Device:	QBS Process Reference:	QBS Package, Process, Product Reference:	QBS Package Reference:	QBS Package Reference:
	TPSI3050SQDWZRQ1	LM74700QDBVRQ1	TPSI3050QDWZRQ1	AMC131M03QDFMRQ1	AMC3311QDWERQ1
Automotive Grade Level	Grade 1	Grade 1	Grade 1	Grade 1	Grade 1
Operating Temp Range (C)	-40 to 125	-40 to 125	-40 to 125	-40 to 125	-40 to 125
Product Function	Power Management	Power Management	Power Management	Signal Chain	Signal Chain
Wafer Fab Supplier	RFAB, RFAB	RFAB	RFAB, RFAB	DMOS6, MH8, MH8	MH8, AIZU, AIZU, MH8
Assembly Site	TAI	UTL2	TAI	TAI	TAI
Package Group	SOIC	SOT	SOIC	SOIC	SOIC
Package Designator	DWZ	DBV	DWZ	DFM	DWE
Pin Count	8	6	8	20	16

QBS: Qual By Similarity, also known as Generic Data
Qual Device TPSI3050SQDWZRQ1 is qualified at MSL3 260C

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Type	#	Test Spec	Min Lot Qty	SS / Lot	Test Name	Condition	Duration	Qual Device:	QBS Process Reference:	QBS Package, Process, Product Reference:	QBS Package Reference:	QBS Package Reference:
								TPSI3050SQDWZRQ1	LM74700QDBVRQ1	TPSI3050QDWZRQ1	AMC131M03QDFMRQ1	AMC3311QDWERQ1
Test Group A - Accelerated Environment Stress Tests												
PC	A1	JEDEC J-STD-020 JESD22-A113	3	77	Preconditioning	MSL3 260C	-	No Fails	-	No Fails	No Fails	No Fails
HAST	A2	JEDEC JESD22-A110	3	77	Biased HAST	110C/85%RH	264 Hours	-	-	3/231/0	3/231/0	1/77/0
AC/UHAST	A3	JEDEC JESD22-A102/JEDEC JESD22-A118	3	77	Unbiased HAST	110C/85%RH	264 Hours	-	-	3/231/0	3/231/0	3/231/0
TC	A4	JEDEC JESD22-A104 and Appendix 3	3	77	Temperature Cycle	-55C/150C	1000 Cycles	1/77/0	-	3/231/0	-	-
TC	A4	JEDEC JESD22-A104 and Appendix 3	3	77	Temperature Cycle	-65C/150C	500 Cycles	-	-	-	3/231/0	3/231/0
TC-BP	A4	MIL-STD883 Method 2011	1	5	Post Temp Cycle Bond Pull	-	-	1/5/0	-	1/5/0	1/5/0	1/5/0
HTSL	A6	JEDEC JESD22-A103	1	45	High Temperature Storage Life	150C	1000 Hours	-	-	3/231/0	-	-
HTSL	A6	JEDEC JESD22-A103	1	45	High Temperature Storage Life	175C	500 Hours	-	-	-	3/135/0	1/45/0
Test Group B - Accelerated Lifetime Simulation Tests												
HTOL	B1	JEDEC JESD22-A108	3	77	Life Test	125C	1000 Hours	-	-	3/231/0	-	-
HTOL	B1	JEDEC JESD22-A108	3	77	Life Test	150C	408 Hours	-	3/231/0	-	-	-
ELFR	B2	AEC Q100-008	3	800	Early Life Failure Rate	150C	24 Hours	-	3/2400/0	-	-	-
Test Group C - Package Assembly Integrity Tests												
WBS	C1	AEC Q100-001	1	30	Wire Bond Shear	Minimum of 5 devices, 30 wires Cpk>1.67	Wires	1/30/0	-	3/90/0	-	3/90/0

WBP	C2	MIL-STD883 Method 2011	1	30	Wire Bond Pull	Minimum of 5 devices, 30 wires Cpk>1.67	Wires	1/30/0	-	3/90/0	-	3/90/0
SD	C3	JEDEC J-STD-002	1	15	PB Solderability	>95% Lead Coverage	-	-	-	1/15/0	1/15/0	-
SD	C3	JEDEC J-STD-002	1	15	PB-Free Solderability	>95% Lead Coverage	-	-	-	1/15/0	1/15/0	-
PD	C4	JEDEC JESD22-B100 and B108	3	10	Physical Dimensions	Cpk>1.67	-	-	-	3/30/0	-	3/30/0
Test Group D - Die Fabrication Reliability Tests												
EM	D1	JESD61	-	-	Electromigration	-	-	Completed Per Process Technology Requirements				
TDD	D2	JESD35	-	-	Time Dependent Dielectric Breakdown	-	-	Completed Per Process Technology Requirements				
HCI	D3	JESD60 & 28	-	-	Hot Carrier Injection	-	-	Completed Per Process Technology Requirements				
BTI	D4	-	-	-	Bias Temperature Instability	-	-	Completed Per Process Technology Requirements				
SM	D5	-	-	-	Stress Migration	-	-	Completed Per Process Technology Requirements				
Test Group E - Electrical Verification Tests												
ESD	E2	AEC Q100-002	1	3	ESD HBM	-	2000 Volts	-	1/3/0	1/3/0	-	-
ESD	E3	AEC Q100-011	1	3	ESD CDM	-	500 Volts	-	1/3/0	1/3/0	-	-
LU	E4	AEC Q100-004	1	3	Latch-Up	Per AEC Q100-004	-	-	1/6/0	1/6/0	-	-
ED	E5	AEC Q100-009	3	30	Electrical Distributions	Cpk>1.67 Room, hot, and cold	-	1/30/0	1/30/0	3/90/0	-	-

Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable

The following are equivalent HTOL options based on an activation energy of 0.7eV : 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours

The following are equivalent HTSL options based on an activation energy of 0.7eV : 150C/1k Hours, and 170C/420 Hours

The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles

Ambient Operating Temperature by Automotive Grade Level:

Grade 0 (or E): -40C to +150C

Grade 1 (or Q): -40C to +125C

Grade 2 (or T): -40C to +105C

Grade 3 (or I) : -40C to +85C

E1 (TEST): Electrical test temperatures of Qual samples (High temperature according to Grade level):

Room/Hot/Cold : HTOL, ED

Room/Hot : THB / HAST, TC / PTC, HTSL, ELFR, ESD & LU

Room : AC/uHAST

Quality and Environmental data is available at TI's external Web site: <http://www.ti.com/>

TI Qualification ID: R-CHG-2312-049

In performing change qualifications, Texas Instruments follows integrated circuit industry standards in performing defect mechanism analysis and failure mechanism-based accelerated environmental testing to ensure wafer fab process, assembly process and product quality and reliability. As encouraged by these standards, TI uses both product-specific and generic (family) data in qualifying its changes. For devices to be categorized as a 'product qualification family' for generic data purposes, they must share similar product, wafer fab process and assembly process elements. The applicability of generic data (also known at TI as Qualification by Similarity (QBS)) is determined by the Reliability Engineering function following these industry standards. Generic data is shown in the qualification report in columns titled "QBS Process" (for wafer fab process), "QBS Package" (for assembly process) and "QBS Product" (for product family).

For questions regarding this notice, e-mails can be sent to the Change Management team or your local Field Sales Representative.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.