



**12500 TI Boulevard, MS 8640, Dallas, Texas 75243**

**PCN#20240227005.1**

**Qualification of Cu as an alternate bond wire & die coat for select devices  
Change Notification / Sample Request**

**Date:** February 27, 2024

**To:** Mouser PCN

Dear Customer:

This is an announcement of a change to a device that is currently offered by Texas Instruments. The details of this change are on the following pages.

Texas Instruments requires acknowledgement of receipt of this notification within **30** days of the date of this notice. Lack of acknowledgement of this notice within 30 days constitutes acceptance and approval of this change. If samples or additional data are required, requests must be received within **30 days** of this notification.

The changes discussed within this PCN will not take effect any earlier than the proposed first ship date on Page 3 of this notification, unless customer agreement has been reached on an earlier implementation of the change.

This notice does not change the end-of-life status of any product. Should product affected be on a previously issued product withdrawal/discontinuance notice, this notification does not extend the life of that product or change the life time buy offering/discontinuance plan.

For questions regarding this notice or to provide acknowledgement of this PCN, you may contact your local Field Sales Representative or the change management team.

For sample requests or sample related questions, contact your local Field Sales Representative.

Sincerely,

Change Management Team  
SC Business Services

**20240227005.1**  
**Change Notification / Sample Request**  
**Attachments**

**Products Affected:**

The devices listed on this page are a subset of the complete list of affected devices. According to our records, you have recently purchased these devices. The corresponding customer part number is also listed, if available.

<b>DEVICE</b>	<b>CUSTOMER PART NUMBER</b>
LMP8640MKX-T/NOPB	NULL
TPL5010DDCR	NULL
TPL5010DDCT	NULL
TPL5110DDCR	NULL
TPS62162DSGT	NULL

Technical details of this Product Change follow on the next page(s).

<b>PCN Number:</b>	20240227005.1			<b>PCN Date:</b>	February 27, 2024									
<b>Title:</b>	Qualification of Cu as an alternate bond wire & die coat for select devices													
<b>Customer Contact:</b>	Change Management Team		<b>Dept:</b>	Quality Services										
<b>Proposed 1<sup>st</sup> Ship Date:</b>	May 27, 2024		<b>Sample Requests accepted until:</b>	March 28, 2024*										
<b>*Sample requests received after March 28, 2024 will not be supported.</b>														
<input type="checkbox"/>	Assembly Site	<input type="checkbox"/>	Design	<input type="checkbox"/>	Wafer Bump Material									
<input checked="" type="checkbox"/>	Assembly Process	<input type="checkbox"/>	Data Sheet	<input type="checkbox"/>	Wafer Bump Process									
<input checked="" type="checkbox"/>	Assembly Materials	<input type="checkbox"/>	Part number change	<input type="checkbox"/>	Wafer Fab Site									
<input type="checkbox"/>	Mechanical Specification	<input type="checkbox"/>	Test Site	<input type="checkbox"/>	Wafer Fab Material									
<input type="checkbox"/>	Packing/Shipping/Labeling	<input type="checkbox"/>	Test Process	<input type="checkbox"/>	Wafer Fab Process									
<b>PCN Details</b>														
<b>Description of Change:</b>														
This PCN is to inform of an alternative bond wire & die coat qualification for the devices in the product affected section as follows:														
<b>Group 1 Devices: Bond wire and die coat change</b>														
<table border="1"> <thead> <tr> <th>What</th> <th>Current</th> <th>Additional</th> </tr> </thead> <tbody> <tr> <td><b>Current Bond wire, Diameter</b></td> <td><b>Au, 1.0 mils</b></td> <td><b>Cu, 0.96 mil</b></td> </tr> <tr> <td><b>Die Coat</b></td> <td><b>BCB</b></td> <td><b>PI</b></td> </tr> </tbody> </table>						What	Current	Additional	<b>Current Bond wire, Diameter</b>	<b>Au, 1.0 mils</b>	<b>Cu, 0.96 mil</b>	<b>Die Coat</b>	<b>BCB</b>	<b>PI</b>
What	Current	Additional												
<b>Current Bond wire, Diameter</b>	<b>Au, 1.0 mils</b>	<b>Cu, 0.96 mil</b>												
<b>Die Coat</b>	<b>BCB</b>	<b>PI</b>												
<b>Group 2 Devices: Bond wire only change</b>														
<table border="1"> <thead> <tr> <th>What</th> <th>Current</th> <th>Additional</th> </tr> </thead> <tbody> <tr> <td><b>Current Bond wire, Diameter</b></td> <td><b>Au, 0.96 mil</b></td> <td><b>Cu, 1.0 mil</b></td> </tr> </tbody> </table>						What	Current	Additional	<b>Current Bond wire, Diameter</b>	<b>Au, 0.96 mil</b>	<b>Cu, 1.0 mil</b>			
What	Current	Additional												
<b>Current Bond wire, Diameter</b>	<b>Au, 0.96 mil</b>	<b>Cu, 1.0 mil</b>												
<b>Reason for Change:</b>														
Continuity of supply.														
<ol style="list-style-type: none"> <li>1) To align with world technology trends and use wiring with enhanced mechanical and electrical properties</li> <li>2) Maximize flexibility within our Assembly/Test production sites.</li> <li>3) Cu is easier to obtain and stock</li> </ol>														
<b>Anticipated impact on Form, Fit, Function, Quality or Reliability (positive / negative):</b>														
None														
<b>Impact on Environmental Ratings</b>														
Checked boxes indicate the status of environmental ratings following implementation of this change. If below boxes are checked, there are no changes to the associated environmental ratings.														
<b>RoHS</b>		<b>REACH</b>	<b>Green Status</b>	<b>IEC 62474</b>										
<input checked="" type="checkbox"/> No Change		<input checked="" type="checkbox"/> No Change	<input checked="" type="checkbox"/> No Change	<input checked="" type="checkbox"/> No Change										
<b>Changes to product identification resulting from this PCN:</b>														
None														

## Product Affected:

### Group 1 Device list:

LMP8640HVMKX-F/NOPB	LMP8640MKX-H/NOPB	TPL5010DDCR	TPL5110DDCR
LMP8640HVMKX-H/NOPB	LMP8640MKX-T/NOPB	TPL5010DDCT	TPL5110DDCT
LMP8640HVMKX-T/NOPB			

### Group 2 Device List

TPS62162DSGT

TI Information  
Selective Disclosure

## Group 1 Qual Memo:

### Qualification Report

**SOT23 6DDC 0.96mil Cu on ABCD150 & CMOS9T DAF+Spincoat Devices**  
Approve Date 05-JANUARY -2024

### Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Type	#	Test Name	Condition	Duration	Qual Device: <a href="#">TPL5010DDCR</a>	Qual Device: <a href="#">LMP8640HVMK-F/NOPB</a>	QBS Reference: <a href="#">LMP7711MK/NOPB</a>	QBS Reference: <a href="#">LM041AIM3X-1.2/NOPB</a>	QBS Reference: <a href="#">LMC7101AIM5/NOPB</a>	QBS Reference: <a href="#">LMV7275MG/NOPB</a>	QBS Reference: <a href="#">LMP8640QMKX-T/NOPB</a>
HAST	A2	Biased HAST	130C/85%RH	96 Hours	-	-	-	3/231/0	3/231/0	-	3/231/0
UHAST	A3	Autoclave	121C/15psig	96 Hours	3/231/0	3/231/0	3/231/0	3/231/0	3/231/0	-	3/231/0
TC	A4	Temperature Cycle	-65C/150C	500 Cycles	3/231/0	3/231/0	3/231/0	3/231/0	3/231/0	1/77/0	3/231/0
HTSL	A6	High Temperature Storage Life	150C	1000 Hours	3/231/0	-	-	1/77/0	1/77/0	1/77/0	3/231/0
HTOL	B1	Life Test	125C	1000 Hours	-	-	-	-	-	-	3/231/0
CHAR	E5	Electrical Characterization	Per Datasheet Parameters	-	1/30/0	1/30/0	2/60/0	1/30/0	1/30/0	3/90/0	1/30/0

- QBS: Qual By Similarity
- Qual Device TPL5010DDCR is qualified at MSL1 260C
- Qual Device LMP8640HVMK-F/NOPB is qualified at MSL1 260C
- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV: 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47: -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: <http://www.ti.com/>

TI Qualification ID: R-CHG-2207-052

## Group 2 Qual Memo:

### Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Type	Test Name / Condition	Duration	Qual Device: <a href="#">TPS62172DSGR</a>	QBS Product Reference: <a href="#">TPS62162DSGR</a>	QBS Product Reference: <a href="#">TPS62160DSGR</a>	QBS Package Reference: <a href="#">TPS65680RSN</a>	QBS Process Reference: <a href="#">TPS62110RSA</a>
ED	Electrical Characterization	Per Datasheet Parameters	-	Pass	Pass	Pass	Pass
HBM	ESD - HBM	3000 V	-	-	1/3/0	2/6/0	-
CDM	ESD - CDM	1500 V	-	-	1/3/0	2/6/0	-
LU	Latch-up	(Per JESD78)	-	-	1/6/0	2/12/0	3/15/0
HTOL	Life Test, 150C	300 Hours	-	-	-	3/231/0	-
HTOL	Life Test, 140C	480 Hours	-	-	-	-	3/231/0
HTOL	Life Test, 125C	1000 Hours	-	-	-	-	-
ELFR	Early Life Failure Rate, 140C	48 Hours	-	-	-	-	3/1881/0
HTSL	High Temp Storage Bake, 170C	420 Hours	-	-	-	2/154/0	3/231/0
HTSL	High Temp Storage Bake, 150C	1000 Hours		-	-	1/77/0	-
HAST	Biased HAST, 130C/85%RH	96 Hours	-	-	-	3/231/0	3/231/0
UHAST	Unbiased HAST, 130C/85%RH	96 Hours	-	-	-	3/231/0	-
AC	Autoclave 121C	96 Hours	-	-	-	-	3/231/0
TC	Temperature Cycle, -65/150C	500 Cycles	-	-	-	3/231/0	-
TC	Temperature Cycle, -55/125C	700 Cycles	-	-	-	-	3/231/0
FTY	Final Test Yield	-	Pass	-	-	-	-
MQ	Manufacturability (Assembly)	(per mfg. Site specification)	Pass	Pass	-	-	-

- QBS: Qual By Similarity

- Qual Device [TPS62172DSGR](#) is qualified at MSL2 280C

- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable

- The following are equivalent HTOL options based on an activation energy of 0.7eV: 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours

- The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours

- The following are equivalent Temp Cycle options per JESD47: -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: <http://www.ti.com/>

#### Green/Pb-free Status:

Qualified Pb-Free(SMT) and Green

TI Qualification ID: R-CHG-2202-061

For questions regarding this notice, e-mails can be sent to Change Management team or your local Field Sales Representative.

### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF

MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale ([www.ti.com/legal/termsofsale.html](http://www.ti.com/legal/termsofsale.html)) or other applicable terms available either on [ti.com](http://ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.