



12500 TI Boulevard, MS 8640, Dallas, Texas 75243

PCN#20240723000.1

**Qualification of RFAB using qualified Process Technology & Die Revision options for
select devices
Change Notification / Sample Request**

Date: July 23, 2024
To: MOUSER PCN

Dear Customer:

This is an announcement of a change to a device that is currently offered by Texas Instruments (TI). The details of this change are on the following pages, and are in alignment with our standard product change notification (PCN) [process](#).

TI requires acknowledgement of receipt of this notification within 30 days of the date of this notice. Lack of acknowledgement of this notice within 30 days constitutes acceptance and approval of this change. If samples or additional data are required, requests must be received within 30 days of this notification, given that samples are not built ahead of the change.

The Proposed First Ship date in this PCN letter is the earliest possible date that customers could receive the changed material. It is our commitment that the changed device will not ship before that date. If samples are requested within the 30 day sample request window, customers will still have 30-days to complete their evaluation regardless of the proposed 1st ship date.

This particular PCN is related to TI's multiyear transition plan for our two remaining factories with 150-millimeter production (DFAB in Dallas, Texas, and SFAB in Sherman, Texas). DFAB will remain open, but will focus on 200-mm production, with a smaller set of technologies. SFAB will close no earlier than 2024 and no later than 2025. As referenced in the "reason for change" below, these changes are part of our multiyear plan to transition these products to newer, more efficient manufacturing processes and technologies, underscoring our commitment to product longevity and supply continuity.

For questions regarding this notice or to provide acknowledgement of this PCN, you may contact your local Field Sales Representative or the Change Management team. For sample requests or sample related questions, contact your local Field Sales Representative. As always, we thank you for your continued business.

Change Management Team
SC Business Services

20240723000.1
Attachment: 1

Products Affected:

The devices listed on this page are a subset of the complete list of affected devices. According to our records, you have recently purchased these devices. The corresponding customer part number is also listed, if available.

DEVICE	CUSTOMER PART NUMBER
MAX211IDBR	NULL
TRS213IDBR	NULL

Technical details of this Product Change follow on the next page(s).

PCN Number:	20240723000.1	PCN Date:	July 23, 2024	
Title:	Qualification of RFAB using qualified Process Technology & Die Revision options for select devices			
Customer Contact:	Change Management Team	Dept:	Quality Services	
Proposed 1st Ship Date:	October 21, 2024	Sample requests accepted until:	August 22, 2024*	
*Sample requests received after August 22, 2024 will not be supported.				
Change Type:				
<input type="checkbox"/>	Assembly Site	<input checked="" type="checkbox"/>	Design	
<input type="checkbox"/>	Assembly Process	<input checked="" type="checkbox"/>	Data Sheet	
<input type="checkbox"/>	Assembly Materials	<input type="checkbox"/>	Part number change	
<input type="checkbox"/>	Mechanical Specification	<input type="checkbox"/>	Test Site	
<input checked="" type="checkbox"/>	Packing/Shipping/Labeling	<input type="checkbox"/>	Test Process	
<input type="checkbox"/>		<input type="checkbox"/>	Wafer Bump Material	
<input type="checkbox"/>		<input type="checkbox"/>	Wafer Bump Process	
<input checked="" type="checkbox"/>		<input checked="" type="checkbox"/>	Wafer Fab Site	
<input checked="" type="checkbox"/>		<input checked="" type="checkbox"/>	Wafer Fab Material	
<input checked="" type="checkbox"/>		<input checked="" type="checkbox"/>	Wafer Fab Process	
PCN Details				
Description of Change:				
Texas Instruments is pleased to announce the qualification of its RFAB fabrication facility as an additional Wafer Fab option plus new die revision for the devices listed below.				
Current Fab Site		Additional Fab Site		
Fab Site	Process	Wafer Diameter	Fab Site	Process
SFAB	LBC3S	150 mm	RFAB	LBC7
				Wafer Diameter
				300 mm
The die was also changed as a result of the process change.				
Qual details are provided in the Qual Data Section.				
Reason for Change:				
These changes are part of our multiyear plan to transition products from our 150-millimeter factories to newer, more efficient manufacturing processes and technologies, underscoring our commitment to product longevity and supply continuity.				
Anticipated impact on Form, Fit, Function, Quality or Reliability (positive / negative):				
None				
Impact on Environmental Ratings:				
Checked boxes indicate the status of environmental ratings following implementation of this change. If below boxes are checked, there are no changes to the associated environmental ratings.				
RoHS	REACH	Green Status	IEC 62474	
<input checked="" type="checkbox"/> No Change	<input checked="" type="checkbox"/> No Change	<input checked="" type="checkbox"/> No Change	<input checked="" type="checkbox"/> No Change	
Changes to product identification resulting from this PCN:				
Fab Site Information:				
Chip Site	Chip Site Origin Code (20L)	Chip Site Country Code (21L)	Chip Site City	
SH-BIP-1	SHE	USA	Sherman	
RFAB	RFB	USA	Richardson	
Die Rev:				

Current

New

Die Rev [2P]	Die Rev [2P]
A, -	-

Sample product shipping label (not actual product label):

TEXAS INSTRUMENTS
 MADE IN: Malaysia
 2DC: 2Q:
 MSL 2 /260C/1 YEAR SEAL DT
 MSL 1 /235C/UNLIM 03/29/04
 OPT:
 ITEM: 39
LBL: 5A (L)T0:1750
 (1P) SN74LS07NSR
 (Q) 2000 (D) 0336
 (31T) LOT: 3959047MLA
 (4W) TKY (1T) 7523483SI2
 (P)
 (2P) REV: (V) 0053317
 (20L) CSO: SHE (21L) CCO:USA
 (22L) ASO: MLA (23L) ACO: MYS

Product Affected:

MAX211IDBR	MAX211IDBRG4	TRS208IDBR	TRS213IDBR
------------	--------------	------------	------------

For alternate parts with similar or improved performance, please visit the product page on TI.com



TI Information
Selective Disclosure

Qualification Report
Approve Date 18-July-2024

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Type	#	Test Name	Condition	Duration	Qual Device: TRS213IDBR	Qual Device: MAX211IDBR	QBS Reference: TCAN1043DQ1	QBS Reference: TPS2074DB	QBS Reference: TPS652510QRHARQ1
HAST	A2	Biased HAST	110C/85%RH	264 Hours	-	-	-	-	3/231/0
HAST	A2	Biased HAST	130C/85%RH	96 Hours	-	-	3/231/0	-	-
UHAST	A3	Autoclave	121C/15psig	96 Hours	-	-	3/231/0	-	-
UHAST	A3	Unbiased HAST	110C/85%RH	264 Hours	-	-	-	-	3/231/0
UHAST	A3	Unbiased HAST	130C/85%RH	96 Hours	-	-	-	3/231/0	-
TC	A4	Temperature Cycle	-65C/150C	500 Cycles	-	-	-	3/231/0	-
HTSL	A6	High Temperature Storage Life	150C	1000 Hours	-	-	-	3/231/0	3/135/0
HTSL	A6	High Temperature Storage Life	175C	500 Hours	-	-	1/45/0	-	-
HTOL	B1	Life Test	125C	1000 Hours	-	-	1/77/0	-	3/231/0
ELFR	B2	Early Life Failure Rate	125C	48 Hours	-	-	-	-	3/2400/0
SD	C3	PB Solderability	Precondition w.155C Dry Bake (4 hrs +/- 15 minutes)	-	-	-	1/15/0	-	-

Type	#	Test Name	Condition	Duration	Qual Device: TRS213IDBR	Qual Device: MAX211IDBR	QBS Reference: TCAN1043DQ1	QBS Reference: TPS2074DB	QBS Reference: TPS652510QRHARQ1
SD	C3	PB-Free Solderability	Precondition w.155C Dry Bake (4 hrs +/- 15 minutes)	-	-	-	1/15/0	-	1/15/0
PD	C4	Physical Dimensions	Cpk>1.67	-	-	-	3/30/0	-	3/30/0
ESD	E2	ESD CDM	-	1500 Volts	1/3/0	-	-	-	-
ESD	E2	ESD CDM	-	500 Volts	-	-	-	-	1/3/0
ESD	E2	ESD HBM	-	15000 Volts	1/3/0	-	-	-	-
ESD	E2	ESD HBM	-	2000 Volts	-	-	-	-	1/3/0
ESD	E2	ESD HBM	-	3000 Volts	1/3/0	-	-	-	-
LU	E4	Latch-Up	Per JESD78	-	1/3/0	-	-	-	1/3/0
CHAR	E5	Electrical Characterization	Per Datasheet Parameters	-	1/30/0	1/30/0	-	-	-
CHAR	E5	Electrical Distributions	Cpk>1.67 Room, hot, and cold	-	-	-	1/30/0	-	3/90/0

- QBS: Qual By Similarity
- Qual Device TRS213IDBR is qualified at MSL1 260C

- Qual Device MAX211IDBR is qualified at MSL1 260C
- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV : 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV : 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: <http://www.ti.com/>

TI Qualification ID: R-CHG-2302-011

Qualification Report

RedBull RS232-9V_Wave2 Core (TRS208IDBR)
Approve Date 16-April-2024

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Type	#	Test Name	Condition	Duration	Qual Device: TRS208IDBR	QBS Reference (Process): TPSS51217DSCR	QBS Reference (Package): TLC320AD77CDBR	QBS Reference (Package, Process): TRS3243EIDBR	QBS Reference (Product): MAX232EIDR
UFAST	A3	Autoclave	121C/15psig	96 Hours	-	-	-	1/77/0	-
UFAST	A3	Unbiased HAST	130C/85%RH	96 Hours	-	-	3/231/0	-	-
TC	A4	Temperature Cycle	-65C/150C	500 Cycles	-	-	3/231/0	1/77/0	-
HTSL	A6	High Temperature Storage Life	150C	1000 Hours	-	-	3/231/0	-	-
HTOL	B1	Life Test	135C	635 Hours	-	3/231/0	-	-	-
WBS	C1	Ball Shear	76 balls, 3 units min	Wires	-	-	-	1/76/0	-
WBP	C2	Bond Pull	76 Wires, 3 units min	Wires	-	-	-	1/76/0	-
ESD	E2	ESD CDM	-	1500 Volts	1/3/0	-	-	-	1/3/0
ESD	E2	ESD HBM (Bus Pins)	-	15000 Volts	1/3/0	-	-	-	1/3/0
ESD	E2	ESD HBM	-	3000 Volts	1/3/0	-	-	-	1/3/0
LU	E4	Latch-Up	Per JESD78	-	1/6/0	-	-	-	1/6/0

Type	#	Test Name	Condition	Duration	Qual Device: TRS208IDBR	QBS Reference (Process): TPSS51217DSCR	QBS Reference (Package): TLC320AD77CDBR	QBS Reference (Package, Process): TRS3243EIDBR	QBS Reference (Product): MAX232EIDR
CHAR	E5	Electrical Characterization	Per Datasheet Parameters	-	1/30/0	-	-	-	1/30/0

- QBS: Qual By Similarity
- Qual Device TRS208IDBR is qualified at MSL1 260C
- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV : 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV : 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: <http://www.ti.com/>

TI Qualification ID: R-CHG-2403-042

For questions regarding this notice, e-mails can be sent to the Change Management team or your local Field Sales Representative.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.