



**12500 TI Boulevard, MS 8640, Dallas, Texas 75243**

**PCN# 20250730004.1**

**Qualification of RFAB using qualified Process Technology, Die Revision, Datasheet  
and BOM options for select devices  
Change Notification / Sample Request**

**Date:** July 31, 2025

**To:** Mouser PCN

Dear Customer:

This is an announcement of a change to a device that is currently offered by Texas Instruments (TI). The details of this change are on the following pages, and are in alignment with our standard product change notification (PCN) [process](#).

TI requires acknowledgement of receipt of this notification within 60 days of the date of this notice. Lack of acknowledgement of this notice within 60 days constitutes acceptance and approval of this change. If samples or additional data are required, requests must be received within 60 days of this notification, given that samples are not built ahead of the change.

The Proposed First Ship date in this PCN letter is the earliest possible date that customers could receive the changed material. It is our commitment that the changed device will not ship before that date. If samples are requested within the 60 day sample request window, customers will still have 30-days to complete their evaluation regardless of the proposed 1st ship date.

Changes outlined in this notification underscore our commitment to product longevity and supply continuity, as well as our continued efforts to transition to newer, more efficient manufacturing processes and technologies. Specifically, this particular notification is related to TI's multiyear transition plan for our two remaining 150-millimeter production lines (DFAB in Dallas, Texas, and SFAB in Sherman, Texas). SFAB closure activities are expected to begin by the end of 2025. DFAB will remain open with a smaller set of 200mm technologies and GaN.

For questions regarding this notice or to provide acknowledgement of this PCN, you may contact your local Field Sales Representative or the Change Management team. For sample requests or sample related questions, contact your local Field Sales Representative. As always, we thank you for your continued business.

TI values customer engagement and feedback related to TI changes. Customers should contact TI if there are questions or concerns regarding a change notification.

Change Management Team  
SC Business Services

**20250730004.1**  
**Attachment: 1**

**Products Affected:**

The devices listed on this page are a subset of the complete list of affected devices. According to our records, you have recently purchased these devices. The corresponding customer part number is also listed, if available.

<b>DEVICE</b>	<b>CUSTOMER PART NUMBER</b>
TLE2141CDR	NULL
TLE2142CPWR	NULL
TLE2142CP	TLE2142CP
TLE2141AIDR	NULL
TLE2142ACDR	595-TLE2142ACDR
TLE2142AIDR	NULL
TLE2141CP	NULL
TLE2142AMDR	NULL
TLE2141IP	NULL
TLE2142IP	NULL
TLE2141IDR	NULL
TLE2142MDR	NULL
TLE2142CDR	NULL
TLE2142IDR	NULL

Technical details of this Product Change follow on the next page(s).

<b>PCN Number:</b>	20250730004.1	<b>PCN Date:</b>	July 31, 2025
<b>Title:</b>	Qualification of RFAB using qualified Process Technology, Die Revision, Datasheet and BOM options for select devices		
<b>Customer Contact:</b>	Change Management Team	<b>Dept:</b>	Quality Services
<b>Proposed 1<sup>st</sup> Ship Date:</b>	October 29, 2025	<b>Sample requests accepted until:</b>	September 29, 2025*
<b>*Sample requests received after September 29, 2025 will not be supported.</b>			
<b>Change Type:</b>			
<input checked="" type="checkbox"/> Assembly Site	<input checked="" type="checkbox"/> Design	<input type="checkbox"/>	Wafer Bump Material
<input checked="" type="checkbox"/> Assembly Process	<input checked="" type="checkbox"/> Data Sheet	<input type="checkbox"/>	Wafer Bump Process
<input type="checkbox"/> Assembly Materials	<input type="checkbox"/> Part number change	<input checked="" type="checkbox"/>	Wafer Fab Site
<input type="checkbox"/> Mechanical Specification	<input type="checkbox"/> Test Site	<input checked="" type="checkbox"/>	Wafer Fab Material
<input checked="" type="checkbox"/> Packing/Shipping/Labeling	<input type="checkbox"/> Test Process	<input checked="" type="checkbox"/>	Wafer Fab Process

### PCN Details

#### Description of Change:

Texas Instruments is pleased to announce the addition of RFAB using the TIB qualified process technology, and assembly BOM options for the devices listed below.

Current Fab Site			Additional Fab Site		
Current Fab Site	Process	Wafer Diameter	Additional Fab Site	Process	Wafer Diameter
DL-LIN-2	EXCAL2	150 mm	RFAB	TIB	300 mm

The die was also changed as a result of the process change.

Construction differences are as follows:

#### Group 1

	<b>Current</b>	<b>Proposed</b>
Assembly site/ Test	FMX/ TAI	MLA
Bond wire diam/type	0.96 mil Cu	0.8 mil Cu
Die thickness	10.5 mil	7.5 mil

#### Group 2

	<b>Current</b>	<b>Proposed</b>
Assembly site/ Test	FMX	FMX
Bond wire diam/type	0.96 mil Cu	0.8 mil Cu
Die thickness	10.5 mil	7.5 mil

The datasheets will be changing as a result of the above mentioned changes. The datasheet change details can be reviewed in the datasheet revision history. For additional information, the standard data package (SDP) should be requested. The request can be sent to [pcn\\_ww\\_admin\\_team@list.ti.com](mailto:pcn_ww_admin_team@list.ti.com)

<b>Changes from Revision D (October 2012) to Revision E (July 2025)</b>		<b>Page</b>
• Updated the numbering format for tables, figures, and cross-references throughout the document.....	1	
• Changed pins 1 and 5 from OFFSET N1 to NC and OFFSET N2 to NC for TLE2141 D, JG, and P package pinouts.....	3	
• Changed typical settling time specification across all devices from 0.34µs (0.1%, ±15V V <sub>S</sub> ) to 0.43µs, 0.4µs (0.01%, ±15V V <sub>S</sub> ) to 0.64µs, 0.16µs (0.1%, 5V V <sub>S</sub> ) to 0.66µs, and 0.22µs (0.01%, 5V V <sub>S</sub> ) to 0.99µs.....	4	
• Changed typical THD+N specification at ±15V V <sub>S</sub> across all devices from 0.01% to 0.06%.....	4	
• Changed typical maximum output bandwidth specification at 5V V <sub>S</sub> across all devices from 660kHz to 380kHz.....	4	

The links to the revised datasheets are available in the table below:

<b>Product Folder</b>	<b>Current Datasheet Number</b>	<b>New Datasheet Number</b>	<b>Link to full datasheet</b>
TLE2141	SLOS183D	<b>SLOS183E</b>	<a href="http://www.ti.com/product/TLE2141">http://www.ti.com/product/TLE2141</a>

Qual details are provided in the Qual Data Section.

**Reason for Change:**

These changes are part of our multiyear plan to transition products from our 200-millimeter factories to newer, more efficient manufacturing processes and technologies, underscoring our commitment to product longevity and supply continuity.

**Anticipated impact on Form, Fit, Function, Quality or Reliability (positive / negative):**

None

**Changes to product identification resulting from this PCN:**

**Fab Site**

**Information:**

**Group 1 and 2**

Chip Site	Chip Site Origin Code (20L)	Chip Site Country Code (21L)	Chip Site City
DL-LIN	DLN	USA	Dallas
<b>RFAB</b>	<b>RFB</b>	<b>USA</b>	<b>Richardson</b>

**Die Rev:**

**Current** **New**

Die Rev [2P]	<b>Die Rev [2P]</b>
B	<b>C</b>

Assembly Site	Assembly Site Origin (22L)	Assembly Country Code (23L)	Assembly City
TAI	TAI	TWN	Chung Ho, New Taipei City
<b>FMX</b>	<b>MEX</b>	<b>MEX</b>	<b>Aguascalientes</b>

Sample product shipping label (not actual product label):

 <b>TEXAS INSTRUMENTS</b> MADE IN: Malaysia 2DC: 29 MSL 2 / 260C / 1 YEAR MSL 1 / 235C / UNLIM OPT: ITEM: 39 <b>LBL: 5A (L)T0:1750</b>	 	<b>(1P) SN74LS07NSR</b> <b>(Q) 2000 (D) 0336</b> <b>(31T) LOT: 3959047MLA</b> <b>(4W) TKY(1T) 7523483SI2</b> <b>(P)</b> <b>(2P) REV: (V) 0053317</b> <b>(20L) CS0: SHE (21L) CCO:USA</b> <b>(22L) AS0: MLA (23L) ACO: MYS</b>	
<b>Product Affected- Group 1:</b>			
TLE2141IDR	TLE2141AIDR	TLE2141CDR	TLE2142IDR
TLE2142ACDR	TLE2142AIDR	TLE2142CDR	TLE2142AMDR
TLE2142MDR			
<b>Product Affected- Group 2:</b>			
TLE2142IP	TLE2142CP		

For alternate parts with similar or improved performance, please visit the product page on [TI.com](http://TI.com)

#### Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Type	#	Test Name	Condition	Duration	Qual Device: TLE2141IDR	QBS Process Reference: TIBQEV231UM0	QBS Package Reference: U1Q2003AQR0Q1	QBS Package Reference: LM2901BQR0Q1	QBS Package Reference: OPA2991QDR0Q1	QBS Package Reference: LM2903BQR0Q1	QBS Package Reference: LM2901QDR0Q1
HAST	A2	Biased HAST	130C/85%RH	96 Hours	-	-	3/231/0	1/77/0	3/231/0	1/77/0	1/77/0
UHAST	A3	Autoclave	121C/15psig	96 Hours	-	-	3/231/0	-	-	-	-
UHAST	A3	Unbiased HAST	130C/85%RH	96 Hours	-	-	-	1/77/0	3/231/0	1/77/0	1/77/0
TC	A4	Temperature Cycle	-65C/150C	500 Cycles	-	3/231/0	3/231/0	1/77/0	3/231/0	1/77/0	1/77/0
HTSL	A6	High Temperature Storage Life	150C	1000 Hours	-	1/45/0	3/135/0	-	3/135/0	-	-
HTSL	A6	High Temperature Storage Life	175C	500 Hours	-	-	-	1/77/0	-	1/45/0	1/77/0
HTOL	B1	Life Test	125C	1000 Hours	-	3/231/0	3/231/0	-	-	-	-
HTOL	B1	Life Test	150C	300 Hours	-	-	-	1/77/0	-	1/77/0	1/77/0
HTOL	B1	Life Test	150C	408 Hours	-	-	-	-	-	-	-
ELFR	B2	Early Life Failure Rate	125C	48 Hours	-	3/2400/0	-	-	-	-	-

Type	#	Test Name	Condition	Duration	Qual Device: <b>TLE2141IDR</b>	QBS Process Reference: <b>TIBQEVT23UM0</b>	QBS Package Reference: <b>ULQ2003AQDRQ1</b>	QBS Package Reference: <b>LM2901BQDRQ1</b>	QBS Package Reference: <b>OPA2991QDRQ1</b>	QBS Package Reference: <b>LM2903BQDRQ1</b>	QBS Package Reference: <b>LM2901QDRQ1</b>
SD	C3	PB Solderability	Precondition w.155C Dry Bake (4 hrs +/- 15 minutes)	-	-	-	1/15/0	1/15/0	-	1/15/0	1/15/0
SD	C3	PB-Free Solderability	Precondition w.155C Dry Bake (4 hrs +/- 15 minutes)	-	-	-	1/15/0	1/15/0	-	1/15/0	1/15/0
PD	C4	Physical Dimensions	Cpk>1.67	-	-	-	-	1/10/0	3/30/0	1/10/0	1/10/0
ESD	E2	ESD CDM	-	250 Volts	1/3/0	-	-	-	-	-	-
ESD	E2	ESD CDM	-	500 Volts	-	-	-	1/3/0	1/3/0	1/3/0	1/3/0
ESD	E2	ESD HBM	-	1000 Volts	1/3/0	-	-	-	-	-	-
ESD	E2	ESD HBM	-	2000 Volts	-	-	-	1/3/0	1/3/0	1/3/0	1/3/0
LU	E4	Latch-Up	Per JESD78	-	1/3/0	-	-	1/6/0	1/6/0	1/6/0	1/6/0
CHAR	E5	Electrical Characterization	Per Datasheet Parameters	-	1/30/0	-	3/90/0	1/30/0	3/90/0	1/30/0	1/30/0
CHAR	E5	Electrical Distributions	Cpk>1.67 Room, hot, and cold	-	-	-	3/90/0	1/30/0	3/90/0	1/30/0	1/30/0
FTY	E6	Final Test Yield	-	-	1/Pass	-	-	-	-	-	-

- QBS: Qual By Similarity, also known as Generic Data
- Qual Device TLE2141IDR is qualified at MSL1 260C

- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV : 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV : 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: <http://www.ti.com/>

TI Qualification ID: R-CHG-2405-015

### Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Type	#	Test Name	Condition	Duration	Qual Device: <b>TLE2142IDR</b>	QBS Reference: <b>ULQ2003AQDRQ1</b>	QBS Reference: <b>MC33063AQDRQ1</b>	QBS Reference: <b>OPA2991QDRQ1</b>
HAST	A2	Biased HAST	130C/85%RH	96 Hours	-	3/231/0	3/231/0	3/231/0
UHAST	A3	Autoclave	121C/15psig	96 Hours	-	3/231/0	-	-
UHAST	A3	Unbiased HAST	130C/85%RH	96 Hours	-	-	3/231/0	3/231/0
TC	A4	Temperature Cycle	-65C/150C	500 Cycles	-	3/231/0	3/231/0	3/231/0
HTSL	A6	High Temperature Storage Life	150C	1000 Hours	-	3/135/0	3/135/0	3/135/0
HTOL	B1	Life Test	125C	1000 Hours	-	3/231/0	3/231/0	-
HTOL	B1	Life Test	150C	408 Hours	-	-	-	1/77/1 <sup>1</sup>
ELFR	B2	Early Life Failure Rate	125C	48 Hours	-	-	3/2400/0	-
SD	C3	PB Solderability	Precondition w.155C Dry Bake (4 hrs +/- 15 minutes)	-	-	1/15/0	1/15/0	-
SD	C3	PB-Free Solderability	Precondition w.155C Dry Bake (4 hrs +/- 15 minutes)	-	-	1/15/0	1/15/0	-
PD	C4	Physical Dimensions	Cpk>1.67	-	-	-	3/30/0	3/30/0

Type	#	Test Name	Condition	Duration	Qual Device: <a href="#">TLE2142IDR</a>	QBS Reference: <a href="#">ULQ2003AQDRQ1</a>	QBS Reference: <a href="#">MC33063AQDRQ1</a>	QBS Reference: <a href="#">OPA2991QDRQ1</a>
ESD	E2	ESD CDM	-	250 Volts	1/3/0	-	-	-
ESD	E2	ESD CDM	-	500 Volts	-	-	1/3/0	1/3/0
ESD	E2	ESD HBM	-	1000 Volts	1/3/0	-	-	-
ESD	E2	ESD HBM	-	2000 Volts	-	-	1/3/0	1/3/0
LU	E4	Latch-Up	Per JESD78	-	-	-	1/6/0	1/6/0
CHAR	E5	Electrical Characterization		Per Datasheet Parameters	-	1/30/0	-	-
CHAR	E5	Electrical Distributions		Cpk>1.67 Room, hot, and cold	-	-	3/90/0	3/90/0

- QBS: Qual By Similarity, also known as Generic Data
- Qual Device TLE2142IDR is qualified at MSL1 260C
- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV : 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV : 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: <http://www.ti.com/>

TI Qualification ID: R-CHG-2404-085

#### Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Type	#	Test Name	Condition	Duration	Qual Device: <a href="#">TLE2142IP</a>	QBS Reference: <a href="#">NE5532P</a>	QBS Reference: <a href="#">TS12A4514P</a>	QBS Reference: <a href="#">UCC37322P</a>	QBS Reference: <a href="#">MC33063AQDRQ1</a>	QBS Reference: <a href="#">OP07CP</a>	QBS Reference: <a href="#">ULN2003AN</a>	QBS Reference: <a href="#">TLE2142IDR</a>
HAST	A2	Biased HAST	130C/85%RH	96 Hours	-	3/231/0	-	-	3/231/0	-	-	-
UHAST	A3	Autoclave	121C/15psig	96 Hours	-	-	1/77/0	3/231/0	-	-	-	-
UHAST	A3	Unbiased HAST	130C/85%RH	96 Hours	-	-	-	-	3/231/0	1/77/0	1/77/0	-
TC	A4	Temperature Cycle	-65C/150C	500 Cycles	-	-	1/77/0	3/231/0	3/231/0	1/77/0	1/77/0	-
HTSL	A6	High Temperature Storage Life	150C	1000 Hours	-	-	-	-	3/135/0	-	1/77/0	-
HTSL	A6	High Temperature Storage Life	170C	420 Hours	-	-	1/77/0	3/231/0	-	-	-	-
HTOL	B1	Life Test	125C	1000 Hours	-	-	-	-	3/231/0	-	-	-
HTOL	B1	Life Test	150C	300 Hours	-	3/231/0	-	-	-	-	-	-
ELFR	B2	Early Life Failure Rate	125C	48 Hours	-	-	-	-	3/2400/0	-	-	-

Type	#	Test Name	Condition	Duration	Qual Device: <a href="#">TLE2142IP</a>	QBS Reference: <a href="#">NE5532P</a>	QBS Reference: <a href="#">TS12A4514P</a>	QBS Reference: <a href="#">UCC37322P</a>	QBS Reference: <a href="#">MC33063AQDRQ1</a>	QBS Reference: <a href="#">OP07CP</a>	QBS Reference: <a href="#">ULN2003AN</a>	QBS Reference: <a href="#">TLE2142IDR</a>
SD	C3	PB Solderability	Precondition w.155C Dry Bake (4 hrs +/- 15 minutes)	-	-	-	-	-	1/15/0	-	-	-
SD	C3	PB-Free Solderability	Precondition w.155C Dry Bake (4 hrs +/- 15 minutes)	-	-	-	-	-	1/15/0	-	-	-
SD	C3	PB-Free Solderability	8 Hours Steam Age	-	-	3/66/0	-	3/66/0	-	-	-	-
PD	C4	Physical Dimensions	Cpk>1.67	-	1000 Volts	1/3/0	-	-	3/30/0	-	-	-
ESD	E2	ESD CDM	-	250 Volts	1/3/0	-	-	-	-	1/3/0	-	1/3/0
ESD	E2	ESD CDM	-	500 Volts	-	-	-	-	1/3/0	-	-	-
ESD	E2	ESD HBM	-	1000 Volts	-	-	-	-	-	-	-	1/3/0
ESD	E2	ESD HBM	-	2000 Volts	-	-	-	-	1/3/0	-	-	-
LU	E4	Latch-Up	Per JESD78	-	-	-	-	-	1/6/0	-	-	-
CHAR	E5	Electrical Characterization	Per Datasheet Parameters	-	1/30/0	-	-	-	-	1/30/0	1/30/0	1/30/0
CHAR	E5	Electrical Distributions	Cpk>1.67 Room, hot, and cold	-	-	-	-	-	3/90/0	-	-	-
FTY	E6	Final Test Yield	-	-	1/Pass	-	-	-	-	-	-	-

- QBS: Qual By Similarity, also known as Generic Data
- Qual Device TLE2142IP is qualified at NOT CLASSIFIED NOT CLASSIFIED
- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV : 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV : 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: <http://www.ti.com/>

TI Qualification ID: R-CHG-2404-087

In performing change qualifications, Texas Instruments follows integrated circuit industry standards in performing defect mechanism analysis and failure mechanism-based accelerated environmental testing to ensure wafer fab process, assembly process and product quality and reliability. As encouraged by these standards, TI uses both product-specific and generic (family) data in qualifying its changes. For devices to be categorized as a 'product qualification family' for generic data purposes, they must share similar product, wafer fab process and assembly process elements. The applicability of generic data (also known at TI as Qualification by Similarity (QBS)) is determined by the Reliability Engineering function following these industry standards. Generic data is shown in the qualification report in columns titled "QBS Process" (for wafer fab process), "QBS Package" (for assembly process) and "QBS Product" (for product family).

For questions regarding this notice, e-mails can be sent to the Change Management team or your local Field Sales Representative.

### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale ([www.ti.com/legal/termsofsale.html](http://www.ti.com/legal/termsofsale.html)) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.