









NOTES	
-	ON MAIN VIEW ASSEMBLY 33340243 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION
-	ASSEMBLY INSTRUCTION NO.: 35269105-CUS71 - PRELIMINARY ASSEMBLY 35269105-CUS72 - HARNESS ASSEMBLY 35269102-CUS73 - CAR ASSEMBLY
-	MATING PARTS: - 12 WAY 1.5 FEMALE CONNECTOR ASM DWG-NO.: 35123477 - FIXING SLIDE APTIV DWG-NO.: 33390630 (HT DWG-NO.: 17-1487-001-CS6) - BACKSHELL 90 DEG APTIV DWG-NO.: 33390631 (HT DWG-NO.: 17-2276-001-CS6) - BACKSHELL 180 DEG APTIV DWG-NO.: 33390632 (HT DWG-NO.: 17-1486-001-CS6) - PROTECTION CAP APTIV DWG-NO.: 35274877 (HT DWG-NO.: 17-2272-001-CS6)
-	MATING TERMINAL SYSTEM: - 1.5 TERMINAL DWG-NO.: 15396739 MAX WIRE CROSS SECTION: 1.0MM ²
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	DATE INSERT
4	TOOL CAVITY NUMBER
5	INDEX REPLACEMENT INSERT
6	PART CAVITY NUMBER
7	MOVING DISTANCE OF SECONDARY LOCK



				9		8			7	6			5			4		
				POSITION	1								2		3	4		
				NAME	MALE HOUSING PANEL MOUNT								MALE SECONDARY LOCK		SL SEAL	FIXING SEAL		
				MATERIAL	PBT GF30 FR17				PBT GF30				PBT GF30 FR17	PBT GF30	LSR 50 SHORE	LSR 70 SHORE		
				COLOR:	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	ORANGE	YELLOW	REDDISH-BROWN	REDDISH-BROWN		
				PART-NO.:	33339451	33339446	33339448	33339452	33349762	33350048	33350049	33350050	33338905	33350071	33283927	33339919		
ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT	-	---	---	---	---	---	---	---	---	---	---	---	---		
33340243	01	CODE A	ALL PARTS VO / 29,6	-	1	---	---	---	---	---	---	1	---	1	1	1		
33340244	01	CODE B		-	---	1	---	---	---	---	---	1	---	1	1	1		
33340246	01	CODE C		-	---	---	1	---	---	---	---	1	---	1	1	1		
33340247	01	CODE D		-	---	---	---	1	---	---	---	1	---	1	1	1		
33350115	01	CODE A	ALL PARTS NVO / 28,8	-	---	---	---	---	1	---	---	---	1	1	1	1		
33350117	01	CODE B		-	---	---	---	---	---	1	---	---	1	1	1	1		
33350119	01	CODE C		-	---	---	---	---	---	1	---	---	1	1	1	1		
33350121	01	CODE D		-	---	---	---	---	---	---	1	---	1	1	1	1		

MOUNTING BRACKET THICKNESS	FIXING SLIDE APTIV/HT PART-NO.:	COLOR
-	PBT GF30 FR17 PBT GF30	-
1MM	33342242 / 151-02383 33350093 / 151-02382	NATURAL
1.5MM	33339586 / 151-02387 33350096 / 151-02386	GRAY
2MM	35037428 35037429	BLUE
2.5MM	33339587 / 151-02391 33350042 / 151-02390	RED
3MM	33339588 / 151-02395 33350046 / 151-02394	YELLOW
3.5MM	35037426 35037427	GRAY
4MM	35037424 35037425	GREEN



DIMENSIONAL RANGE (MM)		CHART	
FROM	TO	> 0	> 300
> 0	> 30	> 30	> 100
> 30	> 70	> 70	> 150
> 70	> 100	> 100	> 200
> 100	> 150	> 150	> 250
> 150	> 200	> 200	> 300
> 200	> 250	> 250	> 400
> 250	> 300	> 300	> 400
> 300	> 400	> 400	> 400
TOLERANCE UNLESS OTHERWISE SPECIFIED		TOLERANCE UNLESS OTHERWISE SPECIFIED	
±0.15		±0.2	
±0.2		±0.3	
±0.3		±0.4	
±0.4		±0.5	
±0.5		±0.6	
±0.6		±0.8	
±0.8		±1	
±1		±1.2	
ANGULAR TOLERANCE		±2°	

DWG STATUS
DATE 18MR19
STG R
REV 01
N/P
CHG

ZONE

REVISION HISTORY
INITIAL RELEASE

AUTH K.FAR

DR P.NAJD

APVD 1 M.GRU

APVD 2

DWG TYP PART DRAWING

WEIGHT (GR) SEE CHART

VOLUME (CM³) ---

ROUTING

DISTR CODE

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES ACCORDING TO:
SEE CHART

GD&T ACCORDING TO:
ISO 1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

APERTIV

CONNECTION SYSTEMS
KRAKOW, POLAND

COPYRIGHT 2019 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WLASNOSCIA APTIV I ZAWIERA POUFNE INFORMACJE. POWIELANIE, ROZPOWISZCZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEKOLWIEK ICH ZAWARTOSCI BEZ NADANIA WYRAZNYCH UPRAWNIEN, JEST ZABRONIONE.

DR K.FARON

APVD1 P.NAJD

APVD2 M.GRUDZEWSKI

APVD3

APVD4

APVD5

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIIE PRZETWORZONE OKRESLA APTIV 10949001

SEE CHART

DRAWING NAME
12 WAY 1.5 PANEL MOUNT MALE ASSEMBLY FOR CTCS GROUP D

DRAWING NUMBER
35123474

SIZE A1

SCALE 2:1

FRAME NO 1 OF 1

SHEET NO 1 OF 1

STG R

REV 01

N/P

APERTIV

CONNECTION SYSTEMS
KRAKOW, POLAND

COPYRIGHT 2019 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WLASNOSCIA APTIV I ZAWIERA POUFNE INFORMACJE. POWIELANIE, ROZPOWISZCZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEKOLWIEK ICH ZAWARTOSCI BEZ NADANIA WYRAZNYCH UPRAWNIEN, JEST ZABRONIONE.

DR K.FARON

APVD1 P.NAJD

APVD2 M.GRUDZEWSKI

APVD3

APVD4

APVD5

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIIE PRZETWORZONE OKRESLA APTIV 10949001

SEE CHART

DRAWING NAME
12 WAY 1.5 PANEL MOUNT MALE ASSEMBLY FOR CTCS GROUP D

DRAWING NUMBER
35123474

SIZE A1

SCALE 2:1

FRAME NO 1 OF 1

SHEET NO 1 OF 1

STG R

REV 01

N/P