







ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL WEIGHT
35015736	01	CODE A	ALL PARTS V0 / 26.8
35015735	01	CODE B	
35015734	01	CODE C	
35015733	01	CODE D	
35015732	01	CODE A	ALL PARTS NVO / 26.0
35015739	01	CODE B	
35015738	01	CODE C	
35015737	01	CODE D	

POSITION	1								2		3
NAME	MALE HOUSING STRAP MOUNT								MALE SECONDARY LOCK		SL SEAL
MATERIAL	PBT GF30 FR17				PBT GF30				PBT GF30 FR17	PBT GF30	LSR 50 SHORE
COLOR:	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	ORANGE	YELLOW	REDDISH-BROWN
PART-NO.:	33390553	33390574	33390578	33390583	33390588	33390589	33390592	33390594	33390570	33390571	33283927
-	---	---	---	---	---	---	---	---	---	---	---
-	1	---	---	---	---	---	---	---	1	---	1
-	---	1	---	---	---	---	---	---	1	---	1
-	---	---	1	---	---	---	---	---	1	---	1
-	---	---	---	1	---	---	---	---	1	---	1
-	---	---	---	---	1	---	---	---	---	1	1
-	---	---	---	---	---	1	---	---	---	1	1
-	---	---	---	---	---	---	1	---	---	1	1
-	---	---	---	---	---	---	---	1	---	1	1



NOTES	
-	ON MAIN VIEW ASSEMBLY 35015736 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION
-	ASSEMBLY INSTRUCTION NO.: 35269104-CUS71 - PRELIMINARY ASSEMBLY 35269104-CUS72 - HARNESS ASSEMBLY 35269103-CUS73 - CAR ASSEMBLY
-	MATING PARTS: - 8 WAY 2.8 FEMALE CONNECTOR ASM DWG-NO.: 35123486 - BACKSHELL 90 DEG APTIV DWG-NO.: 33390631 (HT DWG-NO.: 17-2276-001-CSG) - BACKSHELL 180 DEG APTIV DWG-NO.: 33390632 (HT DWG-NO.: 17-1486-001-CSG) - PROTECTION CAP APTIV DWG-NO.: 35274877 (HT DWG-NO.: 17-2272-001-CSG)
-	MATING TERMINAL SYSTEM: - 2.8 TERMINAL DWG-NO.: 13548085 MAX WIRE CROSS SECTION: 2.5MM ²
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	DATE INSERT
4	TOOL CAVITY NUMBER
5	INDEX REPLACEMENT INSERT
6	PART CAVITY NUMBER
7	MOVING DISTANCE OF SECONDARY LOCK

		SHARP CORNER TOLERANCE								
☐ DIM TO CHECK	DIMENSIONAL RANGE (MM)	CHART E1								
	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300
☐ DIM FOR HELP		20	30	70	100	150	250	300	400	
TOLERANCE UNLESS OTHERWISE SPECIFIED										
☐ THEORETIC DIM		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2
ANGULAR TOL TOLERANCE ±2°										

DWG. TYPE PART DRAWING		DISTR. CODE
WEIGHT (GR) SEE CHART		
VOLUME (CM ³) ---		
ROUTING		
UNLESS OTHERWISE SPECIFIED		
GENERAL TOLERANCES ACCORDING TO: SEE CHART		
GD&T ACCORDING TO: ISO 1101		
REFERENCE		
FIRST ANGLE PROJECTION		
DO NOT SCALE USE MATH DATA		

• APTIV •									
CONNECTION SYSTEMS KRAKOW, POLAND COPYRIGHT 2019 APTIV. ALL RIGHTS RESERVED.									
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.									
TEN RYSUNEK JEST WŁASNOŚCIĄ APTIV I ZAWIERA POŁNE INFORMACJE POWIELANE, ROZPOWSZECZANE I WYKORZYSTYWANE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH (AD, JAK RÓWNIŻ PRZEKAZYWANYMI INNYMI JAKIEKOLWIEKICH ZAWARTOŚCI) BEZ NADANIA WYRAŻNYCH UPRAWIEŃ, JEST ZABRONIONE.									
								DATE	
DR	K. FARON							15MR19	
APVD1	P. NAJDUCH							18MR19	
APVD2	M. GRUDZEWSKI							18MR19	
APVD3									
APVD4									
APVD5									
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001 SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIIE PRZETWORZONE OKRESLA APTIV 10949001									
MATERIAL SEE CHART									
DRAWING NAME 8 WAY 2.8 STRAP MOUNT MALE ASSEMBLY FOR CTC5 GROUP D									
DRAWING NUMBER 35123487									
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P			
A1	2:1	1 OF 1	1 OF 1	R	01				