




TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN

TYPE 103
SAME AS TYPE 10
EXCEPT AS SHOWN


TYPE 104
SAME AS TYPE 10
EXCEPT AS SHOWN



CONNECTOR IN PRE-LOCKED POSITION INCL. COVER



TYPE 101





33337564	03	AA	104	33337569	GREEN	33111390	33273376	33273377	33337572	33337575	V-O		
33337581	03	AA	103	33337568	DK BLUE	33111390	33273376	33273377	33337572	33337575	V-O		
33337582	03	AB	102	33337567	MD GRAY	33111390	33273376	33273377	33337572	33337575	V-O		
33337581	03	AB	101	33337566	BLACK	33111390	33273376	33273377	33337572	33337575	V-O		
33337580	03	AA	104	33337565	GREEN	33111390	33199207	33199208	33337571	33337574	-		
33337579	03	AB	103	33337564	DK BLUE	33111390	33199207	33199208	33337571	33337574	-		
33337578	03	AB	102	33337563	MD GRAY	33111390	33199207	33199208	33337571	33337574	-		
33337577	03	AB	101	33337562	BLACK	33111390	33199207	33199208	33337571	33337574	-		
PART NO	REV	N/P	TYPE	CONNECTOR	CONN BODY COLOR	SEAL COV	LOCK MECH ASST	GEAR LEFT	LOCK MECH ASST	GEAR RIGHT	LOCK SECONDARY SLC	INNER CONN	UL94 FLAMMABILITY STD

A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.

TOTAL NO OF INSPECTIONS REQUIRED	151
----------------------------------	-----

NO MISSING SYMBOL NUMBER

DATE	STATUS	NP	DESCRIPTION	QTY	UNIT	PRICE	AMOUNT	REMARKS
07AP16	R	01	-	ALL PARTS - SUSPENDED DESIGN	432340	KV	TKS	
10MR17	R	02	-	ALL PARTS - RELEASED PART DRAWING	435182	SM	SK	
04MR17	R	03	-	ALL PARTS - REVISED GRAPHICS	346593	NKS	MS	
06SE17	R	04	-	ALL PARTS - ADDED PROBE-LOCK POSITION P14 + CORRUPTED CABLE TIE WIDTH NOTES, CONN BODY COLOR AND REMOVED UL94 FLAMMABILITY COLUMN	437278	JVM	JVM	TKS
14NO18	R	05	-	33335757 - UPDATED PART AVAILABILITY	441596	WH	MR	TKS
20FE19	R	06	-	33335758 - UPDATED PART AVAILABILITY	442480	NKS	MS	TKS
06MR19	R	07	-	33335759 - UPDATED PART AVAILABILITY	442584	SM	RRR	TKS
11AP19	R	08	-	33335758 - UPDATED PART AVAILABILITY	442948	OV	SKS	TKS
12SE19	R	09	-	33335752 - UPDATED PART AVAILABILITY	500055	KV	CV	TKS



NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
 - DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. SEALING CODE 2 - DESIGN WILL PASS SALT FOOT TEST AFTER CONDITIONING AS SPECIFIED IN ESA-644 (WEATHER-PACK), ESA-710 (METRI-PACK), ESA-650 (UNDERHOOD MICRO-PACK), C-4006 (WORLD CONNECTOR), ETC WHEN MATED TO MATING PART OR EQUIVALENT.
3. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO: FLOW MARKS, COLOR BLENDING, DATE VESTIGE, AND SPOKE FLASH THAT DO NOT AFFECT THE FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPMV 47-65-01.
4. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
5. THESE ASSEMBLIES WERE DESIGNED WITHOUT CPA
6. MAXIMUM CABLE TIE FORCE = 100N
7. DESIGNED FOR CORRUGATED TUBE M2N26
8. MAXIMUM CABLE TIE WIDTH 5 MM

A LINE DRAWN THROUGH * PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING. PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING. CONTACT ARTIV SALES TO ASSURE AVAILABILITY OF PARTS.	
DWG TYPE PART DRAWING	
STYLE	
VOLUME (CM³)	DISTR CODE D

• APTV:
 CONNECTION SYSTEMS
 Chennai, India
 COPYRIGHT 2016 APTV. ALL RIGHTS RESERVED.
 THIS DRAWING IS THE PROPERTY OF APTV AND CONTAINS APTV
 CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND
 UTILIZATION OF THIS DOCUMENT OR ITS RELATED DATA WITH DATA, AS WELL
 AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS
 AUTHORIZATION, IS PROHIBITED.

DR		DATE
APV01	V. KANDASAMY	07AP16
APV02	V. KANDASAMY	07AP16
APV03	TURNER KEVIN S	07AP16

APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APT IV [094900]	
MATERIAL SEE DRAWING	
DRAWING NAME TAXI ASM CONN 62 F CTS SLD	
DRAWING NUMBER 33337585	
SIZE A1	SCALE
FRAME NO	SHEET NO
STS	REV
NO	NO
NO	NO