






ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33340130	01	CODE A	ALL PARTS V0 / 26,1
33339571	01	CODE B	
33340234	01	CODE C	
33340235	01	CODE D	
33350122	01	CODE A	ALL PARTS NVO / 25,3
33350276	01	CODE B	
33350334	01	CODE C	
33350335	01	CODE D	

POSITION	1		2								3	4		5	
NAME	HOUSING		INSERT								HOUSING SEAL	SECONDARY LOCK		SLIDER	
MATERIAL	PBT GF30 FR17	PBT GF30	PBT GF30 FR17				PBT GF30				LSR 50 SHORE	PBT GF30 FR17	PBT GF30	PBT GF30 FR17	PBT GF30
COLOR:	BLACK	BLACK	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	REDDISH-BROWN	ORANGE	YELLOW	ORANGE	YELLOW
PART-NO.:	33338835	33349754	33338899	33338897	33338900	33338903	33350053	33350055	33350054	33349767	33339449	33338904	33350081	33338837	33350047
-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
-	1	-	1	-	-	-	-	-	-	-	1	1	-	1	-
-	1	-	-	1	-	-	-	-	-	-	1	1	-	1	-
-	1	-	-	-	1	-	-	-	-	-	1	1	-	1	-
-	1	-	-	-	-	1	-	-	-	-	1	1	-	1	-
-	-	1	-	-	-	-	1	-	-	-	1	-	1	-	1
-	-	1	-	-	-	-	-	1	-	-	1	-	1	-	1
-	-	1	-	-	-	-	-	-	1	-	1	-	1	-	1
-	-	1	-	-	-	-	-	-	-	1	1	-	1	-	1



NOTES	
-	ON MAIN VIEW ASSEMBLY 33340130 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK AND SLIDER IN OPEN POSITION
ASSEMBLY INSTRUCTION NO.:	
35269106-CUS71 - PRELIMINARY ASSEMBLY	
35269106-CUS72 - HARNESS ASSEMBLY	
35269103-CUS73 - CAR ASSEMBLY	
35269102-CUS73 - CAR ASSEMBLY	
MATING PARTS:	
- 12 WAY 1.5 MALE PANEL MOUNT ASM DWG-NO.: 35123474	
- BACKSHELL 90 DEG APTIV DWG-NO.: 33390631 (HT DWG-NO.: 17-2276-001-CSG)	
- BACKSHELL 180 DEG APTIV DWG-NO.: 33390632 (HT DWG-NO.: 17-1486-001-CSG)	
- PROTECTION CAP APTIV DWG-NO.: 35149888 (HT DWG-NO.: 17-2267-001-CSG)	
MATING TERMINAL SYSTEM:	
- 1.5 TERMINAL DWG-NO.: 15432214	
MAX WIRE CROSS SECTION: 1.0MM ²	
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	TOOL CAVITY NUMBER
4	PART CAVITY NUMBER
5	MOVING DISTANCE OF SECONDARY LOCK
6	MOVING DISTANCE OF SLIDER

DIM TO CHECK	DIMENSIONAL RANGE (MM)	CHART
FROM	> 0	> 20
TO	> 20	> 30
	> 30	> 70
	> 70	> 100
	> 100	> 150
	> 150	> 200
	> 200	> 250
	> 250	> 300
	> 300	> 400
1) DIM FOR HELP	TOLERANCE UNLESS OTHERWISE SPECIFIED	
	±0.15	±0.2
	±0.3	±0.4
	±0.5	±0.6
	±0.8	±1
	±1.2	±1.6
THEORETIC DIM	ANGULAR TOLERANCE ±2°	

DWG STATUS
DATE 15MR19
STG R
REV 01
N/P
CHG

ZONE

REVISION HISTORY
INITIAL RELEASE

AUTH
K.FAR

DR
P.NAJ

APVD 1
M.GRU

APVD 2

SCALE:
1:1

APTIV

CONNECTION SYSTEMS
KRAKOW, POLAND
COPYRIGHT 2019 APTIV. ALL RIGHTS RESERVED.
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.
TEN RYSUNEK JEST WLASNOSCIA APTIV I ZAWIERA POUFNE INFORMACJE POWELANE, ROZPOWISZCZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEKOLWIEK ICH ZAWARTOSCI BEZ NADANIA WYRAŻNYCH UPRAWNIEN, JEST ZABRONIONE

DR	K.FARON	DATE	14MR19
APVD1	P.NAJDUCH		15MR19
APVD2	M.GRUDZEWSKI		15MR19
APVD3			
APVD4			
APVD5			

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIIE PRZETWORZONE OKRESLA APTIV 10949001

MATERIAL

SEE CHART

DRAWING NAME

12 WAY 1.5
CTCS FEMALE ASSEMBLY

DRAWING NUMBER

35123477

SIZE	A1	SCALE	2:1	FRAME NO	1 OF 1	SHEET NO	1 OF 1	STG	R	REV	01	N/P
------	----	-------	-----	----------	--------	----------	--------	-----	---	-----	----	-----

DWG TYPE
PART DRAWING

WEIGHT (GRI)
SEE CHART

VOLUME (CM)

ROUTING

DISTR CODE
D

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:
SEE CHART

GD&T
ACCORDING TO:
ISO 1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

CONTROLLED DOCUMENTS ARE ONLY AVAILABLE ON THE SERVER
User: 3509977-CUS01-S01/01 Date: 15-mar-19 Time: 10:51:36
DocNo: 35123477-10/51/47/pos.5.cus