











9				8				7				6				5				4				3	
				POSITION	1										2				3						
				NAME	HOUSING STRAP MOUNT										SECONDARY LOCK				SL SEAL						
				MATERIAL	PBT GF30 FR17					PBT GF30					PBT GF30 FR17	PBT GF30	LSR 50 SHORE								
				COLOR:	BLACK	GREY	GREEN	BLUE	BLACK	GREY	GREEN	BLUE	ORANGE	YELLOW	REDDISH-BROWN										
				PART-NO.:	33325393	33325392	33325389	33325376	33347468	33347885	33347891	33347892	33283290	33347486	33283927										
ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT	-	---	---	---	---	---	---	---	---	---	---	---	---									
33342243	01	CODE A	ALL PARTS VO / 31,9	-	1	---	---	---	---	---	---	---	1	---	---	1									
33342248	01	CODE B		-	---	1	---	---	---	---	---	---	1	---	---	1									
33342251	01	CODE C		-	---	---	1	---	---	---	---	---	1	---	---	1									
33342236	01	CODE D		-	---	---	---	1	---	---	---	---	1	---	---	1									
33347860	01	CODE A		-	---	---	---	---	1	---	---	---	---	---	1	---	1								
33349147	01	CODE B	ALL PARTS NVO / 30,9	-	---	---	---	---	1	---	---	---	---	---	1	---	1								
33349148	01	CODE C		-	---	---	---	---	---	---	1	---	---	---	1	---	1								
33349149	01	CODE D		-	---	---	---	---	---	---	---	1	---	---	1	---	1								



NOTES	
-	ON MAIN VIEW ASSEMBLY 33342243 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION
ASSEMBLY INSTRUCTION NO.:	
-	35269104-CUS71 - PRELIMINARY ASSEMBLY
-	35269104-CUS72 - HARNESS ASSEMBLY
-	35269103-CUS73 - CAR ASSEMBLY
MATING PARTS:	
-	16 WAY 1.5/2.8 FEMALE CONNECTOR ASM DWG-NO.: 35195556
-	BACKSHELL 90 DEG APTIV DWG-NO.: 35024552 (HT DWG-NO.: 17-2277-001-CSG)
-	BACKSHELL 180 DEG APTIV DWG-NO.: 35024553 (HT DWG-NO.: 17-1491-001-CSG)
-	PROTECTION CAP APTIV DWG-NO.: 35274879 (HT DWG-NO.: 17-2273-001-CSG)
MATING TERMINAL SYSTEM:	
-	1.5 TERMINAL DWG-NO.: 15396739
-	MAX WIRE CROSS SECTION: 1.0MM ²
-	2.8 TERMINAL DWG-NO.: 13548085
-	MAX WIRE CROSS SECTION: 2.5MM ²
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	DATE INSERT
4	TOOL CAVITY NUMBER
5	INDEX REPLACEMENT INSERT
6	PART CAVITY NUMBER
7	MOVING DISTANCE OF SECONDARY LOCK

DIM TO CHECK	DIMENSIONAL RANGE (MM)	CHART
FROM	> 0	> 20
TO	> 20	> 30
	> 30	> 70
	> 70	> 100
	> 100	> 150
	> 150	> 200
	> 200	> 250
	> 250	> 300
	> 300	> 400
TOLERANCE UNLESS OTHERWISE SPECIFIED		
	±0.15	±0.2
	±0.3	±0.4
	±0.5	±0.6
	±0.8	±1
	±1.2	±1.6
ANGULAR TOLERANCE ±2°		

DWG STATUS

DATE	STG	REV	N/P	CHG	ZONE
28NO18	R	01			

REVISION HISTORY

AUTH	DR	APVD 1	APVD 2
		A.RAJ	P.NAJ
		M.GRU	K.PIT

28NO18

R

01

AA

B6

REFERENCE HELLERMANN TYTON DWG-NO. ADDED

SCALE

1:1

DISTR CODE

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES ACCORDING TO:

SEE CHART

GD&T ACCORDING TO:

ISO 1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

APTIV

CONNECTION SYSTEMS

KRAKOW, POLAND

COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WLASNOSCIA APTIV I ZAWIERA POUFNE INFORMACJE POWELANE, ROZPOWISZCZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEKOLWIEK ICH ZAWARTOSCI BEZ NADANIA WYRAZNYCH UPRAWNIEN, JEST ZABRONIONE.

DR	DATE
A.RAJEEV	27NO18
P.NAJDUCH	28NO18
M.GRUDZEWSKI	29NO18

MATERIAL

SEE CHART

DRAWING NAME

16 WAY 1.5/2.8 CTCS STRAP MOUNT MALE ASSEMBLY

DRAWING NUMBER

35195554

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	2:1	1 OF 1	1 OF 1	R	01	AA