



Revision Number: 001.2

Issue date: 12/11/2020

1. PRODUCT AND COMPANY IDENTIFICATION

Product name: LOCTITE EA 3501HT GY CR310ML **IDH number:** 2589420
Product type/use: 1-c- epoxide adhesive **Region:** United States
Restriction of Use: None identified **Contact information:**
Company address: Henkel Corporation Telephone: +1 (860) 571-5100
 One Henkel Way MEDICAL EMERGENCY Phone: Poison Control Center
 Rocky Hill, Connecticut 06067 1-877-671-4608 (toll free) or 1-303-592-1711
 TRANSPORT EMERGENCY Phone: CHEMTREC
 1-800-424-9300 (toll free) or 1-703-527-3887
 Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW
WARNING: CAUSES SKIN IRRITATION.
 MAY CAUSE AN ALLERGIC SKIN REACTION.
 CAUSES SERIOUS EYE IRRITATION.

HAZARD CLASS	HAZARD CATEGORY
SKIN IRRITATION	2
EYE IRRITATION	2A
SKIN SENSITIZATION	1



Precautionary Statements

Prevention: Avoid breathing dust or fumes. Wash affected area thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves, eye protection, and face protection.
Response: IF ON SKIN: Wash with plenty of water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If skin irritation or rash occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.
Storage: Not prescribed
Disposal: Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Limestone	1317-65-3	30 - 60
Cashew, nutshell liq., polymer with epichlorohydrin and phenol	68390-54-5	10 - 30
2-Propenenitrile, polymer with 1,3-butadiene, carboxy-terminated, polymers with bisphenol A and epichlorohydrin	68610-41-3	10 - 30

Cashew, nutshell liq. polymer with epichlorohydrin	68413-24-1	10 - 30
Treated fumed silica	67762-90-7	5 - 10
Bisphenol A diglycidyl ether-bisphenol A copolymer	25036-25-3	1 - 5
Adipohydrazide	1071-93-8	1 - 5
Titanium dioxide	13463-67-7	0.1 - 1

* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. If symptoms develop and persist, get medical attention.
Skin contact:	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. If symptoms develop and persist, get medical attention. Wash clothing before reuse. Thoroughly clean shoes before reuse.
Eye contact:	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
Ingestion:	DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention.
Symptoms:	See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Water spray (fog), foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.
Unusual fire or explosion hazards:	Closed containers may rupture (due to build up of pressure) when exposed to extreme heat. In case of fire, keep containers cool with water spray.
Hazardous combustion products:	Oxides of carbon. Phenolics. Toxic fumes. Irritating vapors.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Ensure adequate ventilation. Wear appropriate personal protective equipment. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Scrape up spilled material and place in a closed container for disposal.

7. HANDLING AND STORAGE

Handling:	Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Use only with adequate ventilation. Keep container closed.
Storage:	Keep container tightly closed and in a cool, well-ventilated place away from incompatible materials. Keep away from heat, spark and flame. Protect from direct sunlight.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Limestone	10 mg/m3 TWA Total dust.	5 mg/m3 PEL Respirable fraction. 15 mg/m3 PEL Total dust.	None	None
Cashew, nutshell liq., polymer with epichlorohydrin and phenol	None	None	None	None
2-Propenenitrile, polymer with 1,3-butadiene, carboxy-terminated, polymers with bisphenol A and epichlorohydrin	None	None	None	None
Cashew, nutshell liq. polymer with epichlorohydrin	None	None	None	None
Treated fumed silica	10 mg/m3 TWA Inhalable dust. 3 mg/m3 TWA Respirable fraction.	15 mg/m3 TWA Total dust. 5 mg/m3 TWA Respirable fraction.	None	None
Bisphenol A diglycidyl ether-bisphenol A copolymer	None	None	None	None
Adipohydrazide	None	None	None	None
Titanium dioxide	10 mg/m3 TWA	15 mg/m3 PEL Total dust. 15 MPPCF TWA Respirable fraction. 15 mg/m3 TWA Total dust. 50 MPPCF TWA Total dust. 5 mg/m3 TWA Respirable fraction.	None	None

Engineering controls:

Use local ventilation if general ventilation is insufficient to maintain vapor concentration below established exposure limits.

Respiratory protection:

Use NIOSH approved respirator if there is potential to exceed exposure limit(s).

Eye/face protection:

Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.

Skin protection:

Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Paste
Color:	Gray
Odor:	Characteristic
Odor threshold:	Not available.
pH:	Not available.
Vapor pressure:	Not available.
Boiling point/range:	Not available.
Melting point/ range:	Not available.
Specific gravity:	1.35
Vapor density:	Not available.
Flash point:	228 °C (442.4 °F)
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not available.
Flammability:	Not applicable
Evaporation rate:	Not available.
Solubility in water:	Not available.
Partition coefficient (n-octanol/water):	Not available.
VOC content:	Not available.
Viscosity:	380,000 - 580,000 mPa.s
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	None under normal processing.
Hazardous decomposition products:	Oxides of carbon. Phenolics. Toxic fumes. Irritating vapors.
Incompatible materials:	Oxidizing agents. Acids. Bases. Amines.
Reactivity:	Not available.
Conditions to avoid:	Keep away from heat, ignition sources and incompatible materials. Protect from direct sunlight.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure: Skin, Inhalation, Eyes

Potential Health Effects/Symptoms

Inhalation:	Inhalation of vapors or mists of the product may be irritating to the respiratory system.
Skin contact:	Causes skin irritation. May cause allergic skin reaction.
Eye contact:	Causes serious eye irritation.
Ingestion:	Not expected under normal conditions of use. May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Limestone	None	Nuisance dust
Cashew, nutshell liq., polymer with epichlorohydrin and phenol	None	Irritant
2-Propenenitrile, polymer with 1,3-butadiene, carboxy-terminated, polymers with bisphenol A and epichlorohydrin	None	No Data
Cashew, nutshell liq. polymer with epichlorohydrin	None	Irritant
Treated fumed silica	None	Irritant
Bisphenol A diglycidyl ether-bisphenol A copolymer	None	No Data
Adipohydrazide	None	No Target Organs
Titanium dioxide	Inhalation LC50 (Rat, 4 h) = > 2.28 mg/l Inhalation LC50 (Rat, 4 h) = > 6.82 mg/l Inhalation LC50 (Rat, 4 h) = > 3.56 mg/l	Irritant, Respiratory, Some evidence of carcinogenicity

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Limestone	No	No	No
Cashew, nutshell liq., polymer with epichlorohydrin and phenol	No	No	No
2-Propenenitrile, polymer with 1,3-butadiene, carboxy-terminated, polymers with bisphenol A and epichlorohydrin	No	No	No
Cashew, nutshell liq. polymer with epichlorohydrin	No	No	No
Treated fumed silica	No	No	No
Bisphenol A diglycidyl ether-bisphenol A copolymer	No	No	No
Adipohydrazide	No	No	No
Titanium dioxide	No	Group 2B	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name:	Not regulated
Hazard class or division:	None
Identification number:	None
Packing group:	None

International Air Transportation (ICAO/IATA)

Proper shipping name:	Not regulated
Hazard class or division:	None
Identification number:	None
Packing group:	None

Water Transportation (IMO/IMDG)

Proper shipping name:	Not regulated
Hazard class or division:	None
Identification number:	None
Packing group:	None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status:	All components are listed as active or are exempt from listing on the Toxic Substances Control Act (TSCA) inventory.
TSCA 12 (b) Export Notification:	None above reporting de minimis
CERCLA/SARA Section 302 EHS:	None above reporting de minimis.
CERCLA/SARA Section 311/312:	Immediate Health
CERCLA/SARA Section 313:	None above reporting de minimis.
California Proposition 65:	This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDSL Status:	All components are listed on or are exempt from listing on the Canadian Domestic Substances List.
------------------------------	---

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: 9,11,13

Prepared by: Product Safety and Regulatory Affairs

Issue date: 12/11/2020

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.

This Safety Data Sheet has been generated based on OSHA Hazard Communication Standard (29 CFR 1910.1200) and provides information in accordance with U.S. federal law only. No warranty or representation of any kind is given with respect to the substantive or export laws of any other jurisdiction or country. Please confirm that the information provided herein conforms to the substantive export or other law of any other jurisdiction prior to export. Please contact Henkel Product Safety and Regulatory Affairs for additional assistance.