



Doc No.	D1B146
	D2B166
	D5B019

EU Declaration of Conformity

Identification of the Product : Switching Power Supply

Name and address of Manufacturer

IDEC CORPORATION

2-6-64 Nishimiyahara, Yodogawa-Ku,
Osaka 532-0004 Japan

Name and address of the authorized representative :

IDEC ELEKTROTECHNIK GmbH

Heseltuecken 8, 22453 Hamburg, Germany

This declaration of conformity is issued under the sole responsibility of the manufacturer.

Object of the declaration : Series Name: PS5R-V Series

Model No.: Details are as per attached sheet

The object of the declaration described above is in conformity with the relevant EU harmonization legislation :

2014/35/EU

Low Voltage Directive

2014/30/EU

Electromagnetic Compatibility Directive

2011/65/EU

Restriction of the use of certain hazardous substances
(RoHS) Directive

Applied Union harmonized legislation and references to the relevant harmonization standards used or references the other technical specifications in relation to which conformity is declared.

EN 60950-1/A2:2013

EN 50178:1997

EN 61204-3:2000

EN 50581:2012

Where applicable, the notified body

Additional Information :

Signed for and on behalf of the above named manufacturer :

Place and date of issue :

Japan, 20 April, 2016

Name, function :

Atsushi Matsumoto, Executive Officer,
Quality Assurance Center

Signature :

Atsushi Matsumoto



Doc No.	D1B146
	D2B166
	D5B019

20 April, 2016

Page 1 of 1



SWITCHING POWER SUPPLY PS5R-V SERIES

<u>Model No.</u>	<u>Input</u>	<u>Output</u>
PS5R-VA05	100-240 V AC, 50/60 Hz, 0.20–0.12A	5 V DC, 1.5 A
PS5R-VA12	100-240 V AC, 50/60 Hz, 0.18–0.10 A	12 V DC, 0.6 A
PS5R-VA24	100-240 V AC, 50/60 Hz, 0.18–0.10 A	24 V DC, 0.3 A
PS5R-VB05	100-240 V AC, 50/60 Hz, 0.25–0.14 A	5 V DC, 2 A
PS5R-VB12	100-240 V AC, 50/60 Hz, 0.35–0.19 A	12 V DC, 1.3 A
PS5R-VB24	100-240 V AC, 50/60 Hz, 0.35–0.19 A	24 V DC, 0.65 A
PS5R-VC12	100-240 V AC, 50/60 Hz, 0.7–0.3 A	12 V DC, 2.5 A
PS5R-VC24	100-240 V AC, 50/60 Hz, 0.7–0.3 A	24 V DC, 1.3 A
PS5R-VD24	100-240 V AC, 50/60 Hz, 1.3–0.8 A	24 V DC, 2.5 A
PS5R-VE24	100-240 V AC, 50/60 Hz, 1.1–0.6 A	24 V DC, 3.75 A
PS5R-VF24	100-240 V AC, 50/60 Hz, 1.4–0.7 A	24 V DC, 5 A
PS5R-VG24	100-240 V AC, 50/60 Hz, 2.7–1.2 A	24 V DC, 10 A