









STATUS: **Obsolete** 2526 Printed: Jun 16, 2011



TYPE "R"	TYPE "C"	42.18 1.661	FOR UNBUFFERED DRAM, SYNC DRAM, REGISTERED SDRAM, 3.3 VOLT.
TYPE "L"	TYPE "C"	44.18 1.739	FOR OPEN, 3.3 VOLT.
TYPE "C"	TYPE "C"	43.18 1.700	FOR STANDARD DRAM, BUFFERED, 3.3 VOLT.
TYPE "R"	TYPE "L"	41.18 1.621	FOR NON-STANDARD DRAM, 5.0 VOLT.
TYPE "L"	TYPE "L"	43.18 1.700	FOR SYNC DRAM, 5.0 VOLT.
TYPE "C"	TYPE "L"	42.18 1.661	FOR STANDARD DRAM, 5.0 VOLT.
KEY POS. #1	KEY POS. #2	DIM. "A"	DESCRIPTION

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		CONFIDENTIAL	
ltr	ecn no	dr	date	linear	.X ±0.38/.015 .XX ±0.25/.010 .XXX ±0.13/.005	projection	title	DIMM, .050" 1-ROW, 168P R/A ASS'Y METAL CLIP	
K				angles	0° ±2°	MM	product family	DIMM	code
				dr	CATHY LIN 11/21/94	scale	size	dwg no	sheet
				enr	CATHY LIN 11/21/94	1.5:1	A4	95566	2 of
				chr	WAYNE YU 11/21/94				
				appd	JENN TSAO 11/21/94				
sheet index	revision sheet								



RECOMMENDED CIRCUIT BOARD HOLE LAYOUT

CONFIDENTIAL

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X ±0.38/.015	projection		title		DIMM, .050" 1-ROW, 168P R/A ASS'Y METAL CLIP	
K					.XX ±0.25/.010			product family		DIMM	
				angles	.XXX ±0.13/.005	MM		size		dwg no	
				dr	0° ±2°	scale		A4		95566	
				enr	CATHY LIN 11/21/94	1.5:1				code	
				chr	WAYNE YU 11/21/94					sheet 3 of	
				appd	JENN TSAO 11/21/94						
sheet index	revision sheet										

A — U — E

TAIL LENGTH		
CODE	DIM. "B"	DIM. "C"
0	2.54 .100	2.39 .094
1	3.30 .130	3.15 .124

TAIL LENGTH

0 : BLACK HOUSING + IVORY EJECTOR + BLACK TAIL GUIDE
1 : IVORY HOUSING + BLACK EJECTOR + IVORY TAIL GUIDE
2 : IVORY HOUSING + IVORY EJECTOR + IVORY TAIL GUIDE

[illegible]