

**Manufacturer's Name:** Liquid Instruments  
**Manufacturer's Address:** 243 Northbourne Avenue  
 Ground Floor, suite 2  
 2602 Lyneham, ACT  
 Canberra, Australia

Declares under sole responsibility that the product as originally delivered:

**Product Name:** Moku:Go  
**Model Number:** Moku:GoV1.3  
**Product Option:** Colours: Black, White, Storm, Fire, Sage, Blush  
 Configurations: M0, M1, M2

complies with the essential requirements of the following applicable European Directives, and carries the CE marking accordingly:

- Low Voltage Directive 2014/35/EU
- EMC Directive 2014/30/EU
- RoHS Directive 2011/65/EU

And conforms with the following standard(s):

	<b>Standard</b>	<b>Phenomena</b>	<b>Limit</b>
<b>EMC</b>	IEC 61326-1:2013		
	CISPR 11		Group 1 Class A
	IEC 61000-4-2	Electrostatic discharge	4kV CD, 8kV AD
	IEC 61000-4-3	Electromagnetic field	10V/m 80MHz – 2GHz, 3V/m 1.4GHz - 27GHz
	IEC 61000-4-4	Burst	0.5kV signal lines, 1 kV power lines
	IEC 61000-4-5	Surge	0.5kV lineline, 1kV lineground, 1kV signal lines
	IEC 61000-4-6	Conducted RF	3V, 150kHz – 80 MHz
	IEC 61000-4-8	Power frequency magnetic field	3A/m; 50Hz, 60Hz
	IEC 61000-4-11	Voltage dips	100% for 0.5 (0°, 180°) cycle, 100% for 1 cycle, 30% for 25 cycles
	IEC 61000-4-11	Short interruptions	100% for 250 cycles

**RoHS** EN IEC 63000:2018

**Supplementary Information:**

- This product is intended for use in a basic environment.
- The products were tested in a typical configuration with Liquid Instruments test system.
- This is a sensitive measurement apparatus by design and may have some performance loss when exposed to ambient continuous electromagnetic phenomenon.

**This DoC applies to the above listed products placed on the EU market after:**

October 18, 2021

Signature



Date

Daniel Shaddock  
CEO – Liquid Instruments