



Revision Number: 006.0

Issue date: 02/05/2019

**1. PRODUCT AND COMPANY IDENTIFICATION**

**Product name:** LOCTITE STYCAST 2850KT BL known as STYCAST 2850KT BLU 3LB  
**Product type/use:** Epoxy resin  
**Restriction of Use:** None identified  
**Company address:** Henkel Corporation  
 One Henkel Way  
 Rocky Hill, Connecticut 06067

**IDH number:** 1188134

**Region:** United States

**Contact information:**  
 Telephone: +1 (860) 571-5100  
 MEDICAL EMERGENCY Phone: Poison Control Center  
 1-877-671-4608 (toll free) or 1-303-592-1711  
 TRANSPORT EMERGENCY Phone: CHEMTREC  
 1-800-424-9300 (toll free) or 1-703-527-3887  
 Internet: www.henkelna.com

**2. HAZARDS IDENTIFICATION**

**EMERGENCY OVERVIEW**

**WARNING:** CAUSES SKIN IRRITATION.  
 MAY CAUSE AN ALLERGIC SKIN REACTION.  
 CAUSES SERIOUS EYE IRRITATION.  
 SUSPECTED OF CAUSING GENETIC DEFECTS.  
 SUSPECTED OF DAMAGING FERTILITY OR THE UNBORN CHILD.

HAZARD CLASS	HAZARD CATEGORY
SKIN IRRITATION	2
EYE IRRITATION	2A
SKIN SENSITIZATION	1
GERM CELL MUTAGENICITY	2
REPRODUCTIVE TOXICITY	2

**PICTOGRAM(S)**



**Precautionary Statements**

**Prevention:** Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Avoid breathing vapors, mist, or spray. Wash affected area thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves, clothing, eye and face protection.

**Response:** IF ON SKIN: Wash with plenty of water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. IF exposed or concerned: Get medical attention. If skin irritation or rash occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.

**Storage:** Store locked up.

**Disposal:** Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

### 3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Aluminium oxide - non fibrous form	1344-28-1	80 - 100
Epichlorohydrin-4,4'-isopropylidene diphenol resin	25068-38-6	10 - 30
Butyl 2,3-epoxypropyl ether	2426-08-6	1 - 5

\* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

### 4. FIRST AID MEASURES

<b>Inhalation:</b>	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.
<b>Skin contact:</b>	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. Wash clothing before reuse. If symptoms develop and persist, get medical attention.
<b>Eye contact:</b>	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
<b>Ingestion:</b>	DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention.
<b>Symptoms:</b>	See Section 11.

### 5. FIRE FIGHTING MEASURES

<b>Extinguishing media:</b>	Water spray (fog), foam, dry chemical or carbon dioxide.
<b>Special firefighting procedures:</b>	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. In case of fire, keep containers cool with water spray.
<b>Unusual fire or explosion hazards:</b>	Closed containers may rupture (due to build up of pressure) when exposed to extreme heat.
<b>Hazardous combustion products:</b>	Oxides of carbon. Halogenated compounds. Irritating organic vapours.

### 6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

<b>Environmental precautions:</b>	Do not allow product to enter sewer or waterways.
<b>Clean-up methods:</b>	Remove all sources of ignition. Ensure adequate ventilation. Isolate area. Keep unnecessary personnel away. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Store in a closed container until ready for disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

## 7. HANDLING AND STORAGE

**Handling:** Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Refer to Section 8.

**Storage:** Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

For information on product shelf life, please review labels on container or check the Technical Data Sheet.

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Aluminium oxide - non fibrous form	1 mg/m3 TWA Respirable fraction.	5 mg/m3 PEL Respirable fraction. 15 mg/m3 PEL Total dust. 50 MPPCF TWA Total dust. 15 MPPCF TWA Respirable fraction. 15 mg/m3 TWA Total dust. 5 mg/m3 TWA Respirable fraction.	None	None
Epichlorohydrin-4,4'-isopropylidene diphenol resin	None	None	None	None
Butyl 2,3-epoxypropyl ether	3 ppm TWA (SKIN) (Dermal sensitization)	50 ppm (270 mg/m3) PEL	None	None

**Engineering controls:** Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.

**Respiratory protection:** Use a NIOSH approved air-purifying respirator if the potential to exceed established exposure limits exists.

**Eye/face protection:** Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.

**Skin protection:** Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Physical state:</b>	Liquid
<b>Color:</b>	Blue
<b>Odor:</b>	Pungent
<b>Odor threshold:</b>	Not available.
<b>pH:</b>	Not available.
<b>Vapor pressure:</b>	< 0.1 mm hg (25 °C (77°F)) None
<b>Boiling point/range:</b>	Not determined
<b>Melting point/ range:</b>	Not available.
<b>Specific gravity:</b>	2.75
<b>Vapor density:</b>	Not available.
<b>Flash point:</b>	> 93.3 °C (> 199.94 °F) no method
<b>Flammable/Explosive limits - lower:</b>	Not available.
<b>Flammable/Explosive limits - upper:</b>	Not available.
<b>Autoignition temperature:</b>	Not available.

**Flammability:** Not applicable  
**Evaporation rate:** Not available.  
**Solubility in water:** Insoluble  
**Partition coefficient (n-octanol/water):** Not available.  
**VOC content:** 48 g/l  
**Viscosity:** Not available.  
**Decomposition temperature:** Not available.

## 10. STABILITY AND REACTIVITY

**Stability:** Stable under normal conditions of storage and use.  
**Hazardous reactions:** None under normal processing.  
**Hazardous decomposition products:** Oxides of carbon. Halogenated compounds. Irritating organic vapours.  
**Incompatible materials:** Amines. Acids. Oxidizers. Alcohols.  
**Reactivity:** Not available.  
**Conditions to avoid:** High temperatures. Store away from incompatible materials. Heat, flames, sparks and other sources of ignition.

## 11. TOXICOLOGICAL INFORMATION

**Relevant routes of exposure:** Eye contact, Skin contact, Inhalation, Ingestion

### Potential Health Effects/Symptoms

**Inhalation:** May cause respiratory tract irritation.  
**Skin contact:** Causes skin irritation. May cause allergic skin reaction.  
**Eye contact:** Causes serious eye irritation.  
**Ingestion:** May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Aluminium oxide - non fibrous form	None	Irritant, Nuisance dust, Corrosive
Epichlorohydrin-4,4'-isopropylidene diphenol resin	None	Allergen, Irritant
Butyl 2,3-epoxypropyl ether	Oral LD50 (Rat) = 2,000 mg/kg Oral LD50 (Rat) = 2.05 g/kg Oral LD50 (Mouse) = 1.53 g/kg Dermal LD50 (Rabbit) = 0.788 g/kg	Irritant, Allergen, Central nervous system, Liver, Mutagen

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Aluminium oxide - non fibrous form	No	No	No
Epichlorohydrin-4,4'-isopropylidene diphenol resin	No	No	No
Butyl 2,3-epoxypropyl ether	No	No	No

## 12. ECOLOGICAL INFORMATION

**Ecological information:** Not available.

## 13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

**Recommended method of disposal:** Follow all local, state, federal and provincial regulations for disposal.

**Hazardous waste number:** Not a RCRA hazardous waste.

## 14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

### U.S. Department of Transportation Ground (49 CFR)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

### International Air Transportation (ICAO/IATA)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

### Water Transportation (IMO/IMDG)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

## 15. REGULATORY INFORMATION

### United States Regulatory Information

**TSCA 8 (b) Inventory Status:** All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.

**TSCA 12 (b) Export Notification:** None above reporting de minimis

**CERCLA/SARA Section 302 EHS:** None above reporting de minimis.

**CERCLA/SARA Section 311/312:** Immediate Health, Delayed Health

**CERCLA/SARA Section 313:** None above reporting de minimis.

**California Proposition 65:** This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

### Canada Regulatory Information

**CEPA DSL/NDSL Status:** All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

## 16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: 2, 16

**Prepared by:** Product Safety and Regulatory Affairs

**Issue date:** 02/05/2019

**DISCLAIMER:** The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.

This Safety Data Sheet has been generated based on OSHA Hazard Communication Standard (29 CFR 1910.1200) and provides information in accordance with U.S. federal law only. No warranty or representation of any kind is given with respect to the substantive or export laws of any other jurisdiction or country. Please confirm that the information provided herein conforms to the substantive export or other law of any other jurisdiction prior to export. Please contact Henkel Product Safety and Regulatory Affairs for additional assistance.