



**TS13102**  
**Single Channel EVM**  
**User Guide**

---

**User Guide**

**TS13120 Single Channel EVM**

**Rev 1.10**

---

# Introduction

The Semtech TS13102 single channel EVM is to emulate a mechanical relay. It's designed to drop-in replace the Panasonic TX Relays TX2 SA LT - 2.

## Objectives

The objective of this User Guide is to provide a fast, easy and thorough method to experiment with and evaluate the Semtech solutions. Sufficient information is provided to support the engineer in all aspects of adding support to their products. Developers are provided with all the information on how this EVM was built as a starting point for their own designs based on the TS13102.

## Table of Contents


<i>Product Description</i> .....	2
<i>EVM Schematic</i> .....	3
<i>EVM board appearance</i> .....	4
<i>How to evaluate the EVM</i> .....	5
A. With debug board.....	5
B. Relay replacement .....	5

# Product Description

The TS13102 single channel EVM is to emulate a mechanical relay. It's designed to drop-in replace the Panasonic TX Relays TX2 SA LT - 2.

The TS13102 is a galvanically isolated 60V power switch device with bi-directional blocking. The device includes a single integrated 290mΩ high voltage switch allowing high efficiency switching of power loads or other high current applications. The single-pin CLK input pin controls the state of the switch through sequence options which control the way the device switches, including immediate on/off,



The TS13102 is ideal for the applications including power load / rail switching, isolated power supplies, solid state relays and HVAC control with the key advantage of no mechanical contact any more.





## EVM board appearance

The EVM board includes two separated portions with pre-cut slots between them. The 'relay replacement board' is a pin to pin compatible and drop-in replacement for the Panasonic relay TX2 SA LT - 2. The 'debug board' provides a microcontroller program interface and two buttons with default functions is ON, OFF respectively.



---

# How to evaluate the EVM


## A. With debug board

Follow below procedures to evaluate EVM with debug board.

1. Power EVM with VCC = +3.3V



2. Connect AC load to SW1, SW2



3. Press 'ON', 'OFF' switch to turn toggle the AC load.

## B. Relay replacement

User just need to detach the 'relay replacement board' from EVM. Drop in to replace the Panasonic TX2 SA LT – 2 in any target PCB. TS13102 EVM is pin two pin compatible with above mechanical relay. Compare to the mechanical relay, TS13102 EVM has more advantage such as long operation life, no mechanical contact noise, low power consumption etc.



---

#### **IMPORTANT NOTICE**

Information relating to this product and the application or design described herein is believed to be reliable, however such information is provided as a guide only and Semtech assumes no liability for any errors in this document, or for the application or design described herein. Semtech the latest relevant information before placing orders and should verify that such information is current and complete. Semtech reserves the right to make changes to the product or this document at any time without notice. Buyers should obtain warrants performance of its products to the specifications applicable at the time of sale, and all sales are made in accordance with Semtech's standard terms and conditions of sale.

**SEMTECH PRODUCTS ARE NOT DESIGNED, INTENDED, AUTHORIZED OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT APPLICATIONS, DEVICES OR SYSTEMS, OR IN NUCLEAR APPLICATIONS IN WHICH THE FAILURE COULD BE REASONABLY EXPECTED TO RESULT IN PERSONAL INJURY, LOSS OF LIFE OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. INCLUSION OF SEMTECH PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE UNDERTAKEN SOLELY AT THE CUSTOMER'S OWN RISK. Should a customer purchase or use Semtech products for any such unauthorized application, the customer shall indemnify and hold Semtech and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs damages and attorney fees which could arise.**

The Semtech name and logo are registered trademarks of the Semtech Corporation. All other trademarks and trade names mentioned may be marks and names of Semtech or their respective companies. Semtech reserves the right to make changes to, or discontinue any products described in this document without further notice. Semtech makes no warranty, representation or guarantee, express or implied, regarding the suitability of its products for any particular purpose. All rights reserved.

© Semtech 2015

---

## **Contact Information**

**Semtech Corporation  
200 Flynn Road, Camarillo, CA 93012  
Phone: (805) 498-2111, Fax: (805) 498-3804  
[www.semtech.com](http://www.semtech.com)**