

- **Type : Adaptateur** (Familles : GE, GEM, GS, GSM, GST, OWA, SGA, SGAS, GP, GC, NGE)

- **Introduction**

Un adaptateur est une sorte d'alimentation électrique à découpage externe conçue pour alimenter de manière extérieure un équipement électrique. Les adaptateurs Mean Well incluent les types suivants : bureau, étanche ou médicaux.

- **Installation**

- (1) Débranchez l'adaptateur du courant alternatif avant de brancher la prise CC d'un adaptateur à l'équipement et vérifiez que l'alimentation respecte les valeurs de tension et de courant prescrites pour l'équipement.
- (2) Maintenez serrée la liaison entre l'adaptateur et son câble électrique et vérifiez que la prise CC est reliée à l'équipement de manière appropriée.
- (3) Protégez le câble électrique pour qu'il ne puisse être ni piétiné ni écrasé.
- (4) Une bonne ventilation de l'alimentation évitera tout risque de surchauffe durant son utilisation. Respectez également un espace de 10 à 15 cm avec tout autre appareil proche produisant de la chaleur.
- (5) Un câble électrique homologué devrait être plus grand ou égal à SVT, 3G×18AWG ou H03VV-F, 3G×0.75mm².
- (6) Si l'équipement final n'est pas utilisé pendant une longue période, débranchez-le de l'alimentation pour éviter qu'il ne soit endommagé par des pics de courant ou par la foudre.
- (7) Pour toute autre information concernant nos produits, veuillez-vous référer au site www.meanwell.com.

- **Avertissement / Attention !!**

- (1) Risque de choc électrique ou tout autre danger électrique. Tout dysfonctionnement devrait être examiné par un technicien qualifié. Ne retirez pas le boîtier de l'adaptateur vous-même !
- (2) Risque de feu ou de choc électrique. Les ouvertures doivent être protégées contre tout objet étranger ou toute infiltration de liquide.
- (3) L'utilisation d'une prise CC inappropriée dans un appareil électronique peut endommager cet appareil ou provoquer un dysfonctionnement. Merci de vous référer aux informations de compatibilité des prises CC du cahier des charges.
- (4) Les adaptateurs doivent être installés sur une surface stable. Toute chute peut provoquer des dégâts.
- (5) N'installez pas les adaptateurs dans des endroits trop humides ou près d'une source d'eau.
- (6) N'installez pas les adaptateurs dans des endroits soumis à une température ambiante élevée ou près d'une source de feu. Merci de vous référer à leurs spécifications.
- (7) Le courant et la puissance de sortie ne doivent pas excéder les valeurs nominales inscrites sur les fiches techniques.
- (8) Débranchez l'unité du courant alternatif avant de la nettoyer. N'utilisez aucun nettoyant liquide ou sous forme d'aérosol. Utilisez uniquement un chiffon humide pour l'essuyer.
- (9) Attention:
 - (a) Pour les équipements utilisant des adaptateurs certifiés BSMI, le boîtier des équipements environnants doit être conforme à la V1 de capacité d'inflammabilité ci-dessus.
 - (b) Le fonctionnement de cet équipement dans un environnement résidentiel peut provoquer des interférences radioélectriques.

- (10) Veuillez contacter un recycleur qualifié si vous souhaitez jeter ce produit.
- (11) Cet appareil est conforme à la partie 15 des règles de la FCC. Son fonctionnement est soumis aux deux conditions suivantes :
 - (a) Cet appareil ne doit pas provoquer d'interférences nuisibles, et
 - (b) Cet appareil doit accepter toute interférence reçue, y compris les interférences pouvant entraîner un fonctionnement indésirable.
- (12) Uniquement pour GST360A/B : Surfaces qui ne doivent pas être touchées pour faire fonctionner l'équipement (temps de contact < 1 s).
- (13) Uniquement pour NGE : pour indiquer que le bloc d'alimentation ne doit pas être utilisé si les broches de la fiche sont endommagées.

● Efficacité énergétique

Model identifier	GST18A/B/E/U(05/07/09/12/15/18/24/28/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/28.0/48.0 (V)
Output current	3.0/2.0/2.0/1.5/1.2/1.0/0.75/0.64/0.375 (A)
Output power	15.0W for 5.0/7.0V output 18.0W for other
Average active efficiency	>81.39% for 5V, >85.0% for other
Efficiency at low load (10 %)	>81.6% (typ)
No-load power consumption	<0.10W

Model identifier	GST25A/B/E/U(05/07/09/12/15/18/24/28/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/28.0/48.0 (V)
Output current	4.0/2.93/2.55/2.08/1.66/1.38/1.04/0.89/0.52(A)
Output power	20.0W for 5.0V, 22.0W for 7.5V, 23.0W for 9.0V, 25.0W for other
Average active efficiency	>83.35% for 5V, >86.35% for other
Efficiency at low load (10 %)	>81.7%(typ)
No-load power consumption	<0.10W

manuel d'installation

Model identifier	GST36B/E/U(05/09/12/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/24.0/48.0 (V)
Output current	4.3/3.11/3.0/1.5/0.75(A)
Output power	21.5W for 5.0V, 28.0W for 9.0V, 36.0W for other
Average active efficiency	>83.6% for 5V, >87.4% for other
Efficiency at low load (10 %)	>82.4%(typ)
No-load power consumption	<0.10W

Model identifier	GST40A(05/07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	5.0/5.34/4.45/3.34/2.67/2.22/1.67/0.84 (A)
Output power	25.0W for 5.0V 40.0W for other
Average active efficiency	>83.46% for 5V, >87.59% for other
Efficiency at low load (10 %)	>84.54%(typ)
No-load power consumption	<0.10W

Model identifier	GST60A(05/07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	6.0/6.0/6.0/5.0/4.0/3.33/2.5/1.25(A)
Output power	30.0W for 5.0V, 45.0W for 7.5V, 54.0 W for 9.0V, 60.0W for other
Average active efficiency	>85.07% for 5V, > 88% for other
Efficiency at low load (10 %)	>85.0%(typ)
No-load power consumption	<0.21W

manuel d'installation

Model identifier	GST90A(12/15/19/24/48)-P1M
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/19.0/24.0/48.0 (V)
Output current	6.67/6.0/4.74/3.75/1.87(A)
Output power	80.0W for 12.0V, 90.0W for other
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>86.1 %(typ)
No-load power consumption	<0.21W

Model identifier	GST120A(12/15/20/24/48)-R7B/P1M
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/48.0 (V)
Output current	8.5/7.0/6.0/5.0/2.5(A)
Output power	102.0W for 12.0V, 105.0W for 15.0V, 120.0W for other
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>86.5 %(typ)
No-load power consumption	<0.21W

Model identifier	GST160A(12/15/20/24/48)-R7B
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/36.0/48.0 (V)
Output current	11.5/9.6/8.0/6.67/4.44/3.34(A)
Output power	138.0W for 12.0V, 144.0W for 15.0V, 160.0W for other
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>80.0 %(typ)
No-load power consumption	<0.21W



manuel d'installation

Model identifier	GST220A(12/15/20/24/36/48)-R7B
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/36.0/48.0 (V)
Output current	15.0/13.4/11.0/9.2/6.1/4.6(A)
Output power	180.0W for 12.0V, 201.0W for 15.0V, 220.0W for 20.0V, 221.0W for 24.0V, 219.6W for 36.0V, 221.0W for 48.0V
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>80.0 %(typ)
No-load power consumption	<0.21W

Model identifier	GST280A(12/15/20/24/48)-C6P
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/48.0(V)
Output current	21.0/17.0/13.0/11.67/5.84(A)
Output power	252.0W for 12.0V,255.0W for 15.0V, 260.0W for 20.0V,280.08W for 24.0V , 280.32W for 48.0V
Average active efficiency	>89.5%
Efficiency at low load (10 %)	>82.5% (typ)
No-load power consumption	<0.50W

manuel d'installation

Model identifier	GST360A/B(12/15/24/36/48/55)-C6P/C8P
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/24.0/36.0/48.0/55.0 (V)
Output current	27.5/22.7/15.0/10.0/7.5/6.55 (A)
Output power	330.0W for 12.0V output, 340.5W for 15.0V output 360.0W for other
Average active efficiency	>88.0%
Efficiency at low load (10 %)	>82.5% (typ)
No-load power consumption	<0.50W

Model identifier	SGAS06E/U(05/07/09/12/15/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/24.0/48.0(V)
Output current	1.0/0.8/0.66/0.5/0.4/0.25/0.125(A)
Output power	5.0W for 5.0V, 6W for other
Average active efficiency	>75.91% for 5V, >81.27% for other
Efficiency at low load (10 %)	>72.22%(typ)
No-load power consumption	<0.10W

Model identifier	SGAS15A/B/E/U (05/09/12/15/24)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/24.0(V)
Output current	2.4/1.66/1.25/1.0/0.625(A)
Output power	12.0W for 5.0V, 15W for other
Average active efficiency	>81.60% for 5V, >84.92% for other
Efficiency at low load (10 %)	>79.85%(typ)
No-load power consumption	<0.10W

manuel d'installation

Model identifier	SGAS60E/U (05/12/15/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/12.0/15.0/24.0/48.0(V)
Output current	6.0/5.0/4.0/2.5/1.25(A)
Output power	30.0W for 5.0V, 60W for other
Average active efficiency	>86.22% for 5V, >89.02% for other
Efficiency at low load (10 %)	>84.59%(typ)
No-load power consumption	<0.15W

Note:

Les séries GSM sont conformes à la réglementation médicale 60601-1. Les paramètres d'efficacité suivants sont une référence de performance.

Model identifier	GSM06E/U(05/06/07/09/12/15/18/24)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/6.0/7.5/9.0/12.0/15.0/18.0/24.0(V)
Output current	1.2/1.0/0.8/0.66/0.5/0.4/0.33/0.25(A)
Output power	6.0W for all
Average active efficiency	>68% for 5.0V, > 74% for other
Efficiency at low load (10 %)	>65% (typ)
No-load power consumption	<0.30W

Model identifier	GSM12U05-P1J/USB,GSM12E/U(07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0(V)
Output current	2.4/1.6/1.33/1.0/0.8/0.66/0.5/0.25(A)
Output power	12.0W for all
Average active efficiency	>80.0%
Efficiency at low load (10 %)	>78% (typ)
No-load power consumption	<0.075W(<0.1W for 18V/48V)



manuel d'installation

Model identifier	GSM18B/E/U(05/07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0//48.0 (V)
Output current	3.0/2.0/2.0/1.5/1.2/1.0/0.75/0.375 (A)
Output power	15.0W for 5.0/7.0V output, 18.0W for other
Average active efficiency	>81.39% for 5V, >85.0% for other
Efficiency at low load (10 %)	>81.6% (typ)
No-load power consumption	<0.10W

Model identifier	GSM25B/E/U(05/07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	4.0/2.93/2.55/2.08/1.66/1.38/1.04/0.52(A)
Output power	20.0W for 5.0V, 22.0W for 7.5V, 25.0W for other
Average active efficiency	>83.35% for 5V, >86.35% for other
Efficiency at low load (10 %)	>81.7%(typ)
No-load power consumption	<0.10W

Model identifier	GSM36B/E/U(05/07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	4.5/4.32/4.0/3.0/2.4/2/1.5/0.75(A)
Output power	22.5W for 5.0V, 32.4W for 7.0V, 36.0W for other
Average active efficiency	>83.6% for 5V, >87.4% for other
Efficiency at low load (10 %)	>82.4%(typ)
No-load power consumption	<0.10W

manuel d'installation

Model identifier	GSM40A/B(05/07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	5.0/5.34/4.45/3.34/2.67/2.22/1.67/0.84 (A)
Output power	25.0W for 5.0V, 40.0W for other
Average active efficiency	>83.46% for 5V, >87.59% for other
Efficiency at low load (10 %)	>84.54%(typ)
No-load power consumption	<0.10W

Model identifier	GSM60A/B/E/U(05/07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	6.0/6.0/5.5/4.5/4/3.33/2.5/1.25(A)
Output power	30.0W for 5.0V, 45.0W for 7.5V, 49.5 W for 9.0V, 54.0W for 12V, 60W for other
Average active efficiency	>85.07% for 5V, > 88% for other
Efficiency at low load (10 %)	>85.0%(typ)
No-load power consumption	<0.21W

Model identifier	GSM90A/B(12/15/19/24/48)-P1M
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/19.0/24.0/48.0 (V)
Output current	6.67/6.0/4.74/3.75/1.87(A)
Output power	80.0W for 12.0V, 90.0W for other
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>87.1 %(typ)
No-load power consumption	<0.21W

manuel d'installation

Model identifier	GSM120A/B(12/15/20/24/48)-R7B
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/48.0 (V)
Output current	8.5/7.0/6.0/5.0/2.5(A)
Output power	102.0W for 12.0V, 105.0W for 15.0V, 120.0W for other
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>86.3 %(typ)
No-load power consumption	<0.21W

Model identifier	GSM160A/B(12/15/20/24/48)-R7B
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/36.0/48.0 (V)
Output current	11.5/9.6/8.0/6.67/4.44/3.34(A)
Output power	138.0W for 12.0V, 144.0W for 15.0V, 160.0W for other
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>87.6 %(typ)
No-load power consumption	<0.21W

Model identifier	GSM220A/B(12/15/20/24/48)-R7B
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/48.0 (V)
Output current	15.0/13.4/11.0/9.2/4.6(A)
Output power	180.0W for 12.0V, 201.0W for 15.0V, 220.0W for 20.0V, 221.0W for other
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>84.6 %(typ)
No-load power consumption	<0.21W

manuel d'installation

Model identifier	OWA-60E-12/15/20/24/30/36/42/48/54
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/30.0/36.0/42.0/48.0/54.0 (V)
Output current	5.0/4.0/3.0/2.5/2.0/1.67/1.5/1.25/1.12(A)
Output power	60.0W for 12.0/15.0/20.0/24.0/30.0/48.0(V), 60.12W for 36.0V, 63.0W for 42.0V, 60.48W for 54.0V
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>80.0 %(typ)
No-load power consumption	<0.21W

Model identifier	OWA-90E-12/15/20/24/30/36/42/48/54
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/30.0/36.0/42.0/48.0/54.0 (V)
Output current	7.5/6.0/4.5/3.75/3.0/2.5/2.15/1.88/1.67 (A)
Output power	90.0W for 12.0/15.0/20.0/24.0/30.0/36.0(V), 90.3W for 42.0V, 90.24W for 48.0V, 90.18W for 54.0V
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>79.0 %(typ)
No-load power consumption	<0.21W

Model identifier	OWA-120E-(12/15/20/24/30/36/42/48/54)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/30.0/36.0/42.0/48.0/54.0 (V)
Output current	9.6/8.0/6.0/5.0/4.0/3.4/2.9/2.5/2.3 (A)
Output power	115W for 12.0V, 120W for 15.0/20.0/24.0/30.0/48.0(V), 122.4W for 36.0V, 121.8W for 42.0V, 124.2W for 54.0V
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>82.5 %(typ)
No-load power consumption	<0.21W



manuel d'installation

Model identifier	OWA-200E-(12/20/24/36/42/48/54)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/20.0/24.0/36.0/42.0/48.0/54.0(V)
Output current	15.0/10.0/8.3/5.55/4.75/4.17/3.71(A)
Output power	180W for 12.0V, 200W for 20V, 199W for other
Average active efficiency	>91% for 12V, >92.5% for other
Efficiency at low load (10 %)	>87.5%(typ)
No-load power consumption	<0.15W

Model identifier	GS06E/U-(1/11/2/3/4/5/6/8)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	1.0/0.8/0.66/0.5/0.4/0.33/0.25/0.125 (A)
Output power	6W
Average active efficiency	>78.88 %
Efficiency at low load (10 %)	>73.0 %(typ)
No-load power consumption	<0.10W

Model identifier	GS15-(1/1-1/2/3/4/5/6/8)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	2.4/1.6/1.66/1.25/1.0/0.83/0.625/0.31 (A)
Output power	12W for 5.0/7.5V, 15.0W for other
Average active efficiency	>82.96% for 5/7.5V, >84.13% for other
Efficiency at low load (10 %)	>79.0 %(typ)
No-load power consumption	<0.10W

manuel d'installation

Model identifier	GP25A/B(13A/13D/14E/58F)-R1B
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	(+5.0,+12.0,-5.0)/(+5.0,+12.0,-12.0)/ (+5.0,+15.0,-15.0) / (+16.0,+48.0,-16.0)(V)
Output current	(2.5,1.2,0.3)/(2.5,1.0,0.3)/(2.5,0.8,0.3)/(1.05,0.087,1.05)(A)
Output power	28.5W for 13A,28.0W for 13D,29.0W for 14E, 37.77W for 58F
Average active efficiency	>80% for 13A、 13D , > 80.5% for 14E , > 85% for 58F
Efficiency at low load (10 %)	>75.0 %(typ)
No-load power consumption	<0.30W

Model identifier	GP50A(13A/13D/14E/58F)-R1B
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	(+5.0,+12.0,-5.0)/(+5.0,+12.0,-12.0)/(+5.0,+15.0,-15.0)/ (+16.0,+48.0,-16.0)(V)
Output current	(4.0,2.0,0.5)/(4.0,2.0,0.5)/(4.0,1.5,0.5)/(2.0,0.15,2.0)(A)
Output power	46.5W for 13A,50.0W for 13D,50.0W for 14E,71.2W for 58F
Average active efficiency	>83.5%
Efficiency at low load (10 %)	>79.0 %(typ)
No-load power consumption	<0.30W

manuel d'installation

Model identifier	GC30B/E/U-(0/1/11/2/4/5/6)P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	4.2/5.6/7.2/8.4/14.3/16.8/28.6(V)
Output current	4.0/3.99/3.0/3.0/2.09/1.6/1.04(A)
Output power	16.8W for 4.2V, 22.38W for 5.6V, 21.6W for 7.2V, 25.2W for 8.4V, 30.0W for 14.3V, 27.0W for 16.8V, 30.0W for 28.6V
Average active efficiency	>55% for 4.2V , > 70% for other
Efficiency at low load (10 %)	>52% for 4.2V , > 67% for other (typ)
No-load power consumption	<1.0W

Model identifier	SGA12-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	2.4/1.6/1.33/1.0/0.8/0.66/0.5/0.25 (A)
Output power	12W
Average active efficiency	>82.96 %
Efficiency at low load (10 %)	>75.0 %(typ)
No-load power consumption	<0.10W

Model identifier	SGA18-(5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	3.0/2.0/1.5/1.2/1.0/0.75/0.375 (A)
Output power	15W for 5.0V, 18.0W for other
Average active efficiency	>84.1 % for 5V, >85.0% for other
Efficiency at low load (10 %)	>78.5 %(typ)
No-load power consumption	<0.10W

manuel d'installation

Model identifier	SGA25-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	4.0/2.93/2.77/2.08/1.66/1.38/1.04/0.52 (A)
Output power	20W for 5.0V, 22W for 7.5V, 25.0W for other
Average active efficiency	>85.4% for 5V, >86.35% for other
Efficiency at low load (10 %)	>81.0 %(typ)
No-load power consumption	<0.10W

Model identifier	SGA40-(5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	5.0/4.44/3.33/2.66/2.22/1.67/0.84 (A)
Output power	25W for 5.0V, 40.0W for other
Average active efficiency	>86.35% for 5V, >87.6% for other
Efficiency at low load (10 %)	>85.0 %(typ)
No-load power consumption	<0.10W

Model identifier	SGA60-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	6.0/6.0/5.5/5.0/4.0/3.33/2.5/1.25 (A)
Output power	30W for 5.0V, 45W for 7.5V, 50W for 9.0V, 60.0W for other
Average active efficiency	>86.95% for 5V, >87.73% for 7.5V, >89.0% for other
Efficiency at low load (10 %)	>84.0 %(typ)
No-load power consumption	<0.21W



manuel d'installation

Model identifier	GE12I-(5/7.5/9/12/15/18/24)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0 (V)
Output current	2.0/1.33/1.33/1.0/0.8/0.83/0.625 (A)
Output power	10W for 5.0/7.5V, 12W for 9/12/15V, 15W for other
Average active efficiency	>81.95% for 5.0/7.5V, >82.96% for 9/12/15V, >84.13% for other
Efficiency at low load (10 %)	>72.1 %(typ)
No-load power consumption	<0.10W

Model identifier	GE18I-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	2.4/1.73/2.0/1.5/1.2/1.0/0.75/0.375 (A)
Output power	12W for 5.0V, 13W for 7.5V, 18W for other
Average active efficiency	>82.96% for 5.0V, >83.38% for 7.5V, >85.00% for other
Efficiency at low load (10 %)	>75.1 %(typ)
No-load power consumption	<0.10W

Model identifier	GE24I-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	3.0/2.0/2.22/2.0/1.6/1.33/1.0/0.5 (A)
Output power	15W for 5.0/7.5V, 20W for 9.0V, 24W for other
Average active efficiency	>84.13% for 5.0/7.5V, >85.47% for 9.0V, >86.20% for other
Efficiency at low load (10 %)	>75.8 %(typ)
No-load power consumption	<0.10W

manuel d'installation

Model identifier	GE30I-(12/15/18/24)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/18.0/24.0 (V)
Output current	2.5/2.0/1.66/1.25 (A)
Output power	30W
Average active efficiency	>86.95%
Efficiency at low load (10 %)	>83.7 %(typ)
No-load power consumption	<0.10W

Model identifier	GEM06I05-P1J/USB,GEM06I (06/07/09/12/15/18/24) -P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/6.0/7.5/9.0/12.0/15.0/18.0/24.0(V)
Output current	1.2/1.0/0.8/0.66/0.5/0.4/0.33/0.25(A)
Output power	6.0W for all
Average active efficiency	>70% for 5.0V , > 74% for other
Efficiency at low load (10 %)	>66 %(typ)
No-load power consumption	<0.30W

Model identifier	GE40I-(5/7.5/9/12/15/18/24/36/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/36.0/48.0 (V)
Output current	4.0/2.66/3.3/3.3/2.7/2.2/1.67/1.00/0.83 (A)
Output power	20W for 5.0/7.5V, 30W for 9.0V, 40W for other
Average active efficiency	>85.47% for 5.0/7.5V, >86.92% for 9.0V, >87.58% for other
Efficiency at low load (10 %)	>77.3 %(typ)
No-load power consumption	<0.10W



manuel d'installation

Model identifier	GSM12E/GEM12I-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	1.6/1.33/1.0/0.8/0.66/0.5/0.25 (A)
Output power	12W
Average active efficiency	>82.96%
Efficiency at low load (10 %)	>72.96%(typ)
No-load power consumption	<0.10W

Model identifier	GEM18I-(5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	3.0/2.0/1.5/1.2/1.0/0.75/0.375 (A)
Output power	15W for 5.0V, 18.0W for other
Average active efficiency	>84.1 % for 5V, >85.0% for other
Efficiency at low load (10 %)	>81.0%(typ)
No-load power consumption	<0.10W

Model identifier	GEM30I-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	4.0/3.33/3.33/2.5/2.0/1.66/1.25/.625 (A)
Output power	20W for 5.0V, 25W for 7.5V, 30.0W for other
Average active efficiency	>85.47% for 5V, >86.35% for 7.5V, >86.95% for other
Efficiency at low load (10 %)	>81.0 %(typ)
No-load power consumption	<0.10W



manuel d'installation

Model identifier	GEM40I-(5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	5.0/4.0/3.33/2.66/2.22/1.66/0.83 (A)
Output power	25W for 5.0V, 36W for 9.0V, 40.0W for other
Average active efficiency	>86.35% for 5V, >87.40% for 9.0V, >87.59% for other
Efficiency at low load (10 %)	>85.0 %(typ)
No-load power consumption	<0.10W

Model identifier	GEM60I-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	6.0/6.0/5.5/4.5/4.0/3.33/2.5/1.25 (A)
Output power	30W for 5.0V, 45W for 7.5V, 50W for 9.0V, 54W for 12V, 40.0W for other
Average active efficiency	>86.95% for 5V, >87.73% for 7.5V, >89.0% for other
Efficiency at low load (10 %)	>83.0 %(typ)
No-load power consumption	<0.21W

Model identifier	NGE12E/U/I05-P1J/USB,NGE12E/U/I (09/12/15/18/24)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0//9.0/12.0/15.0/18.0/24.0(V)
Output current	2.4/1.33/1.0/0.8/0.83/0.625(A)
Output power	15W for 18/24V output, 12W for other
Average active efficiency	>82% for 5V,>86% for other
Efficiency at low load (10 %)	>64.5% for 5V,>73.5% for other
No-load power consumption	<0.075W
Protective current (input)	2A

manuel d'installation

Model identifier	NGE18E/U/I(05/09/12/15/18/24)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0(V)
Output current	3.0/2.0/1.5/1.2/1.0/0.75(A)
Output power	15W for 5V output,18W for other
Average active efficiency	>82% for 5V,>87% for other
Efficiency at low load (10 %)	>78% for 5V,>79.5% for other
No-load power consumption	<0.075W
Protective current (input)	2A

Model identifier	NGE30E/U/I(05/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0(V)
Output current	4.0/3.33/2.5/2.0/1.66/1.25/0.63(A)
Output power	20W for 5V output,30W for other
Average active efficiency	>82% for 5V,>87% for other
Efficiency at low load (10 %)	>79% for 5V,>83.5% for other
No-load power consumption	<0.075W
Protective current (input)	3.15A

Model identifier	NGE45E/U/I(05/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0(V)
Output current	5.63/4.5/3.75/3.0/2.5/1.88/0.94(A)
Output power	28.1W for 5V output,40.5W for 9V OUTPUT,45W for other
Average active efficiency	>84% for 5V,>87% for other
Efficiency at low load (10 %)	>80% for 5V,>85% for other
No-load power consumption	<0.075W
Protective current (input)	3.15A



manuel d'installation

Model identifier	NGE65E/U/I(05/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0(V)
Output current	6.0/5.96/4.88/4.34/3.62/2.71/1.36(A)
Output power	30W for 5V output,53.6W for 9V OUTPUT,58.5W for 12V OUTPUT,65W for other
Average active efficiency	>84% for 5V,>87% for other
Efficiency at low load (10 %)	>80% for 5V,>85% for other
No-load power consumption	<0.075W
Protective current (input)	3.15A

Model identifier	NGE90E/U/I(12/15/18/24/48/55)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/18.0/24.0/48.0/55.0(V)
Output current	6.25/5.5/5.0/3.75/1.875/1.64(A)
Output power	75/82.5/90/90/90/90.2(W)
Average active efficiency	>90%
Efficiency at low load (10 %)	>86% for 12V,>88% for other
No-load power consumption	<0.1W
Protective current (input)	3.15A



manuel d'installation

Model identifier	NGE100/NGE100U
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/20.0(V)
Output current	USB C1/2(5.0V,9.0V,12.0V,15.0V) for 3A, USB C1/2 20V for 5A,USB A1/2(5.0V for 3A,9.0V for 2A,12V for 1.5A,20V for 0.9A)
Output power	100W
Average active efficiency	>88.5%
Efficiency at low load (10 %)	83%forC1:20*0.5
No-load power consumption	<0.3W
Protective current (input)	3.15A
Pour des informations détaillées, veuillez scanner le code QR ci-dessous 	



manuel d'installation

Manufacturer :

MEAN WELL ENTERPRISES Co., LTD.
No.28, Wuquan 3rd Rd., Wugu Dist.,
New Taipei City 24891, Taiwan
Tel: +886-2-2299-6100
Web: www.meanwell.com

Branch Office :

China

MEAN WELL (GUANGZHOU)
ENTERPRISES Co., LTD.
No.11, Jingu South Road, Huadong
Town, Huadu Distric, Guangzhou,
Gungzhou, China
Tel: +86-20-3773-7100
Web: www.meanwell.com.cn

China

SUZHOU MEAN WELL
TECHNOLOGY Co., LTD.
No.269 Changping Rd. , Huangdai
Town, Xiangcheng District
Suzhou, Jiangsu Province, China
Post Code: 215152
Tel: +86-512-6508-8600
Web: www.meanwell.cc

U.S.A.

MEAN WELL USA, INC.
44030 Fremont Blvd., Fremont,
CA 94538, U.S.A.
Tel: +1-510-683-8886
Web: www.meanwellusa.com

Europe

MEAN WELL EUROPE B.V.
Langs de Werf 8, 1185XT Amstelveen, The
Netherlands
Tel: +31-20-758-6000
Web: www.meanwell.eu

2024.01.02



MEAN WELL ENTERPRISES CO., LTD.

No.28, Wuquan 3rd Rd., Wugu Dist., New Taipei City 24891, Taiwan (R.O.C.)

Tel: +886-2-2299-6100

Fax: +886-2-2299-6200

E-mail: info@meanwell.com

http://www.meanwell.com

Declaration of China RoHS Conformity

In order to reduce the impacts on the environment and take the more responsibility for protecting the earth, MEAN WELL is confirming and announcing the conformity to China RoHS, an Administrative Measures for the Restriction of the Use of Hazardous Substances in Electrical and Electronic Products.

Environment Friendly Use Period Label

	Observing SJT 11364-2014, Marking for the Restricted Use of Hazardous Substances in Electronic and Electrical Products
	Observing SJ/Z 11388-2009, General Guidelines of Environment-friendly Use Period of Electronic Information Products Appendix B, adopting table look-up to verify the Environment Friendly Use Period

Names and Contents of Hazardous Substances Lists

Part Name	Hazardous Substances					
	Lead (Pb)	Mercury (Hg)	Cadmium (Cd)	Hexavalent chromium (Cr ⁶⁺)	Polybrominated biphenyls (PBB)	Polybrominated diphenyl ethers (PBDE)
PCB and its components	X	O	X	O	O	O
Metal structure parts	X	O	O	O	O	O
Plastic structure parts	O	O	O	O	O	O
Accessories	O	O	O	O	O	O
Cables	X	O	O	O	O	O
O: The concentration of the hazardous substances within the homogeneous material of that product is less than the concentration limits set by GB/T 26572-2011. X: The concentration of the hazardous substances within the homogeneous material of that product is over the concentration limits set by GB/T 26572-2011; however, it follows the standard advised by 2011/65/EU.						

ISO-9001 CERTIFIED

Your Reliable Power Partner



MEAN WELL ENTERPRISES CO., LTD.

No.28, Wuquan 3rd Rd., Wugu Dist., New Taipei City 24891, Taiwan (R.O.C.)

Tel: +886-2-2299-6100

Fax: +886-2-2299-6200

E-mail: info@meanwell.com

<http://www.meanwell.com>

Declaration of China VOC Conformity

In order to reduce the impacts on the environment and take the more responsibility for protecting the earth, MEAN WELL is confirming and announcing the conformity to China's Standardization Administration Releases VOC Standards

Standard No.	Name of the Standard
GB 30981-2020	Limit of harmful substances of industrial protective coatings
GB 33372-2020	Limits for volatile organic compounds content in adhesive
GB 38507-2020	Limits for volatile organic compounds (VOCs) In printing ink
GB 38508-2020	Limits for volatile organic compounds content in cleaning agents

ISO-9001 CERTIFIED

Your Reliable Power Partner



MEAN WELL ENTERPRISES CO., LTD.

No.28, Wuquan 3rd Rd., Wugu Dist., New Taipei City 24891, Taiwan (R.O.C.)

Tel: +886-2-2299-6100

Fax: +886-2-2299-6200

E-mail: info@meanwell.com

<http://www.meanwell.com>

Declaration of Five PBT TSCA Conformity

In order to reduce the impacts on the environment and take the more responsibility for protecting the earth, MEAN WELL hereby confirms that MEAN WELL product series comply with Use and Risk Management for Five PBT Chemicals under TSCA section 6(h)

CAS No.	Substance Name
1163-19-5	Decabromodiphenyl ether (DecaBDE)
68937-41-7	Phenol, isopropylated, phosphate (3:1) PIP (3:1)
732-26-3	2,4,6-Tris (tert-butyl) phenol (2,4,6-TTBP)
133-49-3	Pentachlorothiophenol (PCTP)
87-68-3	Hexachlorobutadiene (HCBD)

ISO-9001 CERTIFIED

Your Reliable Power Partner