



Manual de instalación

- **Tipo: Adaptador/Alimentador**

(Familias GE, GEM, GS, GSM, GST, OWA, SGA, SGAS, GP, GC, NGE)

- **Introducción:**

Los adaptadores/alimentadores son un tipo de fuente de alimentación externa, diseñados para conectar piezas de equipos eléctricos externamente. Los tipos de adaptadores que Meanwell son adaptadores de sobremesa, de pared y médicos.

- **Instalación:**

- (1) Antes de conectar el enchufe de CC del adaptador al equipo, desconecte el adaptador de la corriente alterna y compruebe que la unidad se encuentra dentro del rango de voltaje y corriente acordes al equipo.
- (2) Mantener conectados el adaptador y el cable de alimentación firmemente y conectar el enchufe de CC al equipo correctamente.
- (3) Proteja el cable de alimentación para no ser pisoteado o aplastado.
- (4) Debemos mantener una buena ventilación del alimentador para evitar que se sobrecaliente. También tendremos que dejar un espacio de unos 10-15 cm cuando el dispositivo adyacente sea una fuente de calor.
- (5) Debemos utilizar un cable de alimentación AC homologado mayor o igual a SVT, 3G × 18 AWG o H03VV-F, 3G × 0,75mm².
- (6) Si el equipo no se utiliza durante un periodo prolongado de tiempo, desconecte el equipo de la red eléctrica para evitar daños por picos de voltaje o rayos.
- (7) Para más información consulte nuestra página web www.meanwell.com.

- **¡¡Peligro!!**

- (1) Riesgo de electrocución y alta tensión. Cualquier fallo o avería debe ser revisada por personal técnico cualificado y entrenado. ¡No abra la fuente de alimentación usted mismo, no existen piezas reemplazables por el usuario y puede poner en riesgo su vida!
- (2) Por favor, no instale fuentes de alimentación en lugares con alta humedad o cerca del agua. Proteja los conectores y cualquier otra parte del contacto con líquidos.
- (3) Usar un conector de salida incorrecto o intentar forzarlo puede dañar el equipo y la fuente de alimentación. Verifique que los diámetros interiores y exteriores, así como la longitud del conector de salida y la polaridad del mismo son las adecuadas para el dispositivo que desea alimentar.
- (4) Instale el adaptador en una superficie segura. La caída del alimentador puede provocar averías en el mismo.
- (5) No instale las Fuentes de alimentación en lugares con altas temperaturas o cerca de fuegos. Por favor, consulte las especificaciones técnicas referente a la temperaturas máximas de funcionamiento.
- (4) No debe usar las Fuentes de alimentación con una corriente o potencia superior a la permitida según las especificaciones técnicas.
- (5) La conexión a una toma de tierra adecuada, del cable de tierra de la fuente de alimentación (FG), es necesaria para un correcto funcionamiento y seguridad eléctrica. Los equipos de clase II sin toma de tierra no necesitan conexión a tierra.
- (6) Todas las Fuentes de alimentación de MEAN WELL han sido diseñadas de acuerdo a las regulaciones de compatibilidad electromagnética. Consulte en nuestra página web las certificaciones disponibles. Las Fuentes de alimentación están consideradas como componentes y debe verificarse la compatibilidad electromagnética del sistema final del cliente.
- (7) Desconecte el equipo de la red eléctrica antes de limpiarlo. No utilice ningún líquido ni producto químico para su limpieza. Use solamente un paño suave para limpiarlo.
- (8) Desconecte la unidad de la alimentación de CA antes de limpiarla.



Manual de instalación

No utilice ningún limpiador líquido o en aerosol.

Do not use any liquid or aerosol cleaners.

Utilice únicamente un paño húmedo para limpiarlo.

(9) WARNING:

(a) For equipment used accompanied by BSMI certified adapters, the surrounding equipment enclosure shall comply with V1 flammability rating above.

(b) Operation of this equipment in a residential environment may cause radio interference.

(10) Please contact your local qualified recyclers when you wish to dispose of this product.

(11) This device complies with Part 15 of the FCC rules.

La operación está sujeta a las dos condiciones siguientes:

The operation is subject to the following two conditions:

El funcionamiento está sujeto a las siguientes dos condiciones:

Operation is subject to the following two conditions:

(a) Es posible que este dispositivo no cause interferencias dañinas y

(b) Este dispositivo debe aceptar cualquier interferencia recibida, incluidas las interferencias que puedan causar un funcionamiento no deseado.

(12) Solo para GST360A/B: Superficies que no necesitan tocarse para operar el equipo (tiempo de contacto < 1 s).

(13) Sólo para NGE: Para indicar que la unidad de fuente de alimentación no se debe utilizar si las clavijas del enchufe están dañadas.

● Energy efficiency

Model identifier	GST18A/B/E/U(05/07/09/12/15/18/24/28/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/28.0/48.0 (V)
Output current	3.0/2.0/2.0/1.5/1.2/1.0/0.75/0.64/0.375 (A)
Output power	15.0W for 5.0/7.0V output 18.0W for other
Average active efficiency	>81.39% for 5V, >85.0% for other
Efficiency at low load (10 %)	>81.6% (typ)
No-load power consumption	<0.10W



Manual de instalación

Model identifier	GST25A/B/E/U(05/07/09/12/15/18/24/28/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/28.0/48.0 (V)
Output current	4.0/2.93/2.55/2.08/1.66/1.38/1.04/0.89/0.52(A)
Output power	20.0W for 5.0V, 22.0W for 7.5V, 23.0W for 9.0V, 25.0W for other
Average active efficiency	>83.35% for 5V, >86.35% for other
Efficiency at low load (10 %)	>81.7%(typ)
No-load power consumption	<0.10W

Model identifier	GST36B/E/U(05/09/12/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/24.0/48.0 (V)
Output current	4.3/3.11/3.0/1.5/0.75(A)
Output power	21.5W for 5.0V, 28.0W for 9.0V, 36.0W for other
Average active efficiency	>83.6% for 5V, >87.4% for other
Efficiency at low load (10 %)	>82.4%(typ)
No-load power consumption	<0.10W

Model identifier	GST40A(05/07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	5.0/5.34/4.45/3.34/2.67/2.22/1.67/0.84 (A)
Output power	25.0W for 5.0V 40.0W for other
Average active efficiency	>83.46% for 5V, >87.59% for other
Efficiency at low load (10 %)	>84.54%(typ)
No-load power consumption	<0.10W



Manual de instalación

Model identifier	GST60A(05/07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	6.0/6.0/6.0/5.0/4.0/3.33/2.5/1.25(A)
Output power	30.0W for 5.0V, 45.0W for 7.5V, 54.0 W for 9.0V, 60.0W for other
Average active efficiency	>85.07% for 5V, > 88% for other
Efficiency at low load (10 %)	>85.0%(typ)
No-load power consumption	<0.21W

Model identifier	GST90A(12/15/19/24/48)-P1M
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/19.0/24.0/48.0 (V)
Output current	6.67/6.0/4.74/3.75/1.87(A)
Output power	80.0W for 12.0V, 90.0W for other
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>86.1 %(typ)
No-load power consumption	<0.21W

Model identifier	GST120A(12/15/20/24/48)-R7B/P1M
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/48.0 (V)
Output current	8.5/7.0/6.0/5.0/2.5(A)
Output power	102.0W for 12.0V, 105.0W for 15.0V, 120.0W for other
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>86.5 %(typ)
No-load power consumption	<0.21W



Manual de instalación

Model identifier	GST160A(12/15/20/24/48)-R7B
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/36.0/48.0 (V)
Output current	11.5/9.6/8.0/6.67/4.44/3.34(A)
Output power	138.0W for 12.0V, 144.0W for 15.0V, 160.0W for other
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>80.0 %(typ)
No-load power consumption	<0.21W

Model identifier	GST220A(12/15/20/24/36/48)-R7B
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/36.0/48.0 (V)
Output current	15.0/13.4/11.0/9.2/6.1/4.6(A)
Output power	180.0W for 12.0V, 201.0W for 15.0V, 220.0W for 20.0V, 221.0W for 24.0V, 219.6W for 36.0V, 221.0W for 48.0V
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>80.0 %(typ)
No-load power consumption	<0.21W

Model identifier	GST280A(12/15/20/24/48)-C6P
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/48.0(V)
Output current	21.0/17.0/13.0/11.67/5.84(A)
Output power	252.0W for 12.0V,255.0W for 15.0V, 260.0W for 20.0V,280.08W for 24.0V , 280.32W for 48.0V
Average active efficiency	>89.5%
Efficiency at low load (10 %)	>82.5% (typ)
No-load power consumption	<0.50W



Manual de instalación

Model identifier	GST360A/B(12/15/24/36/48/55)-C6P/C8P
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/24.0/36.0/48.0/55.0 (V)
Output current	27.5/22.7/15.0/10.0/7.5/6.55 (A)
Output power	330.0W for 12.0V output, 340.5W for 15.0V output 360.0W for other
Average active efficiency	>88.0%
Efficiency at low load (10 %)	>82.5% (typ)
No-load power consumption	<0.50W

Model identifier	SGAS06E/U(05/07/09/12/15/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/24.0/48.0(V)
Output current	1.0/0.8/0.66/0.5/0.4/0.25/0.125(A)
Output power	5.0W for 5.0V, 6W for other
Average active efficiency	>75.91% for 5V, >81.27% for other
Efficiency at low load (10 %)	>72.22%(typ)
No-load power consumption	<0.10W

Model identifier	SGAS15A/B/E/U (05/09/12/15/24)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/24.0(V)
Output current	2.4/1.66/1.25/1.0/0.625(A)
Output power	12.0W for 5.0V, 15W for other
Average active efficiency	>81.60% for 5V, >84.92% for other
Efficiency at low load (10 %)	>79.85%(typ)
No-load power consumption	<0.10W



Manual de instalación

Model identifier	SGAS60E/U (05/12/15/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/12.0/15.0/24.0/48.0(V)
Output current	6.0/5.0/4.0/2.5/1.25(A)
Output power	30.0W for 5.0V, 60W for other
Average active efficiency	>86.22% for 5V, >89.02% for other
Efficiency at low load (10 %)	>84.59%(typ)
No-load power consumption	<0.15W

Note:

GSM series are complied with medical 60601-1 regulation. Following efficiency parameters are for performance reference.

Model identifier	GSM06E/U(05/06/07/09/12/15/18/24)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/6.0/7.5/9.0/12.0/15.0/18.0/24.0(V)
Output current	1.2/1.0/0.8/0.66/0.5/0.4/0.33/0.25(A)
Output power	6.0W for all
Average active efficiency	>68% for 5.0V, > 74% for other
Efficiency at low load (10 %)	>65% (typ)
No-load power consumption	<0.30W

Model identifier	GSM12U05-P1J/USB,GSM12E/U(07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0(V)
Output current	2.4/1.6/1.33/1.0/0.8/0.66/0.5/0.25(A)
Output power	12.0W for all
Average active efficiency	>80.0%
Efficiency at low load (10 %)	>78% (typ)
No-load power consumption	<0.075W(<0.1W for 18V/48V)



Manual de instalación

Model identifier	GSM18B/E/U(05/07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0//48.0 (V)
Output current	3.0/2.0/2.0/1.5/1.2/1.0/0.75/0.375 (A)
Output power	15.0W for 5.0/7.0V output, 18.0W for other
Average active efficiency	>81.39% for 5V, >85.0% for other
Efficiency at low load (10 %)	>81.6% (typ)
No-load power consumption	<0.10W

Model identifier	GSM25B/E/U(05/07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	4.0/2.93/2.55/2.08/1.66/1.38/1.04/0.52(A)
Output power	20.0W for 5.0V, 22.0W for 7.5V, 25.0W for other
Average active efficiency	>83.35% for 5V, >86.35% for other
Efficiency at low load (10 %)	>81.7%(typ)
No-load power consumption	<0.10W

Model identifier	GSM36B/E/U(05/07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	4.5/4.32/4.0/3.0/2.4/2/1.5/0.75(A)
Output power	22.5W for 5.0V, 32.4W for 7.0V, 36.0W for other
Average active efficiency	>83.6% for 5V, >87.4% for other
Efficiency at low load (10 %)	>82.4%(typ)
No-load power consumption	<0.10W



Manual de instalación

Model identifier	GSM40A/B(05/07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	5.0/5.34/4.45/3.34/2.67/2.22/1.67/0.84 (A)
Output power	25.0W for 5.0V, 40.0W for other
Average active efficiency	>83.46% for 5V, >87.59% for other
Efficiency at low load (10 %)	>84.54%(typ)
No-load power consumption	<0.10W

Model identifier	GSM60A/B/E/U(05/07/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	6.0/6.0/5.5/4.5/4/3.33/2.5/1.25(A)
Output power	30.0W for 5.0V, 45.0W for 7.5V, 49.5 W for 9.0V, 54.0W for 12V, 60W for other
Average active efficiency	>85.07% for 5V, > 88% for other
Efficiency at low load (10 %)	>85.0%(typ)
No-load power consumption	<0.21W

Model identifier	GSM90A/B(12/15/19/24/48)-P1M
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/19.0/24.0/48.0 (V)
Output current	6.67/6.0/4.74/3.75/1.87(A)
Output power	80.0W for 12.0V, 90.0W for other
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>87.1 %(typ)
No-load power consumption	<0.21W



Manual de instalación

Model identifier	GSM120A/B(12/15/20/24/48)-R7B
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/48.0 (V)
Output current	8.5/7.0/6.0/5.0/2.5(A)
Output power	102.0W for 12.0V, 105.0W for 15.0V, 120.0W for other
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>86.3 %(typ)
No-load power consumption	<0.21W

Model identifier	GSM160A/B(12/15/20/24/48)-R7B
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/36.0/48.0 (V)
Output current	11.5/9.6/8.0/6.67/4.44/3.34(A)
Output power	138.0W for 12.0V, 144.0W for 15.0V, 160.0W for other
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>87.6 %(typ)
No-load power consumption	<0.21W

Model identifier	GSM220A/B(12/15/20/24/48)-R7B
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/48.0 (V)
Output current	15.0/13.4/11.0/9.2/4.6(A)
Output power	180.0W for 12.0V, 201.0W for 15.0V, 220.0W for 20.0V, 221.0W for other
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>84.6 %(typ)
No-load power consumption	<0.21W



Manual de instalación

Model identifier	OWA-60E-12/15/20/24/30/36/42/48/54
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/30.0/36.0/42.0/48.0/54.0 (V)
Output current	5.0/4.0/3.0/2.5/2.0/1.67/1.5/1.25/1.12(A)
Output power	60.0W for 12.0/15.0/20.0/24.0/30.0/48.0(V), 60.12W for 36.0V, 63.0W for 42.0V, 60.48W for 54.0V
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>80.0 %(typ)
No-load power consumption	<0.21W

Model identifier	OWA-90E-12/15/20/24/30/36/42/48/54
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/30.0/36.0/42.0/48.0/54.0 (V)
Output current	7.5/6.0/4.5/3.75/3.0/2.5/2.15/1.88/1.67 (A)
Output power	90.0W for 12.0/15.0/20.0/24.0/30.0/36.0(V), 90.3W for 42.0V, 90.24W for 48.0V, 90.18W for 54.0V
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>79.0 %(typ)
No-load power consumption	<0.21W

Model identifier	OWA-120E-(12/15/20/24/30/36/42/48/54)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/20.0/24.0/30.0/36.0/42.0/48.0/54.0 (V)
Output current	9.6/8.0/6.0/5.0/4.0/3.4/2.9/2.5/2.3 (A)
Output power	115W for 12.0V, 120W for 15.0/20.0/24.0/30.0/48.0(V), 122.4W for 36.0V, 121.8W for 42.0V, 124.2W for 54.0V
Average active efficiency	>88.0 %
Efficiency at low load (10 %)	>82.5 %(typ)
No-load power consumption	<0.21W



Manual de instalación

Model identifier	OWA-200E-(12/20/24/36/42/48/54)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/20.0/24.0/36.0/42.0/48.0/54.0(V)
Output current	15.0/10.0/8.3/5.55/4.75/4.17/3.71(A)
Output power	180W for 12.0V, 200W for 20V, 199W for other
Average active efficiency	>91% for 12V, >92.5% for other
Efficiency at low load (10 %)	>87.5%(typ)
No-load power consumption	<0.15W

Model identifier	GS06E/U-(1/11/2/3/4/5/6/8)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	1.0/0.8/0.66/0.5/0.4/0.33/0.25/0.125 (A)
Output power	6W
Average active efficiency	>78.88 %
Efficiency at low load (10 %)	>73.0 %(typ)
No-load power consumption	<0.10W

Model identifier	GS15-(1/1-1/2/3/4/5/6/8)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	2.4/1.6/1.66/1.25/1.0/0.83/0.625/0.31 (A)
Output power	12W for 5.0/7.5V, 15.0W for other
Average active efficiency	>82.96% for 5/7.5V, >84.13% for other
Efficiency at low load (10 %)	>79.0 %(typ)
No-load power consumption	<0.10W



Manual de instalación

Model identifier	GP25A/B(13A/13D/14E/58F)-R1B
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	(+5.0,+12.0,-5.0)/(+5.0,+12.0,-12.0)/(+5.0,+15.0,-15.0) / (+16.0,+48.0,-16.0)(V)
Output current	(2.5,1.2,0.3)/(2.5,1.0,0.3)/(2.5,0.8,0.3)/(1.05,0.087,1.05)(A)
Output power	28.5W for 13A,28.0W for 13D,29.0W for 14E, 37.77W for 58F
Average active efficiency	>80% for 13A、 13D , > 80.5% for 14E , > 85% for 58F
Efficiency at low load (10 %)	>75.0 %(typ)
No-load power consumption	<0.30W

Model identifier	GP50A(13A/13D/14E/58F)-R1B
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	(+5.0,+12.0,-5.0)/(+5.0,+12.0,-12.0)/(+5.0,+15.0,-15.0)/ (+16.0,+48.0,-16.0)(V)
Output current	(4.0,2.0,0.5)/(4.0,2.0,0.5)/(4.0,1.5,0.5)/(2.0,0.15,2.0)(A)
Output power	46.5W for 13A,50.0W for 13D,50.0W for 14E,71.2W for 58F
Average active efficiency	>83.5%
Efficiency at low load (10 %)	>79.0 %(typ)
No-load power consumption	<0.30W



Manual de instalación

Model identifier	GC30B/E/U-(0/1/11/2/4/5/6)P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	4.2/5.6/7.2/8.4/14.3/16.8/28.6(V)
Output current	4.0/3.99/3.0/3.0/2.09/1.6/1.04(A)
Output power	16.8W for 4.2V,22.38W for 5.6V,21.6W for 7.2V, 25.2W for 8.4V,30.0W for 14.3V,27.0W for 16.8V, 30.0W for 28.6V
Average active efficiency	>55% for 4.2V , > 70% for other
Efficiency at low load (10 %)	>52% for 4.2V , > 67% for other (typ)
No-load power consumption	<1.0W

Model identifier	SGA12-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	2.4/1.6/1.33/1.0/0.8/0.66/0.5/0.25 (A)
Output power	12W
Average active efficiency	>82.96 %
Efficiency at low load (10 %)	>75.0 %(typ)
No-load power consumption	<0.10W

Model identifier	SGA18-(5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	3.0/2.0/1.5/1.2/1.0/0.75/0.375 (A)
Output power	15W for 5.0V, 18.0W for other
Average active efficiency	>84.1 % for 5V, >85.0% for other
Efficiency at low load (10 %)	>78.5 %(typ)
No-load power consumption	<0.10W



Manual de instalación

Model identifier	SGA25-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	4.0/2.93/2.77/2.08/1.66/1.38/1.04/0.52 (A)
Output power	20W for 5.0V, 22W for 7.5V, 25.0W for other
Average active efficiency	>85.4% for 5V, >86.35% for other
Efficiency at low load (10 %)	>81.0 %(typ)
No-load power consumption	<0.10W

Model identifier	SGA40-(5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	5.0/4.44/3.33/2.66/2.22/1.67/0.84 (A)
Output power	25W for 5.0V, 40.0W for other
Average active efficiency	>86.35% for 5V, >87.6% for other
Efficiency at low load (10 %)	>85.0 %(typ)
No-load power consumption	<0.10W

Model identifier	SGA60-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	6.0/6.0/5.5/5.0/4.0/3.33/2.5/1.25 (A)
Output power	30W for 5.0V, 45W for 7.5V, 50W for 9.0V, 60.0W for other
Average active efficiency	>86.95% for 5V, >87.73% for 7.5V, >89.0% for other
Efficiency at low load (10 %)	>84.0 %(typ)
No-load power consumption	<0.21W



Manual de instalación

Model identifier	GE12I-(5/7.5/9/12/15/18/24)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0 (V)
Output current	2.0/1.33/1.33/1.0/0.8/0.83/0.625 (A)
Output power	10W for 5.0/7.5V, 12W for 9/12/15V, 15W for other
Average active efficiency	>81.95% for 5.0/7.5V, >82.96% for 9/12/15V, >84.13% for other
Efficiency at low load (10 %)	>72.1 %(typ)
No-load power consumption	<0.10W

Model identifier	GE18I-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	2.4/1.73/2.0/1.5/1.2/1.0/0.75/0.375 (A)
Output power	12W for 5.0V, 13W for 7.5V, 18W for other
Average active efficiency	>82.96% for 5.0V, >83.38% for 7.5V, >85.00% for other
Efficiency at low load (10 %)	>75.1 %(typ)
No-load power consumption	<0.10W

Model identifier	GE24I-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	3.0/2.0/2.22/2.0/1.6/1.33/1.0/0.5 (A)
Output power	15W for 5.0/7.5V, 20W for 9.0V, 24W for other
Average active efficiency	>84.13% for 5.0/7.5V, >85.47% for 9.0V, >86.20% for other
Efficiency at low load (10 %)	>75.8 %(typ)
No-load power consumption	<0.10W



Manual de instalación

Model identifier	GE30I-(12/15/18/24)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/18.0/24.0 (V)
Output current	2.5/2.0/1.66/1.25 (A)
Output power	30W
Average active efficiency	>86.95%
Efficiency at low load (10 %)	>83.7 %(typ)
No-load power consumption	<0.10W

Model identifier	GEM06I05-P1J/USB,GEM06I (06/07/09/12/15/18/24) -P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/6.0/7.5/9.0/12.0/15.0/18.0/24.0(V)
Output current	1.2/1.0/0.8/0.66/0.5/0.4/0.33/0.25(A)
Output power	6.0W for all
Average active efficiency	>70% for 5.0V , > 74% for other
Efficiency at low load (10 %)	>66 %(typ)
No-load power consumption	<0.30W

Model identifier	GE40I-(5/7.5/9/12/15/18/24/36/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/36.0/48.0 (V)
Output current	4.0/2.66/3.3/3.3/2.7/2.2/1.67/1.00/0.83 (A)
Output power	20W for 5.0/7.5V, 30W for 9.0V, 40W for other
Average active efficiency	>85.47% for 5.0/7.5V, >86.92% for 9.0V, >87.58% for other
Efficiency at low load (10 %)	>77.3 %(typ)
No-load power consumption	<0.10W



Manual de instalación

Model identifier	GSM12E/GEM12I-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	1.6/1.33/1.0/0.8/0.66/0.5/0.25 (A)
Output power	12W
Average active efficiency	>82.96%
Efficiency at low load (10 %)	>72.96%(typ)
No-load power consumption	<0.10W

Model identifier	GEM18I-(5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	3.0/2.0/1.5/1.2/1.0/0.75/0.375 (A)
Output power	15W for 5.0V, 18.0W for other
Average active efficiency	>84.1 % for 5V, >85.0% for other
Efficiency at low load (10 %)	>81.0%(typ)
No-load power consumption	<0.10W

Model identifier	GEM30I-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	4.0/3.33/3.33/2.5/2.0/1.66/1.25/.625 (A)
Output power	20W for 5.0V, 25W for 7.5V, 30.0W for other
Average active efficiency	>85.47% for 5V, >86.35% for 7.5V, >86.95% for other
Efficiency at low load (10 %)	>81.0 %(typ)
No-load power consumption	<0.10W



Manual de instalación

Model identifier	GEM40I-(5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	5.0/4.0/3.33/2.66/2.22/1.66/0.83 (A)
Output power	25W for 5.0V, 36W for 9.0V, 40.0W for other
Average active efficiency	>86.35% for 5V, >87.40% for 9.0V, >87.59% for other
Efficiency at low load (10 %)	>85.0 %(typ)
No-load power consumption	<0.10W

Model identifier	GEM60I-(5/7.5/9/12/15/18/24/48)
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/7.5/9.0/12.0/15.0/18.0/24.0/48.0 (V)
Output current	6.0/6.0/5.5/4.5/4.0/3.33/2.5/1.25 (A)
Output power	30W for 5.0V, 45W for 7.5V, 50W for 9.0V, 54W for 12V, 40.0W for other
Average active efficiency	>86.95% for 5V, >87.73% for 7.5V, >89.0% for other
Efficiency at low load (10 %)	>83.0 %(typ)
No-load power consumption	<0.21W

Model identifier	NGE12E/U/I05-P1J/USB,NGE12E/U/I (09/12/15/18/24)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0//9.0/12.0/15.0/18.0/24.0(V)
Output current	2.4/1.33/1.0/0.8/0.83/0.625(A)
Output power	15W for 18/24V output,12W for other
Average active efficiency	>82% for 5V,>86% for other
Efficiency at low load (10 %)	>64.5% for 5V,>73.5% for other
No-load power consumption	<0.075W
Protective current (input)	2A



Manual de instalación

Model identifier	NGE18E/U/I(05/09/12/15/18/24)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0(V)
Output current	3.0/2.0/1.5/1.2/1.0/0.75(A)
Output power	15W for 5V output,18W for other
Average active efficiency	>82% for 5V,>87% for other
Efficiency at low load (10 %)	>78% for 5V,>79.5% for other
No-load power consumption	<0.075W
Protective current (input)	2A

Model identifier	NGE30E/U/I(05/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0(V)
Output current	4.0/3.33/2.5/2.0/1.66/1.25/0.63(A)
Output power	20W for 5V output,30W for other
Average active efficiency	>82% for 5V,>87% for other
Efficiency at low load (10 %)	>79% for 5V,>83.5% for other
No-load power consumption	<0.075W
Protective current (input)	3.15A

Model identifier	NGE45E/U/I(05/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0(V)
Output current	5.63/4.5/3.75/3.0/2.5/1.88/0.94(A)
Output power	28.1W for 5V output,40.5W for 9V OUTPUT,45W for other
Average active efficiency	>84% for 5V,>87% for other
Efficiency at low load (10 %)	>80% for 5V,>85% for other
No-load power consumption	<0.075W
Protective current (input)	3.15A




Manual de instalación

Model identifier	NGE65E/U/I(05/09/12/15/18/24/48)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/18.0/24.0/48.0(V)
Output current	6.0/5.96/4.88/4.34/3.62/2.71/1.36(A)
Output power	30W for 5V output,53.6W for 9V OUTPUT,58.5W for 12V OUTPUT,65W for other
Average active efficiency	>84% for 5V,>87% for other
Efficiency at low load (10 %)	>80% for 5V,>85% for other
No-load power consumption	<0.075W
Protective current (input)	3.15A

Model identifier	NGE90E/U/I(12/15/18/24/48/55)-P1J
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	12.0/15.0/18.0/24.0/48.0/55.0(V)
Output current	6.25/5.5/5.0/3.75/1.875/1.64(A)
Output power	75/82.5/90/90/90/90.2(W)
Average active efficiency	>90%
Efficiency at low load (10 %)	>86% for 12V,>88% for other
No-load power consumption	<0.1W
Protective current (input)	3.15A



Manual de instalación

Model identifier	NGE100/NGE100U
Input voltage	230Vac
Input AC frequency	50Hz
Output voltage	5.0/9.0/12.0/15.0/20.0(V)
Output current	USB C1/2(5.0V,9.0V,12.0V,15.0V) for 3A, USB C1/2 20V for 5A,USB A1/2(5.0V for 3A,9.0V for 2A,12V for 1.5A,20V for 0.9A)
Output power	100W
Average active efficiency	>88.5%
Efficiency at low load (10 %)	83%forC1:20*0.5
No-load power consumption	<0.3W
Protective current (input)	3.15A
Para obtener información detallada, escanee el código QR a continuación	
	



Manual de instalación

Manufacturer :

MEAN WELL ENTERPRISES Co., LTD.
No.28, Wuquan 3rd Rd., Wugu Dist.,
New Taipei City 24891, Taiwan
Tel: +886-2-2299-6100
Web: www.meanwell.com

Branch Office :

China

MEAN WELL (GUANGZHOU)
ENTERPRISES Co., LTD.
No.11, Jingu South Road, Huadong
Town, Huadu Distric, Guangzhou,
Gungzhou, China
Tel: +86-20-3773-7100
Web: www.meanwell.com.cn

China

SUZHOU MEAN WELL
TECHNOLOGY Co., LTD.
No.269 Changping Rd. , Huangdai
Town, Xiangcheng District
Suzhou, Jiangsu Province, China
Post Code: 215152
Tel: +86-512-6508-8600
Web: www.meanwell.cc

U.S.A.

MEAN WELL USA, INC.
44030 Fremont Blvd., Fremont,
CA 94538, U.S.A.
Tel: +1-510-683-8886
Web: www.meanwellusa.com

Europe

MEAN WELL EUROPE B.V.
Langs de Werf 8, 1185XT Amstelveen, The
Netherlands
Tel: +31-20-758-6000
Web: www.meanwell.eu

2024.01.02



Declaration of China RoHS Conformity

In order to reduce the impacts on the environment and take the more responsibility for protecting the earth, MEAN WELL is confirming and announcing the conformity to China RoHS, an Administrative Measures for the Restriction of the Use of Hazardous Substances in Electrical and Electronic Products.

Environment Friendly Use Period Label

	<p>Observing SJT 11364-2014, Marking for the Restricted Use of Hazardous Substances in Electronic and Electrical Products</p> <p>Observing SJ/Z 11388-2009, General Guidelines of Environment-friendly Use Period of Electronic Information Products Appendix B, adopting table look-up to verify the Environment Friendly Use Period</p>
--	---

Names and Contents of Hazardous Substances Lists

Part Name	Hazardous Substances					
	Lead (Pb)	Mercury (Hg)	Cadmium (Cd)	Hexavalent chromium (Cr ⁶⁺)	Polybrominated biphenyls (PBB)	Polybrominated diphenyl ethers (PBDE)
PCB and its components	X	O	X	O	O	O
Metal structure parts	X	O	O	O	O	O
Plastic structure parts	O	O	O	O	O	O
Accessories	O	O	O	O	O	O
Cables	X	O	O	O	O	O

O: The concentration of the hazardous substances within the homogeneous material of that product is less than the concentration limits set by GB/T 26572-2011.
X: The concentration of the hazardous substances within the homogeneous material of that product is over the concentration limits set by GB/T 26572-2011; however, it follows the standard advised by 2011/65/EU.



MEAN WELL ENTERPRISES CO., LTD.

No.28, Wuquan 3rd Rd., Wugu Dist., New Taipei City 24891, Taiwan (R.O.C.)

Tel: + 886-2-2299-6100

Fax: + 886-2-2299-6200

E-mail: info@meanwell.com

<http://www.meanwell.com>

Declaration of China VOC Conformity

In order to reduce the impacts on the environment and take the more responsibility for protecting the earth, MEAN WELL is confirming and announcing the conformity to China's Standardization Administration Releases VOC Standards

Standard No.	Name of the Standard
GB 30981-2020	Limit of harmful substances of industrial protective coatings
GB 33372-2020	Limits for volatile organic compounds content in adhesive
GB 38507-2020	Limits for volatile organic compounds (VOCs) In printing ink
GB 38508-2020	Limits for volatile organic compounds content in cleaning agents

ISO-9001 CERTIFIED

Your Reliable Power Partner



Declaration of Five PBT TSCA Conformity

In order to reduce the impacts on the environment and take the more responsibility for protecting the earth, MEAN WELL hereby confirms that MEAN WELL product series comply with Use and Risk Management for Five PBT Chemicals under TSCA section 6(h)

CAS No.	Substance Name
1163-19-5	Decabromodiphenyl ether (DecaBDE)
68937-41-7	Phenol, isopropylated, phosphate (3:1) PIP (3:1)
732-26-3	2,4,6-Tris (tert-butyl) phenol (2,4,6-TTBP)
133-49-3	Pentachlorothiophenol (PCTP)
87-68-3	Hexachlorobutadiene (HCBD)