




# MESSRS.

## SPECIFICATION FOR APPROVAL

Product	ELECTRET CONDENSER MICROPHONE
Part No.	AMF-O60C38-1CW2
Customer Approval	
Customer Part No.	

Approved By	Checked By	Made By
		



### Advanced Acoustic Technology Corporation



ISO 9001 Certified

ISO 14001 Certified

Head Office / 2F, No.207, Sec. 6, Chung Shan N. Rd., Taipei, Taiwan

Tel: +886-2-8866-5255

Fax: +886-2-8866-5250

RoHS



## 1. SPECIFICATIONS

AMF-O60C38-1CW2

01	Sensitivity	-38±3dB (0dB=1V/Pa,1KHz)
02	Standard Operation Voltage	2.0 V
03	Output Impedance	2.2 KΩ
04	Directivity	Omni directional
05	Frequency Range	100 - 10K Hz
06	Max. Operation Voltage	10V
07	Current Consumption	Max.0.5mA
08	Sensitivity Reduction	Within -3dB 0dB=1V/Pa,1KHz Vs=2.0to 1.5V
09	S/N Ratio	≥58dB
10	Sound Pressure Level	110 dB
11	Operating Temperature	-20~+60℃
12	Storage Temperature	-25~+70℃

※ For noise-cancelling use, please refer to unidirectional or bidirectional types.

## 2. MEASURING METHOD

### 2-1. Test Condition

#### Standard Conditions:

Generally Temperature 15~35℃

Generally Humidity 45~85%

Generally Atmospheric Pressure 860~1060hpa

#### Basic Test Conditions:


Temperature 20±2℃

Humidity 60~70%


Generally Atmospheric Pressure 860~1060hpa

### 2-2. Standard Test Circuit

Vs=2.0V RL=2.2KΩ Te=20℃ R.H.=60%




## 2-3. Standard Test Fixture




## 2-4. Frequency Response Curve

### XY Graph 2



3. DIMENSIONS



#### 4. RELIABILITY TEST

Item		Test Conditions	Evaluation Standard
01	High Temp. Test	After exposure at +70°C for 96 hours	After any tests , the sensitivity to be within $\pm 3\text{dB}$ of initial sensitivity after 3 hours of conditioning at 20°C and shall keep their initial operation and appearance.
02	Low Temp. Test	After exposure at -25°C for 96 hours	
03	Temp. Cycle Test	A After exposure at +70°C for 30 minutes, at room temp. for 10 minutes, at -25°C for 30 minutes, at room temp. for 10 minutes, at 5 cycles.	
04	Humidity Test	After exposure at 40°C and 90 $\pm$ 5% relative humidity for 96 hour.	
05	Vibration Test	10~50Hz for 1 minute full amplitude 1.52mm for 2 hours at three axis.	
06	Drop test	The microphone unit without packaged must be subjected to each 3 drops at three axis from the height of 1 meter to 20mm thick hardwood.	

##### Criterion :

- AATC reserves the right to change product material without prior notice, guaranteeing the same specification. Materials are subject to change due to environmental regulations, sourcing, and process improvements.**
- If you need more information, please contact our technology department, thank you.**

6. PACKING

	DRAWING	QTY(PCS)	SIZE(MM)	MATERIAL	MARKIN G
PACKING		100		Tie wire	
		1000	287×187	ESD Pag	
OUTER BOX			230×230×275	Paper	