

TEXAS INSTRUMENTS Logic

Products may be RoHS compliant. Check mouser.com for RoHS status.



LOGIC (CONT.)

For quantities greater than listed, call for quote.

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Package	Description	Price Each	
			1	10
595-SN74HC74PWR	TSSOP-14	Dual D-Type Flip-Flop	.48	.329
595-SN74HC86D	SOP-14	Quad Exclusive-OR Gates	.51	.39
595-SN74HC86N	DIP-14	Quad Exclusive-OR Gates	.39	.325
595-SN74HC700D	SOP-14	Quad Positive-NAND Gate	.40	.31
595-SN74HC700N	DIP-14	Quad Positive-NAND Gate	.46	.354
595-SN74HC702D	SOP-14	Quad Positive-NOR Gate	.40	.31
595-SN74HC702N	DIP-14	Quad Positive-NOR Gate	.46	.354
595-SN74HC704D	SOIC-14	Hex Inverter	.40	.31
595-SN74HC704N	DIP-14	Hex Inverter	.46	.354
595-SN74HC74PWR	TSSOP-14	Hex Inverter	.48	.329
595-SN74HC708D	SOP-14	Quad Positive-AND Gates	.40	.31
595-SN74HC708N	DIP-14	Quad Positive-AND Gates	.46	.354
595-SN74HC708PW	TSSOP-14	Quad Positive-AND Gates	.40	.31
595-SN74HC7125D	SOIC-14	Quad Bus Buff Gates	.51	.39
595-SN74HC7138D	SOIC-16	3-Line To 8-Line Decoder	.51	.39
595-SN74HC7138N	DIP-16	3-Line To 8-Line Decoder	.58	.484
595-SN74HC7139N	DIP-16	Dual 2-Line To 4-Line Decoder	.59	.493
595-SN74HC714D	SOIC-14	Hex Inverter	.40	.31
595-SN74HC714N	DIP-14	Hex Inverter	.54	.448
595-SN74HC74PWR	TSSOP-14	Hex Inverter	.48	.329
595-SN74HC7240N	DIP-20	Octal Buff and Line Driver	.57	.477
595-SN74HC7244DBR	SSOP-20	Octal Buff and Line Driver	.50	.419
595-SN74HC7244DW	SOIC-20	Octal Buff and Line Driver	.59	.495
595-SN74HC7244N	DIP-20	Octal Buff and Line Driver	.57	.477
595-SN74HC7244PW	TSSOP-20	Octal Buff and Line Driver	.54	.455
595-SN74HC7245DW	SOIC-20	Octal Bus Transceiver	.59	.495
595-SN74HC7245N	DIP-20	Octal Bus Transceiver	.57	.477
595-SN74HC7245PWR	TSSOP-20	Octal Bus Transceiver	.45	.379
595-SN74HC7273DW	SOP-20	Octal D-Type Flip-Flop	.59	.495
595-SN74HC7273N	DIP-20	Octal D-Type Flip-Flop	.57	.477
595-SN74HC732D	SOIC-14	Quad Positive-OR Gate	.40	.31
595-SN74HC732N	DIP-14	Quad Positive-OR Gate	.46	.354
595-SN74HC7373N	DIP-20	Octal D-Type Latch	.57	.477
595-SN74HC7374N	DIP-20	Octal D-type Flip-Flop	.64	.533
595-SN74HC7540DW	SOP-20	Octal Buff and Line Driver	.63	.524
595-SN74HC7541DW	SOIC-20	Octal Buff and Line Driver	.63	.524
595-SN74HC7541N	DIP-20	Octal Buff and Line Driver	.62	.516
595-SN74HC7573DWR	SOIC-20	Octal D-Type Latch	.63	.53
595-SN74HC7573N	DIP-20	Octal D-Type Latch	.57	.477
595-SN74HC7574DW	SOIC-20	Octal D-Type Flip-Flop	.59	.495
595-SN74HC7574N	DIP-20	Octal D-Type Flip-Flop	.70	.589
595-SN74HC774D	SOIC-14	Dual D-Type Flip-Flop	.40	.31
595-SN74HC774N	DIP-14	Dual D-Type Flip-Flop	.46	.354
595-SN74HC7040N	DIP-14	Hex Inverter	.54	.448
595-SN74L2G17MDCRKP	SC-70	Dual Schmitt Trigger Buffer	1.11	.952
595-SN74LS00DR	SOIC-14	Quad positive-NAND Gate	.57	.474
595-SN74LS00N	DIP-14	Quad positive-NAND Gate	1.13	.966
595-SN74LS02D	SOIC-14	Quad positive-NOR Gate	.68	.57
595-SN74LS02N	DIP-14	Quad positive-NOR Gate	.62	.521
595-SN74LS03N	PDIP-14	Quad positive-NAND Gate	.94	.806
595-SN74LS04D	SOIC-14	Hex Inverter	.75	.626
595-SN74LS04DBR	SSOP-14	CMOS Hex Inverter	.89	.741
595-SN74LS04N	DIP-14	Hex Inverter	.69	.573
595-SN74LS05D	SOIC-14	Hex Inverter	.94	.806
595-SN74LS05N	DIP-14	Hex Inverter	.86	.739
595-SN74LS06D	SOIC-14	Hex Inverter Buff/Driver	.94	.806
595-SN74LS07D	SOP-14	Hex Buff/Driver	.86	.733
595-SN74LS07N	PDIP-14	Hex Buff/Driver	.94	.806
595-SN74LS08D	SOIC-14	Quad Positive-AND Gate	.68	.57
595-SN74LS08N	DIP-14	Quad Positive-AND Gate	.62	.521
595-SN74LS09N	PDIP-14	Quad 2-Input Positive-AND Gate	.94	.806
595-SN74LS10N	DIP-14	Triple Positive-NAND Gate	.76	.632
595-SN74LS122N	DIP-14	Monostable Multivibrator	1.18	1.00
595-SN74LS123D	SOIC-16	Dual Monostable Multivibrator	.87	.728
595-SN74LS123N	DIP-16	Dual Monostable Multivibrator	.80	.67
595-SN74LS125AD	SOIC-14	Quad Bus Buff	.87	.728
595-SN74LS125AN	DIP-14	Quad Bus Buff	.80	.67
595-SN74LS132D	SOIC-14	Quad Schmitt Trigger	.92	.769
595-SN74LS132N	PDIP-14	Quad Schmitt Trigger	.85	.707
595-SN74LS138D	SOIC-16	3-Line to 8-Line Decoder	.87	.728
595-SN74LS138N	DIP-16	3-Line to 8-Line Decoder	.80	.67
595-SN74LS139AN	DIP-16	Dual 2-Line to 4-Line Decoder	.80	.67
595-SN74LS145N	DIP-16	BCD-To-Decimal Decoder	1.06	.904
595-SN74LS148N	DIP-16	8 to 3-Line priority encoder	1.57	1.34
595-SN74LS14D	SOIC-14	Hex Inverter	.68	.57
595-SN74LS14N	DIP-14	Hex Inverter	.62	.521
595-SN74LS151N	DIP-16	8-Line To 1-Line Data Selector	.86	.739
595-SN74LS155AD	SOIC-16	Dual 2-Line to 4-Line Decoder	1.58	1.35
595-SN74LS155AN	PDIP-16	Dual 2-Line to 4-Line Decoder	1.45	1.24
595-SN74LS157DR	SOIC-16	Quad 2 To 1-Line Data Selector	.69	.573
595-SN74LS157N	DIP-16	Quad 2 To 1-Line Data Selector	.76	.632
595-SN74LS164N	DIP-14	Serial-In Shift Register	.76	.632
595-SN74LS165AN	PDIP-16	Serial-Out Shift Register	.76	.632
595-SN74LS173AN	PDIP-16	4-Bit D-type Register	1.49	1.27
595-SN74LS174N	PDIP-16	Hex D-Type Flip-Flop	.90	.773
595-SN74LS175N	DIP-16	Quad D-Type Flip-Flop	.89	.744
595-SN74LS193N	DIP-16	4-Bit Binary Cntr	1.06	.904
595-SN74LS20N	DIP-14	Dual positive-NAND Gate	.94	.806
595-SN74LS21N	DIP-14	Dual positive-AND gates	.71	.592
595-SN74LS221D	SOIC-16	Dual Monostable Multivibrator	1.33	1.13

MOUSER STOCK NO.	Package	Description	Price Each	
			1	10
595-SN74LS221N	PDIP-16	Dual Monostable Multivibrator	1.22	1.04
595-SN74LS240DBR	SSOP-20	3-State, Octal Buffer/Line Driver	1.07	.918
595-SN74LS240N	DIP-20	Octal Buff and Line Driver	.82	.705
595-SN74LS241N	PDIP-20	Octal Buff and Line Driver	.82	.705
595-SN74LS244DW	SOIC-20	Octal Buff and Line Driver	.94	.806
595-SN74LS244DWR	SOIC-20	Octal Buff and Line Driver	.86	.739
595-SN74LS244N	DIP-20	Octal Buff and Line Driver	.86	.739
595-SN74LS245DW	SOIC-20	Octal Bus Transceiver	.94	.806
595-SN74LS245N	DIP-20	Octal Bus Transceiver	.86	.739
595-SN74LS247N	DIP-16	BCD-To-7 Decoder	1.76	1.50
595-SN74LS251N	PDIP-16	8-Line To 1-Line Data Selector	.86	.739
595-SN74LS259BN	PDIP-16	Octal Addressable Latch	1.10	.941
595-SN74LS273DW	SOIC-20	Octal D-Type Flip-Flop	.90	.77
595-SN74LS273N	DIP-20	Octal D-Type Flip-Flop	.82	.705
595-SN74LS279AN	PDIP-16	Quad /S-/R Latch	1.26	1.07
595-SN74LS30N	DIP-14	8-input Positive-NAND Gate	.94	.806
595-SN74LS32DR	SOIC-14	Quad Positive-OR Gate	.61	.513
595-SN74LS32N	DIP-14	Quad Positive-OR Gate	.58	.484
595-SN74LS33N	PDIP-14	Quad Positive-NOR Buff	1.47	1.25
595-SN74LS365AN	PDIP-16	Hex Bus Driver	1.61	1.37
595-SN74LS368AN	DIP-16	6-bit Buff and Line Driver	1.37	1.17
595-SN74LS373DW	SOIC-20	Octal D-Type Flip-Flop	.92	.792
595-SN74LS373N	DIP-20	Octal D-Type Flip-Flop	.89	.744
595-SN74LS374N	DIP-20	Octal D-Type Flip-Flop	.89	.744
595-SN74LS38N	DIP-14	Quad Positive-NAND Buff	.86	.739
595-SN74LS390N	PDIP-16	Dual 4-Bit Decade Counter	1.47	1.25
595-SN74LS393N	DIP-14	Dual 4-Bit Binary Counter	1.18	1.00
595-SN74LS241DW	SOIC-20	Octal Buffer/Driver w/3-State Outputs	.90	.77
595-SN74LS47N	DIP-16	BCD-To-7 Decoder	1.76	1.50
595-SN74LS540DW	SOIC-20	Octal Buff and Line Driver	1.61	1.37
595-SN74LS540N	PDIP-20	Octal Buff and Line Driver	1.57	1.34
595-SN74LS541DW	SOIC-20	Octal Buff and Line Driver	1.28	1.09
595-SN74LS541N	DIP-20	Octal Buff and Line Driver	1.18	1.00
595-SN74LS74AD	SOIC-14	Dual D-type Flip-Flop	.63	.527
595-SN74LS74AN	DIP-14	Dual D-type Flip-Flop	.58	.484
595-SN74LS86ADR	SOIC-14	Quad Exclusive-OR Gate	.61	.513
595-SN74LS86AN	DIP-14	Quad Exclusive-OR Gate	.58	.484
595-SN74LS93N	PDIP	4-Bit Binary Cntr	2.35	2.00
595-SN74LV04AD	SOIC-14	Hex Inverter	.42	.323
595-SN74LV04APWR	TSSOP-14	Hex Inverter	.35	.27
595-SN74LV08APWR	TSSOP-14	Quad Positive-AND Gate	.35	.27
595-SN74LV1T02DBVR	SOT-23-5	Single 2-Input NOR Gate	.44	.341
595-SN74LV1T02DCKR	SC-70-5	Single 2-Input NOR Gate	.40	.332
595-SN74LV1T125DBVR	SOT-23-5	3-State Single Buff Gate	.44	.341
595-SN74LV1T125DCKR	SC-70-5	3-State Single Buff Gate	.44	.332
595-SN74LV1T126DBVR	SOT-23-5	3-State Single Buff Gate	.44	.341
595-SN74LV1T126DCKR	SC-70-5	3-State Single Buff Gate	.44	.332
595-SN74LV1T32DBVR	SOT-23-5	Single 2-Input OR Gate	.50	.385
595-SN74LV1T32DCKR	SC-70-5	Single 2-Input OR Gate	.49	.376
595-SN74LV1T34DBVR	SOT-23-5	Single Buff Logic Level Shifter	.44	.341
595-SN74LV1T34DCKR	SC-70-5	Single Buff Logic Level Shifter	.43	.332
595-SN74LV1T86DBVR	SOT-23-5	Single 2-Input OR Gate	.50	.385
595-SN74LV1T86DCKR	SC-70-5	Single 2-Input OR Gate	.49	.376
595-SN74LV123AD	SOIC-16	Dual Regis Monostable Multivibrator	.62	.52
595-SN74LV123APWR	TSSOP-16	Dual Regis Monostable Multivibrator	.52	.433
595-SN74LV125APWR	TSSOP-14	Quad Bus Buff Gates	.40	.31
595-SN74LV138APWR	TSSOP-16	3-Line to 8-Line Decoder/Demult	.40	.31
595-SN74LV14APWR	TSSOP-14	Hex Inverter	.35	.27
595-SN74LV165APWR	TSSOP-16	8-Bit Serial Shift Register	.45	.379
595-SN74LV165APWRG3	TSSOP-16	8-Bit Serial Shift Register	.44	.365
595-SN74LV166AD	SOIC-16	8-Bit Parallel Load Shift Register	1.29	1.10
595-SN74LV244ADW	SOIC-20	Octal Buff/Driver	.55	.462
595-SN74LV244APWR	TSSOP-20	Octal Buff/Driver	.46	.383
595-SN74LV273ANSR	SOP-20	Octal D-Type Flip Flop	.45	.379
595-SN74LV4040APWR	TSSOP-16	12-Bit Async Binary Cntr	1.31	1.12
595-SN74LV4051ADR	SOIC-16	8-Chann Mux/Demux	.43	.361
595-SN74LV4051APWR	TSSOP-16	8-Chann Mux/Demux	.43	.361
595-SN74LV541APWR	TSSOP-20	Octal Buff/Driver	.85	.728
595-SN74LV595ADRG3	SOIC-16	8-Bit Shift Register	.89	.744
595-SN74LV595APWR	TSSOP-16	8-Bit Shift Register	.89	.744
595-SN74LV595APWRG3	TSSOP-16	8-Bit Shift Register	.85	.713
595-SN74LV8153N	PDIP-20	Serial-To-Parallel Interface	2.06	1.75
595-SN74LV8154N	PDIP-20	Dual 16-Bit Binary Cntr	1.04	.893
595-SN74LV86AD	SOIC-14	Quad Exclusive-OR Gate	.39	.297
595-SN74LVC00AD	SOIC-14	Quad 2-Input NAND Gate	.45	.345
595-SN74LVC00APW	TSSOP-14	Quad 2-Input NAND Gate	.45	.345
595-SN74LVC02ADR	SOP-14	Quad 2-Input NAND Gate	.37	.288
595-SN74LVC02APWR	TSSOP-14	Quad 2-Input NAND Gate	.37	.288
595-SN74LVC04AD	SOIC-14	Hex Inverter	.45	.345
595-SN74LVC04ADBR	SSOP-14	Hex Inverter	.42	.323
595-SN74LVC04APW	TSSOP-14	Hex Inverter	.45	.345
595-SN74LVC04APWR	TSSOP-14	Hex Inverter	.37	.288
595-SN74LVC06AD	SOIC-14	Hex Inverter Buff	.46	.354
595-SN74LVC06APWR	TSSOP-14	Hex Inverter Buff	.39	.297
595-SN74LVC07AD	SOIC-14	Hex Buff	.46	.354
595-SN74LVC07ADBR	SSOP-14	Hex Buff	.43	.328
595-SN74LVC07ADGVR	TVSOP-14	Hex Buff	.39	.297
595-SN74LVC07APW	TSSOP-14	Hex Buff	.46	.354
595-SN74LVC07APWR	TSSOP-14	Hex Buff	.39	.297