

Aluminum Capacitors

Radial Standard, High Voltage





Fig.1 Component outline.



QUICK REFERENCE DATA

DESCRIPTION	VALUE
Nominal case sizes (ØD × L in mm)	6.3 × 11 to 16 × 31
Rated capacitance range, C _R	1.0 to 100 µF
Tolerance on C _R	± 20 %
Rated voltage range, U _R	160 to 450 V
Category temperature range	≤ 400 V: – 40 to + 85 °C; 450 V: – 25 to + 85 °C
Endurance test at 85 °C	2000 hours
Useful life at 85 °C	3000 hours
Useful life at 40 °C, 1.4 × I _R applied	80000 hours
Shelf life at 0 V, 85 °C	500 hours
Based on sectional specification	IEC 60384-4/EN130300
Climatic category IEC 60068	≤ 400 V: 40/085/56; 450 V: 25/085/56

SELECTION CHART FOR C_R, U_R AND RELEVANT NOMINAL CASE SIZES (ØD × L in mm)

C _R (µF)	U _R (V)					
	160	200	250	350	400	450
1.0	–	–	6.3 × 11	–	8 × 12	10 × 12
2.2	–	–	8 × 12	10 × 12	10 × 12	10 × 16
4.7	–	10 × 12	10 × 12	10 × 16	10 × 20	12.5 × 20
10	10 × 16	10 × 16	10 × 20	12.5 × 20	12.5 × 20	12.5 × 25
22	10 × 20	10 × 20	12.5 × 25	12.5 × 25	16 × 25	16 × 31
47	–	12.5 × 25	16 × 25	16 × 31	–	–
100	16 × 25	16 × 31	–	–	–	–

FEATURES

- Polarized aluminum electrolytic capacitors, non-solid electrolyte.
- Radial leads, cylindrical aluminum case, insulated with a blue vinyl sleeve.
- Pressure relief.
- Charge and discharge proof.
- Reduced dimensions.
- High rated voltage, up to 450 V.
- Lead (Pb)-free versions are RoHS compliant.



Available
RoHS*
COMPLIANT

APPLICATIONS

- General purpose, audio-video, lighting, general industrial.
- Smoothing, filtering, buffering of high voltages.

MARKING

The capacitors are marked (where possible) with the following information:

- Rated capacitance (in µF).
- Tolerance on rated capacitance, code letter in accordance with IEC 60062 (M for ± 20 %).
- Rated voltage (in V).
- Date code, in accordance with IEC 60062.
- Code indicating factory of origin.
- Name of manufacturer.
- Negative terminal identification.
- Series number (044).

* Pb containing terminations are not RoHS compliant, exemptions may apply




DIMENSIONS in millimeters, **AND AVAILABLE FORMS**

Fig.2 **Form CA:** Long leads.

Fig.3 **Form CB:** Cut leads.

Case $\varnothing D = 6.3$ and 8 mm, pitch $F = 5$ mm


Fig.4 **Form TFA:** Taped in box (ammopack), formed leads

Dimensions of pitch F see table 1 and 2

Fig.5 **Form TNA, TFA:** Taped in box (ammopack), straight leads

Table 1

DIMENSIONS in millimeters, MASS AND PACKAGING QUANTITIES									
NOMINAL CASE SIZE $\varnothing D \times L$	CASE CODE	$\varnothing d$	$\varnothing D_{max}$	L_{max}	F	MASS (g)	PACKAGING QUANTITIES		
							FORM CA	FORM CB	FORM TFA, TNA
6.3 x 11	12	0.5	6.8	12.5	2.5 ± 0.5	≈ 0.6	2000	2000	2000
8 x 12	13	0.6	8.5	13.0	3.5 ± 0.5	≈ 1.1	1000	2000	1000
10 x 12	14	0.6	10.5	14.0	5.0 ± 0.5	≈ 1.6	2000	1500	800
10 x 16	15	0.6	10.5	17.5	5.0 ± 0.5	≈ 1.9	2000	1500	800
10 x 20	16	0.6	10.5	22.0	5.0 ± 0.5	≈ 2.2	2000	1500	800
12.5 x 20	17	0.6	13.0	22.0	5.0 ± 0.5	≈ 4.0	1000	1500	500
12.5 x 25	18	0.6	13.0	27.0	5.0 ± 0.5	≈ 5.0	1000	1500	500
16 x 25	19	0.8	16.5	27.0	7.5 ± 0.5	≈ 8.0	500	500	—
16 x 31	20	0.8	16.5	33.5	7.5 ± 0.5	≈ 9.0	500	500	—

Note

1. Detailed tape dimensions see section 'PACKAGING'.

ELECTRICAL DATA	
SYMBOL	DESCRIPTION
C_R	rated capacitance at 100 Hz, tolerance $\pm 20\%$
I_R	rated RMS ripple current at 100 Hz, 85 °C
I_{L1}	max. leakage current after 1 minute at U_R
$\tan \delta$	max. dissipation factor at 100 Hz
Z	max. impedance at 10 kHz and + 20 °C

Note

1. Unless otherwise specified, all electrical values in Table 2 apply at $T_{amb} = 20\text{ °C}$, $P = 86$ to 106 kPa , $RH = 45$ to 75% .

ORDERING EXAMPLE*

Electrolytic capacitor 044 series

47 $\mu\text{F}/250\text{ V}$; $\pm 20\%$

Nominal case size: $\varnothing 16 \times 25\text{ mm}$; Form CB

Catalog number: 2222 044 63479.


* To ensure delivery of lead (Pb)-free parts during the transition period, please contact your Vishay sales agent.

Table 2

ELECTRICAL DATA AND ORDERING INFORMATION														
U _R (V)	C _R 100 Hz (μF)	NOMINAL CASE SIZE ØD × L (mm)	I _R 100 Hz 85 °C (mA)	I _{L1} 1 min (μA)	Tan δ 100 Hz	Z 10 kHz (Ω)	CATALOG NUMBER 2222 044							
							BULK PACKAGING				TAPED AMMOPACK			
							LONG LEADS		CUT LEADS					
							FORM CA	F (mm)	FORM CB	F (mm)	FORM TFA	F (mm)	FORM TNA	F (mm)
160	10	10 × 16	83	120	0.14	12	51109	5.0	61109	5.0	31109	5.0	–	–
	22	10 × 20	140	180	0.14	5.5	51229	5.0	61229	5.0	31229	5.0	–	–
	100	16 × 25	380	550	0.14	1.8	51101	7.5	61101	7.5	–	–	–	–
200	4.7	10 × 12	51	96	0.14	26	52478	5.0	62478	5.0	32478	5.0	–	–
	10	10 × 16	85	130	0.14	12	52109	5.0	62109	5.0	32109	5.0	–	–
	22	10 × 20	140	200	0.14	5.5	52229	5.0	62229	5.0	32229	5.0	–	–
	47	12.5 × 25	230	350	0.14	2.6	90516	5.0	90517	5.0	90519	5.0	–	–
	100	16 × 31	400	670	0.14	1.5	52101	7.5	62101	7.5	–	–	–	–
250	1.0	6.3 × 11	17	55	0.14	110	90501	2.5	–	–	90506	5.0	90507	2.5
	2.2	8 × 12	30	73	0.14	55	90015	3.5	–	–	90019	5.0	90529	3.5
	4.7	10 × 12	51	110	0.14	26	53478	5.0	63478	5.0	33478	5.0	–	–
	10	10 × 20	95	150	0.14	12	53109	5.0	63109	5.0	33109	5.0	–	–
	22	12.5 × 25	160	240	0.14	5.5	53229	5.0	63229	5.0	33229	5.0	–	–
	47	16 × 25	260	420	0.14	2.6	53479	7.5	63479	7.5	–	–	–	–
350	2.2	10 × 12	39	86	0.13	39	55228	5.0	65228	5.0	35228	5.0	–	–
	4.7	10 × 16	63	120	0.13	18	55478	5.0	65478	5.0	35478	5.0	–	–
	10	12.5 × 20	120	180	0.13	8.5	55109	5.0	65109	5.0	35109	5.0	–	–
	22	12.5 × 25	180	300	0.13	3.9	90525	5.0	90526	5.0	90528	5.0	–	–
	47	16 × 31	320	560	0.13	2.3	55479	7.5	65479	7.5	–	–	–	–
400	1.0	8 × 12	22	64	0.15	85	56108	3.5	–	–	36108	5.0	76108	3.5
	2.2	10 × 12	39	93	0.15	39	56228	5.0	66228	5.0	36228	5.0	–	–
	4.7	10 × 20	70	130	0.15	18	56478	5.0	66478	5.0	36478	5.0	–	–
	10	12.5 × 20	110	190	0.15	8.5	56109	5.0	66109	5.0	36109	5.0	–	–
	22	16 × 25	200	330	0.15	3.9	56229	7.5	66229	7.5	–	–	–	–
450	1.0	10 × 12	25	67	0.26	120	57108	5.0	67108	5.0	37108	5.0	–	–
	2.2	10 × 16	42	99	0.26	55	57228	5.0	67228	5.0	37228	5.0	–	–
	4.7	12.5 × 20	75	130	0.26	26	57478	5.0	67478	5.0	37478	5.0	–	–
	10	12.5 × 25	120	210	0.26	12	57109	5.0	67109	5.0	37109	5.0	–	–
	22	16 × 31	210	370	0.26	5.5	57229	7.5	67229	7.5	–	–	–	–


ADDITIONAL ELECTRICAL DATA		
PARAMETER	CONDITIONS	VALUE
Voltage		
Surge voltage	$U_R = 160 \text{ to } 250 \text{ V}$	$U_S \leq 1.15 \times U_R$
	$U_R = 350 \text{ to } 450 \text{ V}$	$U_S \leq 1.1 \times U_R$
Reverse voltage		$U_{rev} \leq 1 \text{ V}$
Current		
Leakage current	after 1 minute at U_R :	
	$CV \leq 1000 \mu\text{C}$	$I_{L1} \leq 0.06 C_R \times U_R + 40 \mu\text{A}$
	$CV > 1000 \mu\text{C}$	$I_{L1} \leq 0.03 C_R \times U_R + 70 \mu\text{A}$
	after 5 minutes at U_R :	
	$CV \leq 1000 \mu\text{C}$	$I_{L5} \leq 0.03 C_R \times U_R + 15 \mu\text{A}$
	$CV > 1000 \mu\text{C}$	$I_{L5} \leq 0.015 C_R \times U_R + 30 \mu\text{A}$
Inductance		
Equivalent series inductance (ESL)	case $\varnothing D = 6.3 \text{ and } 8 \text{ mm}$	typ. 13 nH
	case $\varnothing D = 10 \text{ mm}$	typ. 16 nH
	case $\varnothing D \geq 12.5 \text{ mm}$	typ. 18 nH
Resistance		
Equivalent series resistance (ESR)	calculated from $\tan \delta_{max}$ and C_R (see Table 2)	$ESR = \tan \delta / 2\pi f C_R$

CAPACITANCE (C)



C_0 = capacitance at 20 °C, 100 Hz.

Fig.6 Typical multiplier of capacitance as a function of ambient temperature.



C_0 = capacitance at 20 °C, 100 Hz.

$T_{amb} = 20 \text{ °C}$.

Fig.7 Typical multiplier of capacitance as a function of frequency.

RIPPLE CURRENT AND USEFUL LIFE

CCC205


 I_A = actual ripple current at 100 Hz. I_R = rated ripple current at 100 Hz, 85 °C.(1) Useful life at 85 °C and I_R applied: 3000 hours.

Fig.8 Multiplier of useful life as a function of ambient temperature and ripple current load.

Table 3

MULTIPLIER OF RIPPLE CURRENT (I_R) AS A FUNCTION OF FREQUENCY	
FREQUENCY (HZ)	I_R MULTIPLIER
50	0.75
100	1.00
300	1.20
1000	1.35
3000	1.45
≥ 10000	1.50

Table 4

TEST PROCEDURES AND REQUIREMENTS			
TEST		PROCEDURE (quick reference)	REQUIREMENTS
NAME OF TEST	REFERENCE		
Endurance	IEC 60384-4/ EN130300 subclause 4.13	$T_{amb} = 85\text{ °C}$; U_R applied; 2000 hours	$\Delta C/C: \pm 20\%$ $\leq 400\text{ V}: \tan \delta \leq 2 \times \text{spec. limit}$ $450\text{ V}: \tan \delta \leq 1.5 \times \text{spec. limit}$ $I_{L5} \leq \text{spec. limit}$
Useful life	CECC 30301 subclause 1.8.1	$T_{amb} = 85\text{ °C}$; U_R and I_R applied; 3000 hours	$\Delta C/C: \pm 50\%$ $\tan \delta \leq 3 \times \text{spec. limit}$ $I_{L5} \leq \text{spec. limit}$ no short or open circuit total failure percentage: $\leq 3\%$
Shelf life (storage at high temperature)	IEC 60384-4/ EN130300 subclause 4.17	$T_{amb} = 85\text{ °C}$; no voltage applied; 500 hours after test: U_R to be applied for 30 minutes, 24 to 48 hours before measurement	$\Delta C/C, \tan \delta, Z:$ for requirements see 'Endurance test' above $I_{L5} \leq 2 \times \text{spec. limit}$



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.