

4



3

2

1

PART NO.	TYPE	A DIA ±.016	B DIA ±.016	C ±.031	MS NUMBER
10-35910-101	I	.125	.210	2.000	MS3420- 3A
-121		.219	.302	2.000	- 4A
-141		.312	.427	2.000	- 6A
-161		.438	.531	2.000	- 8A
-181		.438	.615	2.000	-10A
-201		.541	.740	2.000	-12A
-241		.750	.927	2.000	-16A
-242		.750	.928	3.000	
-301		.938	1.115	2.000	MS3420-18A
-321		.938	1.240	2.000	-20A
-361		1.125	1.365	2.000	-24A
-401		1.250	1.614	2.000	-28A
-441		1.625	1.865	2.000	-32A
-481		1.875	2.365	2.000	-40A

REVISIONS				
ZONE	LTR	DESCRIPTION	DATE	APPROVED
	B	(CLII) REDRAWN, SAME SIZE, STANDARDIZED SEE CHANGE NOTICE ECN: 76686-1	1/7/86 BIVIANO	<i>[Signature]</i>
	C	(CLII) SEE CHANGE NOTICE ECN: 27564	3-8-93 DE MATTEO	<i>[Signature]</i>



TYPE I

1. MATERIAL SPEC: RUBBER PER MIL-STD-417
TYPE SC 515 A₁ B₁ C₁ E₃ F₂ GM.

NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED.
HOWEVER, DOCUMENTS REFERENCED HEREON
MAY CONTAIN LIMITED RIGHTS DATA.

10-35900

NEXT ASSEMBLY

UNLESS OTHERWISE SPECIFIED
LINEAR DIMENSIONS ARE IN
INCHES.
TOLERANCES: .XXX±.010,
.XX ±.03, .X ±.1,
ANGLES ±2°.
OTHER STANDARDS PER 9-3800
AND DOD-D-1000.

NOTE REF. =

FIND NO.	QTY REQD.	FSCM NO.	PART NUMBER	DESCRIPTION	NOTE REF.
PARTS LIST					
SPECIFICATIONS		SIGNATURES	DATES	ALLIED, AMPHENOL PRODUCTS BENDIX CONNECTOR OPERATIONS SIDNEY, N.Y.	
MATERIAL SPEC.		HENNEASEY	3/23/50	SLEEVE-REDUCING	
SEE NOTE 1		CHECKED <i>[Signature]</i>	3/27/86		
		MATERIAL <i>[Signature]</i>	3-26-86		
		APPROVED <i>[Signature]</i>	3-26-86		
PROCESS SPEC.		APPROVED <i>[Signature]</i>	3-27-86		
		ORIGINAL PREPARED DATE			
		SIZE	FSCM NO.		
		C	77820	10-35910	
		SCALE	NONE	WT.	REF
				SHEET	1 OF 2

COMPUTER GENERATED DRAWING.

TAB.