
OPERATION

The ISO Series single channel devices are used to provide a safe and reliable means of controlling loads from hazardous locations without releasing sufficient energy, under normal or abnormal conditions, to cause ignition of a flammable or combustible atmospheric mixture while in its most easily ignited concentration. An isolated output turns on when the control switch input from the hazardous location is closed. When the control switch input opens, the isolated output turns off. The Style A single channel plug-in devices come equipped with integral spring mating clips and socket (PF083A) which secure the device to make this unit the only UL913 Intrinsically Safe plug-in associated apparatus available on the market today. The Style N, surface mounted enclosure is sealed with a high quality epoxy resin material and has five (5) #8-32 screw terminals.



Single Channel Isolated Switch

DIMENSIONS (INCHES)



SPECIFICATIONS

CONTROL VOLTAGE	24 or 120 VAC ±10%, 50/60 Hz		
CONTROL SWITCH	Open Circuit V Short Circuit (16 VDC 200 μAmps
RESPONSE	Operate Release		(Approx.)
POWER REQUIRED	1.5 VA		
DUTY CYCLE	Continuous		
CONTACT RATING	SPST-N.O., 5 amps @ 24 or 120 VAC, Resistive; 278 VA, Inductive		
SENSITIVITY	100 k ohm		
ISOLATION	2500 Volts, Input to Output		
LIFE EXPECTANCY	Mechanical Electrical		on Operations Operations @ Rated Load
INDICATORS	On When Output is On		
TEMPERATURE RATING	Operate Storage		31°F (-20° to +55°C) 185°F (-40° to +85°C)
ENCLOSURE	Style "A" and "N"		
TERMINATIONS	(12) #8-32 Screw terminals		
WEIGHT	20 oz.		


ORDERING INFORMATION


MODEL Number	CONTROL VOLTAGE	ENCLOSURE STYLE
ISO-24-AFA	24 VAC	A
ISO-120-AFA	120 VAC	A
ISO-24-AFN	24 VAC	N
ISO-120-AFN	120 VAC	N

Style "A" Socket Included (PF083A) with clips


SOLATED SWITCHES

CONTROL DRAWING 191





CONTROL DRAWING 193



5. Wiring to terminals 6 and 12 is omitted for models with the suffix ABE.

or inductance.