



PART NUMBER	A DIA	B	C	D DIA	WT-LB	COMMENT	RELEASE
10-36298-8	.516 ^{+0.000} _{-0.010}	.63	22°	.288	.0010	22387-6	30508-227
-10	.609	↓		.359	.0011		
-12	.766	↓		.484	.0016		
-13	.766	.851		.484			
-14	.844	.633		.609	.0020		
-15	.844	.851		.609	.0027		
-16	.969	.633		.734	.0020		
-17	.969	.851		.734	.0023		
-18	1.094 ↓			.859	.0040		
-20	1.219 ^{+0.000} _{-0.015}	↓		.984	.0047		
-22	1.344	↓		1.109	.0051		
-24	1.469	.788		1.234	.0052		
-28	1.719 ↓	.788	↓	1.427	.0063		
-32	2.000 ^{+0.000} _{-0.020}	.726	34°	1.708	.0070		
-36	2.219	↓		1.895	.0066		
-40	2.469	↓		2.130			
↓ -44	2.782 ↓	↓	↓	2.400			

10-36298

REL.	30508-227	WAS	DATE	D'MAN	APPD.
1	31018-1	ADD. NOTE "FLASH PERMISSIBLE .015 MAX."	5-16-55	I. NILES	<i>[Signature]</i>
2	30525-314	REV COL A	9-16-55	JONES	<i>[Signature]</i>
3	31662-2	ADD D DIA FOR -10, RELOC C DIM, REV COL C	1-17-56	E. GEORGE	<i>[Signature]</i>
4	33199-1	REV COL C	6-24-57	MUGGLIN	<i>[Signature]</i>
5	35525-881	ADD -44 AND DATA	8-31-59	FAIRCHILD	<i>[Signature]</i>
A	49525-85	(MFG); ADD. WT LB COL	11-8-59	Randall	<i>[Signature]</i>



FLASH PERMISSIBLE
.015 MAX.

USE OF THIS DOCUMENT IS UNLIMITED. DOCUMENTS
REFERENCED HEREON CONTAIN LIMITED RIGHTS DATA.

NOTES:

- PARTS TO BE TRANSPARENT TO TRANSLUCENT.
- E. I. DUPONT DE NEMOURS & CO, INC
ZYTEL 101.
- ENGINEERING SOURCE APPROVAL REQUIRED.

MATERIAL SPEC. NYLON SEE NOTE 2		PROCESS SPEC.		SCINTILLA MAGNETO DIVISION BENDIX AVIATION CORPORATION SIDNEY, N. Y., U.S.A.				TOLERANCES UNLESS OTHERWISE SPECIFIED	
HEAT TREAT SPEC.		FINISH SPEC.						CONCENTRICITY .015 FIR	
END BELL, POTTING, ELECTRICAL CONNECTOR				NAME		NEXT ASSEMBLY		10-87217 THRU 10-87232 10-87201 THRU 10-87216	
				D'MAN		WEIGHT - LBS		SEE WT COL	
TOOL ACC.		COM. REC 22387-6		9-16-54		2-23-55		1.6-55	
				CH. D'MAN		APPROVED		SCALE	
				CH. D'MAN		APPROVED		SCALE	
				2-25-55		2-25-55		NO SCALE	
								10-36298	
								DWG SIZE B	
								TAB. CODE 77820	